

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011957

Luminaire Tested: S123DIP-B775D1195UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011957
REPORT IS A COMBINATION OF REPORTS P990311 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1195UB30-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7514.1 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011957

CATALOG NUMBER: S123DIP-B775D1195UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1011957

CATALOG NUMBER: S123DIP-B775D1195UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	43	42	41
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	34	32	30
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	28	25
5	67	55	47	41	61	51	44	39	42	37	33	35	31	28	27	24	22
6	62	50	42	36	56	46	39	33	38	33	29	31	27	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	22	20	17
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13177	13177	13177
5°	13209	12722	12703
10°	13092	12292	12165
15°	12910	11844	11580
20°	12701	11347	10999
25°	12431	10822	10378
30°	12136	10279	9725
35°	11827	9725	9076
40°	11503	9142	8438
45°	11146	8575	7771
50°	10783	7943	7102
55°	10319	7284	6424
60°	9838	6557	5702
65°	9389	5771	4949
70°	8740	4899	4072
75°	7809	3879	3161
80°	6743	2725	2236
85°	5254	1465	1119

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11146 cd/sqm

TEST NUMBER: P1011957

CATALOG NUMBER: S123DIP-B775D1195UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.4	1.5
10°-20°	325.9	4.3
20°-30°	481.3	6.4
30°-40°	562.1	7.5
40°-50°	565.1	7.5
50°-60°	496.4	6.6
60°-70°	369.7	4.9
70°-80°	210.4	2.8
80°-90°	63.0	0.8
90°-100°	326.0	4.3
100°-110°	911.1	12.1
110°-120°	888.4	11.8
120°-130°	707.4	9.4
130°-140°	558.4	7.4
140°-150°	416.6	5.5
150°-160°	290.6	3.9
160°-170°	170.7	2.3
170°-180°	55.5	0.7
0°-30°	922.6	12.3
0°-40°	1484.6	19.8
0°-60°	2546.1	33.9
0°-90°	3189.2	42.4
90°-120°	2125.5	28.3
90°-150°	3807.9	50.7
90°-180°	4325.0	57.6
0°-180°	7514.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1224	1224	1224	1224	1224	
5°	1225	1220	1208	1219	1217	116
15°	1166	1162	1148	1157	1150	329
25°	1059	1053	1039	1040	1037	488
35°	916	910	896	890	884	573
45°	750	746	733	720	715	579
55°	570	568	555	543	538	510
65°	388	383	373	364	361	383
75°	205	201	198	193	190	219
85°	55	53	53	50	50	59
90°	2	14	29	33	34	7
95°	40	128	689	201	135	42
105°	135	199	934	1633	1477	143
115°	238	297	714	1566	1796	236
125°	331	391	666	1208	1417	294
135°	388	463	657	995	1148	300
145°	442	507	649	816	898	277
155°	503	542	628	714	744	231
165°	549	565	602	638	649	155
175°	572	573	577	585	584	54
180°	574	574	574	574	574	

TEST NUMBER: P1011957

CATALOG NUMBER: S123DIP-B775D1195UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1224.2	1224.2	1224.2	1224.2	1224.2
2.5°	1229.4	1225.2	1213.7	1224.2	1223.1
5°	1225.2	1220.0	1208.4	1218.9	1216.8
7.5°	1215.8	1210.5	1198.9	1208.4	1207.3
10°	1203.1	1197.9	1184.2	1193.7	1191.5
12.5°	1186.3	1182.1	1169.4	1175.8	1174.7
15°	1166.3	1162.1	1148.4	1156.8	1150.5
17.5°	1144.2	1138.9	1125.2	1131.6	1129.4
20°	1118.9	1112.6	1098.9	1103.1	1100.0
22.5°	1090.5	1084.2	1070.5	1073.7	1069.4
25°	1058.9	1052.6	1038.9	1040.0	1036.8
27.5°	1026.3	1020.0	1005.2	1006.3	1003.1
30°	990.5	985.2	970.5	970.5	963.1
32.5°	954.7	947.3	936.8	929.5	926.3
35°	915.8	909.5	895.8	889.5	884.2
37.5°	876.8	868.4	854.7	847.3	844.2
40°	835.8	829.5	814.7	806.3	802.1
42.5°	794.7	787.3	772.6	764.2	760.0
45°	750.5	746.3	732.6	720.0	714.7
47.5°	707.4	701.0	688.4	675.8	671.6
50°	663.1	657.9	644.2	632.6	626.3
52.5°	616.8	613.7	598.9	589.5	583.1
55°	569.5	568.4	554.7	543.1	537.9
57.5°	525.3	521.0	510.5	500.0	493.7
60°	476.8	475.8	463.1	453.7	448.4
62.5°	433.7	430.5	417.9	408.4	405.3
65°	388.4	383.1	372.6	364.2	361.0
67.5°	340.0	335.8	327.4	320.0	315.8
70°	296.8	290.5	284.2	276.8	271.6
72.5°	251.6	247.4	240.0	233.7	231.6
75°	205.3	201.0	197.9	192.6	189.5
77.5°	164.2	162.1	157.9	153.7	153.7
80°	124.2	121.0	118.9	117.9	117.9
82.5°	85.3	85.3	85.3	83.2	82.1
85°	54.7	52.6	52.6	50.5	50.5
87.5°	27.4	24.2	23.2	22.1	22.1
90°	2.3	14.0	29.0	32.6	33.7
92.5°	17.4	69.6	216.0	73.8	61.5
95°	39.5	128.4	688.6	200.9	134.7
97.5°	62.7	146.9	1059.0	505.1	276.4
100°	85.9	162.0	1099.6	1056.6	728.1
102.5°	110.3	179.4	1024.2	1414.9	1153.0
105°	134.7	199.1	933.6	1632.6	1477.0
107.5°	160.2	222.4	853.5	1728.4	1688.3
110°	188.1	246.2	787.3	1731.4	1809.1

TEST NUMBER: P1011957

CATALOG NUMBER: S123DIP-B775D1195UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	213.7	271.2	743.2	1665.7	1833.5
115°	238.0	296.7	714.1	1565.8	1796.3
117.5°	262.4	321.0	694.4	1459.0	1715.1
120°	288.0	345.4	681.6	1358.0	1608.2
122.5°	310.0	368.6	673.5	1278.4	1508.4
125°	330.9	390.8	666.5	1207.6	1416.6
127.5°	347.2	411.6	663.0	1149.6	1337.7
130°	362.3	430.2	659.5	1096.2	1272.6
132.5°	373.9	447.0	658.4	1046.2	1208.8
135°	387.8	462.8	657.2	994.6	1148.4
137.5°	400.6	475.5	654.9	945.8	1084.5
140°	413.4	487.1	653.7	898.2	1017.2
142.5°	427.3	497.6	651.4	854.6	954.5
145°	442.4	506.8	649.1	815.8	897.6
147.5°	457.5	516.7	645.6	785.5	848.8
150°	472.6	524.8	641.0	758.8	807.0
152.5°	487.7	533.6	635.2	735.6	772.2
155°	502.8	542.2	628.2	714.2	744.3
157.5°	514.4	549.8	622.4	693.2	717.6
160°	528.3	556.2	615.4	674.0	692.1
162.5°	538.8	560.8	608.5	656.0	668.8
165°	549.2	564.9	601.5	638.1	649.1
167.5°	557.4	568.4	594.5	622.4	629.4
170°	564.3	570.2	587.6	608.4	611.9
172.5°	569.0	571.9	581.7	596.2	595.7
175°	572.5	573.0	577.1	585.2	584.1
177.5°	574.8	573.6	573.6	578.3	575.9
180°	573.6	573.6	573.6	573.6	573.6

(END OF REPORT)