

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012288

Luminaire Tested: S123RDIP-B1165D1025UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012288
REPORT IS A COMBINATION OF REPORTS P992957 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1165D1025UB50-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7574.0 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012288

CATALOG NUMBER: S123RDIP-B1165D1025UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012288

CATALOG NUMBER: S123RDIP-B1165D1025UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		73	73	73		61	61	61
1	99	95	91	88		92	89	85	82		76	74	72		65	64	62		55	54	53
2	91	84	78	73		84	78	73	68		67	63	60		58	55	52		49	47	45
3	83	74	67	61		77	69	63	57		60	55	51		51	48	45		43	41	39
4	76	66	58	52		71	61	54	49		53	48	44		46	42	39		39	36	34
5	70	59	51	45		65	55	48	42		48	42	38		41	37	34		35	32	29
6	65	53	45	39		60	49	42	37		43	38	33		38	33	30		32	29	26
7	60	48	40	34		56	45	38	33		39	34	29		34	30	26		29	26	23
8	56	43	36	30		52	41	34	29		36	30	26		31	27	24		27	24	21
9	52	40	32	27		48	37	31	26		33	28	24		29	25	21		25	22	19
10	49	37	29	25		45	34	28	24		31	25	21		27	22	19		23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20106	20106	20106
5°	20139	19395	19343
10°	19980	18665	18298
15°	19721	17764	17154
20°	19381	16784	15875
25°	19030	15765	14664
30°	18581	14682	13231
35°	18116	13618	11928
40°	17681	12462	10487
45°	17122	11332	9191
50°	16505	10124	7851
55°	15865	8832	6623
60°	15255	7507	5376
65°	14465	6147	4195
70°	13473	4649	2999
75°	12043	3148	2376
80°	10282	2187	1667
85°	7713	1181	873

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17122 cd/sqm

TEST NUMBER: P1012288

CATALOG NUMBER: S123RDIP-B1165D1025UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.6	2.3
10°-20°	488.5	6.4
20°-30°	703.3	9.3
30°-40°	792.1	10.5
40°-50°	757.6	10.0
50°-60°	620.2	8.2
60°-70°	418.1	5.5
70°-80°	209.7	2.8
80°-90°	57.4	0.8
90°-100°	77.9	1.0
100°-110°	235.7	3.1
110°-120°	401.2	5.3
120°-130°	527.8	7.0
130°-140°	593.3	7.8
140°-150°	583.2	7.7
150°-160°	491.0	6.5
160°-170°	326.9	4.3
170°-180°	114.5	1.5
0°-30°	1367.4	18.1
0°-40°	2159.5	28.5
0°-60°	3537.3	46.7
0°-90°	4222.6	55.8
90°-120°	714.7	9.4
90°-150°	2419.0	31.9
90°-180°	3351.0	44.2
0°-180°	7574.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1868	1868	1868	1868	1868	
5°	1868	1860	1842	1856	1853	177
15°	1782	1765	1722	1715	1704	502
25°	1621	1583	1513	1482	1465	746
35°	1403	1348	1254	1189	1162	878
45°	1153	1085	968	882	845	890
55°	876	801	673	585	554	785
65°	598	515	397	323	306	592
75°	317	244	161	145	142	337
85°	80	47	42	39	39	88
90°	1	10	23	27	28	9
95°	56	63	70	74	74	62
105°	214	216	224	224	226	229
115°	404	407	405	406	405	400
125°	591	594	592	588	584	527
135°	767	772	772	768	766	591
145°	930	932	935	934	930	581
155°	1065	1065	1066	1070	1063	490
165°	1160	1157	1157	1163	1156	327
175°	1207	1203	1203	1209	1202	115
180°	1210	1210	1210	1210	1210	

TEST NUMBER: P1012288

CATALOG NUMBER: S123RDIP-B1165D1025UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1867.9	1867.9	1867.9	1867.9	1867.9
2.5°	1875.5	1869.5	1851.3	1867.9	1864.9
5°	1867.9	1860.4	1842.2	1855.8	1852.8
7.5°	1854.3	1846.7	1824.0	1833.1	1828.5
10°	1836.1	1825.5	1798.2	1799.8	1792.2
12.5°	1810.4	1798.2	1763.4	1761.9	1752.8
15°	1781.6	1764.9	1722.5	1714.9	1704.3
17.5°	1746.7	1728.6	1675.5	1660.4	1645.2
20°	1707.4	1683.1	1625.5	1605.8	1587.7
22.5°	1663.4	1634.6	1572.5	1546.8	1530.1
25°	1621.0	1583.1	1513.4	1481.6	1465.0
27.5°	1569.5	1528.6	1452.8	1410.4	1384.7
30°	1516.5	1471.0	1386.2	1334.7	1310.4
32.5°	1463.4	1410.4	1319.5	1262.0	1236.2
35°	1402.8	1348.3	1254.4	1189.2	1162.0
37.5°	1342.2	1283.2	1184.7	1112.0	1078.6
40°	1284.7	1218.0	1110.5	1031.7	996.8
42.5°	1219.5	1152.9	1040.8	952.9	922.6
45°	1152.9	1084.7	968.1	881.7	845.3
47.5°	1087.7	1012.0	896.9	802.9	771.1
50°	1015.0	943.8	821.1	727.2	692.3
52.5°	949.9	871.1	749.9	651.4	621.1
55°	875.6	801.4	672.6	584.8	554.5
57.5°	809.0	728.7	598.4	515.1	489.3
60°	739.3	656.0	530.2	448.4	422.7
62.5°	669.6	586.3	460.5	384.8	357.5
65°	598.4	515.1	396.9	322.7	306.0
67.5°	527.2	442.4	327.2	271.2	253.0
70°	457.5	375.7	269.7	216.6	200.0
72.5°	387.8	307.5	213.6	172.7	168.2
75°	316.6	243.9	160.6	145.4	142.4
77.5°	251.5	184.8	125.7	116.7	113.6
80°	189.4	127.3	95.4	90.9	87.9
82.5°	130.3	78.8	68.2	63.6	63.6
85°	80.3	47.0	42.4	39.4	39.4
87.5°	36.4	19.7	19.7	18.2	16.7
90°	1.0	10.5	22.8	26.6	28.5
92.5°	28.5	34.2	39.9	42.8	40.9
95°	56.1	62.7	70.3	74.1	74.1
97.5°	92.2	96.9	102.6	107.4	106.4
100°	129.2	134.9	139.7	142.5	144.4
102.5°	172.0	174.8	181.5	184.3	183.4
105°	213.8	215.7	224.2	224.2	226.1
107.5°	263.2	264.1	267.9	270.8	269.8
110°	308.8	310.7	312.6	316.4	314.5

TEST NUMBER: P1012288

CATALOG NUMBER: S123RDIP-B1165D1025UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	356.3	357.3	357.3	362.0	362.0
115°	403.8	406.7	404.8	405.7	404.8
117.5°	452.3	453.2	451.3	451.3	448.5
120°	496.9	502.6	497.9	496.9	495.0
122.5°	543.5	547.3	545.4	542.5	539.7
125°	591.0	593.8	591.9	588.1	584.3
127.5°	634.7	640.4	638.5	632.8	629.0
130°	678.4	686.0	683.2	679.4	672.7
132.5°	722.1	729.7	727.8	723.1	718.3
135°	766.8	772.5	771.5	767.7	765.8
137.5°	807.6	812.4	815.2	810.5	807.6
140°	850.4	855.1	856.1	855.1	848.5
142.5°	889.3	894.1	896.0	895.0	890.3
145°	930.2	932.1	935.0	934.0	930.2
147.5°	965.4	969.2	972.0	972.0	966.3
150°	1002.4	1004.3	1006.2	1006.2	1000.5
152.5°	1032.8	1035.7	1036.6	1038.5	1033.8
155°	1065.1	1065.1	1066.1	1069.9	1063.2
157.5°	1092.7	1091.7	1092.7	1096.5	1090.8
160°	1118.3	1116.4	1116.4	1121.2	1117.4
162.5°	1141.1	1138.3	1139.2	1144.0	1137.3
165°	1160.1	1157.3	1157.3	1163.0	1156.3
167.5°	1176.3	1172.5	1173.4	1179.1	1173.4
170°	1189.6	1185.8	1185.8	1192.4	1185.8
172.5°	1200.0	1196.2	1196.2	1201.9	1195.3
175°	1206.7	1202.9	1202.9	1208.6	1201.9
177.5°	1210.5	1206.7	1206.7	1212.4	1205.7
180°	1209.5	1209.5	1209.5	1209.5	1209.5

(END OF REPORT)