

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1011964

Luminaire Tested: S123DIP-B775D1195UB35-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1011964
REPORT IS A COMBINATION OF REPORTS P990318 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D1195UB35-4F0-XX-W2A-F
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7988.0 lumens
Efficiency: N/A
Efficacy: 112.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1011964

CATALOG NUMBER: S123DIP-B775D1195UB35-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1011964

CATALOG NUMBER: S123DIP-B775D1195UB35-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	47	47	40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	41	40	40	40	40	34
2	87	80	74	68	79	73	67	63	60	56	53	48	45	43	36	35	33	33	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	28	28	24
4	72	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	24	24	20
5	66	55	47	41	60	50	43	38	42	36	32	34	30	27	26	23	21	21	21	18
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	24	21	19	19	19	16
7	56	44	37	31	51	41	34	29	34	29	25	27	24	21	21	19	17	17	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	15	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13	13	13	11
10	45	34	26	22	41	31	25	20	26	21	18	21	17	15	17	14	12	12	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13235	13235	13235
5°	13268	12778	12759
10°	13150	12346	12219
15°	12967	11895	11631
20°	12757	11396	11047
25°	12486	10870	10424
30°	12190	10325	9768
35°	11879	9767	9117
40°	11552	9183	8475
45°	11195	8612	7806
50°	10832	7977	7134
55°	10364	7316	6452
60°	9882	6586	5728
65°	9430	5797	4971
70°	8779	4922	4090
75°	7844	3897	3175
80°	6775	2739	2245
85°	5283	1473	1124

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11195 cd/sqm

TEST NUMBER: P1011964

CATALOG NUMBER: S123DIP-B775D1195UB35-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.9	1.5
10°-20°	327.3	4.1
20°-30°	483.4	6.1
30°-40°	564.6	7.1
40°-50°	567.5	7.1
50°-60°	498.6	6.2
60°-70°	371.3	4.6
70°-80°	211.3	2.6
80°-90°	63.2	0.8
90°-100°	55.3	0.7
100°-110°	267.6	3.4
110°-120°	655.8	8.2
120°-130°	832.5	10.4
130°-140°	889.3	11.1
140°-150°	831.6	10.4
150°-160°	670.8	8.4
160°-170°	432.9	5.4
170°-180°	149.2	1.9
0°-30°	926.6	11.6
0°-40°	1491.2	18.7
0°-60°	2557.3	32.0
0°-90°	3203.1	40.1
90°-120°	978.7	12.3
90°-150°	3532.1	44.2
90°-180°	4785.0	59.9
0°-180°	7988.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1231	1225	1214	1224	1222	117
15°	1171	1167	1153	1162	1156	330
25°	1064	1057	1044	1044	1041	490
35°	920	913	900	893	888	575
45°	754	750	736	723	718	582
55°	572	571	557	546	540	512
65°	390	385	374	366	363	385
75°	206	202	199	194	190	220
85°	55	53	53	51	51	59
90°	1	13	28	33	35	8
95°	71	23	36	44	44	85
105°	348	360	255	49	51	368
115°	652	659	669	681	686	644
125°	919	928	933	935	938	821
135°	1144	1151	1156	1159	1156	881
145°	1320	1328	1330	1333	1333	826
155°	1454	1452	1453	1459	1452	670
165°	1533	1530	1529	1538	1530	433
175°	1570	1564	1565	1573	1564	149
180°	1570	1570	1570	1570	1570	

TEST NUMBER: P1011964

CATALOG NUMBER: S123DIP-B775D1195UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1229.6	1229.6	1229.6	1229.6	1229.6
2.5°	1234.8	1230.6	1219.0	1229.6	1228.5
5°	1230.6	1225.3	1213.7	1224.3	1222.2
7.5°	1221.1	1215.8	1204.2	1213.7	1212.6
10°	1208.4	1203.1	1189.4	1198.9	1196.8
12.5°	1191.5	1187.3	1174.6	1180.9	1179.9
15°	1171.4	1167.2	1153.4	1161.9	1155.6
17.5°	1149.2	1143.9	1130.2	1136.5	1134.4
20°	1123.8	1117.5	1103.7	1108.0	1104.8
22.5°	1095.3	1088.9	1075.2	1078.4	1074.1
25°	1063.6	1057.2	1043.5	1044.5	1041.4
27.5°	1030.8	1024.5	1009.7	1010.7	1007.5
30°	994.9	989.6	974.8	974.8	967.4
32.5°	958.9	951.5	940.9	933.5	930.4
35°	919.8	913.4	899.7	893.4	888.1
37.5°	880.7	872.2	858.5	851.1	847.9
40°	839.4	833.1	818.3	809.8	805.6
42.5°	798.2	790.8	776.0	767.5	763.3
45°	753.8	749.6	735.8	723.1	717.9
47.5°	710.5	704.1	691.4	678.7	674.5
50°	666.1	660.8	647.0	635.4	629.1
52.5°	619.5	616.4	601.6	592.0	585.7
55°	572.0	570.9	557.2	545.5	540.2
57.5°	527.6	523.3	512.8	502.2	495.8
60°	478.9	477.9	465.2	455.7	450.4
62.5°	435.6	432.4	419.7	410.2	407.0
65°	390.1	384.8	374.3	365.8	362.6
67.5°	341.5	337.3	328.8	321.4	317.2
70°	298.1	291.8	285.5	278.1	272.8
72.5°	252.7	248.4	241.0	234.7	232.6
75°	206.2	201.9	198.8	193.5	190.3
77.5°	164.9	162.8	158.6	154.4	154.4
80°	124.8	121.6	119.5	118.4	118.4
82.5°	85.6	85.6	85.6	83.5	82.5
85°	55.0	52.9	52.9	50.7	50.7
87.5°	27.5	24.3	23.3	22.2	22.2
90°	1.2	12.8	28.0	32.7	35.0
92.5°	26.8	19.8	30.3	38.5	39.6
95°	71.1	23.3	36.1	44.3	44.3
97.5°	129.4	96.8	37.3	46.6	47.8
100°	197.1	220.4	38.5	47.8	49.0
102.5°	274.0	289.2	86.3	47.8	50.1
105°	347.5	360.3	255.4	49.0	51.3
107.5°	425.6	436.1	453.6	274.0	121.3
110°	503.7	513.1	525.9	487.4	320.7

TEST NUMBER: P1011964

CATALOG NUMBER: S123DIP-B775D1195UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	578.4	586.5	599.4	609.9	607.5
115°	651.8	658.8	669.3	681.0	685.7
117.5°	724.1	732.3	738.1	747.5	748.6
120°	790.6	801.1	804.6	813.9	813.9
122.5°	858.2	866.4	871.1	876.9	878.1
125°	918.9	928.2	932.9	935.2	937.5
127.5°	979.5	988.8	994.7	998.2	995.8
130°	1035.5	1044.8	1049.5	1054.1	1051.8
132.5°	1089.1	1098.4	1101.9	1106.6	1103.1
135°	1143.9	1150.9	1155.6	1159.1	1155.6
137.5°	1190.6	1199.9	1202.2	1208.1	1205.7
140°	1237.2	1244.2	1247.7	1252.4	1250.0
142.5°	1280.4	1287.3	1290.8	1294.3	1290.8
145°	1320.0	1328.2	1330.5	1332.8	1332.8
147.5°	1358.5	1364.3	1366.6	1369.0	1363.1
150°	1393.5	1397.0	1399.3	1401.6	1398.1
152.5°	1424.9	1426.1	1427.3	1431.9	1426.1
155°	1454.1	1451.8	1452.9	1458.8	1451.8
157.5°	1477.4	1477.4	1476.3	1483.2	1473.9
160°	1498.4	1497.2	1496.1	1503.1	1494.9
162.5°	1518.2	1514.7	1513.6	1521.7	1514.7
165°	1533.4	1529.9	1528.7	1538.1	1529.9
167.5°	1546.2	1541.6	1541.6	1550.9	1541.6
170°	1556.7	1552.0	1552.0	1561.4	1552.0
172.5°	1563.7	1557.9	1559.0	1568.4	1557.9
175°	1569.5	1563.7	1564.9	1573.0	1563.7
177.5°	1571.9	1566.0	1567.2	1576.5	1564.9
180°	1569.5	1569.5	1569.5	1569.5	1569.5

(END OF REPORT)