

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012296

Luminaire Tested: S123RDIP-B1165D1195UB30-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012296
REPORT IS A COMBINATION OF REPORTS P992975 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1165D1195UB30-4F0-XX-W2A-A
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9349.0 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012296

CATALOG NUMBER: S123RDIP-B1165D1195UB30-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1012296

CATALOG NUMBER: S123RDIP-B1165D1195UB30-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49		
1	98	94	90	87	90	87	84	81	73	71	69	61	60	58	50	49	48	42		
2	90	83	77	72	83	77	72	67	65	61	58	54	52	49	44	43	41	37		
3	82	73	66	61	76	68	62	57	58	53	50	49	45	42	40	38	36	32		
4	76	65	58	52	69	61	54	49	52	47	43	44	40	37	36	33	31	28		
5	70	58	51	45	64	54	47	42	47	41	37	39	35	32	33	30	28	24		
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	24	22		
7	59	48	40	34	55	44	37	33	38	33	29	33	29	25	27	24	22	19		
8	55	43	36	31	51	40	34	29	35	30	26	30	26	23	25	22	20	17		
9	52	40	32	27	48	37	30	26	32	27	23	28	24	21	23	20	18	16		
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	16	14		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19807	19807	19807	19807
5°	19822	22812	19873	16924
10°	19647	27538	19732	14782
15°	19445	31253	19445	13034
20°	19045	33712	19153	11563
25°	18754	32028	18718	10550
30°	18415	22191	18376	9560
35°	18006	14248	17925	8814
40°	17498	10061	17411	8071
45°	16613	8052	16589	7349
50°	15525	6735	15474	6503
55°	14302	5551	14187	5513
60°	13101	4588	12971	4689
65°	11693	3671	11768	3974
70°	10392	2550	10672	3213
75°	8810	1892	9168	2471
80°	7014	1255	7611	1853
85°	4995	594	5446	1153

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 26443 cd/sqm

TEST NUMBER: P1012296

CATALOG NUMBER: S123RDIP-B1165D1195UB30-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.7	1.9
10°-20°	565.7	6.1
20°-30°	890.9	9.5
30°-40°	926.4	9.9
40°-50°	792.6	8.5
50°-60°	604.3	6.5
60°-70°	387.1	4.1
70°-80°	185.5	2.0
80°-90°	51.9	0.6
90°-100°	55.1	0.6
100°-110°	266.4	2.8
110°-120°	652.9	7.0
120°-130°	828.8	8.9
130°-140°	885.4	9.5
140°-150°	827.9	8.9
150°-160°	667.8	7.1
160°-170°	431.0	4.6
170°-180°	148.5	1.6
0°-30°	1637.3	17.5
0°-40°	2563.8	27.4
0°-60°	3960.6	42.4
0°-90°	4585.1	49.0
90°-120°	974.4	10.4
90°-150°	3516.6	37.6
90°-180°	4764.0	51.0
0°-180°	9349.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1840	1840	1840	1840	1840	
5°	1838	2185	1843	1621	1838	174
15°	1757	3105	1757	1295	1757	494
25°	1598	3200	1594	1054	1598	736
35°	1394	1388	1388	859	1394	873
45°	1119	740	1117	676	1119	861
55°	789	465	783	462	789	707
65°	484	268	487	290	484	483
75°	232	113	241	148	232	250
85°	52	27	57	52	52	58
90°	1	35	1	35	1	7
95°	71	44	71	44	71	85
105°	346	51	346	51	346	367
115°	649	683	649	683	649	641
125°	915	933	915	933	915	817
135°	1139	1150	1139	1150	1139	877
145°	1314	1327	1314	1327	1314	823
155°	1448	1445	1448	1445	1448	667
165°	1527	1523	1527	1523	1527	431
175°	1563	1557	1563	1557	1563	149
180°	1563	1563	1563	1563	1563	

TEST NUMBER: P1012296

CATALOG NUMBER: S123RDIP-B1165D1195UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1
2.5°	1844.8	1857.4	1866.9	1873.2	1889.0	1898.4	1906.3	1920.5	1920.5	1923.6	1929.9
5°	1838.5	1865.3	1884.2	1909.4	1942.5	1958.3	1980.3	1999.2	2026.0	2040.2	2054.4
7.5°	1824.4	1862.2	1901.6	1939.4	1988.2	2019.7	2041.8	2090.6	2125.3	2167.8	2200.9
10°	1805.5	1857.4	1907.9	1966.2	2032.3	2079.6	2112.7	2177.3	2243.4	2303.3	2353.7
12.5°	1781.8	1844.8	1917.3	1988.2	2081.2	2128.4	2182.0	2262.3	2356.9	2432.5	2500.2
15°	1756.6	1829.1	1911.0	1997.7	2114.2	2180.4	2257.6	2355.3	2460.8	2569.6	2662.5
17.5°	1717.2	1808.6	1900.0	2026.0	2163.1	2202.5	2268.6	2402.6	2533.3	2631.0	2744.4
20°	1677.8	1780.3	1895.3	2008.7	2156.8	2248.2	2309.6	2451.4	2591.6	2709.8	2818.5
22.5°	1641.6	1748.7	1868.5	2011.8	2150.5	2241.9	2319.1	2467.1	2629.4	2761.8	2895.7
25°	1597.5	1714.1	1846.4	1981.9	2150.5	2219.8	2304.9	2476.6	2648.3	2801.1	2966.6
27.5°	1550.2	1668.4	1799.2	1937.8	2092.2	2194.6	2278.1	2462.4	2672.0	2835.8	3005.9
30°	1503.0	1624.3	1750.3	1874.8	2048.1	2145.8	2241.9	2445.1	2684.6	2872.0	3002.8
32.5°	1457.3	1559.7	1684.2	1805.5	1977.2	2084.3	2193.0	2427.8	2689.3	2846.8	2909.8
35°	1394.3	1501.4	1602.2	1731.4	1904.7	2010.3	2137.9	2426.2	2668.8	2766.5	2735.0
37.5°	1336.0	1425.8	1521.9	1636.9	1814.9	1952.0	2084.3	2385.2	2601.1	2607.4	2429.3
40°	1271.4	1345.4	1425.8	1547.1	1739.3	1874.8	2018.1	2322.2	2478.2	2385.2	2071.7
42.5°	1197.3	1263.5	1326.5	1444.7	1654.2	1805.5	1959.9	2243.4	2300.1	2085.9	1759.8
45°	1118.6	1172.1	1230.4	1354.9	1564.4	1714.1	1868.5	2122.1	2063.8	1761.3	1451.0
47.5°	1036.6	1082.3	1139.0	1252.5	1468.3	1621.1	1767.6	1948.8	1800.7	1476.2	1216.2
50°	954.7	991.0	1046.1	1162.7	1370.6	1509.3	1644.8	1762.9	1555.0	1266.7	1005.1
52.5°	874.4	902.7	959.4	1058.7	1260.4	1392.7	1490.4	1536.1	1324.9	1046.1	872.8
55°	789.3	820.8	858.6	959.4	1159.5	1257.2	1321.8	1320.2	1102.8	887.0	721.6
57.5°	707.4	735.7	768.8	869.6	1031.9	1098.1	1153.2	1126.4	920.1	726.3	619.1
60°	634.9	650.7	686.9	772.0	894.9	951.6	983.1	937.4	751.5	612.8	512.0
62.5°	556.1	571.9	601.8	682.2	757.8	787.7	814.5	756.2	620.7	499.4	438.0
65°	483.7	504.1	523.0	587.6	628.6	664.8	661.7	612.8	485.2	406.5	356.1
67.5°	420.6	428.5	444.3	483.7	502.6	529.3	530.9	475.8	390.7	330.8	300.9
70°	352.9	360.8	371.8	390.7	403.3	409.6	406.5	357.6	294.6	258.4	231.6
72.5°	294.6	293.0	300.9	300.9	313.5	311.9	302.5	264.7	223.7	193.8	178.0
75°	231.6	233.2	234.7	231.6	226.9	220.6	212.7	184.3	157.5	143.4	129.2
77.5°	181.2	178.0	179.6	168.6	162.3	156.0	144.9	130.8	108.7	105.6	99.3
80°	129.2	127.6	126.0	121.3	107.1	100.8	93.0	85.1	80.3	77.2	75.6
82.5°	86.6	86.6	83.5	74.0	66.2	61.4	59.9	56.7	52.0	52.0	50.4
85°	52.0	50.4	47.3	37.8	33.1	33.1	33.1	33.1	29.9	29.9	28.4
87.5°	20.5	18.9	14.2	14.2	12.6	12.6	12.6	11.0	11.0	9.5	9.5
90°	1.2	3.8	6.4	8.9	11.5	12.8	14.5	17.8	21.2	24.5	27.9
92.5°	26.7	25.1	23.6	22.0	20.5	19.7	20.9	23.2	25.5	27.9	30.2
95°	70.8	60.2	49.6	39.1	28.5	23.2	24.6	27.5	30.3	33.2	36.0
97.5°	128.9	121.7	114.5	107.2	100.0	96.4	89.8	76.7	63.5	50.4	37.2
100°	196.2	201.4	206.5	211.7	216.8	219.4	199.3	159.0	118.8	78.5	38.3
102.5°	272.8	276.2	279.5	282.9	286.2	287.9	265.5	220.6	175.7	130.8	85.9
105°	346.0	348.8	351.6	354.5	357.3	358.7	347.1	323.9	300.7	277.5	254.3
107.5°	423.8	426.1	428.4	430.7	433.0	434.2	436.1	440.0	443.9	447.7	451.6
110°	501.5	503.6	505.6	507.7	509.8	510.8	512.2	515.1	517.9	520.8	523.6

TEST NUMBER: P1012296

CATALOG NUMBER: S123RDIP-B1165D1195UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	575.8	577.6	579.4	581.3	583.1	584.0	585.4	588.2	591.1	593.9	596.7
115°	649.0	650.5	652.1	653.6	655.1	655.9	657.1	659.4	661.7	664.1	666.4
117.5°	721.0	722.8	724.6	726.4	728.2	729.1	729.7	731.0	732.3	733.6	734.9
120°	787.1	789.4	791.8	794.1	796.4	797.6	798.0	798.8	799.5	800.3	801.1
122.5°	854.5	856.3	858.1	859.9	861.7	862.6	863.1	864.1	865.2	866.2	867.2
125°	914.8	916.9	918.9	921.0	923.1	924.1	924.6	925.7	926.7	927.8	928.8
127.5°	975.2	977.3	979.3	981.4	983.5	984.5	985.1	986.4	987.7	989.0	990.3
130°	1030.9	1033.0	1035.0	1037.1	1039.2	1040.2	1040.7	1041.8	1042.8	1043.9	1044.9
132.5°	1084.3	1086.4	1088.4	1090.5	1092.6	1093.6	1094.0	1094.8	1095.5	1096.3	1097.1
135°	1138.9	1140.5	1142.0	1143.6	1145.1	1145.9	1146.4	1147.4	1148.5	1149.5	1150.5
137.5°	1185.3	1187.4	1189.4	1191.5	1193.6	1194.6	1194.9	1195.4	1195.9	1196.5	1197.0
140°	1231.8	1233.3	1234.9	1236.4	1237.9	1238.7	1239.1	1239.9	1240.6	1241.4	1242.2
142.5°	1274.7	1276.3	1277.8	1279.4	1280.9	1281.7	1282.1	1282.9	1283.6	1284.4	1285.2
145°	1314.2	1316.0	1317.8	1319.6	1321.4	1322.3	1322.6	1323.1	1323.6	1324.2	1324.7
147.5°	1352.5	1353.8	1355.1	1356.4	1357.7	1358.3	1358.6	1359.1	1359.6	1360.1	1360.6
150°	1387.3	1388.1	1388.9	1389.6	1390.4	1390.8	1391.1	1391.6	1392.1	1392.7	1393.2
152.5°	1418.7	1419.0	1419.2	1419.5	1419.8	1419.9	1420.0	1420.3	1420.5	1420.8	1421.0
155°	1447.7	1447.2	1446.7	1446.2	1445.7	1445.4	1445.5	1445.8	1446.1	1446.3	1446.6
157.5°	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9	1470.8	1470.5	1470.3	1470.0	1469.8
160°	1491.8	1491.6	1491.3	1491.1	1490.8	1490.7	1490.6	1490.3	1490.0	1489.8	1489.5
162.5°	1511.6	1510.8	1510.0	1509.3	1508.5	1508.1	1508.0	1507.7	1507.4	1507.2	1506.9
165°	1526.7	1525.9	1525.1	1524.4	1523.6	1523.2	1523.1	1522.8	1522.5	1522.3	1522.0
167.5°	1539.4	1538.4	1537.4	1536.3	1535.3	1534.8	1534.8	1534.8	1534.8	1534.8	1534.8
170°	1549.9	1548.9	1547.8	1546.8	1545.7	1545.2	1545.2	1545.2	1545.2	1545.2	1545.2
172.5°	1556.8	1555.5	1554.2	1552.9	1551.6	1551.0	1551.1	1551.4	1551.7	1551.9	1552.2
175°	1562.7	1561.4	1560.1	1558.8	1557.5	1556.8	1556.9	1557.2	1557.5	1557.7	1558.0
177.5°	1565.0	1563.7	1562.4	1561.1	1559.8	1559.2	1559.3	1559.6	1559.8	1560.1	1560.3
180°	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7

TEST NUMBER: P1012296

CATALOG NUMBER: S123RDIP-B1165D1195UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1
2.5°	1942.5	1942.5	1956.7	1970.9	1963.0	1967.7	1985.1	1978.8	1991.4	1989.8	1994.5
5°	2089.0	2106.4	2120.5	2150.5	2155.2	2150.5	2180.4	2188.3	2202.5	2185.1	2193.0
7.5°	2254.5	2290.7	2325.4	2369.5	2383.6	2386.8	2402.6	2424.6	2443.5	2408.9	2426.2
10°	2415.2	2470.3	2541.2	2580.6	2615.2	2627.8	2640.4	2654.6	2676.7	2697.2	2681.4
12.5°	2588.5	2668.8	2736.5	2807.4	2850.0	2845.3	2881.5	2890.9	2908.3	2913.0	2919.3
15°	2730.2	2843.7	2886.2	2991.8	3001.2	3032.7	3073.7	3109.9	3114.7	3105.2	3105.2
17.5°	2865.7	2963.4	3039.0	3124.1	3141.4	3168.2	3220.2	3237.5	3243.8	3242.3	3242.3
20°	2976.0	3040.6	3168.2	3239.1	3267.5	3302.1	3338.4	3360.4	3365.2	3371.5	3362.0
22.5°	3048.5	3146.2	3250.1	3308.4	3332.1	3344.7	3368.3	3374.6	3366.7	3368.3	3369.9
25°	3105.2	3201.3	3264.3	3280.1	3278.5	3262.7	3245.4	3215.5	3212.3	3199.7	3174.5
27.5°	3121.0	3157.2	3149.3	3084.7	3020.1	3013.8	2909.8	2853.1	2788.5	2798.0	2761.8
30°	3035.9	2988.6	2876.8	2712.9	2645.2	2534.9	2418.3	2297.0	2249.7	2197.7	2293.8
32.5°	2827.9	2659.4	2460.8	2248.2	2134.7	2037.1	1912.6	1824.4	1774.0	1731.4	1813.3
35°	2514.4	2251.3	1988.2	1786.6	1693.6	1605.4	1488.8	1444.7	1381.7	1388.0	1395.8
37.5°	2111.1	1821.2	1622.7	1424.2	1362.8	1326.5	1241.5	1173.7	1151.7	1145.3	1145.3
40°	1733.0	1495.1	1318.6	1162.7	1115.4	1085.5	1017.7	986.2	962.6	956.3	964.2
42.5°	1433.7	1230.4	1093.4	989.4	956.3	918.5	890.1	850.7	846.0	835.0	849.2
45°	1203.6	1027.2	924.8	849.2	820.8	806.6	775.1	751.5	742.0	740.5	751.5
47.5°	1020.9	883.8	794.0	746.8	724.7	710.5	683.7	674.3	664.8	668.0	663.3
50°	857.0	754.6	696.3	653.8	639.6	625.5	608.1	598.7	593.9	593.9	592.4
52.5°	735.7	650.7	612.8	573.5	567.2	559.3	540.4	534.1	526.2	524.6	530.9
55°	630.2	571.9	534.1	510.4	504.1	488.4	480.5	472.6	467.9	464.8	466.3
57.5°	538.8	494.7	469.5	449.0	438.0	431.7	417.5	415.9	412.8	412.8	411.2
60°	463.2	431.7	401.7	389.1	381.3	373.4	371.8	362.4	357.6	360.8	359.2
62.5°	392.3	367.1	349.7	335.6	330.8	324.5	319.8	316.7	311.9	313.5	313.5
65°	327.7	307.2	294.6	282.0	280.4	274.1	272.6	269.4	269.4	267.8	271.0
67.5°	269.4	255.2	244.2	236.3	231.6	233.2	226.9	222.1	222.1	220.6	225.3
70°	214.3	206.4	195.4	185.9	179.6	179.6	171.7	170.1	170.1	170.1	168.6
72.5°	165.4	151.2	146.5	143.4	143.4	143.4	140.2	140.2	138.6	140.2	138.6
75°	122.9	121.3	118.2	116.6	116.6	115.0	113.4	113.4	113.4	113.4	113.4
77.5°	96.1	96.1	93.0	91.4	91.4	91.4	89.8	89.8	88.2	88.2	88.2
80°	70.9	70.9	67.7	67.7	67.7	66.2	66.2	66.2	67.7	66.2	66.2
82.5°	48.8	48.8	47.3	48.8	47.3	45.7	45.7	45.7	44.1	45.7	45.7
85°	28.4	28.4	26.8	25.2	26.8	26.8	25.2	26.8	25.2	26.8	25.2
87.5°	11.0	9.5	9.5	9.5	7.9	9.5	7.9	7.9	9.5	7.9	9.5
90°	28.9	29.9	31.0	32.0	32.5	32.8	33.3	33.8	34.3	34.8	34.3
92.5°	32.0	33.8	35.6	37.4	38.3	38.4	38.7	39.0	39.2	39.5	39.2
95°	37.8	39.6	41.4	43.2	44.1	44.1	44.1	44.1	44.1	44.1	44.1
97.5°	39.2	41.3	43.3	45.4	46.4	46.5	46.8	47.1	47.3	47.6	47.3
100°	40.4	42.4	44.5	46.6	47.6	47.7	48.0	48.3	48.5	48.8	48.5
102.5°	77.4	68.9	60.4	51.9	47.6	47.9	48.4	48.9	49.4	49.9	49.4
105°	208.6	163.0	117.3	71.6	48.8	49.1	49.6	50.1	50.6	51.1	50.6
107.5°	411.9	372.1	332.4	292.7	272.8	255.9	222.1	188.3	154.5	120.7	154.5
110°	515.1	506.6	498.1	489.6	485.3	466.9	430.0	393.1	356.2	319.3	356.2

TEST NUMBER: P1012296

CATALOG NUMBER: S123RDIP-B1165D1195UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	599.0	601.4	603.7	606.0	607.2	606.9	606.4	605.9	605.4	604.9	605.4
115°	669.0	671.6	674.1	676.7	678.0	678.5	679.5	680.6	681.6	682.6	681.6
117.5°	737.0	739.0	741.1	743.2	744.2	744.3	744.6	744.8	745.1	745.3	745.1
120°	803.2	805.2	807.3	809.4	810.4	810.4	810.4	810.4	810.4	810.4	810.4
122.5°	868.5	869.8	871.1	872.4	873.0	873.1	873.4	873.7	873.9	874.2	873.9
125°	929.3	929.8	930.3	930.8	931.1	931.4	931.9	932.4	932.9	933.4	932.9
127.5°	991.1	991.9	992.6	993.4	993.8	993.5	993.0	992.5	992.0	991.5	992.0
130°	1045.9	1046.9	1048.0	1049.0	1049.5	1049.2	1048.7	1048.2	1047.7	1047.2	1047.7
132.5°	1098.1	1099.2	1100.2	1101.3	1101.8	1101.4	1100.6	1099.9	1099.1	1098.3	1099.1
135°	1151.3	1152.1	1152.8	1153.6	1154.0	1153.6	1152.8	1152.1	1151.3	1150.5	1151.3
137.5°	1198.3	1199.6	1200.9	1202.2	1202.8	1202.5	1202.0	1201.5	1200.9	1200.4	1200.9
140°	1243.2	1244.3	1245.3	1246.4	1246.9	1246.6	1246.1	1245.6	1245.0	1244.5	1245.0
142.5°	1286.0	1286.8	1287.5	1288.3	1288.7	1288.3	1287.5	1286.8	1286.0	1285.2	1286.0
145°	1325.2	1325.7	1326.2	1326.7	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0
147.5°	1361.1	1361.7	1362.2	1362.7	1363.0	1362.4	1361.1	1359.8	1358.5	1357.2	1358.5
150°	1393.7	1394.2	1394.7	1395.2	1395.5	1395.1	1394.3	1393.6	1392.8	1392.0	1392.8
152.5°	1422.0	1423.1	1424.1	1425.2	1425.7	1425.1	1423.8	1422.5	1421.2	1419.9	1421.2
155°	1447.9	1449.2	1450.5	1451.8	1452.4	1451.6	1450.1	1448.5	1447.0	1445.4	1447.0
157.5°	1471.3	1472.9	1474.4	1475.9	1476.7	1475.7	1473.6	1471.6	1469.5	1467.5	1469.5
160°	1491.1	1492.6	1494.2	1495.7	1496.5	1495.6	1493.8	1492.0	1490.2	1488.4	1490.2
162.5°	1508.7	1510.5	1512.4	1514.2	1515.1	1514.3	1512.8	1511.2	1509.7	1508.1	1509.7
165°	1524.1	1526.1	1528.2	1530.3	1531.3	1530.4	1528.6	1526.8	1525.0	1523.2	1525.0
167.5°	1536.9	1538.9	1541.0	1543.1	1544.1	1543.1	1541.0	1538.9	1536.9	1534.8	1536.9
170°	1547.3	1549.3	1551.4	1553.5	1554.5	1553.5	1551.4	1549.3	1547.3	1545.2	1547.3
172.5°	1554.3	1556.3	1558.4	1560.5	1561.5	1560.3	1558.0	1555.7	1553.3	1551.0	1553.3
175°	1559.8	1561.6	1563.4	1565.2	1566.1	1565.1	1563.0	1560.9	1558.9	1556.8	1558.9
177.5°	1562.4	1564.4	1566.5	1568.6	1569.6	1568.3	1565.7	1563.2	1560.6	1558.0	1560.6
180°	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7

TEST NUMBER: P1012296

CATALOG NUMBER: S123RDIP-B1165D1195UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1
2.5°	1986.6	1977.2	1970.9	1966.2	1961.4	1975.6	1956.7	1936.2	1922.0	1912.6	1909.4
5°	2194.6	2174.1	2156.8	2142.6	2145.8	2145.8	2112.7	2076.4	2044.9	2027.6	2008.7
7.5°	2435.6	2413.6	2378.9	2371.0	2364.7	2325.4	2292.3	2226.1	2186.7	2147.3	2112.7
10°	2675.1	2646.7	2613.7	2602.6	2586.9	2538.0	2487.6	2402.6	2353.7	2281.2	2235.6
12.5°	2898.8	2864.2	2831.1	2823.2	2799.6	2757.0	2670.4	2582.2	2498.7	2421.5	2341.1
15°	3086.3	3076.8	3026.4	2994.9	2942.9	2884.6	2865.7	2746.0	2640.4	2560.1	2415.2
17.5°	3243.8	3199.7	3152.5	3132.0	3111.5	3043.8	2976.0	2853.1	2739.7	2621.5	2528.6
20°	3369.9	3321.0	3288.0	3258.0	3248.6	3171.4	3064.2	2955.5	2831.1	2698.7	2577.4
22.5°	3376.2	3369.9	3347.8	3330.5	3311.6	3261.2	3176.1	3040.6	2908.3	2763.3	2604.2
25°	3245.4	3236.0	3299.0	3283.2	3295.8	3276.9	3231.2	3117.8	2963.4	2793.3	2632.6
27.5°	2851.6	2947.7	3046.9	3081.6	3105.2	3172.9	3195.0	3132.0	3007.5	2826.3	2646.7
30°	2315.9	2443.5	2604.2	2690.9	2757.0	2883.1	3046.9	3067.4	3009.1	2864.2	2643.6
32.5°	1818.1	1934.6	2063.8	2166.2	2254.5	2512.8	2733.4	2892.5	2920.9	2845.3	2651.5
35°	1465.2	1515.6	1638.5	1736.1	1855.9	2076.4	2336.4	2593.2	2766.5	2775.9	2627.8
37.5°	1208.4	1235.1	1342.3	1397.4	1468.3	1662.1	1904.7	2240.3	2509.7	2637.3	2561.7
40°	1000.4	1061.8	1123.3	1154.8	1205.2	1339.1	1572.3	1835.4	2169.4	2405.7	2459.3
42.5°	868.1	894.9	934.2	978.4	1009.9	1126.4	1282.4	1523.5	1824.4	2153.6	2301.7
45°	765.7	775.1	816.1	844.4	877.5	959.4	1069.7	1271.4	1536.1	1860.6	2112.7
47.5°	680.6	699.5	721.6	738.9	760.9	824.0	918.5	1065.0	1298.2	1588.0	1859.0
50°	605.0	616.0	644.4	652.2	668.0	712.1	784.6	896.4	1088.6	1320.2	1600.7
52.5°	534.1	554.6	565.6	576.6	590.8	627.0	674.3	765.7	910.6	1128.0	1365.9
55°	478.9	485.2	501.0	510.4	521.5	546.7	587.6	655.4	768.8	942.1	1167.4
57.5°	425.4	425.4	441.1	449.0	460.0	478.9	515.2	567.2	649.1	778.3	984.7
60°	368.7	370.2	382.8	392.3	395.4	414.3	444.3	485.2	548.3	642.8	811.4
62.5°	318.2	326.1	332.4	335.6	346.6	357.6	382.8	411.2	455.3	538.8	658.5
65°	275.7	277.3	282.0	285.2	289.9	302.5	321.4	340.3	378.1	439.5	537.2
67.5°	226.9	233.2	239.5	239.5	244.2	250.5	269.4	285.2	313.5	349.7	415.9
70°	170.1	173.3	182.8	187.5	193.8	204.8	214.3	223.7	245.8	272.6	323.0
72.5°	141.8	141.8	144.9	146.5	146.5	154.4	168.6	178.0	189.1	208.0	242.6
75°	113.4	113.4	118.2	116.6	119.7	122.9	124.5	130.8	137.1	151.2	171.7
77.5°	89.8	91.4	91.4	93.0	93.0	94.5	96.1	99.3	102.4	110.3	119.7
80°	66.2	67.7	67.7	69.3	69.3	70.9	72.5	74.0	77.2	80.3	85.1
82.5°	45.7	47.3	47.3	48.8	47.3	48.8	50.4	50.4	52.0	55.1	56.7
85°	26.8	26.8	28.4	26.8	26.8	26.8	28.4	28.4	29.9	34.7	34.7
87.5°	7.9	9.5	7.9	9.5	9.5	9.5	9.5	11.0	11.0	12.6	14.2
90°	33.8	33.3	32.8	32.5	32.0	31.0	29.9	28.9	27.9	24.5	21.2
92.5°	39.0	38.7	38.4	38.3	37.4	35.6	33.8	32.0	30.2	27.9	25.5
95°	44.1	44.1	44.1	44.1	43.2	41.4	39.6	37.8	36.0	33.2	30.3
97.5°	47.1	46.8	46.5	46.4	45.4	43.3	41.3	39.2	37.2	50.4	63.5
100°	48.3	48.0	47.7	47.6	46.6	44.5	42.4	40.4	38.3	78.5	118.8
102.5°	48.9	48.4	47.9	47.6	51.9	60.4	68.9	77.4	85.9	130.8	175.7
105°	50.1	49.6	49.1	48.8	71.6	117.3	163.0	208.6	254.3	277.5	300.7
107.5°	188.3	222.1	255.9	272.8	292.7	332.4	372.1	411.9	451.6	447.7	443.9
110°	393.1	430.0	466.9	485.3	489.6	498.1	506.6	515.1	523.6	520.8	517.9

TEST NUMBER: P1012296

CATALOG NUMBER: S123RDIP-B1165D1195UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	605.9	606.4	606.9	607.2	606.0	603.7	601.4	599.0	596.7	593.9	591.1
115°	680.6	679.5	678.5	678.0	676.7	674.1	671.6	669.0	666.4	664.1	661.7
117.5°	744.8	744.6	744.3	744.2	743.2	741.1	739.0	737.0	734.9	733.6	732.3
120°	810.4	810.4	810.4	810.4	809.4	807.3	805.2	803.2	801.1	800.3	799.5
122.5°	873.7	873.4	873.1	873.0	872.4	871.1	869.8	868.5	867.2	866.2	865.2
125°	932.4	931.9	931.4	931.1	930.8	930.3	929.8	929.3	928.8	927.8	926.7
127.5°	992.5	993.0	993.5	993.8	993.4	992.6	991.9	991.1	990.3	989.0	987.7
130°	1048.2	1048.7	1049.2	1049.5	1049.0	1048.0	1046.9	1045.9	1044.9	1043.9	1042.8
132.5°	1099.9	1100.6	1101.4	1101.8	1101.3	1100.2	1099.2	1098.1	1097.1	1096.3	1095.5
135°	1152.1	1152.8	1153.6	1154.0	1153.6	1152.8	1152.1	1151.3	1150.5	1149.5	1148.5
137.5°	1201.5	1202.0	1202.5	1202.8	1202.2	1200.9	1199.6	1198.3	1197.0	1196.5	1195.9
140°	1245.6	1246.1	1246.6	1246.9	1246.4	1245.3	1244.3	1243.2	1242.2	1241.4	1240.6
142.5°	1286.8	1287.5	1288.3	1288.7	1288.3	1287.5	1286.8	1286.0	1285.2	1284.4	1283.6
145°	1327.0	1327.0	1327.0	1327.0	1326.7	1326.2	1325.7	1325.2	1324.7	1324.2	1323.6
147.5°	1359.8	1361.1	1362.4	1363.0	1362.7	1362.2	1361.7	1361.1	1360.6	1360.1	1359.6
150°	1393.6	1394.3	1395.1	1395.5	1395.2	1394.7	1394.2	1393.7	1393.2	1392.7	1392.1
152.5°	1422.5	1423.8	1425.1	1425.7	1425.2	1424.1	1423.1	1422.0	1421.0	1420.8	1420.5
155°	1448.5	1450.1	1451.6	1452.4	1451.8	1450.5	1449.2	1447.9	1446.6	1446.3	1446.1
157.5°	1471.6	1473.6	1475.7	1476.7	1475.9	1474.4	1472.9	1471.3	1469.8	1470.0	1470.3
160°	1492.0	1493.8	1495.6	1496.5	1495.7	1494.2	1492.6	1491.1	1489.5	1489.8	1490.0
162.5°	1511.2	1512.8	1514.3	1515.1	1514.2	1512.4	1510.5	1508.7	1506.9	1507.2	1507.4
165°	1526.8	1528.6	1530.4	1531.3	1530.3	1528.2	1526.1	1524.1	1522.0	1522.3	1522.5
167.5°	1538.9	1541.0	1543.1	1544.1	1543.1	1541.0	1538.9	1536.9	1534.8	1534.8	1534.8
170°	1549.3	1551.4	1553.5	1554.5	1553.5	1551.4	1549.3	1547.3	1545.2	1545.2	1545.2
172.5°	1555.7	1558.0	1560.3	1561.5	1560.5	1558.4	1556.3	1554.3	1552.2	1551.9	1551.7
175°	1560.9	1563.0	1565.1	1566.1	1565.2	1563.4	1561.6	1559.8	1558.0	1557.7	1557.5
177.5°	1563.2	1565.7	1568.3	1569.6	1568.6	1566.5	1564.4	1562.4	1560.3	1560.1	1559.8
180°	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7

TEST NUMBER: P1012296

CATALOG NUMBER: S123RDIP-B1165D1195UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1
2.5°	1904.7	1896.8	1889.0	1889.0	1871.6	1855.9	1848.0	1851.1	1841.7	1829.1	1816.5
5°	1988.2	1956.7	1950.4	1933.1	1909.4	1876.4	1859.0	1843.3	1824.4	1799.2	1775.5
7.5°	2065.4	2024.4	2002.4	1985.1	1939.4	1893.7	1855.9	1830.7	1797.6	1759.8	1731.4
10°	2166.2	2090.6	2067.0	2027.6	1963.0	1898.4	1854.3	1813.3	1767.6	1723.5	1685.7
12.5°	2246.6	2159.9	2115.8	2076.4	1992.9	1911.0	1837.0	1786.6	1731.4	1682.6	1633.7
15°	2338.0	2240.3	2163.1	2115.8	2010.3	1911.0	1827.5	1756.6	1695.2	1635.3	1592.8
17.5°	2382.1	2259.2	2224.5	2156.8	2004.0	1904.7	1802.3	1726.7	1652.6	1583.3	1532.9
20°	2451.4	2308.0	2221.4	2175.7	2040.2	1893.7	1774.0	1687.3	1610.1	1536.1	1482.5
22.5°	2456.1	2300.1	2243.4	2156.8	1989.8	1860.6	1748.7	1643.2	1553.4	1484.1	1428.9
25°	2445.1	2286.0	2207.2	2137.9	1999.2	1841.7	1698.3	1594.4	1506.1	1425.8	1361.2
27.5°	2440.4	2245.0	2171.0	2101.6	1945.7	1786.6	1668.4	1550.2	1449.4	1378.5	1312.3
30°	2434.1	2200.9	2111.1	2030.7	1887.4	1744.0	1602.2	1499.8	1403.7	1313.9	1247.8
32.5°	2393.1	2141.0	2049.7	1964.6	1810.2	1666.8	1555.0	1446.3	1342.3	1258.8	1198.9
35°	2380.5	2085.9	1966.2	1874.8	1723.5	1595.9	1477.8	1388.0	1290.3	1206.8	1135.9
37.5°	2344.3	2029.2	1900.0	1783.4	1625.9	1504.6	1417.9	1328.1	1233.6	1143.8	1087.1
40°	2281.2	1963.0	1816.5	1696.8	1534.5	1411.6	1331.3	1265.1	1172.1	1091.8	1022.5
42.5°	2188.3	1895.3	1737.7	1611.7	1432.1	1317.1	1250.9	1187.9	1109.1	1025.6	968.9
45°	2081.2	1805.5	1658.9	1518.7	1336.0	1224.1	1154.8	1117.0	1044.5	973.6	907.5
47.5°	1934.6	1712.5	1567.6	1422.6	1236.7	1128.0	1072.9	1035.1	984.7	907.5	853.9
50°	1750.3	1592.8	1455.7	1326.5	1139.0	1035.1	979.9	951.6	909.0	853.9	801.9
52.5°	1545.5	1454.1	1340.7	1221.0	1039.8	942.1	891.7	869.6	838.1	786.1	742.0
55°	1339.1	1299.7	1222.5	1104.4	935.8	855.5	811.4	783.0	759.4	721.6	683.7
57.5°	1154.8	1135.9	1082.3	991.0	849.2	765.7	727.9	709.0	690.0	661.7	623.9
60°	964.2	984.7	929.5	883.8	754.6	682.2	649.1	628.6	619.1	593.9	570.3
62.5°	798.8	817.7	786.1	751.5	660.1	595.5	575.0	556.1	549.8	527.8	504.1
65°	649.1	672.7	649.1	630.2	575.0	521.5	496.3	486.8	480.5	466.3	447.4
67.5°	516.7	540.4	529.3	505.7	488.4	444.3	430.1	420.6	417.5	406.5	390.7
70°	389.1	422.2	425.4	411.2	395.4	375.0	365.5	362.4	354.5	345.0	335.6
72.5°	280.4	318.2	319.8	319.8	310.4	310.4	300.9	296.2	296.2	286.7	275.7
75°	206.4	231.6	234.7	237.9	242.6	247.3	241.0	241.0	239.5	230.0	225.3
77.5°	137.1	159.1	167.0	178.0	184.3	184.3	187.5	190.6	187.5	182.8	179.6
80°	88.2	104.0	113.4	119.7	129.2	133.9	138.6	140.2	137.1	135.5	130.8
82.5°	58.3	63.0	67.7	75.6	86.6	94.5	94.5	93.0	96.1	94.5	93.0
85°	33.1	36.2	37.8	39.4	45.7	53.6	55.1	56.7	59.9	56.7	53.6
87.5°	12.6	14.2	14.2	14.2	17.3	18.9	23.6	29.9	28.4	25.2	25.2
90°	17.8	14.5	12.8	11.5	8.9	6.4	3.8	1.2	3.8	6.4	8.9
92.5°	23.2	20.9	19.7	20.5	22.0	23.6	25.1	26.7	25.1	23.6	22.0
95°	27.5	24.6	23.2	28.5	39.1	49.6	60.2	70.8	60.2	49.6	39.1
97.5°	76.7	89.8	96.4	100.0	107.2	114.5	121.7	128.9	121.7	114.5	107.2
100°	159.0	199.3	219.4	216.8	211.7	206.5	201.4	196.2	201.4	206.5	211.7
102.5°	220.6	265.5	287.9	286.2	282.9	279.5	276.2	272.8	276.2	279.5	282.9
105°	323.9	347.1	358.7	357.3	354.5	351.6	348.8	346.0	348.8	351.6	354.5
107.5°	440.0	436.1	434.2	433.0	430.7	428.4	426.1	423.8	426.1	428.4	430.7
110°	515.1	512.2	510.8	509.8	507.7	505.6	503.6	501.5	503.6	505.6	507.7

TEST NUMBER: P1012296

CATALOG NUMBER: S123RDIP-B1165D1195UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	588.2	585.4	584.0	583.1	581.3	579.4	577.6	575.8	577.6	579.4	581.3
115°	659.4	657.1	655.9	655.1	653.6	652.1	650.5	649.0	650.5	652.1	653.6
117.5°	731.0	729.7	729.1	728.2	726.4	724.6	722.8	721.0	722.8	724.6	726.4
120°	798.8	798.0	797.6	796.4	794.1	791.8	789.4	787.1	789.4	791.8	794.1
122.5°	864.1	863.1	862.6	861.7	859.9	858.1	856.3	854.5	856.3	858.1	859.9
125°	925.7	924.6	924.1	923.1	921.0	918.9	916.9	914.8	916.9	918.9	921.0
127.5°	986.4	985.1	984.5	983.5	981.4	979.3	977.3	975.2	977.3	979.3	981.4
130°	1041.8	1040.7	1040.2	1039.2	1037.1	1035.0	1033.0	1030.9	1033.0	1035.0	1037.1
132.5°	1094.8	1094.0	1093.6	1092.6	1090.5	1088.4	1086.4	1084.3	1086.4	1088.4	1090.5
135°	1147.4	1146.4	1145.9	1145.1	1143.6	1142.0	1140.5	1138.9	1140.5	1142.0	1143.6
137.5°	1195.4	1194.9	1194.6	1193.6	1191.5	1189.4	1187.4	1185.3	1187.4	1189.4	1191.5
140°	1239.9	1239.1	1238.7	1237.9	1236.4	1234.9	1233.3	1231.8	1233.3	1234.9	1236.4
142.5°	1282.9	1282.1	1281.7	1280.9	1279.4	1277.8	1276.3	1274.7	1276.3	1277.8	1279.4
145°	1323.1	1322.6	1322.3	1321.4	1319.6	1317.8	1316.0	1314.2	1316.0	1317.8	1319.6
147.5°	1359.1	1358.6	1358.3	1357.7	1356.4	1355.1	1353.8	1352.5	1353.8	1355.1	1356.4
150°	1391.6	1391.1	1390.8	1390.4	1389.6	1388.9	1388.1	1387.3	1388.1	1388.9	1389.6
152.5°	1420.3	1420.0	1419.9	1419.8	1419.5	1419.2	1419.0	1418.7	1419.0	1419.2	1419.5
155°	1445.8	1445.5	1445.4	1445.7	1446.2	1446.7	1447.2	1447.7	1447.2	1446.7	1446.2
157.5°	1470.5	1470.8	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9	1470.9
160°	1490.3	1490.6	1490.7	1490.8	1491.1	1491.3	1491.6	1491.8	1491.6	1491.3	1491.1
162.5°	1507.7	1508.0	1508.1	1508.5	1509.3	1510.0	1510.8	1511.6	1510.8	1510.0	1509.3
165°	1522.8	1523.1	1523.2	1523.6	1524.4	1525.1	1525.9	1526.7	1525.9	1525.1	1524.4
167.5°	1534.8	1534.8	1534.8	1535.3	1536.3	1537.4	1538.4	1539.4	1538.4	1537.4	1536.3
170°	1545.2	1545.2	1545.2	1545.7	1546.8	1547.8	1548.9	1549.9	1548.9	1547.8	1546.8
172.5°	1551.4	1551.1	1551.0	1551.6	1552.9	1554.2	1555.5	1556.8	1555.5	1554.2	1552.9
175°	1557.2	1556.9	1556.8	1557.5	1558.8	1560.1	1561.4	1562.7	1561.4	1560.1	1558.8
177.5°	1559.6	1559.3	1559.2	1559.8	1561.1	1562.4	1563.7	1565.0	1563.7	1562.4	1561.1
180°	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7

TEST NUMBER: P1012296

CATALOG NUMBER: S123RDIP-B1165D1195UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1
2.5°	1816.5	1808.6	1805.5	1797.6	1778.7	1766.1	1751.9	1742.4	1744.0	1736.1	1740.9
5°	1759.8	1758.2	1747.2	1731.4	1704.6	1690.5	1665.2	1652.6	1646.3	1647.9	1638.5
7.5°	1712.5	1698.3	1690.5	1665.2	1640.0	1610.1	1589.6	1578.6	1569.1	1559.7	1553.4
10°	1658.9	1646.3	1633.7	1607.0	1572.3	1543.9	1515.6	1504.6	1490.4	1484.1	1479.3
12.5°	1602.2	1594.4	1578.6	1547.1	1507.7	1480.9	1447.8	1441.5	1422.6	1410.0	1406.9
15°	1550.2	1545.5	1517.2	1480.9	1441.5	1414.7	1386.4	1367.5	1336.0	1342.3	1331.3
17.5°	1495.1	1474.6	1457.3	1408.4	1389.5	1348.6	1315.5	1306.0	1284.0	1269.8	1255.6
20°	1433.7	1421.1	1399.0	1367.5	1321.8	1274.5	1249.3	1233.6	1221.0	1198.9	1192.6
22.5°	1375.4	1359.6	1340.7	1299.7	1260.4	1221.0	1186.3	1172.1	1156.4	1140.6	1131.2
25°	1329.7	1306.0	1285.6	1235.1	1195.8	1162.7	1140.6	1117.0	1094.9	1085.5	1082.3
27.5°	1258.8	1244.6	1224.1	1176.9	1140.6	1104.4	1083.9	1068.2	1044.5	1033.5	1024.0
30°	1213.1	1184.7	1161.1	1123.3	1087.1	1047.7	1028.8	1009.9	995.7	981.5	970.5
32.5°	1151.7	1129.6	1110.7	1072.9	1036.6	1000.4	979.9	951.6	943.7	932.7	920.1
35°	1091.8	1077.6	1057.1	1016.2	976.8	951.6	929.5	902.7	893.3	885.4	874.4
37.5°	1035.1	1014.6	1000.4	961.0	926.4	896.4	879.1	857.0	850.7	841.3	833.4
40°	986.2	965.7	951.6	912.2	875.9	844.4	833.4	811.4	801.9	790.9	786.1
42.5°	931.1	913.8	894.9	866.5	828.7	797.2	775.1	762.5	749.9	745.2	735.7
45°	872.8	857.0	842.9	811.4	772.0	749.9	731.0	713.7	704.2	696.3	690.0
47.5°	822.4	808.2	789.3	754.6	723.1	702.6	683.7	666.4	657.0	647.5	639.6
50°	764.1	756.2	735.7	702.6	672.7	649.1	631.8	616.0	609.7	598.7	586.1
52.5°	712.1	697.9	680.6	653.8	627.0	598.7	575.0	565.6	554.6	548.3	537.2
55°	650.7	641.2	622.3	598.7	570.3	546.7	529.3	516.7	502.6	496.3	482.1
57.5°	598.7	581.3	571.9	542.0	515.2	491.5	478.9	466.3	450.6	441.1	434.8
60°	542.0	526.2	512.0	486.8	467.9	442.7	423.8	412.8	401.7	389.1	382.8
62.5°	486.8	474.2	456.9	436.4	412.8	392.3	378.1	362.4	356.1	343.4	338.7
65°	426.9	417.5	403.3	379.7	360.8	343.4	329.3	316.7	310.4	305.6	302.5
67.5°	373.4	360.8	351.3	330.8	310.4	296.2	288.3	280.4	272.6	267.8	263.1
70°	318.2	308.8	299.3	280.4	266.3	253.6	247.3	241.0	236.3	231.6	226.9
72.5°	261.5	256.8	247.3	234.7	223.7	214.3	209.5	201.7	196.9	189.1	185.9
75°	215.8	208.0	203.2	192.2	182.8	174.9	168.6	159.1	152.8	149.7	148.1
77.5°	170.1	167.0	160.7	151.2	146.5	138.6	129.2	126.0	122.9	122.9	121.3
80°	127.6	122.9	118.2	110.3	105.6	99.3	99.3	99.3	97.7	99.3	97.7
82.5°	86.6	83.5	80.3	75.6	74.0	74.0	75.6	75.6	75.6	75.6	75.6
85°	50.4	50.4	50.4	52.0	50.4	50.4	52.0	53.6	52.0	52.0	50.4
87.5°	23.6	23.6	25.2	25.2	26.8	26.8	26.8	26.8	26.8	26.8	28.4
90°	11.5	12.8	14.5	17.8	21.2	24.5	27.9	28.9	29.9	31.0	32.0
92.5°	20.5	19.7	20.9	23.2	25.5	27.9	30.2	32.0	33.8	35.6	37.4
95°	28.5	23.2	24.6	27.5	30.3	33.2	36.0	37.8	39.6	41.4	43.2
97.5°	100.0	96.4	89.8	76.7	63.5	50.4	37.2	39.2	41.3	43.3	45.4
100°	216.8	219.4	199.3	159.0	118.8	78.5	38.3	40.4	42.4	44.5	46.6
102.5°	286.2	287.9	265.5	220.6	175.7	130.8	85.9	77.4	68.9	60.4	51.9
105°	357.3	358.7	347.1	323.9	300.7	277.5	254.3	208.6	163.0	117.3	71.6
107.5°	433.0	434.2	436.1	440.0	443.9	447.7	451.6	411.9	372.1	332.4	292.7
110°	509.8	510.8	512.2	515.1	517.9	520.8	523.6	515.1	506.6	498.1	489.6

TEST NUMBER: P1012296

CATALOG NUMBER: S123RDIP-B1165D1195UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	583.1	584.0	585.4	588.2	591.1	593.9	596.7	599.0	601.4	603.7	606.0
115°	655.1	655.9	657.1	659.4	661.7	664.1	666.4	669.0	671.6	674.1	676.7
117.5°	728.2	729.1	729.7	731.0	732.3	733.6	734.9	737.0	739.0	741.1	743.2
120°	796.4	797.6	798.0	798.8	799.5	800.3	801.1	803.2	805.2	807.3	809.4
122.5°	861.7	862.6	863.1	864.1	865.2	866.2	867.2	868.5	869.8	871.1	872.4
125°	923.1	924.1	924.6	925.7	926.7	927.8	928.8	929.3	929.8	930.3	930.8
127.5°	983.5	984.5	985.1	986.4	987.7	989.0	990.3	991.1	991.9	992.6	993.4
130°	1039.2	1040.2	1040.7	1041.8	1042.8	1043.9	1044.9	1045.9	1046.9	1048.0	1049.0
132.5°	1092.6	1093.6	1094.0	1094.8	1095.5	1096.3	1097.1	1098.1	1099.2	1100.2	1101.3
135°	1145.1	1145.9	1146.4	1147.4	1148.5	1149.5	1150.5	1151.3	1152.1	1152.8	1153.6
137.5°	1193.6	1194.6	1194.9	1195.4	1195.9	1196.5	1197.0	1198.3	1199.6	1200.9	1202.2
140°	1237.9	1238.7	1239.1	1239.9	1240.6	1241.4	1242.2	1243.2	1244.3	1245.3	1246.4
142.5°	1280.9	1281.7	1282.1	1282.9	1283.6	1284.4	1285.2	1286.0	1286.8	1287.5	1288.3
145°	1321.4	1322.3	1322.6	1323.1	1323.6	1324.2	1324.7	1325.2	1325.7	1326.2	1326.7
147.5°	1357.7	1358.3	1358.6	1359.1	1359.6	1360.1	1360.6	1361.1	1361.7	1362.2	1362.7
150°	1390.4	1390.8	1391.1	1391.6	1392.1	1392.7	1393.2	1393.7	1394.2	1394.7	1395.2
152.5°	1419.8	1419.9	1420.0	1420.3	1420.5	1420.8	1421.0	1422.0	1423.1	1424.1	1425.2
155°	1445.7	1445.4	1445.5	1445.8	1446.1	1446.3	1446.6	1447.9	1449.2	1450.5	1451.8
157.5°	1470.9	1470.9	1470.8	1470.5	1470.3	1470.0	1469.8	1471.3	1472.9	1474.4	1475.9
160°	1490.8	1490.7	1490.6	1490.3	1490.0	1489.8	1489.5	1491.1	1492.6	1494.2	1495.7
162.5°	1508.5	1508.1	1508.0	1507.7	1507.4	1507.2	1506.9	1508.7	1510.5	1512.4	1514.2
165°	1523.6	1523.2	1523.1	1522.8	1522.5	1522.3	1522.0	1524.1	1526.1	1528.2	1530.3
167.5°	1535.3	1534.8	1534.8	1534.8	1534.8	1534.8	1534.8	1536.9	1538.9	1541.0	1543.1
170°	1545.7	1545.2	1545.2	1545.2	1545.2	1545.2	1545.2	1547.3	1549.3	1551.4	1553.5
172.5°	1551.6	1551.0	1551.1	1551.4	1551.7	1551.9	1552.2	1554.3	1556.3	1558.4	1560.5
175°	1557.5	1556.8	1556.9	1557.2	1557.5	1557.7	1558.0	1559.8	1561.6	1563.4	1565.2
177.5°	1559.8	1559.2	1559.3	1559.6	1559.8	1560.1	1560.3	1562.4	1564.4	1566.5	1568.6
180°	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7

TEST NUMBER: P1012296

CATALOG NUMBER: S123RDIP-B1165D1195UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1
2.5°	1739.3	1740.9	1736.1	1726.7	1725.1	1728.3	1737.7	1734.6	1726.7	1740.9	1728.3
5°	1643.2	1635.3	1632.2	1635.3	1625.9	1621.1	1630.6	1625.9	1630.6	1632.2	1636.9
7.5°	1550.2	1551.8	1542.4	1543.9	1531.3	1534.5	1534.5	1534.5	1539.2	1542.4	1548.7
10°	1469.9	1473.0	1462.0	1463.6	1454.1	1447.8	1452.6	1462.0	1462.0	1462.0	1465.2
12.5°	1405.3	1391.1	1383.2	1381.7	1370.6	1367.5	1376.9	1380.1	1388.0	1388.0	1392.7
15°	1324.9	1321.8	1315.5	1315.5	1288.7	1295.0	1298.2	1309.2	1324.9	1312.3	1315.5
17.5°	1252.5	1244.6	1236.7	1233.6	1230.4	1221.0	1233.6	1232.0	1241.5	1243.0	1247.8
20°	1187.9	1181.6	1165.8	1167.4	1170.6	1156.4	1164.3	1164.3	1173.7	1183.2	1194.2
22.5°	1124.9	1118.6	1110.7	1113.8	1104.4	1101.2	1101.2	1109.1	1120.1	1128.0	1126.4
25°	1076.0	1065.0	1060.3	1055.5	1050.8	1054.0	1049.2	1057.1	1065.0	1069.7	1065.0
27.5°	1020.9	1016.2	1006.7	1002.0	994.1	997.3	1000.4	1006.7	1011.4	1011.4	1016.2
30°	967.3	961.0	957.9	953.1	953.1	946.8	948.4	954.7	959.4	964.2	970.5
32.5°	915.3	910.6	905.9	905.9	902.7	901.2	899.6	909.0	909.0	918.5	918.5
35°	872.8	864.9	864.9	857.0	860.2	858.6	855.5	861.8	863.3	869.6	868.1
37.5°	825.5	825.5	822.4	814.5	808.2	809.8	817.7	817.7	822.4	820.8	825.5
40°	778.3	775.1	775.1	770.4	768.8	767.2	768.8	770.4	778.3	776.7	778.3
42.5°	731.0	732.6	724.7	724.7	724.7	720.0	721.6	723.1	726.3	729.4	734.2
45°	685.3	682.2	680.6	677.4	674.3	675.9	674.3	680.6	679.0	682.2	686.9
47.5°	636.5	631.8	630.2	623.9	623.9	627.0	625.5	630.2	631.8	636.5	633.3
50°	589.2	582.9	578.2	579.8	570.3	573.5	573.5	578.2	582.9	584.5	587.6
52.5°	534.1	532.5	530.9	523.0	521.5	519.9	521.5	523.0	529.3	534.1	535.7
55°	480.5	478.9	469.5	466.3	461.6	461.6	464.8	466.3	477.4	478.9	485.2
57.5°	431.7	426.9	415.9	414.3	414.3	414.3	409.6	415.9	419.1	426.9	426.9
60°	378.1	378.1	368.7	368.7	370.2	368.7	368.7	370.2	370.2	376.5	379.7
62.5°	335.6	334.0	334.0	330.8	329.3	330.8	329.3	329.3	330.8	335.6	340.3
65°	297.8	296.2	294.6	293.0	289.9	289.9	291.5	294.6	294.6	297.8	299.3
67.5°	261.5	261.5	258.4	258.4	256.8	255.2	256.8	255.2	261.5	261.5	263.1
70°	225.3	223.7	219.0	217.4	212.7	214.3	214.3	219.0	220.6	223.7	226.9
72.5°	181.2	181.2	178.0	174.9	176.4	173.3	173.3	174.9	174.9	179.6	181.2
75°	149.7	146.5	144.9	146.5	144.9	148.1	144.9	144.9	148.1	148.1	148.1
77.5°	122.9	122.9	121.3	121.3	122.9	121.3	122.9	122.9	122.9	121.3	122.9
80°	100.8	99.3	99.3	99.3	97.7	97.7	97.7	97.7	97.7	97.7	97.7
82.5°	75.6	75.6	74.0	75.6	75.6	74.0	75.6	74.0	74.0	75.6	75.6
85°	50.4	53.6	50.4	50.4	52.0	52.0	53.6	52.0	53.6	50.4	52.0
87.5°	26.8	28.4	28.4	26.8	26.8	28.4	28.4	28.4	29.9	26.8	28.4
90°	32.5	32.8	33.3	33.8	34.3	34.8	34.3	33.8	33.3	32.8	32.5
92.5°	38.3	38.4	38.7	39.0	39.2	39.5	39.2	39.0	38.7	38.4	38.3
95°	44.1	44.1	44.1	44.1	44.1	44.1	44.1	44.1	44.1	44.1	44.1
97.5°	46.4	46.5	46.8	47.1	47.3	47.6	47.3	47.1	46.8	46.5	46.4
100°	47.6	47.7	48.0	48.3	48.5	48.8	48.5	48.3	48.0	47.7	47.6
102.5°	47.6	47.9	48.4	48.9	49.4	49.9	49.4	48.9	48.4	47.9	47.6
105°	48.8	49.1	49.6	50.1	50.6	51.1	50.6	50.1	49.6	49.1	48.8
107.5°	272.8	255.9	222.1	188.3	154.5	120.7	154.5	188.3	222.1	255.9	272.8
110°	485.3	466.9	430.0	393.1	356.2	319.3	356.2	393.1	430.0	466.9	485.3

TEST NUMBER: P1012296

CATALOG NUMBER: S123RDIP-B1165D1195UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	607.2	606.9	606.4	605.9	605.4	604.9	605.4	605.9	606.4	606.9	607.2
115°	678.0	678.5	679.5	680.6	681.6	682.6	681.6	680.6	679.5	678.5	678.0
117.5°	744.2	744.3	744.6	744.8	745.1	745.3	745.1	744.8	744.6	744.3	744.2
120°	810.4	810.4	810.4	810.4	810.4	810.4	810.4	810.4	810.4	810.4	810.4
122.5°	873.0	873.1	873.4	873.7	873.9	874.2	873.9	873.7	873.4	873.1	873.0
125°	931.1	931.4	931.9	932.4	932.9	933.4	932.9	932.4	931.9	931.4	931.1
127.5°	993.8	993.5	993.0	992.5	992.0	991.5	992.0	992.5	993.0	993.5	993.8
130°	1049.5	1049.2	1048.7	1048.2	1047.7	1047.2	1047.7	1048.2	1048.7	1049.2	1049.5
132.5°	1101.8	1101.4	1100.6	1099.9	1099.1	1098.3	1099.1	1099.9	1100.6	1101.4	1101.8
135°	1154.0	1153.6	1152.8	1152.1	1151.3	1150.5	1151.3	1152.1	1152.8	1153.6	1154.0
137.5°	1202.8	1202.5	1202.0	1201.5	1200.9	1200.4	1200.9	1201.5	1202.0	1202.5	1202.8
140°	1246.9	1246.6	1246.1	1245.6	1245.0	1244.5	1245.0	1245.6	1246.1	1246.6	1246.9
142.5°	1288.7	1288.3	1287.5	1286.8	1286.0	1285.2	1286.0	1286.8	1287.5	1288.3	1288.7
145°	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0
147.5°	1363.0	1362.4	1361.1	1359.8	1358.5	1357.2	1358.5	1359.8	1361.1	1362.4	1363.0
150°	1395.5	1395.1	1394.3	1393.6	1392.8	1392.0	1392.8	1393.6	1394.3	1395.1	1395.5
152.5°	1425.7	1425.1	1423.8	1422.5	1421.2	1419.9	1421.2	1422.5	1423.8	1425.1	1425.7
155°	1452.4	1451.6	1450.1	1448.5	1447.0	1445.4	1447.0	1448.5	1450.1	1451.6	1452.4
157.5°	1476.7	1475.7	1473.6	1471.6	1469.5	1467.5	1469.5	1471.6	1473.6	1475.7	1476.7
160°	1496.5	1495.6	1493.8	1492.0	1490.2	1488.4	1490.2	1492.0	1493.8	1495.6	1496.5
162.5°	1515.1	1514.3	1512.8	1511.2	1509.7	1508.1	1509.7	1511.2	1512.8	1514.3	1515.1
165°	1531.3	1530.4	1528.6	1526.8	1525.0	1523.2	1525.0	1526.8	1528.6	1530.4	1531.3
167.5°	1544.1	1543.1	1541.0	1538.9	1536.9	1534.8	1536.9	1538.9	1541.0	1543.1	1544.1
170°	1554.5	1553.5	1551.4	1549.3	1547.3	1545.2	1547.3	1549.3	1551.4	1553.5	1554.5
172.5°	1561.5	1560.3	1558.0	1555.7	1553.3	1551.0	1553.3	1555.7	1558.0	1560.3	1561.5
175°	1566.1	1565.1	1563.0	1560.9	1558.9	1556.8	1558.9	1560.9	1563.0	1565.1	1566.1
177.5°	1569.6	1568.3	1565.7	1563.2	1560.6	1558.0	1560.6	1563.2	1565.7	1568.3	1569.6
180°	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7

TEST NUMBER: P1012296

CATALOG NUMBER: S123RDIP-B1165D1195UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1
2.5°	1740.9	1747.2	1740.9	1728.3	1740.9	1748.7	1756.6	1769.2	1775.5	1775.5	1785.0
5°	1641.6	1654.2	1649.5	1646.3	1658.9	1666.8	1679.4	1695.2	1712.5	1723.5	1736.1
7.5°	1553.4	1561.3	1569.1	1569.1	1581.7	1599.1	1618.0	1636.9	1658.9	1674.7	1684.2
10°	1476.2	1482.5	1487.2	1493.5	1512.4	1531.3	1556.5	1580.2	1599.1	1616.4	1632.2
12.5°	1402.1	1411.6	1422.6	1427.4	1441.5	1465.2	1488.8	1517.2	1547.1	1564.4	1580.2
15°	1331.3	1336.0	1348.6	1362.8	1375.4	1400.6	1430.5	1460.4	1485.6	1512.4	1526.6
17.5°	1258.8	1260.4	1293.4	1285.6	1326.5	1350.2	1365.9	1394.3	1435.2	1457.3	1479.3
20°	1187.9	1203.6	1217.8	1225.7	1247.8	1274.5	1320.2	1342.3	1375.4	1395.8	1414.7
22.5°	1132.7	1156.4	1156.4	1175.3	1186.3	1211.5	1244.6	1287.1	1323.4	1337.6	1364.3
25°	1083.9	1094.9	1113.8	1120.1	1140.6	1162.7	1184.7	1230.4	1269.8	1288.7	1307.6
27.5°	1020.9	1035.1	1060.3	1060.3	1087.1	1110.7	1137.5	1167.4	1206.8	1233.6	1254.1
30°	972.0	986.2	997.3	1014.6	1025.6	1047.7	1094.9	1117.0	1151.7	1175.3	1200.5
32.5°	926.4	937.4	946.8	965.7	978.4	1003.6	1028.8	1068.2	1098.1	1120.1	1146.9
35°	875.9	887.0	899.6	913.8	932.7	956.3	979.9	1013.0	1042.9	1063.4	1085.5
37.5°	828.7	836.6	855.5	864.9	880.7	902.7	932.7	967.3	994.1	1009.9	1031.9
40°	783.0	789.3	803.5	820.8	831.8	849.2	880.7	910.6	943.7	962.6	979.9
42.5°	734.2	742.0	754.6	772.0	789.3	808.2	825.5	860.2	890.1	905.9	924.8
45°	691.6	696.3	705.8	723.1	740.5	754.6	781.4	812.9	841.3	853.9	874.4
47.5°	641.2	645.9	660.1	668.0	686.9	705.8	732.6	764.1	789.3	801.9	820.8
50°	589.2	593.9	603.4	620.7	633.3	653.8	677.4	704.2	735.7	753.1	764.1
52.5°	538.8	548.3	556.1	570.3	586.1	606.5	628.6	653.8	680.6	697.9	710.5
55°	488.4	496.3	505.7	513.6	532.5	551.4	576.6	600.2	623.9	639.6	653.8
57.5°	431.7	442.7	452.2	467.9	482.1	497.8	526.2	545.1	573.5	584.5	597.1
60°	382.8	393.9	401.7	414.3	426.9	447.4	466.3	490.0	513.6	527.8	543.5
62.5°	341.9	346.6	351.3	363.9	376.5	395.4	414.3	438.0	463.2	471.1	483.7
65°	300.9	305.6	313.5	324.5	334.0	345.0	365.5	384.4	408.0	420.6	425.4
67.5°	266.3	271.0	272.6	280.4	288.3	300.9	311.9	330.8	352.9	360.8	370.2
70°	226.9	234.7	236.3	242.6	245.8	253.6	266.3	280.4	297.8	311.9	319.8
72.5°	181.2	192.2	195.4	204.8	209.5	217.4	226.9	237.9	248.9	255.2	261.5
75°	148.1	151.2	152.8	160.7	168.6	179.6	184.3	190.6	200.1	208.0	214.3
77.5°	122.9	124.5	126.0	126.0	127.6	133.9	143.4	151.2	157.5	160.7	165.4
80°	99.3	97.7	97.7	99.3	99.3	99.3	102.4	113.4	116.6	124.5	122.9
82.5°	77.2	74.0	75.6	74.0	74.0	74.0	74.0	75.6	75.6	80.3	83.5
85°	50.4	52.0	50.4	50.4	48.8	50.4	48.8	48.8	47.3	47.3	45.7
87.5°	26.8	28.4	26.8	26.8	25.2	26.8	25.2	25.2	23.6	23.6	20.5
90°	32.0	31.0	29.9	28.9	27.9	24.5	21.2	17.8	14.5	12.8	11.5
92.5°	37.4	35.6	33.8	32.0	30.2	27.9	25.5	23.2	20.9	19.7	20.5
95°	43.2	41.4	39.6	37.8	36.0	33.2	30.3	27.5	24.6	23.2	28.5
97.5°	45.4	43.3	41.3	39.2	37.2	50.4	63.5	76.7	89.8	96.4	100.0
100°	46.6	44.5	42.4	40.4	38.3	78.5	118.8	159.0	199.3	219.4	216.8
102.5°	51.9	60.4	68.9	77.4	85.9	130.8	175.7	220.6	265.5	287.9	286.2
105°	71.6	117.3	163.0	208.6	254.3	277.5	300.7	323.9	347.1	358.7	357.3
107.5°	292.7	332.4	372.1	411.9	451.6	447.7	443.9	440.0	436.1	434.2	433.0
110°	489.6	498.1	506.6	515.1	523.6	520.8	517.9	515.1	512.2	510.8	509.8

TEST NUMBER: P1012296

CATALOG NUMBER: S123RDIP-B1165D1195UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	606.0	603.7	601.4	599.0	596.7	593.9	591.1	588.2	585.4	584.0	583.1
115°	676.7	674.1	671.6	669.0	666.4	664.1	661.7	659.4	657.1	655.9	655.1
117.5°	743.2	741.1	739.0	737.0	734.9	733.6	732.3	731.0	729.7	729.1	728.2
120°	809.4	807.3	805.2	803.2	801.1	800.3	799.5	798.8	798.0	797.6	796.4
122.5°	872.4	871.1	869.8	868.5	867.2	866.2	865.2	864.1	863.1	862.6	861.7
125°	930.8	930.3	929.8	929.3	928.8	927.8	926.7	925.7	924.6	924.1	923.1
127.5°	993.4	992.6	991.9	991.1	990.3	989.0	987.7	986.4	985.1	984.5	983.5
130°	1049.0	1048.0	1046.9	1045.9	1044.9	1043.9	1042.8	1041.8	1040.7	1040.2	1039.2
132.5°	1101.3	1100.2	1099.2	1098.1	1097.1	1096.3	1095.5	1094.8	1094.0	1093.6	1092.6
135°	1153.6	1152.8	1152.1	1151.3	1150.5	1149.5	1148.5	1147.4	1146.4	1145.9	1145.1
137.5°	1202.2	1200.9	1199.6	1198.3	1197.0	1196.5	1195.9	1195.4	1194.9	1194.6	1193.6
140°	1246.4	1245.3	1244.3	1243.2	1242.2	1241.4	1240.6	1239.9	1239.1	1238.7	1237.9
142.5°	1288.3	1287.5	1286.8	1286.0	1285.2	1284.4	1283.6	1282.9	1282.1	1281.7	1280.9
145°	1326.7	1326.2	1325.7	1325.2	1324.7	1324.2	1323.6	1323.1	1322.6	1322.3	1321.4
147.5°	1362.7	1362.2	1361.7	1361.1	1360.6	1360.1	1359.6	1359.1	1358.6	1358.3	1357.7
150°	1395.2	1394.7	1394.2	1393.7	1393.2	1392.7	1392.1	1391.6	1391.1	1390.8	1390.4
152.5°	1425.2	1424.1	1423.1	1422.0	1421.0	1420.8	1420.5	1420.3	1420.0	1419.9	1419.8
155°	1451.8	1450.5	1449.2	1447.9	1446.6	1446.3	1446.1	1445.8	1445.5	1445.4	1445.7
157.5°	1475.9	1474.4	1472.9	1471.3	1469.8	1470.0	1470.3	1470.5	1470.8	1470.9	1470.9
160°	1495.7	1494.2	1492.6	1491.1	1489.5	1489.8	1490.0	1490.3	1490.6	1490.7	1490.8
162.5°	1514.2	1512.4	1510.5	1508.7	1506.9	1507.2	1507.4	1507.7	1508.0	1508.1	1508.5
165°	1530.3	1528.2	1526.1	1524.1	1522.0	1522.3	1522.5	1522.8	1523.1	1523.2	1523.6
167.5°	1543.1	1541.0	1538.9	1536.9	1534.8	1534.8	1534.8	1534.8	1534.8	1534.8	1535.3
170°	1553.5	1551.4	1549.3	1547.3	1545.2	1545.2	1545.2	1545.2	1545.2	1545.2	1545.7
172.5°	1560.5	1558.4	1556.3	1554.3	1552.2	1551.9	1551.7	1551.4	1551.1	1551.0	1551.6
175°	1565.2	1563.4	1561.6	1559.8	1558.0	1557.7	1557.5	1557.2	1556.9	1556.8	1557.5
177.5°	1568.6	1566.5	1564.4	1562.4	1560.3	1560.1	1559.8	1559.6	1559.3	1559.2	1559.8
180°	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7	1562.7

TEST NUMBER: P1012296

CATALOG NUMBER: S123RDIP-B1165D1195UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1840.1	1840.1	1840.1	1840.1
2.5°	1792.9	1803.9	1825.9	1844.8
5°	1755.0	1772.4	1805.5	1838.5
7.5°	1709.4	1736.1	1778.7	1824.4
10°	1665.2	1699.9	1751.9	1805.5
12.5°	1621.1	1657.4	1712.5	1781.8
15°	1569.1	1607.0	1673.1	1756.6
17.5°	1523.5	1573.9	1633.7	1717.2
20°	1474.6	1512.4	1589.6	1677.8
22.5°	1413.2	1476.2	1548.7	1641.6
25°	1364.3	1419.5	1491.9	1597.5
27.5°	1304.5	1369.1	1457.3	1550.2
30°	1255.6	1309.2	1391.1	1503.0
32.5°	1198.9	1261.9	1347.0	1457.3
35°	1148.5	1202.1	1282.4	1394.3
37.5°	1088.6	1146.9	1236.7	1336.0
40°	1036.6	1093.4	1178.4	1271.4
42.5°	973.6	1033.5	1118.6	1197.3
45°	923.2	978.4	1046.1	1118.6
47.5°	861.8	920.1	986.2	1036.6
50°	806.6	860.2	912.2	954.7
52.5°	746.8	795.6	842.9	874.4
55°	691.6	729.4	767.2	789.3
57.5°	627.0	663.3	694.8	707.4
60°	570.3	600.2	620.7	634.9
62.5°	510.4	532.5	548.3	556.1
65°	452.2	467.9	475.8	483.7
67.5°	392.3	406.5	411.2	420.6
70°	329.3	345.0	348.2	352.9
72.5°	282.0	282.0	288.3	294.6
75°	225.3	228.4	231.6	231.6
77.5°	176.4	176.4	179.6	181.2
80°	129.2	130.8	130.8	129.2
82.5°	88.2	91.4	88.2	86.6
85°	48.8	55.1	52.0	52.0
87.5°	20.5	20.5	23.6	20.5
90°	8.9	6.4	3.8	1.2
92.5°	22.0	23.6	25.1	26.7
95°	39.1	49.6	60.2	70.8
97.5°	107.2	114.5	121.7	128.9
100°	211.7	206.5	201.4	196.2
102.5°	282.9	279.5	276.2	272.8
105°	354.5	351.6	348.8	346.0
107.5°	430.7	428.4	426.1	423.8
110°	507.7	505.6	503.6	501.5

TEST NUMBER: P1012296

CATALOG NUMBER: S123RDIP-B1165D1195UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	581.3	579.4	577.6	575.8
115°	653.6	652.1	650.5	649.0
117.5°	726.4	724.6	722.8	721.0
120°	794.1	791.8	789.4	787.1
122.5°	859.9	858.1	856.3	854.5
125°	921.0	918.9	916.9	914.8
127.5°	981.4	979.3	977.3	975.2
130°	1037.1	1035.0	1033.0	1030.9
132.5°	1090.5	1088.4	1086.4	1084.3
135°	1143.6	1142.0	1140.5	1138.9
137.5°	1191.5	1189.4	1187.4	1185.3
140°	1236.4	1234.9	1233.3	1231.8
142.5°	1279.4	1277.8	1276.3	1274.7
145°	1319.6	1317.8	1316.0	1314.2
147.5°	1356.4	1355.1	1353.8	1352.5
150°	1389.6	1388.9	1388.1	1387.3
152.5°	1419.5	1419.2	1419.0	1418.7
155°	1446.2	1446.7	1447.2	1447.7
157.5°	1470.9	1470.9	1470.9	1470.9
160°	1491.1	1491.3	1491.6	1491.8
162.5°	1509.3	1510.0	1510.8	1511.6
165°	1524.4	1525.1	1525.9	1526.7
167.5°	1536.3	1537.4	1538.4	1539.4
170°	1546.8	1547.8	1548.9	1549.9
172.5°	1552.9	1554.2	1555.5	1556.8
175°	1558.8	1560.1	1561.4	1562.7
177.5°	1561.1	1562.4	1563.7	1565.0
180°	1562.7	1562.7	1562.7	1562.7

(END OF REPORT)