

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012303

Luminaire Tested: S123RDIP-B1165D1195UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012303
REPORT IS A COMBINATION OF REPORTS P992982 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1165D1195UB35-4F0-XX-W2A-A1
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8718.0 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012303

CATALOG NUMBER: S123RDIP-B1165D1195UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1012303

CATALOG NUMBER: S123RDIP-B1165D1195UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	47	45	44
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38
4	76	66	58	53	71	62	55	50	53	48	44	46	42	39	38	36	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29
6	65	53	45	40	60	50	43	38	43	38	34	37	33	30	32	29	26
7	60	48	40	35	56	45	38	33	40	34	30	34	30	27	29	26	23
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19894	19894	19894	19894
5°	19909	22912	19960	16998
10°	19732	27657	19819	14847
15°	19530	31390	19530	13091
20°	19129	33859	19237	11613
25°	18837	32168	18799	10596
30°	18495	22288	18457	9602
35°	18085	14310	18002	8853
40°	17573	10105	17487	8107
45°	16684	8086	16662	7381
50°	15593	6764	15541	6532
55°	14363	5575	14249	5537
60°	13159	4609	13026	4709
65°	11744	3688	11818	3991
70°	10437	2562	10716	3227
75°	8848	1900	9209	2481
80°	7047	1261	7644	1860
85°	5014	596	5475	1157

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 26558 cd/sqm

TEST NUMBER: P1012303

CATALOG NUMBER: S123RDIP-B1165D1195UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.5	2.1
10°-20°	568.1	6.5
20°-30°	894.8	10.3
30°-40°	930.5	10.7
40°-50°	796.0	9.1
50°-60°	606.9	7.0
60°-70°	388.8	4.5
70°-80°	186.3	2.1
80°-90°	52.1	0.6
90°-100°	95.6	1.1
100°-110°	289.2	3.3
110°-120°	492.4	5.6
120°-130°	647.7	7.4
130°-140°	728.0	8.4
140°-150°	715.8	8.2
150°-160°	602.6	6.9
160°-170°	401.2	4.6
170°-180°	140.5	1.6
0°-30°	1644.5	18.9
0°-40°	2574.9	29.5
0°-60°	3977.9	45.6
0°-90°	4605.1	52.8
90°-120°	877.1	10.1
90°-150°	2968.6	34.1
90°-180°	4113.0	47.2
0°-180°	8718.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1848	1848	1848	1848	1848	
5°	1847	2195	1851	1628	1847	175
15°	1764	3119	1764	1301	1764	496
25°	1604	3214	1601	1059	1604	739
35°	1400	1394	1394	862	1400	876
45°	1123	744	1122	679	1123	865
55°	793	467	786	464	793	710
65°	486	269	489	291	486	485
75°	233	114	242	149	233	251
85°	52	27	57	52	52	58
90°	1	35	1	35	1	8
95°	69	91	69	91	69	76
105°	262	278	262	278	262	281
115°	496	497	496	497	496	490
125°	725	717	725	717	725	647
135°	941	940	941	940	941	725
145°	1142	1142	1142	1142	1142	713
155°	1307	1305	1307	1305	1307	602
165°	1424	1419	1424	1419	1424	402
175°	1481	1475	1481	1475	1481	141
180°	1484	1484	1484	1484	1484	

TEST NUMBER: P1012303

CATALOG NUMBER: S123RDIP-B1165D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1852.9	1865.6	1875.1	1881.4	1897.2	1906.7	1914.6	1928.9	1928.9	1932.0	1938.3
5°	1846.6	1873.5	1892.5	1917.8	1951.0	1966.8	1989.0	2008.0	2034.9	2049.1	2063.3
7.5°	1832.3	1870.3	1909.9	1947.8	1996.9	2028.5	2050.7	2099.7	2134.6	2177.3	2210.5
10°	1813.3	1865.6	1916.2	1974.7	2041.2	2088.7	2121.9	2186.8	2253.2	2313.4	2364.0
12.5°	1789.6	1852.9	1925.7	1996.9	2090.2	2137.7	2191.5	2272.2	2367.2	2443.1	2511.1
15°	1764.3	1837.1	1919.4	2006.4	2123.5	2189.9	2267.5	2365.6	2471.6	2580.8	2674.1
17.5°	1724.7	1816.5	1908.3	2034.9	2172.5	2212.1	2278.5	2413.0	2544.4	2642.5	2756.4
20°	1685.2	1788.0	1903.5	2017.5	2166.2	2258.0	2319.7	2462.1	2602.9	2721.6	2830.8
22.5°	1648.8	1756.4	1876.6	2020.6	2159.9	2251.6	2329.2	2477.9	2640.9	2773.8	2908.3
25°	1604.5	1721.6	1854.5	1990.6	2159.9	2229.5	2314.9	2487.4	2659.9	2813.4	2979.5
27.5°	1557.0	1675.7	1807.0	1946.3	2101.3	2204.2	2288.0	2473.2	2683.6	2848.2	3019.1
30°	1509.5	1631.4	1758.0	1883.0	2057.0	2155.1	2251.6	2455.8	2696.3	2884.6	3015.9
32.5°	1463.6	1566.5	1691.5	1813.3	1985.8	2093.4	2202.6	2438.4	2701.0	2859.3	2922.5
35°	1400.4	1508.0	1609.2	1739.0	1913.0	2019.0	2147.2	2436.8	2680.5	2778.6	2746.9
37.5°	1341.8	1432.0	1528.5	1644.0	1822.8	1960.5	2093.4	2395.6	2612.4	2618.7	2439.9
40°	1276.9	1351.3	1432.0	1553.8	1746.9	1883.0	2027.0	2332.3	2489.0	2395.6	2080.8
42.5°	1202.6	1269.0	1332.3	1451.0	1661.4	1813.3	1968.4	2253.2	2310.2	2095.0	1767.5
45°	1123.4	1177.2	1235.8	1360.8	1571.2	1721.6	1876.6	2131.4	2072.8	1769.0	1457.3
47.5°	1041.2	1087.1	1144.0	1257.9	1474.7	1628.2	1775.4	1957.3	1808.6	1482.6	1221.6
50°	958.9	995.3	1050.7	1167.8	1376.6	1515.9	1651.9	1770.6	1561.8	1272.2	1009.5
52.5°	878.2	906.7	963.6	1063.3	1265.9	1398.8	1496.9	1542.8	1330.7	1050.7	876.6
55°	792.7	824.4	862.4	963.6	1164.6	1262.7	1327.6	1326.0	1107.6	890.8	724.7
57.5°	710.5	738.9	772.2	873.4	1036.4	1102.9	1158.3	1131.4	924.1	729.5	621.9
60°	637.7	653.5	689.9	775.3	898.8	955.7	987.4	941.5	754.8	615.5	514.3
62.5°	558.6	574.4	604.4	685.1	761.1	791.2	818.1	759.5	623.4	501.6	439.9
65°	485.8	506.3	525.3	590.2	631.3	667.7	664.6	615.5	487.4	408.2	357.6
67.5°	422.5	430.4	446.2	485.8	504.8	531.7	533.2	477.9	392.4	332.3	302.2
70°	354.4	362.4	373.4	392.4	405.1	411.4	408.2	359.2	295.9	259.5	232.6
72.5°	295.9	294.3	302.2	302.2	314.9	313.3	303.8	265.8	224.7	194.6	178.8
75°	232.6	234.2	235.8	232.6	227.9	221.5	213.6	185.1	158.2	144.0	129.8
77.5°	182.0	178.8	180.4	169.3	163.0	156.6	145.6	131.3	109.2	106.0	99.7
80°	129.8	128.2	126.6	121.8	107.6	101.3	93.4	85.4	80.7	77.5	76.0
82.5°	87.0	87.0	83.9	74.4	66.5	61.7	60.1	57.0	52.2	52.2	50.6
85°	52.2	50.6	47.5	38.0	33.2	33.2	33.2	33.2	30.1	30.1	28.5
87.5°	20.6	19.0	14.2	14.2	12.7	12.7	12.7	11.1	11.1	9.5	9.5
90°	1.2	3.8	6.4	8.9	11.5	12.8	14.5	17.9	21.2	24.6	28.0
92.5°	35.0	36.6	38.1	39.7	41.2	42.0	42.8	44.3	45.9	47.4	49.0
95°	68.8	70.6	72.4	74.3	76.1	77.0	78.0	80.1	82.2	84.2	86.3
97.5°	113.1	114.4	115.7	117.0	118.3	118.9	119.7	121.2	122.8	124.3	125.9
100°	158.6	160.2	161.7	163.3	164.8	165.6	166.2	167.5	168.8	170.1	171.4
102.5°	211.1	211.9	212.6	213.4	214.1	214.5	215.4	217.2	219.1	220.9	222.7
105°	262.4	262.9	263.4	263.9	264.4	264.7	265.9	268.2	270.5	272.9	275.2
107.5°	323.0	323.3	323.5	323.8	324.1	324.2	324.7	325.7	326.8	327.8	328.8
110°	379.0	379.5	380.0	380.5	381.0	381.3	381.6	382.1	382.6	383.1	383.6

TEST NUMBER: P1012303

CATALOG NUMBER: S123RDIP-B1165D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	437.3	437.5	437.8	438.0	438.3	438.4	438.4	438.4	438.4	438.4	438.4
115°	495.6	496.4	497.2	497.9	498.7	499.1	498.8	498.3	497.8	497.2	496.7
117.5°	555.0	555.3	555.5	555.8	556.1	556.2	555.9	555.4	554.9	554.4	553.9
120°	609.8	611.4	612.9	614.5	616.0	616.8	616.2	614.9	613.6	612.3	611.0
122.5°	667.0	668.0	669.0	670.1	671.1	671.6	671.3	670.8	670.3	669.8	669.3
125°	725.3	726.1	726.9	727.6	728.4	728.8	728.5	728.0	727.5	726.9	726.4
127.5°	778.9	780.5	782.0	783.6	785.1	785.9	785.6	785.1	784.6	784.1	783.6
130°	832.5	834.6	836.7	838.8	840.9	841.9	841.5	840.7	840.0	839.2	838.4
132.5°	886.2	888.3	890.3	892.4	894.5	895.5	895.2	894.7	894.2	893.7	893.2
135°	941.0	942.6	944.1	945.7	947.2	948.0	947.9	947.6	947.3	947.1	946.8
137.5°	991.1	992.4	993.7	995.0	996.3	997.0	997.4	998.1	998.9	999.6	1000.4
140°	1043.6	1044.9	1046.2	1047.5	1048.8	1049.4	1049.5	1049.8	1050.1	1050.3	1050.6
142.5°	1091.4	1092.7	1094.0	1095.3	1096.6	1097.2	1097.5	1098.0	1098.5	1099.1	1099.6
145°	1141.5	1142.0	1142.6	1143.1	1143.6	1143.9	1144.3	1145.1	1145.8	1146.6	1147.4
147.5°	1184.7	1185.7	1186.7	1187.8	1188.8	1189.3	1189.7	1190.5	1191.2	1192.0	1192.8
150°	1230.2	1230.7	1231.2	1231.7	1232.2	1232.5	1232.8	1233.3	1233.8	1234.3	1234.8
152.5°	1267.5	1268.3	1269.1	1269.8	1270.6	1271.0	1271.1	1271.4	1271.6	1271.9	1272.1
155°	1307.1	1307.1	1307.1	1307.1	1307.1	1307.1	1307.2	1307.5	1307.8	1308.0	1308.3
157.5°	1340.9	1340.7	1340.4	1340.2	1339.9	1339.8	1339.9	1340.2	1340.4	1340.7	1340.9
160°	1372.4	1371.9	1371.4	1370.9	1370.4	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1
162.5°	1400.4	1399.6	1398.8	1398.1	1397.3	1396.9	1397.0	1397.3	1397.6	1397.8	1398.1
165°	1423.7	1422.9	1422.1	1421.4	1420.6	1420.2	1420.2	1420.2	1420.2	1420.2	1420.2
167.5°	1443.5	1442.5	1441.5	1440.4	1439.4	1438.9	1439.0	1439.3	1439.5	1439.8	1440.0
170°	1459.9	1458.9	1457.8	1456.8	1455.7	1455.2	1455.2	1455.2	1455.2	1455.2	1455.2
172.5°	1472.7	1471.7	1470.6	1469.6	1468.5	1468.0	1468.0	1468.0	1468.0	1468.0	1468.0
175°	1480.9	1479.9	1478.8	1477.8	1476.7	1476.2	1476.2	1476.2	1476.2	1476.2	1476.2
177.5°	1485.5	1484.5	1483.5	1482.4	1481.4	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9
180°	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3

TEST NUMBER: P1012303

CATALOG NUMBER: S123RDIP-B1165D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1951.0	1951.0	1965.2	1979.5	1971.6	1976.3	1993.7	1987.4	2000.1	1998.5	2003.2
5°	2098.2	2115.6	2129.8	2159.9	2164.6	2159.9	2189.9	2197.8	2212.1	2194.7	2202.6
7.5°	2264.3	2300.7	2335.5	2379.8	2394.1	2397.2	2413.0	2435.2	2454.2	2419.4	2436.8
10°	2425.7	2481.1	2552.3	2591.8	2626.7	2639.3	2652.0	2666.2	2688.4	2708.9	2693.1
12.5°	2599.8	2680.5	2748.5	2819.7	2862.4	2857.7	2894.1	2903.6	2921.0	2925.7	2932.0
15°	2742.2	2856.1	2898.8	3004.8	3014.3	3046.0	3087.1	3123.5	3128.3	3118.8	3118.8
17.5°	2878.2	2976.3	3052.3	3137.7	3155.1	3182.0	3234.3	3251.7	3258.0	3256.4	3256.4
20°	2989.0	3053.9	3182.0	3253.3	3281.7	3316.5	3352.9	3375.1	3379.8	3386.2	3376.7
22.5°	3061.8	3159.9	3264.3	3322.9	3346.6	3359.3	3383.0	3389.3	3381.4	3383.0	3384.6
25°	3118.8	3215.3	3278.6	3294.4	3292.8	3277.0	3259.6	3229.5	3226.4	3213.7	3188.4
27.5°	3134.6	3171.0	3163.1	3098.2	3033.3	3027.0	2922.5	2865.6	2800.7	2810.2	2773.8
30°	3049.1	3001.7	2889.3	2724.8	2656.7	2546.0	2428.9	2307.0	2259.6	2207.3	2303.9
32.5°	2840.3	2671.0	2471.6	2258.0	2144.0	2045.9	1920.9	1832.3	1781.7	1739.0	1821.3
35°	2525.4	2261.1	1996.9	1794.4	1701.0	1612.4	1495.3	1451.0	1387.7	1394.0	1401.9
37.5°	2120.3	1829.2	1629.8	1430.4	1368.7	1332.3	1246.9	1178.8	1156.7	1150.3	1150.3
40°	1740.6	1501.6	1324.4	1167.8	1120.3	1090.2	1022.2	990.5	966.8	960.5	968.4
42.5°	1439.9	1235.8	1098.1	993.7	960.5	922.5	894.0	854.5	849.7	838.6	852.9
45°	1208.9	1031.7	928.8	852.9	824.4	810.1	778.5	754.8	745.3	743.7	754.8
47.5°	1025.3	887.7	797.5	750.0	727.9	713.6	686.7	677.2	667.7	670.9	666.2
50°	860.8	757.9	699.4	656.7	642.4	628.2	610.8	601.3	596.5	596.5	595.0
52.5°	738.9	653.5	615.5	576.0	569.6	561.7	542.7	536.4	528.5	526.9	533.2
55°	632.9	574.4	536.4	512.7	506.3	490.5	482.6	474.7	469.9	466.8	468.4
57.5°	541.2	496.8	471.5	451.0	439.9	433.6	419.3	417.7	414.6	414.6	413.0
60°	465.2	433.6	403.5	390.8	382.9	375.0	373.4	363.9	359.2	362.4	360.8
62.5°	394.0	368.7	351.3	337.0	332.3	326.0	321.2	318.0	313.3	314.9	314.9
65°	329.1	308.6	295.9	283.2	281.7	275.3	273.7	270.6	270.6	269.0	272.2
67.5°	270.6	256.3	245.3	237.3	232.6	234.2	227.9	223.1	223.1	221.5	226.3
70°	215.2	207.3	196.2	186.7	180.4	180.4	172.5	170.9	170.9	170.9	169.3
72.5°	166.1	151.9	147.2	144.0	144.0	144.0	140.8	140.8	139.2	140.8	139.2
75°	123.4	121.8	118.7	117.1	117.1	115.5	113.9	113.9	113.9	113.9	113.9
77.5°	96.5	96.5	93.4	91.8	91.8	91.8	90.2	90.2	88.6	88.6	88.6
80°	71.2	71.2	68.0	68.0	68.0	66.5	66.5	66.5	68.0	66.5	66.5
82.5°	49.1	49.1	47.5	49.1	47.5	45.9	45.9	45.9	44.3	45.9	45.9
85°	28.5	28.5	26.9	25.3	26.9	26.9	25.3	26.9	25.3	26.9	25.3
87.5°	11.1	9.5	9.5	9.5	7.9	9.5	7.9	7.9	9.5	7.9	9.5
90°	29.0	30.0	31.1	32.1	32.6	32.9	33.4	33.9	34.5	35.0	34.5
92.5°	49.8	50.6	51.3	52.1	52.5	52.2	51.7	51.2	50.6	50.1	50.6
95°	87.3	88.3	89.4	90.4	90.9	90.9	90.9	90.9	90.9	90.9	90.9
97.5°	127.2	128.5	129.8	131.1	131.8	131.7	131.4	131.1	130.9	130.6	130.9
100°	172.2	173.0	173.7	174.5	174.9	175.2	175.7	176.2	176.7	177.2	176.7
102.5°	223.5	224.3	225.0	225.8	226.2	226.1	225.8	225.5	225.3	225.0	225.3
105°	275.2	275.2	275.2	275.2	275.2	275.5	276.0	276.5	277.0	277.5	277.0
107.5°	329.6	330.4	331.1	331.9	332.3	332.2	331.9	331.7	331.4	331.2	331.4
110°	384.6	385.7	386.7	387.8	388.3	388.0	387.5	387.0	386.5	386.0	386.5

TEST NUMBER: P1012303

CATALOG NUMBER: S123RDIP-B1165D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	439.7	441.0	442.3	443.6	444.3	444.3	444.3	444.3	444.3	444.3	444.3
115°	497.0	497.2	497.5	497.8	497.9	497.8	497.5	497.2	497.0	496.7	497.0
117.5°	553.9	553.9	553.9	553.9	553.9	553.5	552.7	552.0	551.2	550.4	551.2
120°	610.7	610.5	610.2	609.9	609.8	609.5	609.0	608.5	608.0	607.5	608.0
122.5°	668.5	667.7	667.0	666.2	665.8	665.4	664.6	663.9	663.1	662.3	663.1
125°	725.4	724.4	723.3	722.3	721.8	721.3	720.2	719.2	718.1	717.1	718.1
127.5°	782.0	780.5	778.9	777.4	776.6	776.1	775.0	774.0	772.9	771.9	772.9
130°	837.4	836.3	835.3	834.2	833.7	832.8	831.0	829.1	827.3	825.5	827.3
132.5°	891.9	890.6	889.3	888.0	887.3	886.7	885.4	884.1	882.8	881.5	882.8
135°	945.8	944.7	943.7	942.6	942.1	941.8	941.3	940.8	940.3	939.8	940.3
137.5°	999.1	997.8	996.5	995.2	994.6	994.2	993.4	992.7	991.9	991.1	991.9
140°	1050.3	1050.1	1049.8	1049.5	1049.4	1048.5	1046.7	1044.9	1043.1	1041.3	1043.1
142.5°	1099.3	1099.1	1098.8	1098.5	1098.4	1097.8	1096.5	1095.2	1093.9	1092.6	1093.9
145°	1147.1	1146.9	1146.6	1146.3	1146.2	1145.7	1144.6	1143.6	1142.5	1141.5	1142.5
147.5°	1192.8	1192.8	1192.8	1192.8	1192.8	1192.0	1190.5	1188.9	1187.4	1185.8	1187.4
150°	1234.8	1234.8	1234.8	1234.8	1234.8	1234.0	1232.5	1230.9	1229.4	1227.8	1229.4
152.5°	1272.6	1273.2	1273.7	1274.2	1274.5	1273.8	1272.5	1271.2	1269.9	1268.6	1269.9
155°	1309.3	1310.3	1311.4	1312.4	1312.9	1312.0	1310.2	1308.4	1306.6	1304.8	1306.6
157.5°	1341.9	1343.0	1344.0	1345.1	1345.6	1344.8	1343.3	1341.7	1340.2	1338.6	1340.2
160°	1371.4	1372.7	1374.0	1375.3	1375.9	1375.4	1374.3	1373.3	1372.2	1371.2	1372.2
162.5°	1399.4	1400.7	1402.0	1403.3	1403.9	1403.0	1401.2	1399.3	1397.5	1395.7	1397.5
165°	1421.8	1423.3	1424.9	1426.4	1427.2	1426.3	1424.5	1422.7	1420.9	1419.1	1420.9
167.5°	1441.6	1443.1	1444.7	1446.2	1447.0	1446.2	1444.7	1443.1	1441.6	1440.0	1441.6
170°	1457.0	1458.8	1460.7	1462.5	1463.4	1462.5	1460.7	1458.8	1457.0	1455.2	1457.0
172.5°	1469.6	1471.1	1472.7	1474.2	1475.0	1474.1	1472.3	1470.5	1468.7	1466.9	1468.7
175°	1477.8	1479.3	1480.9	1482.4	1483.2	1482.3	1480.5	1478.6	1476.8	1475.0	1476.8
177.5°	1482.4	1484.0	1485.5	1487.0	1487.8	1486.9	1485.1	1483.3	1481.5	1479.7	1481.5
180°	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3

TEST NUMBER: P1012303

CATALOG NUMBER: S123RDIP-B1165D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1995.3	1985.8	1979.5	1974.7	1970.0	1984.2	1965.2	1944.7	1930.4	1920.9	1917.8
5°	2204.2	2183.6	2166.2	2152.0	2155.1	2155.1	2121.9	2085.5	2053.9	2036.4	2017.5
7.5°	2446.3	2424.1	2389.3	2381.4	2375.1	2335.5	2302.3	2235.8	2196.3	2156.7	2121.9
10°	2686.8	2658.3	2625.1	2614.0	2598.2	2549.1	2498.5	2413.0	2364.0	2291.2	2245.3
12.5°	2911.5	2876.7	2843.4	2835.5	2811.8	2769.1	2682.0	2593.4	2509.6	2432.0	2351.3
15°	3099.8	3090.3	3039.6	3008.0	2955.8	2897.2	2878.2	2758.0	2652.0	2571.3	2425.7
17.5°	3258.0	3213.7	3166.2	3145.7	3125.1	3057.0	2989.0	2865.6	2751.7	2633.0	2539.6
20°	3384.6	3335.5	3302.3	3272.2	3262.7	3185.2	3077.6	2968.4	2843.4	2710.5	2588.7
22.5°	3390.9	3384.6	3362.4	3345.0	3326.0	3275.4	3190.0	3053.9	2921.0	2775.4	2615.6
25°	3259.6	3250.1	3313.4	3297.6	3310.2	3291.2	3245.3	3131.4	2976.3	2805.5	2644.1
27.5°	2864.0	2960.5	3060.2	3095.0	3118.8	3186.8	3208.9	3145.7	3020.7	2838.7	2658.3
30°	2326.0	2454.2	2615.6	2702.6	2769.1	2895.6	3060.2	3080.8	3022.2	2876.7	2655.1
32.5°	1826.0	1943.1	2072.8	2175.7	2264.3	2523.8	2745.3	2905.1	2933.6	2857.7	2663.0
35°	1471.6	1522.2	1645.6	1743.7	1864.0	2085.5	2346.6	2604.5	2778.6	2788.1	2639.3
37.5°	1213.6	1240.5	1348.1	1403.5	1474.7	1669.3	1913.0	2250.1	2520.6	2648.8	2572.9
40°	1004.8	1066.5	1128.2	1159.8	1210.5	1345.0	1579.2	1843.4	2178.9	2416.2	2470.0
42.5°	871.9	898.8	938.3	982.6	1014.3	1131.4	1288.0	1530.1	1832.3	2163.0	2311.8
45°	769.0	778.5	819.6	848.1	881.4	963.6	1074.4	1276.9	1542.8	1868.7	2121.9
47.5°	683.6	702.6	724.7	742.1	764.3	827.6	922.5	1069.6	1303.8	1595.0	1867.1
50°	607.6	618.7	647.2	655.1	670.9	715.2	788.0	900.3	1093.4	1326.0	1607.6
52.5°	536.4	557.0	568.1	579.1	593.4	629.8	677.2	769.0	914.6	1132.9	1371.9
55°	481.0	487.4	503.2	512.7	523.7	549.1	590.2	658.2	772.2	946.2	1172.5
57.5°	427.2	427.2	443.1	451.0	462.0	481.0	517.4	569.6	651.9	781.7	989.0
60°	370.3	371.8	384.5	394.0	397.2	416.2	446.2	487.4	550.6	645.6	814.9
62.5°	319.6	327.5	333.9	337.0	348.1	359.2	384.5	413.0	457.3	541.2	661.4
65°	276.9	278.5	283.2	286.4	291.1	303.8	322.8	341.8	379.8	441.5	539.6
67.5°	227.9	234.2	240.5	240.5	245.3	251.6	270.6	286.4	314.9	351.3	417.7
70°	170.9	174.1	183.5	188.3	194.6	205.7	215.2	224.7	246.8	273.7	324.4
72.5°	142.4	142.4	145.6	147.2	147.2	155.1	169.3	178.8	189.9	208.9	243.7
75°	113.9	113.9	118.7	117.1	120.3	123.4	125.0	131.3	137.7	151.9	172.5
77.5°	90.2	91.8	91.8	93.4	93.4	94.9	96.5	99.7	102.9	110.8	120.3
80°	66.5	68.0	68.0	69.6	69.6	71.2	72.8	74.4	77.5	80.7	85.4
82.5°	45.9	47.5	47.5	49.1	47.5	49.1	50.6	50.6	52.2	55.4	57.0
85°	26.9	26.9	28.5	26.9	26.9	26.9	28.5	28.5	30.1	34.8	34.8
87.5°	7.9	9.5	7.9	9.5	9.5	9.5	9.5	11.1	11.1	12.7	14.2
90°	33.9	33.4	32.9	32.6	32.1	31.1	30.0	29.0	28.0	24.6	21.2
92.5°	51.2	51.7	52.2	52.5	52.1	51.3	50.6	49.8	49.0	47.4	45.9
95°	90.9	90.9	90.9	90.9	90.4	89.4	88.3	87.3	86.3	84.2	82.2
97.5°	131.1	131.4	131.7	131.8	131.1	129.8	128.5	127.2	125.9	124.3	122.8
100°	176.2	175.7	175.2	174.9	174.5	173.7	173.0	172.2	171.4	170.1	168.8
102.5°	225.5	225.8	226.1	226.2	225.8	225.0	224.3	223.5	222.7	220.9	219.1
105°	276.5	276.0	275.5	275.2	275.2	275.2	275.2	275.2	275.2	272.9	270.5
107.5°	331.7	331.9	332.2	332.3	331.9	331.1	330.4	329.6	328.8	327.8	326.8
110°	387.0	387.5	388.0	388.3	387.8	386.7	385.7	384.6	383.6	383.1	382.6

TEST NUMBER: P1012303

CATALOG NUMBER: S123RDIP-B1165D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	444.3	444.3	444.3	444.3	443.6	442.3	441.0	439.7	438.4	438.4	438.4
115°	497.2	497.5	497.8	497.9	497.8	497.5	497.2	497.0	496.7	497.2	497.8
117.5°	552.0	552.7	553.5	553.9	553.9	553.9	553.9	553.9	553.9	554.4	554.9
120°	608.5	609.0	609.5	609.8	609.9	610.2	610.5	610.7	611.0	612.3	613.6
122.5°	663.9	664.6	665.4	665.8	666.2	667.0	667.7	668.5	669.3	669.8	670.3
125°	719.2	720.2	721.3	721.8	722.3	723.3	724.4	725.4	726.4	726.9	727.5
127.5°	774.0	775.0	776.1	776.6	777.4	778.9	780.5	782.0	783.6	784.1	784.6
130°	829.1	831.0	832.8	833.7	834.2	835.3	836.3	837.4	838.4	839.2	840.0
132.5°	884.1	885.4	886.7	887.3	888.0	889.3	890.6	891.9	893.2	893.7	894.2
135°	940.8	941.3	941.8	942.1	942.6	943.7	944.7	945.8	946.8	947.1	947.3
137.5°	992.7	993.4	994.2	994.6	995.2	996.5	997.8	999.1	1000.4	999.6	998.9
140°	1044.9	1046.7	1048.5	1049.4	1049.5	1049.8	1050.1	1050.3	1050.6	1050.3	1050.1
142.5°	1095.2	1096.5	1097.8	1098.4	1098.5	1098.8	1099.1	1099.3	1099.6	1099.1	1098.5
145°	1143.6	1144.6	1145.7	1146.2	1146.3	1146.6	1146.9	1147.1	1147.4	1146.6	1145.8
147.5°	1188.9	1190.5	1192.0	1192.8	1192.8	1192.8	1192.8	1192.8	1192.8	1192.0	1191.2
150°	1230.9	1232.5	1234.0	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8	1234.3	1233.8
152.5°	1271.2	1272.5	1273.8	1274.5	1274.2	1273.7	1273.2	1272.6	1272.1	1271.9	1271.6
155°	1308.4	1310.2	1312.0	1312.9	1312.4	1311.4	1310.3	1309.3	1308.3	1308.0	1307.8
157.5°	1341.7	1343.3	1344.8	1345.6	1345.1	1344.0	1343.0	1341.9	1340.9	1340.7	1340.4
160°	1373.3	1374.3	1375.4	1375.9	1375.3	1374.0	1372.7	1371.4	1370.1	1370.1	1370.1
162.5°	1399.3	1401.2	1403.0	1403.9	1403.3	1402.0	1400.7	1399.4	1398.1	1397.8	1397.6
165°	1422.7	1424.5	1426.3	1427.2	1426.4	1424.9	1423.3	1421.8	1420.2	1420.2	1420.2
167.5°	1443.1	1444.7	1446.2	1447.0	1446.2	1444.7	1443.1	1441.6	1440.0	1439.8	1439.5
170°	1458.8	1460.7	1462.5	1463.4	1462.5	1460.7	1458.8	1457.0	1455.2	1455.2	1455.2
172.5°	1470.5	1472.3	1474.1	1475.0	1474.2	1472.7	1471.1	1469.6	1468.0	1468.0	1468.0
175°	1478.6	1480.5	1482.3	1483.2	1482.4	1480.9	1479.3	1477.8	1476.2	1476.2	1476.2
177.5°	1483.3	1485.1	1486.9	1487.8	1487.0	1485.5	1484.0	1482.4	1480.9	1480.9	1480.9
180°	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3

TEST NUMBER: P1012303

CATALOG NUMBER: S123RDIP-B1165D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1913.0	1905.1	1897.2	1897.2	1879.8	1864.0	1856.1	1859.2	1849.7	1837.1	1824.4
5°	1996.9	1965.2	1958.9	1941.5	1917.8	1884.5	1867.1	1851.3	1832.3	1807.0	1783.3
7.5°	2074.4	2033.3	2011.1	1993.7	1947.8	1902.0	1864.0	1838.7	1805.4	1767.5	1739.0
10°	2175.7	2099.7	2076.0	2036.4	1971.6	1906.7	1862.4	1821.3	1775.4	1731.1	1693.1
12.5°	2256.4	2169.4	2125.1	2085.5	2001.6	1919.4	1845.0	1794.4	1739.0	1689.9	1640.9
15°	2348.2	2250.1	2172.5	2125.1	2019.0	1919.4	1835.5	1764.3	1702.6	1642.4	1599.7
17.5°	2392.5	2269.0	2234.2	2166.2	2012.7	1913.0	1810.2	1734.2	1659.9	1590.2	1539.6
20°	2462.1	2318.1	2231.1	2185.2	2049.1	1902.0	1781.7	1694.7	1617.1	1542.8	1489.0
22.5°	2466.8	2310.2	2253.2	2166.2	1998.5	1868.7	1756.4	1650.4	1560.2	1490.5	1435.2
25°	2455.8	2295.9	2216.8	2147.2	2008.0	1849.7	1705.7	1601.3	1512.7	1432.0	1367.1
27.5°	2451.0	2254.8	2180.4	2110.8	1954.2	1794.4	1675.7	1557.0	1455.7	1384.5	1318.1
30°	2444.7	2210.5	2120.3	2039.6	1895.6	1751.6	1609.2	1506.4	1409.8	1319.7	1253.2
32.5°	2403.5	2150.4	2058.6	1973.2	1818.1	1674.1	1561.8	1452.6	1348.1	1264.3	1204.1
35°	2390.9	2095.0	1974.7	1883.0	1731.1	1602.9	1484.2	1394.0	1295.9	1212.1	1140.9
37.5°	2354.5	2038.0	1908.3	1791.2	1633.0	1511.1	1424.1	1333.9	1239.0	1148.8	1091.8
40°	2291.2	1971.6	1824.4	1704.2	1541.2	1417.8	1337.1	1270.6	1177.2	1096.5	1026.9
42.5°	2197.8	1903.5	1745.3	1618.7	1438.3	1322.8	1256.4	1193.1	1114.0	1030.1	973.1
45°	2090.2	1813.3	1666.2	1525.4	1341.8	1229.5	1159.8	1121.9	1049.1	977.9	911.4
47.5°	1943.1	1720.0	1574.4	1428.8	1242.1	1132.9	1077.6	1039.6	989.0	911.4	857.6
50°	1758.0	1599.7	1462.1	1332.3	1144.0	1039.6	984.2	955.7	913.0	857.6	805.4
52.5°	1552.3	1460.5	1346.6	1226.3	1044.3	946.2	895.6	873.4	841.8	789.6	745.3
55°	1345.0	1305.4	1227.9	1109.2	939.9	859.2	814.9	786.4	762.7	724.7	686.7
57.5°	1159.8	1140.9	1087.1	995.3	852.9	769.0	731.0	712.0	693.1	664.6	626.6
60°	968.4	989.0	933.6	887.7	757.9	685.1	651.9	631.3	621.9	596.5	572.8
62.5°	802.2	821.2	789.6	754.8	663.0	598.1	577.5	558.6	552.2	530.1	506.3
65°	651.9	675.7	651.9	632.9	577.5	523.7	498.4	488.9	482.6	468.4	449.4
67.5°	519.0	542.7	531.7	507.9	490.5	446.2	432.0	422.5	419.3	408.2	392.4
70°	390.8	424.1	427.2	413.0	397.2	376.6	367.1	363.9	356.0	346.5	337.0
72.5°	281.7	319.6	321.2	321.2	311.7	311.7	302.2	297.5	297.5	288.0	276.9
75°	207.3	232.6	235.8	238.9	243.7	248.4	242.1	242.1	240.5	231.0	226.3
77.5°	137.7	159.8	167.7	178.8	185.1	185.1	188.3	191.5	188.3	183.5	180.4
80°	88.6	104.4	113.9	120.3	129.8	134.5	139.2	140.8	137.7	136.1	131.3
82.5°	58.5	63.3	68.0	76.0	87.0	94.9	94.9	93.4	96.5	94.9	93.4
85°	33.2	36.4	38.0	39.6	45.9	53.8	55.4	57.0	60.1	57.0	53.8
87.5°	12.7	14.2	14.2	14.2	17.4	19.0	23.7	30.1	28.5	25.3	25.3
90°	17.9	14.5	12.8	11.5	8.9	6.4	3.8	1.2	3.8	6.4	8.9
92.5°	44.3	42.8	42.0	41.2	39.7	38.1	36.6	35.0	36.6	38.1	39.7
95°	80.1	78.0	77.0	76.1	74.3	72.4	70.6	68.8	70.6	72.4	74.3
97.5°	121.2	119.7	118.9	118.3	117.0	115.7	114.4	113.1	114.4	115.7	117.0
100°	167.5	166.2	165.6	164.8	163.3	161.7	160.2	158.6	160.2	161.7	163.3
102.5°	217.2	215.4	214.5	214.1	213.4	212.6	211.9	211.1	211.9	212.6	213.4
105°	268.2	265.9	264.7	264.4	263.9	263.4	262.9	262.4	262.9	263.4	263.9
107.5°	325.7	324.7	324.2	324.1	323.8	323.5	323.3	323.0	323.3	323.5	323.8
110°	382.1	381.6	381.3	381.0	380.5	380.0	379.5	379.0	379.5	380.0	380.5

TEST NUMBER: P1012303

CATALOG NUMBER: S123RDIP-B1165D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	438.4	438.4	438.4	438.3	438.0	437.8	437.5	437.3	437.5	437.8	438.0
115°	498.3	498.8	499.1	498.7	497.9	497.2	496.4	495.6	496.4	497.2	497.9
117.5°	555.4	555.9	556.2	556.1	555.8	555.5	555.3	555.0	555.3	555.5	555.8
120°	614.9	616.2	616.8	616.0	614.5	612.9	611.4	609.8	611.4	612.9	614.5
122.5°	670.8	671.3	671.6	671.1	670.1	669.0	668.0	667.0	668.0	669.0	670.1
125°	728.0	728.5	728.8	728.4	727.6	726.9	726.1	725.3	726.1	726.9	727.6
127.5°	785.1	785.6	785.9	785.1	783.6	782.0	780.5	778.9	780.5	782.0	783.6
130°	840.7	841.5	841.9	840.9	838.8	836.7	834.6	832.5	834.6	836.7	838.8
132.5°	894.7	895.2	895.5	894.5	892.4	890.3	888.3	886.2	888.3	890.3	892.4
135°	947.6	947.9	948.0	947.2	945.7	944.1	942.6	941.0	942.6	944.1	945.7
137.5°	998.1	997.4	997.0	996.3	995.0	993.7	992.4	991.1	992.4	993.7	995.0
140°	1049.8	1049.5	1049.4	1048.8	1047.5	1046.2	1044.9	1043.6	1044.9	1046.2	1047.5
142.5°	1098.0	1097.5	1097.2	1096.6	1095.3	1094.0	1092.7	1091.4	1092.7	1094.0	1095.3
145°	1145.1	1144.3	1143.9	1143.6	1143.1	1142.6	1142.0	1141.5	1142.0	1142.6	1143.1
147.5°	1190.5	1189.7	1189.3	1188.8	1187.8	1186.7	1185.7	1184.7	1185.7	1186.7	1187.8
150°	1233.3	1232.8	1232.5	1232.2	1231.7	1231.2	1230.7	1230.2	1230.7	1231.2	1231.7
152.5°	1271.4	1271.1	1271.0	1270.6	1269.8	1269.1	1268.3	1267.5	1268.3	1269.1	1269.8
155°	1307.5	1307.2	1307.1	1307.1	1307.1	1307.1	1307.1	1307.1	1307.1	1307.1	1307.1
157.5°	1340.2	1339.9	1339.8	1339.9	1340.2	1340.4	1340.7	1340.9	1340.7	1340.4	1340.2
160°	1370.1	1370.1	1370.1	1370.4	1370.9	1371.4	1371.9	1372.4	1371.9	1371.4	1370.9
162.5°	1397.3	1397.0	1396.9	1397.3	1398.1	1398.8	1399.6	1400.4	1399.6	1398.8	1398.1
165°	1420.2	1420.2	1420.2	1420.6	1421.4	1422.1	1422.9	1423.7	1422.9	1422.1	1421.4
167.5°	1439.3	1439.0	1438.9	1439.4	1440.4	1441.5	1442.5	1443.5	1442.5	1441.5	1440.4
170°	1455.2	1455.2	1455.2	1455.7	1456.8	1457.8	1458.9	1459.9	1458.9	1457.8	1456.8
172.5°	1468.0	1468.0	1468.0	1468.5	1469.6	1470.6	1471.7	1472.7	1471.7	1470.6	1469.6
175°	1476.2	1476.2	1476.2	1476.7	1477.8	1478.8	1479.9	1480.9	1479.9	1478.8	1477.8
177.5°	1480.9	1480.9	1480.9	1481.4	1482.4	1483.5	1484.5	1485.5	1484.5	1483.5	1482.4
180°	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3

TEST NUMBER: P1012303

CATALOG NUMBER: S123RDIP-B1165D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1824.4	1816.5	1813.3	1805.4	1786.4	1773.8	1759.5	1750.0	1751.6	1743.7	1748.5
5°	1767.5	1765.9	1754.8	1739.0	1712.1	1697.8	1672.5	1659.9	1653.5	1655.1	1645.6
7.5°	1720.0	1705.7	1697.8	1672.5	1647.2	1617.1	1596.6	1585.5	1576.0	1566.5	1560.2
10°	1666.2	1653.5	1640.9	1614.0	1579.2	1550.7	1522.2	1511.1	1496.9	1490.5	1485.8
12.5°	1609.2	1601.3	1585.5	1553.8	1514.3	1487.4	1454.2	1447.8	1428.8	1416.2	1413.0
15°	1557.0	1552.3	1523.8	1487.4	1447.8	1420.9	1392.4	1373.5	1341.8	1348.1	1337.1
17.5°	1501.6	1481.1	1463.6	1414.6	1395.6	1354.5	1321.2	1311.7	1289.6	1275.4	1261.1
20°	1439.9	1427.3	1405.1	1373.5	1327.6	1280.1	1254.8	1239.0	1226.3	1204.1	1197.8
22.5°	1381.4	1365.5	1346.6	1305.4	1265.9	1226.3	1191.5	1177.2	1161.4	1145.6	1136.1
25°	1335.5	1311.7	1291.2	1240.5	1201.0	1167.8	1145.6	1121.9	1099.7	1090.2	1087.1
27.5°	1264.3	1250.0	1229.5	1182.0	1145.6	1109.2	1088.6	1072.8	1049.1	1038.0	1028.5
30°	1218.4	1189.9	1166.2	1128.2	1091.8	1052.2	1033.3	1014.3	1000.0	985.8	974.7
32.5°	1156.7	1134.5	1115.5	1077.6	1041.2	1004.8	984.2	955.7	947.8	936.7	924.1
35°	1096.5	1082.3	1061.7	1020.6	981.0	955.7	933.6	906.7	897.2	889.3	878.2
37.5°	1039.6	1019.0	1004.8	965.2	930.4	900.3	882.9	860.8	854.5	845.0	837.0
40°	990.5	970.0	955.7	916.2	879.8	848.1	837.0	814.9	805.4	794.3	789.6
42.5°	935.2	917.7	898.8	870.3	832.3	800.7	778.5	765.8	753.2	748.4	738.9
45°	876.6	860.8	846.5	814.9	775.3	753.2	734.2	716.8	707.3	699.4	693.1
47.5°	826.0	811.7	792.7	757.9	726.3	705.7	686.7	669.3	659.8	650.3	642.4
50°	767.4	759.5	738.9	705.7	675.7	651.9	634.5	618.7	612.4	601.3	588.6
52.5°	715.2	701.0	683.6	656.7	629.8	601.3	577.5	568.1	557.0	550.6	539.6
55°	653.5	644.0	625.0	601.3	572.8	549.1	531.7	519.0	504.8	498.4	484.2
57.5°	601.3	583.9	574.4	544.3	517.4	493.7	481.0	468.4	452.5	443.1	436.7
60°	544.3	528.5	514.3	488.9	469.9	444.6	425.6	414.6	403.5	390.8	384.5
62.5°	488.9	476.3	458.9	438.3	414.6	394.0	379.8	363.9	357.6	344.9	340.2
65°	428.8	419.3	405.1	381.3	362.4	344.9	330.7	318.0	311.7	307.0	303.8
67.5°	375.0	362.4	352.9	332.3	311.7	297.5	289.6	281.7	273.7	269.0	264.2
70°	319.6	310.1	300.6	281.7	267.4	254.8	248.4	242.1	237.3	232.6	227.9
72.5°	262.7	257.9	248.4	235.8	224.7	215.2	210.4	202.5	197.8	189.9	186.7
75°	216.8	208.9	204.1	193.0	183.5	175.6	169.3	159.8	153.5	150.3	148.7
77.5°	170.9	167.7	161.4	151.9	147.2	139.2	129.8	126.6	123.4	123.4	121.8
80°	128.2	123.4	118.7	110.8	106.0	99.7	99.7	99.7	98.1	99.7	98.1
82.5°	87.0	83.9	80.7	76.0	74.4	74.4	76.0	76.0	76.0	76.0	76.0
85°	50.6	50.6	50.6	52.2	50.6	50.6	52.2	53.8	52.2	52.2	50.6
87.5°	23.7	23.7	25.3	25.3	26.9	26.9	26.9	26.9	26.9	26.9	28.5
90°	11.5	12.8	14.5	17.9	21.2	24.6	28.0	29.0	30.0	31.1	32.1
92.5°	41.2	42.0	42.8	44.3	45.9	47.4	49.0	49.8	50.6	51.3	52.1
95°	76.1	77.0	78.0	80.1	82.2	84.2	86.3	87.3	88.3	89.4	90.4
97.5°	118.3	118.9	119.7	121.2	122.8	124.3	125.9	127.2	128.5	129.8	131.1
100°	164.8	165.6	166.2	167.5	168.8	170.1	171.4	172.2	173.0	173.7	174.5
102.5°	214.1	214.5	215.4	217.2	219.1	220.9	222.7	223.5	224.3	225.0	225.8
105°	264.4	264.7	265.9	268.2	270.5	272.9	275.2	275.2	275.2	275.2	275.2
107.5°	324.1	324.2	324.7	325.7	326.8	327.8	328.8	329.6	330.4	331.1	331.9
110°	381.0	381.3	381.6	382.1	382.6	383.1	383.6	384.6	385.7	386.7	387.8

TEST NUMBER: P1012303

CATALOG NUMBER: S123RDIP-B1165D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	438.3	438.4	438.4	438.4	438.4	438.4	438.4	439.7	441.0	442.3	443.6
115°	498.7	499.1	498.8	498.3	497.8	497.2	496.7	497.0	497.2	497.5	497.8
117.5°	556.1	556.2	555.9	555.4	554.9	554.4	553.9	553.9	553.9	553.9	553.9
120°	616.0	616.8	616.2	614.9	613.6	612.3	611.0	610.7	610.5	610.2	609.9
122.5°	671.1	671.6	671.3	670.8	670.3	669.8	669.3	668.5	667.7	667.0	666.2
125°	728.4	728.8	728.5	728.0	727.5	726.9	726.4	725.4	724.4	723.3	722.3
127.5°	785.1	785.9	785.6	785.1	784.6	784.1	783.6	782.0	780.5	778.9	777.4
130°	840.9	841.9	841.5	840.7	840.0	839.2	838.4	837.4	836.3	835.3	834.2
132.5°	894.5	895.5	895.2	894.7	894.2	893.7	893.2	891.9	890.6	889.3	888.0
135°	947.2	948.0	947.9	947.6	947.3	947.1	946.8	945.8	944.7	943.7	942.6
137.5°	996.3	997.0	997.4	998.1	998.9	999.6	1000.4	999.1	997.8	996.5	995.2
140°	1048.8	1049.4	1049.5	1049.8	1050.1	1050.3	1050.6	1050.3	1050.1	1049.8	1049.5
142.5°	1096.6	1097.2	1097.5	1098.0	1098.5	1099.1	1099.6	1099.3	1099.1	1098.8	1098.5
145°	1143.6	1143.9	1144.3	1145.1	1145.8	1146.6	1147.4	1147.1	1146.9	1146.6	1146.3
147.5°	1188.8	1189.3	1189.7	1190.5	1191.2	1192.0	1192.8	1192.8	1192.8	1192.8	1192.8
150°	1232.2	1232.5	1232.8	1233.3	1233.8	1234.3	1234.8	1234.8	1234.8	1234.8	1234.8
152.5°	1270.6	1271.0	1271.1	1271.4	1271.6	1271.9	1272.1	1272.6	1273.2	1273.7	1274.2
155°	1307.1	1307.1	1307.2	1307.5	1307.8	1308.0	1308.3	1309.3	1310.3	1311.4	1312.4
157.5°	1339.9	1339.8	1339.9	1340.2	1340.4	1340.7	1340.9	1341.9	1343.0	1344.0	1345.1
160°	1370.4	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1371.4	1372.7	1374.0	1375.3
162.5°	1397.3	1396.9	1397.0	1397.3	1397.6	1397.8	1398.1	1399.4	1400.7	1402.0	1403.3
165°	1420.6	1420.2	1420.2	1420.2	1420.2	1420.2	1420.2	1421.8	1423.3	1424.9	1426.4
167.5°	1439.4	1438.9	1439.0	1439.3	1439.5	1439.8	1440.0	1441.6	1443.1	1444.7	1446.2
170°	1455.7	1455.2	1455.2	1455.2	1455.2	1455.2	1455.2	1457.0	1458.8	1460.7	1462.5
172.5°	1468.5	1468.0	1468.0	1468.0	1468.0	1468.0	1468.0	1469.6	1471.1	1472.7	1474.2
175°	1476.7	1476.2	1476.2	1476.2	1476.2	1476.2	1476.2	1477.8	1479.3	1480.9	1482.4
177.5°	1481.4	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1482.4	1484.0	1485.5	1487.0
180°	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3

TEST NUMBER: P1012303

CATALOG NUMBER: S123RDIP-B1165D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1746.9	1748.5	1743.7	1734.2	1732.6	1735.8	1745.3	1742.1	1734.2	1748.5	1735.8
5°	1650.4	1642.4	1639.3	1642.4	1633.0	1628.2	1637.7	1633.0	1637.7	1639.3	1644.0
7.5°	1557.0	1558.6	1549.1	1550.7	1538.0	1541.2	1541.2	1541.2	1545.9	1549.1	1555.4
10°	1476.3	1479.5	1468.4	1470.0	1460.5	1454.2	1458.9	1468.4	1468.4	1468.4	1471.6
12.5°	1411.4	1397.2	1389.3	1387.7	1376.6	1373.5	1382.9	1386.1	1394.0	1394.0	1398.8
15°	1330.7	1327.6	1321.2	1321.2	1294.3	1300.7	1303.8	1314.9	1330.7	1318.1	1321.2
17.5°	1257.9	1250.0	1242.1	1239.0	1235.8	1226.3	1239.0	1237.4	1246.9	1248.5	1253.2
20°	1193.1	1186.7	1170.9	1172.5	1175.7	1161.4	1169.3	1169.3	1178.8	1188.3	1199.4
22.5°	1129.8	1123.4	1115.5	1118.7	1109.2	1106.0	1106.0	1114.0	1125.0	1132.9	1131.4
25°	1080.7	1069.6	1064.9	1060.2	1055.4	1058.6	1053.8	1061.7	1069.6	1074.4	1069.6
27.5°	1025.3	1020.6	1011.1	1006.4	998.4	1001.6	1004.8	1011.1	1015.9	1015.9	1020.6
30°	971.5	965.2	962.1	957.3	957.3	951.0	952.6	958.9	963.6	968.4	974.7
32.5°	919.3	914.6	909.8	909.8	906.7	905.1	903.5	913.0	913.0	922.5	922.5
35°	876.6	868.7	868.7	860.8	863.9	862.4	859.2	865.5	867.1	873.4	871.9
37.5°	829.1	829.1	826.0	818.1	811.7	813.3	821.2	821.2	826.0	824.4	829.1
40°	781.7	778.5	778.5	773.8	772.2	770.6	772.2	773.8	781.7	780.1	781.7
42.5°	734.2	735.8	727.9	727.9	727.9	723.1	724.7	726.3	729.5	732.6	737.4
45°	688.3	685.1	683.6	680.4	677.2	678.8	677.2	683.6	682.0	685.1	689.9
47.5°	639.3	634.5	632.9	626.6	626.6	629.8	628.2	632.9	634.5	639.3	636.1
50°	591.8	585.5	580.7	582.3	572.8	576.0	576.0	580.7	585.5	587.0	590.2
52.5°	536.4	534.8	533.2	525.3	523.7	522.2	523.7	525.3	531.7	536.4	538.0
55°	482.6	481.0	471.5	468.4	463.6	463.6	466.8	468.4	479.4	481.0	487.4
57.5°	433.6	428.8	417.7	416.2	416.2	416.2	411.4	417.7	420.9	428.8	428.8
60°	379.8	379.8	370.3	370.3	371.8	370.3	370.3	371.8	371.8	378.2	381.3
62.5°	337.0	335.5	335.5	332.3	330.7	332.3	330.7	330.7	332.3	337.0	341.8
65°	299.1	297.5	295.9	294.3	291.1	291.1	292.7	295.9	295.9	299.1	300.6
67.5°	262.7	262.7	259.5	259.5	257.9	256.3	257.9	256.3	262.7	262.7	264.2
70°	226.3	224.7	219.9	218.4	213.6	215.2	215.2	219.9	221.5	224.7	227.9
72.5°	182.0	182.0	178.8	175.6	177.2	174.1	174.1	175.6	175.6	180.4	182.0
75°	150.3	147.2	145.6	147.2	145.6	148.7	145.6	145.6	148.7	148.7	148.7
77.5°	123.4	123.4	121.8	121.8	123.4	121.8	123.4	123.4	123.4	121.8	123.4
80°	101.3	99.7	99.7	99.7	98.1	98.1	98.1	98.1	98.1	98.1	98.1
82.5°	76.0	76.0	74.4	76.0	76.0	74.4	76.0	74.4	74.4	76.0	76.0
85°	50.6	53.8	50.6	50.6	52.2	52.2	53.8	52.2	53.8	50.6	52.2
87.5°	26.9	28.5	28.5	26.9	26.9	28.5	28.5	28.5	30.1	26.9	28.5
90°	32.6	32.9	33.4	33.9	34.5	35.0	34.5	33.9	33.4	32.9	32.6
92.5°	52.5	52.2	51.7	51.2	50.6	50.1	50.6	51.2	51.7	52.2	52.5
95°	90.9	90.9	90.9	90.9	90.9	90.9	90.9	90.9	90.9	90.9	90.9
97.5°	131.8	131.7	131.4	131.1	130.9	130.6	130.9	131.1	131.4	131.7	131.8
100°	174.9	175.2	175.7	176.2	176.7	177.2	176.7	176.2	175.7	175.2	174.9
102.5°	226.2	226.1	225.8	225.5	225.3	225.0	225.3	225.5	225.8	226.1	226.2
105°	275.2	275.5	276.0	276.5	277.0	277.5	277.0	276.5	276.0	275.5	275.2
107.5°	332.3	332.2	331.9	331.7	331.4	331.2	331.4	331.7	331.9	332.2	332.3
110°	388.3	388.0	387.5	387.0	386.5	386.0	386.5	387.0	387.5	388.0	388.3

TEST NUMBER: P1012303

CATALOG NUMBER: S123RDIP-B1165D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	444.3	444.3	444.3	444.3	444.3	444.3	444.3	444.3	444.3	444.3	444.3
115°	497.9	497.8	497.5	497.2	497.0	496.7	497.0	497.2	497.5	497.8	497.9
117.5°	553.9	553.5	552.7	552.0	551.2	550.4	551.2	552.0	552.7	553.5	553.9
120°	609.8	609.5	609.0	608.5	608.0	607.5	608.0	608.5	609.0	609.5	609.8
122.5°	665.8	665.4	664.6	663.9	663.1	662.3	663.1	663.9	664.6	665.4	665.8
125°	721.8	721.3	720.2	719.2	718.1	717.1	718.1	719.2	720.2	721.3	721.8
127.5°	776.6	776.1	775.0	774.0	772.9	771.9	772.9	774.0	775.0	776.1	776.6
130°	833.7	832.8	831.0	829.1	827.3	825.5	827.3	829.1	831.0	832.8	833.7
132.5°	887.3	886.7	885.4	884.1	882.8	881.5	882.8	884.1	885.4	886.7	887.3
135°	942.1	941.8	941.3	940.8	940.3	939.8	940.3	940.8	941.3	941.8	942.1
137.5°	994.6	994.2	993.4	992.7	991.9	991.1	991.9	992.7	993.4	994.2	994.6
140°	1049.4	1048.5	1046.7	1044.9	1043.1	1041.3	1043.1	1044.9	1046.7	1048.5	1049.4
142.5°	1098.4	1097.8	1096.5	1095.2	1093.9	1092.6	1093.9	1095.2	1096.5	1097.8	1098.4
145°	1146.2	1145.7	1144.6	1143.6	1142.5	1141.5	1142.5	1143.6	1144.6	1145.7	1146.2
147.5°	1192.8	1192.0	1190.5	1188.9	1187.4	1185.8	1187.4	1188.9	1190.5	1192.0	1192.8
150°	1234.8	1234.0	1232.5	1230.9	1229.4	1227.8	1229.4	1230.9	1232.5	1234.0	1234.8
152.5°	1274.5	1273.8	1272.5	1271.2	1269.9	1268.6	1269.9	1271.2	1272.5	1273.8	1274.5
155°	1312.9	1312.0	1310.2	1308.4	1306.6	1304.8	1306.6	1308.4	1310.2	1312.0	1312.9
157.5°	1345.6	1344.8	1343.3	1341.7	1340.2	1338.6	1340.2	1341.7	1343.3	1344.8	1345.6
160°	1375.9	1375.4	1374.3	1373.3	1372.2	1371.2	1372.2	1373.3	1374.3	1375.4	1375.9
162.5°	1403.9	1403.0	1401.2	1399.3	1397.5	1395.7	1397.5	1399.3	1401.2	1403.0	1403.9
165°	1427.2	1426.3	1424.5	1422.7	1420.9	1419.1	1420.9	1422.7	1424.5	1426.3	1427.2
167.5°	1447.0	1446.2	1444.7	1443.1	1441.6	1440.0	1441.6	1443.1	1444.7	1446.2	1447.0
170°	1463.4	1462.5	1460.7	1458.8	1457.0	1455.2	1457.0	1458.8	1460.7	1462.5	1463.4
172.5°	1475.0	1474.1	1472.3	1470.5	1468.7	1466.9	1468.7	1470.5	1472.3	1474.1	1475.0
175°	1483.2	1482.3	1480.5	1478.6	1476.8	1475.0	1476.8	1478.6	1480.5	1482.3	1483.2
177.5°	1487.8	1486.9	1485.1	1483.3	1481.5	1479.7	1481.5	1483.3	1485.1	1486.9	1487.8
180°	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3

TEST NUMBER: P1012303

CATALOG NUMBER: S123RDIP-B1165D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1748.5	1754.8	1748.5	1735.8	1748.5	1756.4	1764.3	1776.9	1783.3	1783.3	1792.8
5°	1648.8	1661.4	1656.7	1653.5	1666.2	1674.1	1686.8	1702.6	1720.0	1731.1	1743.7
7.5°	1560.2	1568.1	1576.0	1576.0	1588.7	1606.1	1625.0	1644.0	1666.2	1682.0	1691.5
10°	1482.6	1489.0	1493.7	1500.0	1519.0	1538.0	1563.3	1587.1	1606.1	1623.5	1639.3
12.5°	1408.3	1417.8	1428.8	1433.6	1447.8	1471.6	1495.3	1523.8	1553.8	1571.2	1587.1
15°	1337.1	1341.8	1354.5	1368.7	1381.4	1406.7	1436.7	1466.8	1492.1	1519.0	1533.3
17.5°	1264.3	1265.9	1299.1	1291.2	1332.3	1356.0	1371.9	1400.4	1441.5	1463.6	1485.8
20°	1193.1	1208.9	1223.1	1231.0	1253.2	1280.1	1326.0	1348.1	1381.4	1401.9	1420.9
22.5°	1137.7	1161.4	1161.4	1180.4	1191.5	1216.8	1250.0	1292.8	1329.2	1343.4	1370.3
25°	1088.6	1099.7	1118.7	1125.0	1145.6	1167.8	1189.9	1235.8	1275.4	1294.3	1313.3
27.5°	1025.3	1039.6	1064.9	1064.9	1091.8	1115.5	1142.4	1172.5	1212.1	1239.0	1259.5
30°	976.3	990.5	1001.6	1019.0	1030.1	1052.2	1099.7	1121.9	1156.7	1180.4	1205.7
32.5°	930.4	941.5	951.0	970.0	982.6	1007.9	1033.3	1072.8	1102.9	1125.0	1151.9
35°	879.8	890.8	903.5	917.7	936.7	960.5	984.2	1017.4	1047.5	1068.1	1090.2
37.5°	832.3	840.2	859.2	868.7	884.5	906.7	936.7	971.5	998.4	1014.3	1036.4
40°	786.4	792.7	807.0	824.4	835.5	852.9	884.5	914.6	947.8	966.8	984.2
42.5°	737.4	745.3	757.9	775.3	792.7	811.7	829.1	863.9	894.0	909.8	928.8
45°	694.6	699.4	708.9	726.3	743.7	757.9	784.8	816.5	845.0	857.6	878.2
47.5°	644.0	648.8	663.0	670.9	689.9	708.9	735.8	767.4	792.7	805.4	824.4
50°	591.8	596.5	606.0	623.4	636.1	656.7	680.4	707.3	738.9	756.3	767.4
52.5°	541.2	550.6	558.6	572.8	588.6	609.2	631.3	656.7	683.6	701.0	713.6
55°	490.5	498.4	507.9	515.8	534.8	553.8	579.1	602.9	626.6	642.4	656.7
57.5°	433.6	444.6	454.1	469.9	484.2	500.0	528.5	547.5	576.0	587.0	599.7
60°	384.5	395.6	403.5	416.2	428.8	449.4	468.4	492.1	515.8	530.1	545.9
62.5°	343.4	348.1	352.9	365.5	378.2	397.2	416.2	439.9	465.2	473.1	485.8
65°	302.2	307.0	314.9	326.0	335.5	346.5	367.1	386.1	409.8	422.5	427.2
67.5°	267.4	272.2	273.7	281.7	289.6	302.2	313.3	332.3	354.4	362.4	371.8
70°	227.9	235.8	237.3	243.7	246.8	254.8	267.4	281.7	299.1	313.3	321.2
72.5°	182.0	193.0	196.2	205.7	210.4	218.4	227.9	238.9	250.0	256.3	262.7
75°	148.7	151.9	153.5	161.4	169.3	180.4	185.1	191.5	201.0	208.9	215.2
77.5°	123.4	125.0	126.6	126.6	128.2	134.5	144.0	151.9	158.2	161.4	166.1
80°	99.7	98.1	98.1	99.7	99.7	99.7	102.9	113.9	117.1	125.0	123.4
82.5°	77.5	74.4	76.0	74.4	74.4	74.4	74.4	76.0	76.0	80.7	83.9
85°	50.6	52.2	50.6	50.6	49.1	50.6	49.1	49.1	47.5	47.5	45.9
87.5°	26.9	28.5	26.9	26.9	25.3	26.9	25.3	25.3	23.7	23.7	20.6
90°	32.1	31.1	30.0	29.0	28.0	24.6	21.2	17.9	14.5	12.8	11.5
92.5°	52.1	51.3	50.6	49.8	49.0	47.4	45.9	44.3	42.8	42.0	41.2
95°	90.4	89.4	88.3	87.3	86.3	84.2	82.2	80.1	78.0	77.0	76.1
97.5°	131.1	129.8	128.5	127.2	125.9	124.3	122.8	121.2	119.7	118.9	118.3
100°	174.5	173.7	173.0	172.2	171.4	170.1	168.8	167.5	166.2	165.6	164.8
102.5°	225.8	225.0	224.3	223.5	222.7	220.9	219.1	217.2	215.4	214.5	214.1
105°	275.2	275.2	275.2	275.2	275.2	272.9	270.5	268.2	265.9	264.7	264.4
107.5°	331.9	331.1	330.4	329.6	328.8	327.8	326.8	325.7	324.7	324.2	324.1
110°	387.8	386.7	385.7	384.6	383.6	383.1	382.6	382.1	381.6	381.3	381.0

TEST NUMBER: P1012303

CATALOG NUMBER: S123RDIP-B1165D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	443.6	442.3	441.0	439.7	438.4	438.4	438.4	438.4	438.4	438.4	438.3
115°	497.8	497.5	497.2	497.0	496.7	497.2	497.8	498.3	498.8	499.1	498.7
117.5°	553.9	553.9	553.9	553.9	553.9	554.4	554.9	555.4	555.9	556.2	556.1
120°	609.9	610.2	610.5	610.7	611.0	612.3	613.6	614.9	616.2	616.8	616.0
122.5°	666.2	667.0	667.7	668.5	669.3	669.8	670.3	670.8	671.3	671.6	671.1
125°	722.3	723.3	724.4	725.4	726.4	726.9	727.5	728.0	728.5	728.8	728.4
127.5°	777.4	778.9	780.5	782.0	783.6	784.1	784.6	785.1	785.6	785.9	785.1
130°	834.2	835.3	836.3	837.4	838.4	839.2	840.0	840.7	841.5	841.9	840.9
132.5°	888.0	889.3	890.6	891.9	893.2	893.7	894.2	894.7	895.2	895.5	894.5
135°	942.6	943.7	944.7	945.8	946.8	947.1	947.3	947.6	947.9	948.0	947.2
137.5°	995.2	996.5	997.8	999.1	1000.4	999.6	998.9	998.1	997.4	997.0	996.3
140°	1049.5	1049.8	1050.1	1050.3	1050.6	1050.3	1050.1	1049.8	1049.5	1049.4	1048.8
142.5°	1098.5	1098.8	1099.1	1099.3	1099.6	1099.1	1098.5	1098.0	1097.5	1097.2	1096.6
145°	1146.3	1146.6	1146.9	1147.1	1147.4	1146.6	1145.8	1145.1	1144.3	1143.9	1143.6
147.5°	1192.8	1192.8	1192.8	1192.8	1192.8	1192.0	1191.2	1190.5	1189.7	1189.3	1188.8
150°	1234.8	1234.8	1234.8	1234.8	1234.8	1234.3	1233.8	1233.3	1232.8	1232.5	1232.2
152.5°	1274.2	1273.7	1273.2	1272.6	1272.1	1271.9	1271.6	1271.4	1271.1	1271.0	1270.6
155°	1312.4	1311.4	1310.3	1309.3	1308.3	1308.0	1307.8	1307.5	1307.2	1307.1	1307.1
157.5°	1345.1	1344.0	1343.0	1341.9	1340.9	1340.7	1340.4	1340.2	1339.9	1339.8	1339.9
160°	1375.3	1374.0	1372.7	1371.4	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.4
162.5°	1403.3	1402.0	1400.7	1399.4	1398.1	1397.8	1397.6	1397.3	1397.0	1396.9	1397.3
165°	1426.4	1424.9	1423.3	1421.8	1420.2	1420.2	1420.2	1420.2	1420.2	1420.2	1420.6
167.5°	1446.2	1444.7	1443.1	1441.6	1440.0	1439.8	1439.5	1439.3	1439.0	1438.9	1439.4
170°	1462.5	1460.7	1458.8	1457.0	1455.2	1455.2	1455.2	1455.2	1455.2	1455.2	1455.7
172.5°	1474.2	1472.7	1471.1	1469.6	1468.0	1468.0	1468.0	1468.0	1468.0	1468.0	1468.5
175°	1482.4	1480.9	1479.3	1477.8	1476.2	1476.2	1476.2	1476.2	1476.2	1476.2	1476.7
177.5°	1487.0	1485.5	1484.0	1482.4	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1481.4
180°	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3	1484.3

TEST NUMBER: P1012303

CATALOG NUMBER: S123RDIP-B1165D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1848.2	1848.2	1848.2	1848.2
2.5°	1800.7	1811.8	1833.9	1852.9
5°	1762.7	1780.1	1813.3	1846.6
7.5°	1716.8	1743.7	1786.4	1832.3
10°	1672.5	1707.3	1759.5	1813.3
12.5°	1628.2	1664.6	1720.0	1789.6
15°	1576.0	1614.0	1680.4	1764.3
17.5°	1530.1	1580.7	1640.9	1724.7
20°	1481.1	1519.0	1596.6	1685.2
22.5°	1419.3	1482.6	1555.4	1648.8
25°	1370.3	1425.7	1498.5	1604.5
27.5°	1310.2	1375.0	1463.6	1557.0
30°	1261.1	1314.9	1397.2	1509.5
32.5°	1204.1	1267.4	1352.9	1463.6
35°	1153.5	1207.3	1288.0	1400.4
37.5°	1093.4	1151.9	1242.1	1341.8
40°	1041.2	1098.1	1183.6	1276.9
42.5°	977.9	1038.0	1123.4	1202.6
45°	927.2	982.6	1050.7	1123.4
47.5°	865.5	924.1	990.5	1041.2
50°	810.1	863.9	916.2	958.9
52.5°	750.0	799.1	846.5	878.2
55°	694.6	732.6	770.6	792.7
57.5°	629.8	666.2	697.8	710.5
60°	572.8	602.9	623.4	637.7
62.5°	512.7	534.8	550.6	558.6
65°	454.1	469.9	477.9	485.8
67.5°	394.0	408.2	413.0	422.5
70°	330.7	346.5	349.7	354.4
72.5°	283.2	283.2	289.6	295.9
75°	226.3	229.4	232.6	232.6
77.5°	177.2	177.2	180.4	182.0
80°	129.8	131.3	131.3	129.8
82.5°	88.6	91.8	88.6	87.0
85°	49.1	55.4	52.2	52.2
87.5°	20.6	20.6	23.7	20.6
90°	8.9	6.4	3.8	1.2
92.5°	39.7	38.1	36.6	35.0
95°	74.3	72.4	70.6	68.8
97.5°	117.0	115.7	114.4	113.1
100°	163.3	161.7	160.2	158.6
102.5°	213.4	212.6	211.9	211.1
105°	263.9	263.4	262.9	262.4
107.5°	323.8	323.5	323.3	323.0
110°	380.5	380.0	379.5	379.0



TEST NUMBER: P1012303

CATALOG NUMBER: S123RDIP-B1165D1195UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	438.0	437.8	437.5	437.3
115°	497.9	497.2	496.4	495.6
117.5°	555.8	555.5	555.3	555.0
120°	614.5	612.9	611.4	609.8
122.5°	670.1	669.0	668.0	667.0
125°	727.6	726.9	726.1	725.3
127.5°	783.6	782.0	780.5	778.9
130°	838.8	836.7	834.6	832.5
132.5°	892.4	890.3	888.3	886.2
135°	945.7	944.1	942.6	941.0
137.5°	995.0	993.7	992.4	991.1
140°	1047.5	1046.2	1044.9	1043.6
142.5°	1095.3	1094.0	1092.7	1091.4
145°	1143.1	1142.6	1142.0	1141.5
147.5°	1187.8	1186.7	1185.7	1184.7
150°	1231.7	1231.2	1230.7	1230.2
152.5°	1269.8	1269.1	1268.3	1267.5
155°	1307.1	1307.1	1307.1	1307.1
157.5°	1340.2	1340.4	1340.7	1340.9
160°	1370.9	1371.4	1371.9	1372.4
162.5°	1398.1	1398.8	1399.6	1400.4
165°	1421.4	1422.1	1422.9	1423.7
167.5°	1440.4	1441.5	1442.5	1443.5
170°	1456.8	1457.8	1458.9	1459.9
172.5°	1469.6	1470.6	1471.7	1472.7
175°	1477.8	1478.8	1479.9	1480.9
177.5°	1482.4	1483.5	1484.5	1485.5
180°	1484.3	1484.3	1484.3	1484.3

(END OF REPORT)