

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012309

Luminaire Tested: S123RDIP-B1165D1195UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012309
REPORT IS A COMBINATION OF REPORTS P992988 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1165D1195UB40-4F0-XX-W2A-A1
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8631.0 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012309

CATALOG NUMBER: S123RDIP-B1165D1195UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1012309

CATALOG NUMBER: S123RDIP-B1165D1195UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	47	45	44
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38
4	76	66	58	53	71	62	55	50	53	48	44	46	42	39	38	36	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29
6	65	53	45	40	60	50	43	38	43	38	34	37	33	30	32	29	26
7	60	48	40	35	56	45	38	33	40	34	30	34	30	27	29	26	23
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19695	19695	19695	19695
5°	19710	22682	19760	16828
10°	19535	27382	19620	14698
15°	19335	31076	19335	12961
20°	18938	33520	19044	11497
25°	18648	31847	18611	10490
30°	18310	22066	18272	9507
35°	17904	14167	17823	8763
40°	17399	10004	17312	8026
45°	16517	8006	16495	7307
50°	15437	6697	15386	6466
55°	14220	5519	14108	5482
60°	13026	4562	12896	4662
65°	11625	3651	11702	3951
70°	10334	2537	10610	3194
75°	8760	1882	9118	2457
80°	6976	1248	7568	1841
85°	4966	590	5417	1146

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 26293 cd/sqm

TEST NUMBER: P1012309

CATALOG NUMBER: S123RDIP-B1165D1195UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.7	2.1
10°-20°	562.5	6.5
20°-30°	885.9	10.3
30°-40°	921.2	10.7
40°-50°	788.1	9.1
50°-60°	600.8	7.0
60°-70°	384.9	4.5
70°-80°	184.4	2.1
80°-90°	51.6	0.6
90°-100°	94.6	1.1
100°-110°	286.3	3.3
110°-120°	487.4	5.6
120°-130°	641.3	7.4
130°-140°	720.8	8.4
140°-150°	708.6	8.2
150°-160°	596.6	6.9
160°-170°	397.2	4.6
170°-180°	139.1	1.6
0°-30°	1628.0	18.9
0°-40°	2549.2	29.5
0°-60°	3938.1	45.6
0°-90°	4559.1	52.8
90°-120°	868.4	10.1
90°-150°	2939.0	34.1
90°-180°	4072.0	47.2
0°-180°	8631.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1830	1830	1830	1830	1830	
5°	1828	2173	1833	1612	1828	173
15°	1747	3088	1747	1288	1747	491
25°	1588	3182	1585	1048	1588	732
35°	1386	1380	1380	854	1386	868
45°	1112	736	1111	672	1112	856
55°	785	462	779	459	785	703
65°	481	266	484	288	481	480
75°	230	113	240	147	230	249
85°	52	27	56	52	52	58
90°	1	35	1	35	1	8
95°	68	90	68	90	68	75
105°	260	275	260	275	260	278
115°	491	492	491	492	491	486
125°	718	710	718	710	718	640
135°	932	930	932	930	932	718
145°	1130	1130	1130	1130	1130	706
155°	1294	1292	1294	1292	1294	596
165°	1410	1405	1410	1405	1410	398
175°	1466	1460	1466	1460	1466	139
180°	1470	1470	1470	1470	1470	

TEST NUMBER: P1012309

CATALOG NUMBER: S123RDIP-B1165D1195UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7
2.5°	1834.4	1846.9	1856.3	1862.6	1878.2	1887.6	1895.5	1909.6	1909.6	1912.7	1919.0
5°	1828.1	1854.7	1873.5	1898.6	1931.5	1947.2	1969.1	1987.9	2014.5	2028.6	2042.7
7.5°	1814.0	1851.6	1890.8	1928.4	1976.9	2008.3	2030.2	2078.8	2113.2	2155.5	2188.4
10°	1795.2	1846.9	1897.0	1955.0	2020.8	2067.8	2100.7	2164.9	2230.7	2290.2	2340.4
12.5°	1771.7	1834.4	1906.4	1976.9	2069.4	2116.3	2169.6	2249.5	2343.5	2418.7	2486.0
15°	1746.7	1818.7	1900.2	1986.3	2102.3	2168.0	2244.8	2341.9	2446.9	2555.0	2647.4
17.5°	1707.5	1798.3	1889.2	2014.5	2150.8	2190.0	2255.8	2388.9	2518.9	2616.1	2728.9
20°	1668.3	1770.2	1884.5	1997.3	2144.5	2235.4	2296.5	2437.5	2576.9	2694.4	2802.5
22.5°	1632.3	1738.8	1857.9	2000.4	2138.3	2229.1	2305.9	2453.1	2614.5	2746.1	2879.2
25°	1588.4	1704.4	1835.9	1970.7	2138.3	2207.2	2291.8	2462.5	2633.3	2785.2	2949.7
27.5°	1541.4	1658.9	1788.9	1926.8	2080.3	2182.1	2265.2	2448.4	2656.8	2819.7	2988.9
30°	1494.4	1615.1	1740.4	1864.1	2036.5	2133.6	2229.1	2431.2	2669.3	2855.7	2985.8
32.5°	1449.0	1550.8	1674.6	1795.2	1966.0	2072.5	2180.6	2414.0	2674.0	2830.7	2893.3
35°	1386.4	1492.9	1593.1	1721.6	1893.9	1998.9	2125.7	2412.4	2653.7	2750.8	2719.5
37.5°	1328.4	1417.7	1513.2	1627.6	1804.6	1940.9	2072.5	2371.7	2586.3	2592.6	2415.6
40°	1264.2	1337.8	1417.7	1538.3	1729.4	1864.1	2006.7	2309.0	2464.1	2371.7	2060.0
42.5°	1190.5	1256.3	1319.0	1436.5	1644.8	1795.2	1948.7	2230.7	2287.1	2074.1	1749.8
45°	1112.2	1165.5	1223.4	1347.2	1555.5	1704.4	1857.9	2110.1	2052.1	1751.4	1442.8
47.5°	1030.8	1076.2	1132.6	1245.4	1460.0	1611.9	1757.6	1937.8	1790.5	1467.8	1209.3
50°	949.3	985.3	1040.2	1156.1	1362.9	1500.7	1635.4	1752.9	1546.1	1259.5	999.4
52.5°	869.4	897.6	954.0	1052.7	1253.2	1384.8	1481.9	1527.3	1317.4	1040.2	867.8
55°	784.8	816.1	853.7	954.0	1152.9	1250.1	1314.3	1312.7	1096.6	881.9	717.5
57.5°	703.4	731.6	764.5	864.7	1026.1	1091.9	1146.7	1120.1	914.8	722.2	615.6
60°	631.3	647.0	683.0	767.6	889.8	946.2	977.5	932.1	747.2	609.4	509.1
62.5°	553.0	568.6	598.4	678.3	753.5	783.3	809.9	751.9	617.2	496.6	435.5
65°	480.9	501.3	520.1	584.3	625.0	661.1	657.9	609.4	482.5	404.2	354.0
67.5°	418.3	426.1	441.8	480.9	499.7	526.3	527.9	473.1	388.5	329.0	299.2
70°	350.9	358.7	369.7	388.5	401.0	407.3	404.2	355.6	292.9	256.9	230.3
72.5°	292.9	291.4	299.2	299.2	311.7	310.2	300.8	263.2	222.4	192.7	177.0
75°	230.3	231.8	233.4	230.3	225.6	219.3	211.5	183.3	156.7	142.6	128.5
77.5°	180.1	177.0	178.6	167.6	161.4	155.1	144.1	130.0	108.1	105.0	98.7
80°	128.5	126.9	125.3	120.6	106.5	100.3	92.4	84.6	79.9	76.8	75.2
82.5°	86.2	86.2	83.0	73.6	65.8	61.1	59.5	56.4	51.7	51.7	50.1
85°	51.7	50.1	47.0	37.6	32.9	32.9	32.9	32.9	29.8	29.8	28.2
87.5°	20.4	18.8	14.1	14.1	12.5	12.5	12.5	11.0	11.0	9.4	9.4
90°	1.2	3.8	6.3	8.9	11.4	12.7	14.4	17.7	21.0	24.4	27.7
92.5°	34.6	36.2	37.7	39.3	40.8	41.6	42.4	43.9	45.4	47.0	48.5
95°	68.1	69.9	71.7	73.5	75.3	76.2	77.2	79.3	81.3	83.4	85.4
97.5°	112.0	113.3	114.5	115.8	117.1	117.7	118.5	120.0	121.6	123.1	124.7
100°	157.0	158.5	160.1	161.6	163.1	163.9	164.5	165.8	167.1	168.4	169.7
102.5°	208.9	209.7	210.5	211.2	212.0	212.4	213.3	215.1	216.9	218.7	220.5
105°	259.7	260.2	260.8	261.3	261.8	262.1	263.2	265.5	267.8	270.1	272.4
107.5°	319.8	320.0	320.3	320.5	320.8	320.9	321.4	322.4	323.5	324.5	325.5
110°	375.2	375.7	376.2	376.7	377.2	377.5	377.8	378.3	378.8	379.3	379.8

TEST NUMBER: P1012309

CATALOG NUMBER: S123RDIP-B1165D1195UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	432.9	433.2	433.4	433.7	434.0	434.1	434.1	434.1	434.1	434.1	434.1
115°	490.6	491.4	492.2	492.9	493.7	494.1	493.8	493.3	492.8	492.3	491.8
117.5°	549.5	549.8	550.0	550.3	550.6	550.7	550.4	549.9	549.4	548.8	548.3
120°	603.8	605.3	606.9	608.4	609.9	610.7	610.1	608.8	607.5	606.2	604.9
122.5°	660.3	661.3	662.3	663.4	664.4	664.9	664.6	664.1	663.6	663.1	662.6
125°	718.0	718.8	719.6	720.3	721.1	721.5	721.2	720.7	720.2	719.7	719.2
127.5°	771.1	772.7	774.2	775.8	777.3	778.1	777.8	777.3	776.8	776.3	775.8
130°	824.2	826.3	828.3	830.4	832.5	833.5	833.1	832.3	831.6	830.8	830.0
132.5°	877.4	879.4	881.5	883.5	885.6	886.6	886.3	885.8	885.3	884.8	884.3
135°	931.6	933.1	934.7	936.2	937.7	938.5	938.4	938.1	937.9	937.6	937.4
137.5°	981.2	982.5	983.8	985.1	986.4	987.0	987.4	988.2	988.9	989.7	990.5
140°	1033.2	1034.5	1035.8	1037.1	1038.4	1039.0	1039.1	1039.4	1039.6	1039.9	1040.1
142.5°	1080.5	1081.8	1083.1	1084.4	1085.7	1086.3	1086.6	1087.1	1087.6	1088.1	1088.6
145°	1130.2	1130.7	1131.2	1131.7	1132.2	1132.5	1132.9	1133.6	1134.4	1135.1	1135.9
147.5°	1172.9	1173.9	1174.9	1176.0	1177.0	1177.5	1177.9	1178.7	1179.4	1180.2	1181.0
150°	1217.9	1218.4	1218.9	1219.4	1219.9	1220.2	1220.5	1221.0	1221.5	1222.0	1222.5
152.5°	1254.8	1255.6	1256.4	1257.1	1257.9	1258.3	1258.4	1258.7	1259.0	1259.2	1259.5
155°	1294.1	1294.1	1294.1	1294.1	1294.1	1294.1	1294.2	1294.5	1294.7	1295.0	1295.2
157.5°	1327.6	1327.3	1327.1	1326.8	1326.5	1326.4	1326.5	1326.8	1327.1	1327.3	1327.6
160°	1358.7	1358.2	1357.7	1357.2	1356.7	1356.4	1356.4	1356.4	1356.4	1356.4	1356.4
162.5°	1386.4	1385.6	1384.9	1384.1	1383.4	1383.0	1383.1	1383.4	1383.6	1383.9	1384.1
165°	1409.5	1408.7	1408.0	1407.2	1406.5	1406.1	1406.1	1406.1	1406.1	1406.1	1406.1
167.5°	1429.2	1428.2	1427.1	1426.1	1425.0	1424.5	1424.6	1424.9	1425.2	1425.4	1425.7
170°	1445.3	1444.3	1443.3	1442.2	1441.2	1440.7	1440.7	1440.7	1440.7	1440.7	1440.7
172.5°	1458.0	1457.0	1456.0	1454.9	1453.9	1453.4	1453.4	1453.4	1453.4	1453.4	1453.4
175°	1466.1	1465.1	1464.1	1463.0	1462.0	1461.5	1461.5	1461.5	1461.5	1461.5	1461.5
177.5°	1470.7	1469.7	1468.7	1467.6	1466.6	1466.1	1466.1	1466.1	1466.1	1466.1	1466.1
180°	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6

TEST NUMBER: P1012309

CATALOG NUMBER: S123RDIP-B1165D1195UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7
2.5°	1931.5	1931.5	1945.6	1959.7	1951.9	1956.6	1973.8	1967.5	1980.1	1978.5	1983.2
5°	2077.2	2094.4	2108.5	2138.3	2143.0	2138.3	2168.0	2175.9	2190.0	2172.7	2180.6
7.5°	2241.7	2277.7	2312.2	2356.0	2370.1	2373.3	2388.9	2410.9	2429.6	2395.2	2412.4
10°	2401.5	2456.3	2526.8	2565.9	2600.4	2612.9	2625.5	2639.6	2661.5	2681.9	2666.2
12.5°	2573.8	2653.7	2721.0	2791.5	2833.8	2829.1	2865.1	2874.5	2891.8	2896.5	2902.7
15°	2714.8	2827.5	2869.8	2974.8	2984.2	3015.5	3056.3	3092.3	3097.0	3087.6	3087.6
17.5°	2849.5	2946.6	3021.8	3106.4	3123.6	3150.2	3201.9	3219.2	3225.4	3223.9	3223.9
20°	2959.1	3023.4	3150.2	3220.7	3248.9	3283.4	3319.4	3341.4	3346.1	3352.3	3342.9
22.5°	3031.2	3128.3	3231.7	3289.7	3313.2	3325.7	3349.2	3355.5	3347.6	3349.2	3350.8
25°	3087.6	3183.1	3245.8	3261.5	3259.9	3244.2	3227.0	3197.2	3194.1	3181.6	3156.5
27.5°	3103.2	3139.3	3131.4	3067.2	3003.0	2996.7	2893.3	2836.9	2772.7	2782.1	2746.1
30°	3018.7	2971.7	2860.4	2697.5	2630.2	2520.5	2404.6	2284.0	2237.0	2185.3	2280.8
32.5°	2811.9	2644.3	2446.9	2235.4	2122.6	2025.5	1901.7	1814.0	1763.9	1721.6	1803.0
35°	2500.1	2238.5	1976.9	1776.4	1684.0	1596.3	1480.3	1436.5	1373.8	1380.1	1387.9
37.5°	2099.1	1810.9	1613.5	1416.1	1355.0	1319.0	1234.4	1167.0	1145.1	1138.8	1138.8
40°	1723.2	1486.6	1311.2	1156.1	1109.1	1079.3	1012.0	980.6	957.1	950.9	958.7
42.5°	1425.5	1223.4	1087.2	983.8	950.9	913.3	885.1	845.9	841.2	830.2	844.3
45°	1196.8	1021.4	919.5	844.3	816.1	802.1	770.7	747.2	737.8	736.3	747.2
47.5°	1015.1	878.8	789.5	742.5	720.6	706.5	679.9	670.5	661.1	664.2	659.5
50°	852.2	750.4	692.4	650.1	636.0	621.9	604.7	595.3	590.6	590.6	589.0
52.5°	731.6	647.0	609.4	570.2	563.9	556.1	537.3	531.0	523.2	521.6	527.9
55°	626.6	568.6	531.0	507.5	501.3	485.6	477.8	470.0	465.3	462.1	463.7
57.5°	535.7	491.9	466.8	446.5	435.5	429.2	415.1	413.6	410.4	410.4	408.9
60°	460.6	429.2	399.5	386.9	379.1	371.3	369.7	360.3	355.6	358.7	357.2
62.5°	390.1	365.0	347.8	333.7	329.0	322.7	318.0	314.9	310.2	311.7	311.7
65°	325.8	305.5	292.9	280.4	278.8	272.6	271.0	267.9	267.9	266.3	269.4
67.5°	267.9	253.8	242.8	235.0	230.3	231.8	225.6	220.9	220.9	219.3	224.0
70°	213.0	205.2	194.2	184.8	178.6	178.6	170.7	169.2	169.2	169.2	167.6
72.5°	164.5	150.4	145.7	142.6	142.6	142.6	139.4	139.4	137.9	139.4	137.9
75°	122.2	120.6	117.5	115.9	115.9	114.4	112.8	112.8	112.8	112.8	112.8
77.5°	95.6	95.6	92.4	90.9	90.9	90.9	89.3	89.3	87.7	87.7	87.7
80°	70.5	70.5	67.4	67.4	67.4	65.8	65.8	65.8	67.4	65.8	65.8
82.5°	48.6	48.6	47.0	48.6	47.0	45.4	45.4	45.4	43.9	45.4	45.4
85°	28.2	28.2	26.6	25.1	26.6	26.6	25.1	26.6	25.1	26.6	25.1
87.5°	11.0	9.4	9.4	9.4	7.8	9.4	7.8	7.8	9.4	7.8	9.4
90°	28.7	29.7	30.8	31.8	32.3	32.6	33.1	33.6	34.1	34.6	34.1
92.5°	49.3	50.0	50.8	51.5	51.9	51.6	51.1	50.6	50.1	49.6	50.1
95°	86.4	87.4	88.5	89.5	90.0	90.0	90.0	90.0	90.0	90.0	90.0
97.5°	126.0	127.2	128.5	129.8	130.4	130.3	130.0	129.8	129.5	129.3	129.5
100°	170.5	171.3	172.0	172.8	173.2	173.5	174.0	174.5	175.0	175.5	175.0
102.5°	221.3	222.1	222.8	223.6	224.0	223.9	223.6	223.3	223.1	222.8	223.1
105°	272.4	272.4	272.4	272.4	272.4	272.7	273.2	273.7	274.2	274.7	274.2
107.5°	326.3	327.1	327.8	328.6	329.0	328.9	328.6	328.4	328.1	327.9	328.1
110°	380.8	381.8	382.9	383.9	384.4	384.1	383.6	383.1	382.6	382.1	382.6

TEST NUMBER: P1012309

CATALOG NUMBER: S123RDIP-B1165D1195UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	435.4	436.6	437.9	439.2	439.8	439.8	439.8	439.8	439.8	439.8	439.8
115°	492.0	492.3	492.5	492.8	492.9	492.8	492.5	492.3	492.0	491.8	492.0
117.5°	548.3	548.3	548.3	548.3	548.3	547.9	547.2	546.4	545.7	544.9	545.7
120°	604.7	604.4	604.2	603.9	603.8	603.5	603.0	602.5	601.9	601.4	601.9
122.5°	661.8	661.1	660.3	659.6	659.2	658.8	658.0	657.3	656.5	655.7	656.5
125°	718.2	717.2	716.1	715.1	714.6	714.1	713.1	712.0	711.0	710.0	711.0
127.5°	774.2	772.7	771.1	769.6	768.8	768.3	767.3	766.2	765.2	764.2	765.2
130°	829.0	828.0	826.9	825.9	825.4	824.5	822.7	820.9	819.1	817.3	819.1
132.5°	883.0	881.7	880.4	879.1	878.5	877.9	876.6	875.3	874.0	872.7	874.0
135°	936.4	935.4	934.3	933.3	932.8	932.5	932.0	931.5	931.0	930.5	931.0
137.5°	989.2	987.9	986.6	985.3	984.7	984.3	983.5	982.8	982.0	981.2	982.0
140°	1039.9	1039.6	1039.4	1039.1	1039.0	1038.1	1036.3	1034.5	1032.7	1030.9	1032.7
142.5°	1088.4	1088.1	1087.9	1087.6	1087.5	1086.9	1085.6	1084.3	1083.0	1081.7	1083.0
145°	1135.7	1135.4	1135.2	1134.9	1134.8	1134.3	1133.3	1132.2	1131.2	1130.2	1131.2
147.5°	1181.0	1181.0	1181.0	1181.0	1181.0	1180.2	1178.7	1177.1	1175.6	1174.0	1175.6
150°	1222.5	1222.5	1222.5	1222.5	1222.5	1221.7	1220.2	1218.7	1217.1	1215.6	1217.1
152.5°	1260.0	1260.5	1261.0	1261.5	1261.8	1261.2	1259.9	1258.6	1257.3	1256.0	1257.3
155°	1296.2	1297.3	1298.3	1299.4	1299.9	1299.0	1297.2	1295.4	1293.6	1291.8	1293.6
157.5°	1328.6	1329.6	1330.7	1331.7	1332.2	1331.4	1329.9	1328.4	1326.8	1325.3	1326.8
160°	1357.7	1359.0	1360.3	1361.6	1362.2	1361.7	1360.7	1359.6	1358.6	1357.6	1358.6
162.5°	1385.4	1386.7	1388.0	1389.3	1389.9	1389.0	1387.2	1385.4	1383.6	1381.8	1383.6
165°	1407.6	1409.2	1410.7	1412.2	1413.0	1412.1	1410.3	1408.5	1406.7	1404.9	1406.7
167.5°	1427.2	1428.8	1430.3	1431.8	1432.6	1431.8	1430.3	1428.8	1427.2	1425.7	1427.2
170°	1442.5	1444.3	1446.1	1447.9	1448.8	1447.9	1446.1	1444.3	1442.5	1440.7	1442.5
172.5°	1454.9	1456.5	1458.0	1459.5	1460.3	1459.4	1457.6	1455.8	1454.0	1452.2	1454.0
175°	1463.0	1464.6	1466.1	1467.6	1468.4	1467.5	1465.7	1463.9	1462.1	1460.3	1462.1
177.5°	1467.6	1469.2	1470.7	1472.2	1473.0	1472.1	1470.3	1468.5	1466.7	1464.9	1466.7
180°	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6

TEST NUMBER: P1012309

CATALOG NUMBER: S123RDIP-B1165D1195UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7
2.5°	1975.4	1966.0	1959.7	1955.0	1950.3	1964.4	1945.6	1925.2	1911.1	1901.7	1898.6
5°	2182.1	2161.8	2144.5	2130.4	2133.6	2133.6	2100.7	2064.7	2033.3	2016.1	1997.3
7.5°	2421.8	2399.9	2365.4	2357.6	2351.3	2312.2	2279.3	2213.5	2174.3	2135.1	2100.7
10°	2659.9	2631.7	2598.8	2587.9	2572.2	2523.6	2473.5	2388.9	2340.4	2268.3	2222.9
12.5°	2882.4	2847.9	2815.0	2807.2	2783.7	2741.4	2655.2	2567.5	2484.5	2407.7	2327.8
15°	3068.8	3059.4	3009.3	2977.9	2926.2	2868.3	2849.5	2730.4	2625.5	2545.6	2401.5
17.5°	3225.4	3181.6	3134.6	3114.2	3093.8	3026.5	2959.1	2836.9	2724.2	2606.7	2514.2
20°	3350.8	3302.2	3269.3	3239.5	3230.1	3153.4	3046.9	2938.8	2815.0	2683.4	2562.8
22.5°	3357.0	3350.8	3328.8	3311.6	3292.8	3242.7	3158.1	3023.4	2891.8	2747.7	2589.4
25°	3227.0	3217.6	3280.3	3264.6	3277.1	3258.3	3212.9	3100.1	2946.6	2777.4	2617.6
27.5°	2835.4	2930.9	3029.6	3064.1	3087.6	3154.9	3176.9	3114.2	2990.5	2810.3	2631.7
30°	2302.8	2429.6	2589.4	2675.6	2741.4	2866.7	3029.6	3050.0	2992.0	2847.9	2628.6
32.5°	1807.7	1923.7	2052.1	2153.9	2241.7	2498.6	2717.9	2876.1	2904.3	2829.1	2636.4
35°	1456.8	1507.0	1629.2	1726.3	1845.3	2064.7	2323.1	2578.5	2750.8	2760.2	2612.9
37.5°	1201.5	1228.1	1334.7	1389.5	1460.0	1652.7	1893.9	2227.6	2495.4	2622.3	2547.1
40°	994.7	1055.8	1116.9	1148.2	1198.4	1331.5	1563.4	1825.0	2157.1	2392.1	2445.3
42.5°	863.1	889.8	928.9	972.8	1004.1	1120.1	1275.1	1514.8	1814.0	2141.4	2288.7
45°	761.3	770.7	811.4	839.6	872.5	954.0	1063.7	1264.2	1527.3	1850.0	2100.7
47.5°	676.7	695.5	717.5	734.7	756.6	819.3	913.3	1059.0	1290.8	1579.0	1848.5
50°	601.5	612.5	640.7	648.5	664.2	708.1	780.1	891.3	1082.5	1312.7	1591.6
52.5°	531.0	551.4	562.4	573.3	587.4	623.5	670.5	761.3	905.4	1121.6	1358.2
55°	476.2	482.5	498.1	507.5	518.5	543.6	584.3	651.7	764.5	936.8	1160.8
57.5°	423.0	423.0	438.6	446.5	457.4	476.2	512.2	563.9	645.4	773.9	979.1
60°	366.6	368.1	380.7	390.1	393.2	412.0	441.8	482.5	545.1	639.1	806.8
62.5°	316.4	324.3	330.5	333.7	344.6	355.6	380.7	408.9	452.7	535.7	654.8
65°	274.1	275.7	280.4	283.5	288.2	300.8	319.6	338.4	376.0	437.1	534.2
67.5°	225.6	231.8	238.1	238.1	242.8	249.1	267.9	283.5	311.7	347.8	413.6
70°	169.2	172.3	181.7	186.4	192.7	203.6	213.0	222.4	244.4	271.0	321.1
72.5°	141.0	141.0	144.1	145.7	145.7	153.5	167.6	177.0	188.0	206.8	241.2
75°	112.8	112.8	117.5	115.9	119.1	122.2	123.8	130.0	136.3	150.4	170.7
77.5°	89.3	90.9	90.9	92.4	92.4	94.0	95.6	98.7	101.8	109.7	119.1
80°	65.8	67.4	67.4	68.9	68.9	70.5	72.1	73.6	76.8	79.9	84.6
82.5°	45.4	47.0	47.0	48.6	47.0	48.6	50.1	50.1	51.7	54.8	56.4
85°	26.6	26.6	28.2	26.6	26.6	26.6	28.2	28.2	29.8	34.5	34.5
87.5°	7.8	9.4	7.8	9.4	9.4	9.4	9.4	11.0	11.0	12.5	14.1
90°	33.6	33.1	32.6	32.3	31.8	30.8	29.7	28.7	27.7	24.4	21.0
92.5°	50.6	51.1	51.6	51.9	51.5	50.8	50.0	49.3	48.5	47.0	45.4
95°	90.0	90.0	90.0	90.0	89.5	88.5	87.4	86.4	85.4	83.4	81.3
97.5°	129.8	130.0	130.3	130.4	129.8	128.5	127.2	126.0	124.7	123.1	121.6
100°	174.5	174.0	173.5	173.2	172.8	172.0	171.3	170.5	169.7	168.4	167.1
102.5°	223.3	223.6	223.9	224.0	223.6	222.8	222.1	221.3	220.5	218.7	216.9
105°	273.7	273.2	272.7	272.4	272.4	272.4	272.4	272.4	272.4	270.1	267.8
107.5°	328.4	328.6	328.9	329.0	328.6	327.8	327.1	326.3	325.5	324.5	323.5
110°	383.1	383.6	384.1	384.4	383.9	382.9	381.8	380.8	379.8	379.3	378.8

TEST NUMBER: P1012309

CATALOG NUMBER: S123RDIP-B1165D1195UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	439.8	439.8	439.8	439.8	439.2	437.9	436.6	435.4	434.1	434.1	434.1
115°	492.3	492.5	492.8	492.9	492.8	492.5	492.3	492.0	491.8	492.3	492.8
117.5°	546.4	547.2	547.9	548.3	548.3	548.3	548.3	548.3	548.3	548.8	549.4
120°	602.5	603.0	603.5	603.8	603.9	604.2	604.4	604.7	604.9	606.2	607.5
122.5°	657.3	658.0	658.8	659.2	659.6	660.3	661.1	661.8	662.6	663.1	663.6
125°	712.0	713.1	714.1	714.6	715.1	716.1	717.2	718.2	719.2	719.7	720.2
127.5°	766.2	767.3	768.3	768.8	769.6	771.1	772.7	774.2	775.8	776.3	776.8
130°	820.9	822.7	824.5	825.4	825.9	826.9	828.0	829.0	830.0	830.8	831.6
132.5°	875.3	876.6	877.9	878.5	879.1	880.4	881.7	883.0	884.3	884.8	885.3
135°	931.5	932.0	932.5	932.8	933.3	934.3	935.4	936.4	937.4	937.6	937.9
137.5°	982.8	983.5	984.3	984.7	985.3	986.6	987.9	989.2	990.5	989.7	988.9
140°	1034.5	1036.3	1038.1	1039.0	1039.1	1039.4	1039.6	1039.9	1040.1	1039.9	1039.6
142.5°	1084.3	1085.6	1086.9	1087.5	1087.6	1087.9	1088.1	1088.4	1088.6	1088.1	1087.6
145°	1132.2	1133.3	1134.3	1134.8	1134.9	1135.2	1135.4	1135.7	1135.9	1135.1	1134.4
147.5°	1177.1	1178.7	1180.2	1181.0	1181.0	1181.0	1181.0	1181.0	1181.0	1180.2	1179.4
150°	1218.7	1220.2	1221.7	1222.5	1222.5	1222.5	1222.5	1222.5	1222.5	1222.0	1221.5
152.5°	1258.6	1259.9	1261.2	1261.8	1261.5	1261.0	1260.5	1260.0	1259.5	1259.2	1259.0
155°	1295.4	1297.2	1299.0	1299.9	1299.4	1298.3	1297.3	1296.2	1295.2	1295.0	1294.7
157.5°	1328.4	1329.9	1331.4	1332.2	1331.7	1330.7	1329.6	1328.6	1327.6	1327.3	1327.1
160°	1359.6	1360.7	1361.7	1362.2	1361.6	1360.3	1359.0	1357.7	1356.4	1356.4	1356.4
162.5°	1385.4	1387.2	1389.0	1389.9	1389.3	1388.0	1386.7	1385.4	1384.1	1383.9	1383.6
165°	1408.5	1410.3	1412.1	1413.0	1412.2	1410.7	1409.2	1407.6	1406.1	1406.1	1406.1
167.5°	1428.8	1430.3	1431.8	1432.6	1431.8	1430.3	1428.8	1427.2	1425.7	1425.4	1425.2
170°	1444.3	1446.1	1447.9	1448.8	1447.9	1446.1	1444.3	1442.5	1440.7	1440.7	1440.7
172.5°	1455.8	1457.6	1459.4	1460.3	1459.5	1458.0	1456.5	1454.9	1453.4	1453.4	1453.4
175°	1463.9	1465.7	1467.5	1468.4	1467.6	1466.1	1464.6	1463.0	1461.5	1461.5	1461.5
177.5°	1468.5	1470.3	1472.1	1473.0	1472.2	1470.7	1469.2	1467.6	1466.1	1466.1	1466.1
180°	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6

TEST NUMBER: P1012309

CATALOG NUMBER: S123RDIP-B1165D1195UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7
2.5°	1893.9	1886.1	1878.2	1878.2	1861.0	1845.3	1837.5	1840.6	1831.2	1818.7	1806.2
5°	1976.9	1945.6	1939.3	1922.1	1898.6	1865.7	1848.5	1832.8	1814.0	1788.9	1765.5
7.5°	2053.7	2013.0	1991.0	1973.8	1928.4	1882.9	1845.3	1820.3	1787.4	1749.8	1721.6
10°	2153.9	2078.8	2055.3	2016.1	1951.9	1887.6	1843.8	1803.0	1757.6	1713.8	1676.2
12.5°	2233.8	2147.7	2103.8	2064.7	1981.6	1900.2	1826.5	1776.4	1721.6	1673.0	1624.5
15°	2324.7	2227.6	2150.8	2103.8	1998.9	1900.2	1817.1	1746.7	1685.6	1626.0	1583.7
17.5°	2368.6	2246.4	2211.9	2144.5	1992.6	1893.9	1792.1	1716.9	1643.3	1574.3	1524.2
20°	2437.5	2294.9	2208.8	2163.3	2028.6	1882.9	1763.9	1677.7	1601.0	1527.3	1474.1
22.5°	2442.2	2287.1	2230.7	2144.5	1978.5	1850.0	1738.8	1633.9	1544.6	1475.6	1420.8
25°	2431.2	2273.0	2194.7	2125.7	1987.9	1831.2	1688.7	1585.3	1497.6	1417.7	1353.5
27.5°	2426.5	2232.3	2158.6	2089.7	1934.6	1776.4	1658.9	1541.4	1441.2	1370.7	1304.9
30°	2420.3	2188.4	2099.1	2019.2	1876.7	1734.1	1593.1	1491.3	1395.8	1306.5	1240.7
32.5°	2379.5	2128.9	2038.0	1953.4	1799.9	1657.4	1546.1	1438.1	1334.7	1251.6	1192.1
35°	2367.0	2074.1	1955.0	1864.1	1713.8	1586.9	1469.4	1380.1	1283.0	1199.9	1129.5
37.5°	2331.0	2017.7	1889.2	1773.3	1616.6	1496.0	1409.9	1320.6	1226.6	1137.3	1080.9
40°	2268.3	1951.9	1806.2	1687.1	1525.8	1403.6	1323.7	1257.9	1165.5	1085.6	1016.7
42.5°	2175.9	1884.5	1727.9	1602.5	1424.0	1309.6	1243.8	1181.1	1102.8	1019.8	963.4
45°	2069.4	1795.2	1649.5	1510.1	1328.4	1217.2	1148.2	1110.7	1038.6	968.1	902.3
47.5°	1923.7	1702.8	1558.7	1414.6	1229.7	1121.6	1066.8	1029.2	979.1	902.3	849.0
50°	1740.4	1583.7	1447.5	1319.0	1132.6	1029.2	974.4	946.2	903.9	849.0	797.4
52.5°	1536.7	1445.9	1333.1	1214.0	1033.9	936.8	886.6	864.7	833.4	781.7	737.8
55°	1331.5	1292.4	1215.6	1098.1	930.5	850.6	806.8	778.6	755.1	717.5	679.9
57.5°	1148.2	1129.5	1076.2	985.3	844.3	761.3	723.7	704.9	686.1	657.9	620.3
60°	958.7	979.1	924.2	878.8	750.4	678.3	645.4	625.0	615.6	590.6	567.1
62.5°	794.2	813.0	781.7	747.2	656.4	592.1	571.8	553.0	546.7	524.8	501.3
65°	645.4	668.9	645.4	626.6	571.8	518.5	493.4	484.1	477.8	463.7	444.9
67.5°	513.8	537.3	526.3	502.8	485.6	441.8	427.7	418.3	415.1	404.2	388.5
70°	386.9	419.8	423.0	408.9	393.2	372.8	363.4	360.3	352.5	343.1	333.7
72.5°	278.8	316.4	318.0	318.0	308.6	308.6	299.2	294.5	294.5	285.1	274.1
75°	205.2	230.3	233.4	236.5	241.2	245.9	239.7	239.7	238.1	228.7	224.0
77.5°	136.3	158.2	166.0	177.0	183.3	183.3	186.4	189.5	186.4	181.7	178.6
80°	87.7	103.4	112.8	119.1	128.5	133.2	137.9	139.4	136.3	134.7	130.0
82.5°	58.0	62.7	67.4	75.2	86.2	94.0	94.0	92.4	95.6	94.0	92.4
85°	32.9	36.0	37.6	39.2	45.4	53.3	54.8	56.4	59.5	56.4	53.3
87.5°	12.5	14.1	14.1	14.1	17.2	18.8	23.5	29.8	28.2	25.1	25.1
90°	17.7	14.4	12.7	11.4	8.9	6.3	3.8	1.2	3.8	6.3	8.9
92.5°	43.9	42.4	41.6	40.8	39.3	37.7	36.2	34.6	36.2	37.7	39.3
95°	79.3	77.2	76.2	75.3	73.5	71.7	69.9	68.1	69.9	71.7	73.5
97.5°	120.0	118.5	117.7	117.1	115.8	114.5	113.3	112.0	113.3	114.5	115.8
100°	165.8	164.5	163.9	163.1	161.6	160.1	158.5	157.0	158.5	160.1	161.6
102.5°	215.1	213.3	212.4	212.0	211.2	210.5	209.7	208.9	209.7	210.5	211.2
105°	265.5	263.2	262.1	261.8	261.3	260.8	260.2	259.7	260.2	260.8	261.3
107.5°	322.4	321.4	320.9	320.8	320.5	320.3	320.0	319.8	320.0	320.3	320.5
110°	378.3	377.8	377.5	377.2	376.7	376.2	375.7	375.2	375.7	376.2	376.7

TEST NUMBER: P1012309

CATALOG NUMBER: S123RDIP-B1165D1195UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	434.1	434.1	434.1	434.0	433.7	433.4	433.2	432.9	433.2	433.4	433.7
115°	493.3	493.8	494.1	493.7	492.9	492.2	491.4	490.6	491.4	492.2	492.9
117.5°	549.9	550.4	550.7	550.6	550.3	550.0	549.8	549.5	549.8	550.0	550.3
120°	608.8	610.1	610.7	609.9	608.4	606.9	605.3	603.8	605.3	606.9	608.4
122.5°	664.1	664.6	664.9	664.4	663.4	662.3	661.3	660.3	661.3	662.3	663.4
125°	720.7	721.2	721.5	721.1	720.3	719.6	718.8	718.0	718.8	719.6	720.3
127.5°	777.3	777.8	778.1	777.3	775.8	774.2	772.7	771.1	772.7	774.2	775.8
130°	832.3	833.1	833.5	832.5	830.4	828.3	826.3	824.2	826.3	828.3	830.4
132.5°	885.8	886.3	886.6	885.6	883.5	881.5	879.4	877.4	879.4	881.5	883.5
135°	938.1	938.4	938.5	937.7	936.2	934.7	933.1	931.6	933.1	934.7	936.2
137.5°	988.2	987.4	987.0	986.4	985.1	983.8	982.5	981.2	982.5	983.8	985.1
140°	1039.4	1039.1	1039.0	1038.4	1037.1	1035.8	1034.5	1033.2	1034.5	1035.8	1037.1
142.5°	1087.1	1086.6	1086.3	1085.7	1084.4	1083.1	1081.8	1080.5	1081.8	1083.1	1084.4
145°	1133.6	1132.9	1132.5	1132.2	1131.7	1131.2	1130.7	1130.2	1130.7	1131.2	1131.7
147.5°	1178.7	1177.9	1177.5	1177.0	1176.0	1174.9	1173.9	1172.9	1173.9	1174.9	1176.0
150°	1221.0	1220.5	1220.2	1219.9	1219.4	1218.9	1218.4	1217.9	1218.4	1218.9	1219.4
152.5°	1258.7	1258.4	1258.3	1257.9	1257.1	1256.4	1255.6	1254.8	1255.6	1256.4	1257.1
155°	1294.5	1294.2	1294.1	1294.1	1294.1	1294.1	1294.1	1294.1	1294.1	1294.1	1294.1
157.5°	1326.8	1326.5	1326.4	1326.5	1326.8	1327.1	1327.3	1327.6	1327.3	1327.1	1326.8
160°	1356.4	1356.4	1356.4	1356.7	1357.2	1357.7	1358.2	1358.7	1358.2	1357.7	1357.2
162.5°	1383.4	1383.1	1383.0	1383.4	1384.1	1384.9	1385.6	1386.4	1385.6	1384.9	1384.1
165°	1406.1	1406.1	1406.1	1406.5	1407.2	1408.0	1408.7	1409.5	1408.7	1408.0	1407.2
167.5°	1424.9	1424.6	1424.5	1425.0	1426.1	1427.1	1428.2	1429.2	1428.2	1427.1	1426.1
170°	1440.7	1440.7	1440.7	1441.2	1442.2	1443.3	1444.3	1445.3	1444.3	1443.3	1442.2
172.5°	1453.4	1453.4	1453.4	1453.9	1454.9	1456.0	1457.0	1458.0	1457.0	1456.0	1454.9
175°	1461.5	1461.5	1461.5	1462.0	1463.0	1464.1	1465.1	1466.1	1465.1	1464.1	1463.0
177.5°	1466.1	1466.1	1466.1	1466.6	1467.6	1468.7	1469.7	1470.7	1469.7	1468.7	1467.6
180°	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6

TEST NUMBER: P1012309

CATALOG NUMBER: S123RDIP-B1165D1195UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7
2.5°	1806.2	1798.3	1795.2	1787.4	1768.6	1756.1	1742.0	1732.6	1734.1	1726.3	1731.0
5°	1749.8	1748.2	1737.3	1721.6	1695.0	1680.9	1655.8	1643.3	1637.0	1638.6	1629.2
7.5°	1702.8	1688.7	1680.9	1655.8	1630.7	1601.0	1580.6	1569.6	1560.2	1550.8	1544.6
10°	1649.5	1637.0	1624.5	1597.8	1563.4	1535.2	1507.0	1496.0	1481.9	1475.6	1470.9
12.5°	1593.1	1585.3	1569.6	1538.3	1499.1	1472.5	1439.6	1433.4	1414.6	1402.0	1398.9
15°	1541.4	1536.7	1508.5	1472.5	1433.4	1406.7	1378.5	1359.7	1328.4	1334.7	1323.7
17.5°	1486.6	1466.2	1449.0	1400.5	1381.7	1340.9	1308.0	1298.6	1276.7	1262.6	1248.5
20°	1425.5	1413.0	1391.1	1359.7	1314.3	1267.3	1242.2	1226.6	1214.0	1192.1	1185.8
22.5°	1367.6	1351.9	1333.1	1292.4	1253.2	1214.0	1179.6	1165.5	1149.8	1134.1	1124.8
25°	1322.1	1298.6	1278.3	1228.1	1189.0	1156.1	1134.1	1110.7	1088.7	1079.3	1076.2
27.5°	1251.6	1237.5	1217.2	1170.2	1134.1	1098.1	1077.8	1062.1	1038.6	1027.6	1018.2
30°	1206.2	1178.0	1154.5	1116.9	1080.9	1041.7	1022.9	1004.1	990.0	975.9	965.0
32.5°	1145.1	1123.2	1104.4	1066.8	1030.8	994.7	974.4	946.2	938.3	927.4	914.8
35°	1085.6	1071.5	1051.1	1010.4	971.2	946.2	924.2	897.6	888.2	880.4	869.4
37.5°	1029.2	1008.8	994.7	955.6	921.1	891.3	874.1	852.2	845.9	836.5	828.7
40°	980.6	960.3	946.2	907.0	871.0	839.6	828.7	806.8	797.4	786.4	781.7
42.5°	925.8	908.6	889.8	861.6	824.0	792.7	770.7	758.2	745.7	741.0	731.6
45°	867.8	852.2	838.1	806.8	767.6	745.7	726.9	709.6	700.2	692.4	686.1
47.5°	817.7	803.6	784.8	750.4	719.0	698.7	679.9	662.6	653.2	643.8	636.0
50°	759.8	751.9	731.6	698.7	668.9	645.4	628.2	612.5	606.2	595.3	582.7
52.5°	708.1	694.0	676.7	650.1	623.5	595.3	571.8	562.4	551.4	545.1	534.2
55°	647.0	637.6	618.8	595.3	567.1	543.6	526.3	513.8	499.7	493.4	479.4
57.5°	595.3	578.0	568.6	538.9	512.2	488.7	476.2	463.7	448.0	438.6	432.4
60°	538.9	523.2	509.1	484.1	465.3	440.2	421.4	410.4	399.5	386.9	380.7
62.5°	484.1	471.5	454.3	433.9	410.4	390.1	376.0	360.3	354.0	341.5	336.8
65°	424.5	415.1	401.0	377.5	358.7	341.5	327.4	314.9	308.6	303.9	300.8
67.5°	371.3	358.7	349.3	329.0	308.6	294.5	286.7	278.8	271.0	266.3	261.6
70°	316.4	307.0	297.6	278.8	264.7	252.2	245.9	239.7	235.0	230.3	225.6
72.5°	260.0	255.3	245.9	233.4	222.4	213.0	208.3	200.5	195.8	188.0	184.8
75°	214.6	206.8	202.1	191.1	181.7	173.9	167.6	158.2	152.0	148.8	147.3
77.5°	169.2	166.0	159.8	150.4	145.7	137.9	128.5	125.3	122.2	122.2	120.6
80°	126.9	122.2	117.5	109.7	105.0	98.7	98.7	98.7	97.1	98.7	97.1
82.5°	86.2	83.0	79.9	75.2	73.6	73.6	75.2	75.2	75.2	75.2	75.2
85°	50.1	50.1	50.1	51.7	50.1	50.1	51.7	53.3	51.7	51.7	50.1
87.5°	23.5	23.5	25.1	25.1	26.6	26.6	26.6	26.6	26.6	26.6	28.2
90°	11.4	12.7	14.4	17.7	21.0	24.4	27.7	28.7	29.7	30.8	31.8
92.5°	40.8	41.6	42.4	43.9	45.4	47.0	48.5	49.3	50.0	50.8	51.5
95°	75.3	76.2	77.2	79.3	81.3	83.4	85.4	86.4	87.4	88.5	89.5
97.5°	117.1	117.7	118.5	120.0	121.6	123.1	124.7	126.0	127.2	128.5	129.8
100°	163.1	163.9	164.5	165.8	167.1	168.4	169.7	170.5	171.3	172.0	172.8
102.5°	212.0	212.4	213.3	215.1	216.9	218.7	220.5	221.3	222.1	222.8	223.6
105°	261.8	262.1	263.2	265.5	267.8	270.1	272.4	272.4	272.4	272.4	272.4
107.5°	320.8	320.9	321.4	322.4	323.5	324.5	325.5	326.3	327.1	327.8	328.6
110°	377.2	377.5	377.8	378.3	378.8	379.3	379.8	380.8	381.8	382.9	383.9

TEST NUMBER: P1012309

CATALOG NUMBER: S123RDIP-B1165D1195UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	434.0	434.1	434.1	434.1	434.1	434.1	434.1	435.4	436.6	437.9	439.2
115°	493.7	494.1	493.8	493.3	492.8	492.3	491.8	492.0	492.3	492.5	492.8
117.5°	550.6	550.7	550.4	549.9	549.4	548.8	548.3	548.3	548.3	548.3	548.3
120°	609.9	610.7	610.1	608.8	607.5	606.2	604.9	604.7	604.4	604.2	603.9
122.5°	664.4	664.9	664.6	664.1	663.6	663.1	662.6	661.8	661.1	660.3	659.6
125°	721.1	721.5	721.2	720.7	720.2	719.7	719.2	718.2	717.2	716.1	715.1
127.5°	777.3	778.1	777.8	777.3	776.8	776.3	775.8	774.2	772.7	771.1	769.6
130°	832.5	833.5	833.1	832.3	831.6	830.8	830.0	829.0	828.0	826.9	825.9
132.5°	885.6	886.6	886.3	885.8	885.3	884.8	884.3	883.0	881.7	880.4	879.1
135°	937.7	938.5	938.4	938.1	937.9	937.6	937.4	936.4	935.4	934.3	933.3
137.5°	986.4	987.0	987.4	988.2	988.9	989.7	990.5	989.2	987.9	986.6	985.3
140°	1038.4	1039.0	1039.1	1039.4	1039.6	1039.9	1040.1	1039.9	1039.6	1039.4	1039.1
142.5°	1085.7	1086.3	1086.6	1087.1	1087.6	1088.1	1088.6	1088.4	1088.1	1087.9	1087.6
145°	1132.2	1132.5	1132.9	1133.6	1134.4	1135.1	1135.9	1135.7	1135.4	1135.2	1134.9
147.5°	1177.0	1177.5	1177.9	1178.7	1179.4	1180.2	1181.0	1181.0	1181.0	1181.0	1181.0
150°	1219.9	1220.2	1220.5	1221.0	1221.5	1222.0	1222.5	1222.5	1222.5	1222.5	1222.5
152.5°	1257.9	1258.3	1258.4	1258.7	1259.0	1259.2	1259.5	1260.0	1260.5	1261.0	1261.5
155°	1294.1	1294.1	1294.2	1294.5	1294.7	1295.0	1295.2	1296.2	1297.3	1298.3	1299.4
157.5°	1326.5	1326.4	1326.5	1326.8	1327.1	1327.3	1327.6	1328.6	1329.6	1330.7	1331.7
160°	1356.7	1356.4	1356.4	1356.4	1356.4	1356.4	1356.4	1357.7	1359.0	1360.3	1361.6
162.5°	1383.4	1383.0	1383.1	1383.4	1383.6	1383.9	1384.1	1385.4	1386.7	1388.0	1389.3
165°	1406.5	1406.1	1406.1	1406.1	1406.1	1406.1	1406.1	1407.6	1409.2	1410.7	1412.2
167.5°	1425.0	1424.5	1424.6	1424.9	1425.2	1425.4	1425.7	1427.2	1428.8	1430.3	1431.8
170°	1441.2	1440.7	1440.7	1440.7	1440.7	1440.7	1440.7	1442.5	1444.3	1446.1	1447.9
172.5°	1453.9	1453.4	1453.4	1453.4	1453.4	1453.4	1453.4	1454.9	1456.5	1458.0	1459.5
175°	1462.0	1461.5	1461.5	1461.5	1461.5	1461.5	1461.5	1463.0	1464.6	1466.1	1467.6
177.5°	1466.6	1466.1	1466.1	1466.1	1466.1	1466.1	1466.1	1467.6	1469.2	1470.7	1472.2
180°	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6

TEST NUMBER: P1012309

CATALOG NUMBER: S123RDIP-B1165D1195UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7
2.5°	1729.4	1731.0	1726.3	1716.9	1715.3	1718.5	1727.9	1724.7	1716.9	1731.0	1718.5
5°	1633.9	1626.0	1622.9	1626.0	1616.6	1611.9	1621.3	1616.6	1621.3	1622.9	1627.6
7.5°	1541.4	1543.0	1533.6	1535.2	1522.6	1525.8	1525.8	1525.8	1530.5	1533.6	1539.9
10°	1461.5	1464.7	1453.7	1455.3	1445.9	1439.6	1444.3	1453.7	1453.7	1453.7	1456.8
12.5°	1397.3	1383.2	1375.4	1373.8	1362.9	1359.7	1369.1	1372.3	1380.1	1380.1	1384.8
15°	1317.4	1314.3	1308.0	1308.0	1281.4	1287.7	1290.8	1301.8	1317.4	1304.9	1308.0
17.5°	1245.4	1237.5	1229.7	1226.6	1223.4	1214.0	1226.6	1225.0	1234.4	1236.0	1240.7
20°	1181.1	1174.9	1159.2	1160.8	1163.9	1149.8	1157.6	1157.6	1167.0	1176.4	1187.4
22.5°	1118.5	1112.2	1104.4	1107.5	1098.1	1095.0	1095.0	1102.8	1113.8	1121.6	1120.1
25°	1069.9	1059.0	1054.3	1049.6	1044.9	1048.0	1043.3	1051.1	1059.0	1063.7	1059.0
27.5°	1015.1	1010.4	1001.0	996.3	988.5	991.6	994.7	1001.0	1005.7	1005.7	1010.4
30°	961.8	955.6	952.4	947.7	947.7	941.5	943.0	949.3	954.0	958.7	965.0
32.5°	910.1	905.4	900.7	900.7	897.6	896.0	894.5	903.9	903.9	913.3	913.3
35°	867.8	860.0	860.0	852.2	855.3	853.7	850.6	856.9	858.4	864.7	863.1
37.5°	820.8	820.8	817.7	809.9	803.6	805.2	813.0	813.0	817.7	816.1	820.8
40°	773.9	770.7	770.7	766.0	764.5	762.9	764.5	766.0	773.9	772.3	773.9
42.5°	726.9	728.4	720.6	720.6	720.6	715.9	717.5	719.0	722.2	725.3	730.0
45°	681.4	678.3	676.7	673.6	670.5	672.0	670.5	676.7	675.2	678.3	683.0
47.5°	632.9	628.2	626.6	620.3	620.3	623.5	621.9	626.6	628.2	632.9	629.7
50°	585.9	579.6	574.9	576.5	567.1	570.2	570.2	574.9	579.6	581.2	584.3
52.5°	531.0	529.5	527.9	520.1	518.5	516.9	518.5	520.1	526.3	531.0	532.6
55°	477.8	476.2	466.8	463.7	459.0	459.0	462.1	463.7	474.7	476.2	482.5
57.5°	429.2	424.5	413.6	412.0	412.0	412.0	407.3	413.6	416.7	424.5	424.5
60°	376.0	376.0	366.6	366.6	368.1	366.6	366.6	368.1	368.1	374.4	377.5
62.5°	333.7	332.1	332.1	329.0	327.4	329.0	327.4	327.4	329.0	333.7	338.4
65°	296.1	294.5	292.9	291.4	288.2	288.2	289.8	292.9	292.9	296.1	297.6
67.5°	260.0	260.0	256.9	256.9	255.3	253.8	255.3	253.8	260.0	260.0	261.6
70°	224.0	222.4	217.7	216.2	211.5	213.0	213.0	217.7	219.3	222.4	225.6
72.5°	180.1	180.1	177.0	173.9	175.4	172.3	172.3	173.9	173.9	178.6	180.1
75°	148.8	145.7	144.1	145.7	144.1	147.3	144.1	144.1	147.3	147.3	147.3
77.5°	122.2	122.2	120.6	120.6	122.2	120.6	122.2	122.2	122.2	120.6	122.2
80°	100.3	98.7	98.7	98.7	97.1	97.1	97.1	97.1	97.1	97.1	97.1
82.5°	75.2	75.2	73.6	75.2	75.2	73.6	75.2	73.6	73.6	75.2	75.2
85°	50.1	53.3	50.1	50.1	51.7	51.7	53.3	51.7	53.3	50.1	51.7
87.5°	26.6	28.2	28.2	26.6	26.6	28.2	28.2	28.2	29.8	26.6	28.2
90°	32.3	32.6	33.1	33.6	34.1	34.6	34.1	33.6	33.1	32.6	32.3
92.5°	51.9	51.6	51.1	50.6	50.1	49.6	50.1	50.6	51.1	51.6	51.9
95°	90.0	90.0	90.0	90.0	90.0	90.0	90.0	90.0	90.0	90.0	90.0
97.5°	130.4	130.3	130.0	129.8	129.5	129.3	129.5	129.8	130.0	130.3	130.4
100°	173.2	173.5	174.0	174.5	175.0	175.5	175.0	174.5	174.0	173.5	173.2
102.5°	224.0	223.9	223.6	223.3	223.1	222.8	223.1	223.3	223.6	223.9	224.0
105°	272.4	272.7	273.2	273.7	274.2	274.7	274.2	273.7	273.2	272.7	272.4
107.5°	329.0	328.9	328.6	328.4	328.1	327.9	328.1	328.4	328.6	328.9	329.0
110°	384.4	384.1	383.6	383.1	382.6	382.1	382.6	383.1	383.6	384.1	384.4

TEST NUMBER: P1012309

CATALOG NUMBER: S123RDIP-B1165D1195UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	439.8	439.8	439.8	439.8	439.8	439.8	439.8	439.8	439.8	439.8	439.8
115°	492.9	492.8	492.5	492.3	492.0	491.8	492.0	492.3	492.5	492.8	492.9
117.5°	548.3	547.9	547.2	546.4	545.7	544.9	545.7	546.4	547.2	547.9	548.3
120°	603.8	603.5	603.0	602.5	601.9	601.4	601.9	602.5	603.0	603.5	603.8
122.5°	659.2	658.8	658.0	657.3	656.5	655.7	656.5	657.3	658.0	658.8	659.2
125°	714.6	714.1	713.1	712.0	711.0	710.0	711.0	712.0	713.1	714.1	714.6
127.5°	768.8	768.3	767.3	766.2	765.2	764.2	765.2	766.2	767.3	768.3	768.8
130°	825.4	824.5	822.7	820.9	819.1	817.3	819.1	820.9	822.7	824.5	825.4
132.5°	878.5	877.9	876.6	875.3	874.0	872.7	874.0	875.3	876.6	877.9	878.5
135°	932.8	932.5	932.0	931.5	931.0	930.5	931.0	931.5	932.0	932.5	932.8
137.5°	984.7	984.3	983.5	982.8	982.0	981.2	982.0	982.8	983.5	984.3	984.7
140°	1039.0	1038.1	1036.3	1034.5	1032.7	1030.9	1032.7	1034.5	1036.3	1038.1	1039.0
142.5°	1087.5	1086.9	1085.6	1084.3	1083.0	1081.7	1083.0	1084.3	1085.6	1086.9	1087.5
145°	1134.8	1134.3	1133.3	1132.2	1131.2	1130.2	1131.2	1132.2	1133.3	1134.3	1134.8
147.5°	1181.0	1180.2	1178.7	1177.1	1175.6	1174.0	1175.6	1177.1	1178.7	1180.2	1181.0
150°	1222.5	1221.7	1220.2	1218.7	1217.1	1215.6	1217.1	1218.7	1220.2	1221.7	1222.5
152.5°	1261.8	1261.2	1259.9	1258.6	1257.3	1256.0	1257.3	1258.6	1259.9	1261.2	1261.8
155°	1299.9	1299.0	1297.2	1295.4	1293.6	1291.8	1293.6	1295.4	1297.2	1299.0	1299.9
157.5°	1332.2	1331.4	1329.9	1328.4	1326.8	1325.3	1326.8	1328.4	1329.9	1331.4	1332.2
160°	1362.2	1361.7	1360.7	1359.6	1358.6	1357.6	1358.6	1359.6	1360.7	1361.7	1362.2
162.5°	1389.9	1389.0	1387.2	1385.4	1383.6	1381.8	1383.6	1385.4	1387.2	1389.0	1389.9
165°	1413.0	1412.1	1410.3	1408.5	1406.7	1404.9	1406.7	1408.5	1410.3	1412.1	1413.0
167.5°	1432.6	1431.8	1430.3	1428.8	1427.2	1425.7	1427.2	1428.8	1430.3	1431.8	1432.6
170°	1448.8	1447.9	1446.1	1444.3	1442.5	1440.7	1442.5	1444.3	1446.1	1447.9	1448.8
172.5°	1460.3	1459.4	1457.6	1455.8	1454.0	1452.2	1454.0	1455.8	1457.6	1459.4	1460.3
175°	1468.4	1467.5	1465.7	1463.9	1462.1	1460.3	1462.1	1463.9	1465.7	1467.5	1468.4
177.5°	1473.0	1472.1	1470.3	1468.5	1466.7	1464.9	1466.7	1468.5	1470.3	1472.1	1473.0
180°	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6

TEST NUMBER: P1012309

CATALOG NUMBER: S123RDIP-B1165D1195UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7	1829.7
2.5°	1731.0	1737.3	1731.0	1718.5	1731.0	1738.8	1746.7	1759.2	1765.5	1765.5	1774.9
5°	1632.3	1644.8	1640.1	1637.0	1649.5	1657.4	1669.9	1685.6	1702.8	1713.8	1726.3
7.5°	1544.6	1552.4	1560.2	1560.2	1572.8	1590.0	1608.8	1627.6	1649.5	1665.2	1674.6
10°	1467.8	1474.1	1478.8	1485.0	1503.8	1522.6	1547.7	1571.2	1590.0	1607.2	1622.9
12.5°	1394.2	1403.6	1414.6	1419.3	1433.4	1456.8	1480.3	1508.5	1538.3	1555.5	1571.2
15°	1323.7	1328.4	1340.9	1355.0	1367.6	1392.6	1422.4	1452.2	1477.2	1503.8	1517.9
17.5°	1251.6	1253.2	1286.1	1278.3	1319.0	1342.5	1358.2	1386.4	1427.1	1449.0	1470.9
20°	1181.1	1196.8	1210.9	1218.7	1240.7	1267.3	1312.7	1334.7	1367.6	1387.9	1406.7
22.5°	1126.3	1149.8	1149.8	1168.6	1179.6	1204.6	1237.5	1279.8	1315.9	1330.0	1356.6
25°	1077.8	1088.7	1107.5	1113.8	1134.1	1156.1	1178.0	1223.4	1262.6	1281.4	1300.2
27.5°	1015.1	1029.2	1054.3	1054.3	1080.9	1104.4	1131.0	1160.8	1199.9	1226.6	1246.9
30°	966.5	980.6	991.6	1008.8	1019.8	1041.7	1088.7	1110.7	1145.1	1168.6	1193.7
32.5°	921.1	932.1	941.5	960.3	972.8	997.9	1022.9	1062.1	1091.9	1113.8	1140.4
35°	871.0	881.9	894.5	908.6	927.4	950.9	974.4	1007.3	1037.0	1057.4	1079.3
37.5°	824.0	831.8	850.6	860.0	875.7	897.6	927.4	961.8	988.5	1004.1	1026.1
40°	778.6	784.8	798.9	816.1	827.1	844.3	875.7	905.4	938.3	957.1	974.4
42.5°	730.0	737.8	750.4	767.6	784.8	803.6	820.8	855.3	885.1	900.7	919.5
45°	687.7	692.4	701.8	719.0	736.3	750.4	777.0	808.3	836.5	849.0	869.4
47.5°	637.6	642.3	656.4	664.2	683.0	701.8	728.4	759.8	784.8	797.4	816.1
50°	585.9	590.6	600.0	617.2	629.7	650.1	673.6	700.2	731.6	748.8	759.8
52.5°	535.7	545.1	553.0	567.1	582.7	603.1	625.0	650.1	676.7	694.0	706.5
55°	485.6	493.4	502.8	510.7	529.5	548.3	573.3	596.8	620.3	636.0	650.1
57.5°	429.2	440.2	449.6	465.3	479.4	495.0	523.2	542.0	570.2	581.2	593.7
60°	380.7	391.6	399.5	412.0	424.5	444.9	463.7	487.2	510.7	524.8	540.4
62.5°	339.9	344.6	349.3	361.9	374.4	393.2	412.0	435.5	460.6	468.4	480.9
65°	299.2	303.9	311.7	322.7	332.1	343.1	363.4	382.2	405.7	418.3	423.0
67.5°	264.7	269.4	271.0	278.8	286.7	299.2	310.2	329.0	350.9	358.7	368.1
70°	225.6	233.4	235.0	241.2	244.4	252.2	264.7	278.8	296.1	310.2	318.0
72.5°	180.1	191.1	194.2	203.6	208.3	216.2	225.6	236.5	247.5	253.8	260.0
75°	147.3	150.4	152.0	159.8	167.6	178.6	183.3	189.5	198.9	206.8	213.0
77.5°	122.2	123.8	125.3	125.3	126.9	133.2	142.6	150.4	156.7	159.8	164.5
80°	98.7	97.1	97.1	98.7	98.7	98.7	101.8	112.8	115.9	123.8	122.2
82.5°	76.8	73.6	75.2	73.6	73.6	73.6	73.6	75.2	75.2	79.9	83.0
85°	50.1	51.7	50.1	50.1	48.6	50.1	48.6	48.6	47.0	47.0	45.4
87.5°	26.6	28.2	26.6	26.6	25.1	26.6	25.1	25.1	23.5	23.5	20.4
90°	31.8	30.8	29.7	28.7	27.7	24.4	21.0	17.7	14.4	12.7	11.4
92.5°	51.5	50.8	50.0	49.3	48.5	47.0	45.4	43.9	42.4	41.6	40.8
95°	89.5	88.5	87.4	86.4	85.4	83.4	81.3	79.3	77.2	76.2	75.3
97.5°	129.8	128.5	127.2	126.0	124.7	123.1	121.6	120.0	118.5	117.7	117.1
100°	172.8	172.0	171.3	170.5	169.7	168.4	167.1	165.8	164.5	163.9	163.1
102.5°	223.6	222.8	222.1	221.3	220.5	218.7	216.9	215.1	213.3	212.4	212.0
105°	272.4	272.4	272.4	272.4	272.4	270.1	267.8	265.5	263.2	262.1	261.8
107.5°	328.6	327.8	327.1	326.3	325.5	324.5	323.5	322.4	321.4	320.9	320.8
110°	383.9	382.9	381.8	380.8	379.8	379.3	378.8	378.3	377.8	377.5	377.2

TEST NUMBER: P1012309

CATALOG NUMBER: S123RDIP-B1165D1195UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	439.2	437.9	436.6	435.4	434.1	434.1	434.1	434.1	434.1	434.1	434.0
115°	492.8	492.5	492.3	492.0	491.8	492.3	492.8	493.3	493.8	494.1	493.7
117.5°	548.3	548.3	548.3	548.3	548.3	548.8	549.4	549.9	550.4	550.7	550.6
120°	603.9	604.2	604.4	604.7	604.9	606.2	607.5	608.8	610.1	610.7	609.9
122.5°	659.6	660.3	661.1	661.8	662.6	663.1	663.6	664.1	664.6	664.9	664.4
125°	715.1	716.1	717.2	718.2	719.2	719.7	720.2	720.7	721.2	721.5	721.1
127.5°	769.6	771.1	772.7	774.2	775.8	776.3	776.8	777.3	777.8	778.1	777.3
130°	825.9	826.9	828.0	829.0	830.0	830.8	831.6	832.3	833.1	833.5	832.5
132.5°	879.1	880.4	881.7	883.0	884.3	884.8	885.3	885.8	886.3	886.6	885.6
135°	933.3	934.3	935.4	936.4	937.4	937.6	937.9	938.1	938.4	938.5	937.7
137.5°	985.3	986.6	987.9	989.2	990.5	989.7	988.9	988.2	987.4	987.0	986.4
140°	1039.1	1039.4	1039.6	1039.9	1040.1	1039.9	1039.6	1039.4	1039.1	1039.0	1038.4
142.5°	1087.6	1087.9	1088.1	1088.4	1088.6	1088.1	1087.6	1087.1	1086.6	1086.3	1085.7
145°	1134.9	1135.2	1135.4	1135.7	1135.9	1135.1	1134.4	1133.6	1132.9	1132.5	1132.2
147.5°	1181.0	1181.0	1181.0	1181.0	1181.0	1180.2	1179.4	1178.7	1177.9	1177.5	1177.0
150°	1222.5	1222.5	1222.5	1222.5	1222.5	1222.0	1221.5	1221.0	1220.5	1220.2	1219.9
152.5°	1261.5	1261.0	1260.5	1260.0	1259.5	1259.2	1259.0	1258.7	1258.4	1258.3	1257.9
155°	1299.4	1298.3	1297.3	1296.2	1295.2	1295.0	1294.7	1294.5	1294.2	1294.1	1294.1
157.5°	1331.7	1330.7	1329.6	1328.6	1327.6	1327.3	1327.1	1326.8	1326.5	1326.4	1326.5
160°	1361.6	1360.3	1359.0	1357.7	1356.4	1356.4	1356.4	1356.4	1356.4	1356.4	1356.7
162.5°	1389.3	1388.0	1386.7	1385.4	1384.1	1383.9	1383.6	1383.4	1383.1	1383.0	1383.4
165°	1412.2	1410.7	1409.2	1407.6	1406.1	1406.1	1406.1	1406.1	1406.1	1406.1	1406.5
167.5°	1431.8	1430.3	1428.8	1427.2	1425.7	1425.4	1425.2	1424.9	1424.6	1424.5	1425.0
170°	1447.9	1446.1	1444.3	1442.5	1440.7	1440.7	1440.7	1440.7	1440.7	1440.7	1441.2
172.5°	1459.5	1458.0	1456.5	1454.9	1453.4	1453.4	1453.4	1453.4	1453.4	1453.4	1453.9
175°	1467.6	1466.1	1464.6	1463.0	1461.5	1461.5	1461.5	1461.5	1461.5	1461.5	1462.0
177.5°	1472.2	1470.7	1469.2	1467.6	1466.1	1466.1	1466.1	1466.1	1466.1	1466.1	1466.6
180°	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6	1469.6

TEST NUMBER: P1012309

CATALOG NUMBER: S123RDIP-B1165D1195UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1829.7	1829.7	1829.7	1829.7
2.5°	1782.7	1793.6	1815.6	1834.4
5°	1745.1	1762.3	1795.2	1828.1
7.5°	1699.7	1726.3	1768.6	1814.0
10°	1655.8	1690.3	1742.0	1795.2
12.5°	1611.9	1648.0	1702.8	1771.7
15°	1560.2	1597.8	1663.6	1746.7
17.5°	1514.8	1564.9	1624.5	1707.5
20°	1466.2	1503.8	1580.6	1668.3
22.5°	1405.2	1467.8	1539.9	1632.3
25°	1356.6	1411.4	1483.5	1588.4
27.5°	1297.1	1361.3	1449.0	1541.4
30°	1248.5	1301.8	1383.2	1494.4
32.5°	1192.1	1254.8	1339.4	1449.0
35°	1142.0	1195.2	1275.1	1386.4
37.5°	1082.5	1140.4	1229.7	1328.4
40°	1030.8	1087.2	1171.7	1264.2
42.5°	968.1	1027.6	1112.2	1190.5
45°	918.0	972.8	1040.2	1112.2
47.5°	856.9	914.8	980.6	1030.8
50°	802.1	855.3	907.0	949.3
52.5°	742.5	791.1	838.1	869.4
55°	687.7	725.3	762.9	784.8
57.5°	623.5	659.5	690.8	703.4
60°	567.1	596.8	617.2	631.3
62.5°	507.5	529.5	545.1	553.0
65°	449.6	465.3	473.1	480.9
67.5°	390.1	404.2	408.9	418.3
70°	327.4	343.1	346.2	350.9
72.5°	280.4	280.4	286.7	292.9
75°	224.0	227.1	230.3	230.3
77.5°	175.4	175.4	178.6	180.1
80°	128.5	130.0	130.0	128.5
82.5°	87.7	90.9	87.7	86.2
85°	48.6	54.8	51.7	51.7
87.5°	20.4	20.4	23.5	20.4
90°	8.9	6.3	3.8	1.2
92.5°	39.3	37.7	36.2	34.6
95°	73.5	71.7	69.9	68.1
97.5°	115.8	114.5	113.3	112.0
100°	161.6	160.1	158.5	157.0
102.5°	211.2	210.5	209.7	208.9
105°	261.3	260.8	260.2	259.7
107.5°	320.5	320.3	320.0	319.8
110°	376.7	376.2	375.7	375.2



TEST NUMBER: P1012309

CATALOG NUMBER: S123RDIP-B1165D1195UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	433.7	433.4	433.2	432.9
115°	492.9	492.2	491.4	490.6
117.5°	550.3	550.0	549.8	549.5
120°	608.4	606.9	605.3	603.8
122.5°	663.4	662.3	661.3	660.3
125°	720.3	719.6	718.8	718.0
127.5°	775.8	774.2	772.7	771.1
130°	830.4	828.3	826.3	824.2
132.5°	883.5	881.5	879.4	877.4
135°	936.2	934.7	933.1	931.6
137.5°	985.1	983.8	982.5	981.2
140°	1037.1	1035.8	1034.5	1033.2
142.5°	1084.4	1083.1	1081.8	1080.5
145°	1131.7	1131.2	1130.7	1130.2
147.5°	1176.0	1174.9	1173.9	1172.9
150°	1219.4	1218.9	1218.4	1217.9
152.5°	1257.1	1256.4	1255.6	1254.8
155°	1294.1	1294.1	1294.1	1294.1
157.5°	1326.8	1327.1	1327.3	1327.6
160°	1357.2	1357.7	1358.2	1358.7
162.5°	1384.1	1384.9	1385.6	1386.4
165°	1407.2	1408.0	1408.7	1409.5
167.5°	1426.1	1427.1	1428.2	1429.2
170°	1442.2	1443.3	1444.3	1445.3
172.5°	1454.9	1456.0	1457.0	1458.0
175°	1463.0	1464.1	1465.1	1466.1
177.5°	1467.6	1468.7	1469.7	1470.7
180°	1469.6	1469.6	1469.6	1469.6

(END OF REPORT)