

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012330

Luminaire Tested: S123RDIP-B1165D365UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012330
REPORT IS A COMBINATION OF REPORTS P993019 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1165D365UB30-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5643.0 lumens
Efficiency: N/A
Efficacy: 79.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012330

CATALOG NUMBER: S123RDIP-B1165D365UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012330

CATALOG NUMBER: S123RDIP-B1165D365UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82
1	105	100	96	93	100	96	92	89	88	85	82	80	78	76	73	71	70
2	96	88	82	77	91	84	79	74	77	73	69	71	67	64	65	62	60
3	88	78	71	65	83	75	68	63	69	63	59	63	59	55	58	54	51
4	80	69	61	55	77	67	59	54	61	55	51	57	52	48	52	48	45
5	74	62	54	48	71	60	52	47	55	49	44	51	46	42	47	43	39
6	69	56	48	42	65	54	47	41	50	44	39	46	41	37	43	38	35
7	64	51	43	37	61	49	42	36	46	39	35	42	37	33	39	35	31
8	59	47	39	33	57	45	38	33	42	36	31	39	34	30	36	32	28
9	55	43	35	30	53	41	34	29	39	32	28	36	31	27	34	29	26
10	52	40	32	27	50	38	31	27	36	30	25	33	28	24	31	27	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20907	20907	20907
5°	20941	20167	20112
10°	20776	19408	19026
15°	20506	18472	17837
20°	20152	17453	16507
25°	19787	16393	15248
30°	19319	15266	13759
35°	18838	14159	12402
40°	18384	12958	10904
45°	17804	11782	9558
50°	17162	10527	8164
55°	16498	9184	6885
60°	15862	7805	5589
65°	15041	6392	4362
70°	14009	4834	3117
75°	12523	3274	2471
80°	10690	2274	1733
85°	8021	1228	909

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17804 cd/sqm

TEST NUMBER: P1012330

CATALOG NUMBER: S123RDIP-B1165D365UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.6	3.2
10°-20°	507.9	9.0
20°-30°	731.3	13.0
30°-40°	823.6	14.6
40°-50°	787.8	14.0
50°-60°	644.9	11.4
60°-70°	434.8	7.7
70°-80°	218.1	3.9
80°-90°	58.0	1.0
90°-100°	29.1	0.5
100°-110°	88.2	1.6
110°-120°	150.1	2.7
120°-130°	197.5	3.5
130°-140°	222.0	3.9
140°-150°	218.2	3.9
150°-160°	183.7	3.3
160°-170°	122.3	2.2
170°-180°	42.8	0.8
0°-30°	1421.8	25.2
0°-40°	2245.4	39.8
0°-60°	3678.1	65.2
0°-90°	4389.0	77.8
90°-120°	267.5	4.7
90°-150°	905.2	16.0
90°-180°	1254.0	22.2
0°-180°	5643.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1942	1942	1942	1942	1942	
5°	1942	1934	1916	1930	1926	184
15°	1852	1835	1791	1783	1772	522
25°	1686	1646	1574	1541	1523	775
35°	1459	1402	1304	1237	1208	913
45°	1199	1128	1007	917	879	925
55°	910	833	699	608	576	817
65°	622	536	413	336	318	616
75°	329	254	167	151	148	351
85°	84	49	44	41	41	91
90°	0	4	8	10	11	7
95°	21	24	26	28	28	23
105°	80	81	84	84	85	86
115°	151	152	152	152	152	150
125°	221	222	222	220	219	197
135°	287	289	289	287	287	221
145°	348	349	350	350	348	217
155°	398	398	399	400	398	183
165°	434	433	433	435	433	122
175°	452	450	450	452	450	43
180°	453	453	453	453	453	

TEST NUMBER: P1012330

CATALOG NUMBER: S123RDIP-B1165D365UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1942.3	1942.3	1942.3	1942.3	1942.3
2.5°	1950.2	1943.9	1925.0	1942.3	1939.1
5°	1942.3	1934.4	1915.5	1929.7	1926.5
7.5°	1928.1	1920.2	1896.6	1906.1	1901.3
10°	1909.2	1898.2	1869.8	1871.4	1863.5
12.5°	1882.4	1869.8	1833.6	1832.0	1822.6
15°	1852.5	1835.2	1791.1	1783.2	1772.2
17.5°	1816.3	1797.4	1742.2	1726.5	1710.7
20°	1775.3	1750.1	1690.3	1669.8	1650.9
22.5°	1729.6	1699.7	1635.1	1608.3	1591.0
25°	1685.5	1646.2	1573.7	1540.6	1523.3
27.5°	1632.0	1589.4	1510.7	1466.6	1439.8
30°	1576.8	1529.6	1441.4	1387.8	1362.6
32.5°	1521.7	1466.6	1372.1	1312.2	1285.4
35°	1458.7	1402.0	1304.3	1236.6	1208.2
37.5°	1395.7	1334.2	1231.9	1156.2	1121.6
40°	1335.8	1266.5	1154.7	1072.8	1036.5
42.5°	1268.1	1198.8	1082.2	990.8	959.3
45°	1198.8	1127.9	1006.6	916.8	879.0
47.5°	1131.0	1052.3	932.6	834.9	801.8
50°	1055.4	981.4	853.8	756.1	719.9
52.5°	987.7	905.8	779.8	677.4	645.9
55°	910.5	833.3	699.4	608.1	576.5
57.5°	841.2	757.7	622.2	535.6	508.8
60°	768.7	682.1	551.3	466.3	439.5
62.5°	696.3	609.6	478.9	400.1	371.8
65°	622.2	535.6	412.7	335.5	318.2
67.5°	548.2	460.0	340.3	282.0	263.1
70°	475.7	390.7	280.4	225.3	207.9
72.5°	403.3	319.8	222.1	179.6	174.9
75°	329.2	253.6	167.0	151.2	148.1
77.5°	261.5	192.2	130.7	121.3	118.1
80°	196.9	132.3	99.2	94.5	91.4
82.5°	135.5	81.9	70.9	66.2	66.2
85°	83.5	48.8	44.1	41.0	41.0
87.5°	37.8	20.5	20.5	18.9	17.3
90°	0.4	3.9	8.5	10.0	10.7
92.5°	10.7	12.8	14.9	16.0	15.3
95°	21.0	23.5	26.3	27.7	27.7
97.5°	34.5	36.3	38.4	40.2	39.8
100°	48.4	50.5	52.3	53.3	54.0
102.5°	64.4	65.4	67.9	69.0	68.6
105°	80.0	80.7	83.9	83.9	84.6
107.5°	98.5	98.8	100.3	101.3	101.0
110°	115.5	116.3	117.0	118.4	117.7

TEST NUMBER: P1012330

CATALOG NUMBER: S123RDIP-B1165D365UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	133.3	133.7	133.7	135.5	135.5
115°	151.1	152.2	151.5	151.8	151.5
117.5°	169.2	169.6	168.9	168.9	167.8
120°	185.9	188.1	186.3	185.9	185.2
122.5°	203.4	204.8	204.1	203.0	201.9
125°	221.1	222.2	221.5	220.1	218.7
127.5°	237.5	239.6	238.9	236.8	235.4
130°	253.8	256.7	255.6	254.2	251.7
132.5°	270.2	273.0	272.3	270.6	268.8
135°	286.9	289.0	288.7	287.3	286.6
137.5°	302.2	304.0	305.0	303.3	302.2
140°	318.2	320.0	320.3	320.0	317.5
142.5°	332.8	334.6	335.3	334.9	333.1
145°	348.1	348.8	349.8	349.5	348.1
147.5°	361.2	362.6	363.7	363.7	361.6
150°	375.1	375.8	376.5	376.5	374.4
152.5°	386.5	387.5	387.9	388.6	386.8
155°	398.5	398.5	398.9	400.3	397.8
157.5°	408.9	408.5	408.9	410.3	408.1
160°	418.5	417.7	417.7	419.5	418.1
162.5°	427.0	425.9	426.3	428.1	425.6
165°	434.1	433.0	433.0	435.2	432.7
167.5°	440.1	438.7	439.1	441.2	439.1
170°	445.1	443.7	443.7	446.2	443.7
172.5°	449.0	447.6	447.6	449.7	447.3
175°	451.5	450.1	450.1	452.2	449.7
177.5°	452.9	451.5	451.5	453.7	451.2
180°	452.6	452.6	452.6	452.6	452.6

(END OF REPORT)