

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012389

Luminaire Tested: S123RDIP-B1165D805UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012389
REPORT IS A COMBINATION OF REPORTS P993100 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1165D805UB30-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7233.6 lumens
Efficiency: N/A
Efficacy: 87.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012389

CATALOG NUMBER: S123RDIP-B1165D805UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012389

CATALOG NUMBER: S123RDIP-B1165D805UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66
1	101	96	93	89	94	90	87	84	79	77	74	69	67	65	59	58	57
2	92	85	79	73	86	79	74	70	70	66	62	61	58	55	52	50	48
3	84	75	67	62	78	70	64	59	62	57	53	54	50	47	47	44	41
4	77	66	59	53	72	63	56	50	55	50	45	48	44	41	42	39	36
5	71	59	51	45	66	56	49	43	50	44	39	44	39	35	38	34	32
6	66	54	45	40	61	51	43	38	45	39	35	40	35	31	35	31	28
7	61	48	41	35	57	46	39	33	41	35	31	36	31	28	32	28	25
8	56	44	36	31	53	42	35	30	37	32	27	33	28	25	29	25	23
9	53	40	33	28	49	38	31	27	34	29	25	31	26	23	27	23	20
10	49	37	30	25	46	35	29	24	32	26	22	28	24	20	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20907	20907	20907
5°	20941	20167	20112
10°	20776	19408	19026
15°	20506	18472	17837
20°	20152	17453	16507
25°	19787	16393	15248
30°	19319	15266	13759
35°	18838	14159	12402
40°	18384	12958	10904
45°	17804	11782	9558
50°	17162	10527	8164
55°	16498	9184	6885
60°	15862	7805	5589
65°	15041	6392	4362
70°	14009	4834	3117
75°	12523	3274	2471
80°	10690	2274	1733
85°	8021	1228	909

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17804 cd/sqm

TEST NUMBER: P1012389

CATALOG NUMBER: S123RDIP-B1165D805UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.6	2.5
10°-20°	507.9	7.0
20°-30°	731.3	10.1
30°-40°	823.6	11.4
40°-50°	787.8	10.9
50°-60°	644.9	8.9
60°-70°	434.8	6.0
70°-80°	218.1	3.0
80°-90°	59.1	0.8
90°-100°	214.3	3.0
100°-110°	599.0	8.3
110°-120°	584.1	8.1
120°-130°	465.1	6.4
130°-140°	367.1	5.1
140°-150°	273.9	3.8
150°-160°	191.1	2.6
160°-170°	112.3	1.6
170°-180°	36.5	0.5
0°-30°	1421.8	19.7
0°-40°	2245.4	31.0
0°-60°	3678.1	50.8
0°-90°	4390.1	60.7
90°-120°	1397.5	19.3
90°-150°	2503.6	34.6
90°-180°	2844.0	39.3
0°-180°	7233.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1942	1942	1942	1942	1942	
5°	1942	1934	1916	1930	1926	184
15°	1852	1835	1791	1783	1772	522
25°	1686	1646	1574	1541	1523	775
35°	1459	1402	1304	1237	1208	913
45°	1199	1128	1007	917	879	925
55°	910	833	699	608	576	817
65°	622	536	413	336	318	616
75°	329	254	167	151	148	351
85°	84	49	44	41	41	91
90°	2	9	19	21	22	7
95°	26	84	453	132	89	28
105°	89	131	614	1073	971	94
115°	156	195	470	1030	1181	155
125°	218	257	438	794	931	193
135°	255	304	432	654	755	197
145°	291	333	427	536	590	182
155°	331	356	413	470	489	152
165°	361	371	396	420	427	102
175°	376	377	379	385	384	36
180°	377	377	377	377	377	

TEST NUMBER: P1012389

CATALOG NUMBER: S123RDIP-B1165D805UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1942.3	1942.3	1942.3	1942.3	1942.3
2.5°	1950.2	1943.9	1925.0	1942.3	1939.1
5°	1942.3	1934.4	1915.5	1929.7	1926.5
7.5°	1928.1	1920.2	1896.6	1906.1	1901.3
10°	1909.2	1898.2	1869.8	1871.4	1863.5
12.5°	1882.4	1869.8	1833.6	1832.0	1822.6
15°	1852.5	1835.2	1791.1	1783.2	1772.2
17.5°	1816.3	1797.4	1742.2	1726.5	1710.7
20°	1775.3	1750.1	1690.3	1669.8	1650.9
22.5°	1729.6	1699.7	1635.1	1608.3	1591.0
25°	1685.5	1646.2	1573.7	1540.6	1523.3
27.5°	1632.0	1589.4	1510.7	1466.6	1439.8
30°	1576.8	1529.6	1441.4	1387.8	1362.6
32.5°	1521.7	1466.6	1372.1	1312.2	1285.4
35°	1458.7	1402.0	1304.3	1236.6	1208.2
37.5°	1395.7	1334.2	1231.9	1156.2	1121.6
40°	1335.8	1266.5	1154.7	1072.8	1036.5
42.5°	1268.1	1198.8	1082.2	990.8	959.3
45°	1198.8	1127.9	1006.6	916.8	879.0
47.5°	1131.0	1052.3	932.6	834.9	801.8
50°	1055.4	981.4	853.8	756.1	719.9
52.5°	987.7	905.8	779.8	677.4	645.9
55°	910.5	833.3	699.4	608.1	576.5
57.5°	841.2	757.7	622.2	535.6	508.8
60°	768.7	682.1	551.3	466.3	439.5
62.5°	696.3	609.6	478.9	400.1	371.8
65°	622.2	535.6	412.7	335.5	318.2
67.5°	548.2	460.0	340.3	282.0	263.1
70°	475.7	390.7	280.4	225.3	207.9
72.5°	403.3	319.8	222.1	179.6	174.9
75°	329.2	253.6	167.0	151.2	148.1
77.5°	261.5	192.2	130.7	121.3	118.1
80°	196.9	132.3	99.2	94.5	91.4
82.5°	135.5	81.9	70.9	66.2	66.2
85°	83.5	48.8	44.1	41.0	41.0
87.5°	37.8	20.5	20.5	18.9	17.3
90°	1.5	9.2	19.1	21.4	22.1
92.5°	11.5	45.8	142.0	48.5	40.5
95°	26.0	84.4	452.7	132.0	88.6
97.5°	41.2	96.6	696.3	332.1	181.7
100°	56.5	106.5	723.0	694.7	478.7
102.5°	72.5	118.0	673.4	930.3	758.1
105°	88.6	131.0	613.8	1073.4	971.1
107.5°	105.4	146.2	561.1	1136.4	1110.1
110°	123.7	161.8	517.6	1138.3	1189.5

TEST NUMBER: P1012389

CATALOG NUMBER: S123RDIP-B1165D805UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	140.5	178.3	488.6	1095.2	1205.5
115°	156.5	195.1	469.5	1029.5	1181.1
117.5°	172.5	211.1	456.5	959.2	1127.6
120°	189.3	227.2	448.1	892.8	1057.4
122.5°	203.8	242.4	442.8	840.6	991.7
125°	217.6	256.9	438.2	794.0	931.4
127.5°	228.3	270.6	435.9	755.8	879.5
130°	238.2	282.9	433.6	720.7	836.7
132.5°	245.8	294.0	432.9	687.8	794.7
135°	255.0	304.2	432.1	653.9	755.1
137.5°	263.4	312.6	430.6	621.8	713.1
140°	271.8	320.2	429.8	590.5	668.8
142.5°	280.9	327.2	428.3	561.9	627.6
145°	290.9	333.2	426.8	536.3	590.1
147.5°	300.8	339.8	424.5	516.5	558.1
150°	310.7	345.0	421.4	499.0	530.6
152.5°	320.6	350.8	417.6	483.6	507.7
155°	330.6	356.5	413.0	469.5	489.4
157.5°	338.2	361.5	409.2	455.8	471.8
160°	347.4	365.7	404.6	443.2	455.0
162.5°	354.2	368.8	400.0	431.4	439.7
165°	361.1	371.4	395.5	419.5	426.8
167.5°	366.5	373.7	390.9	409.2	413.8
170°	371.0	374.8	386.3	400.0	402.3
172.5°	374.1	376.0	382.5	392.0	391.6
175°	376.4	376.8	379.4	384.8	384.0
177.5°	377.9	377.1	377.1	380.2	378.7
180°	377.1	377.1	377.1	377.1	377.1

(END OF REPORT)