

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012052

Luminaire Tested: S123DIP-B775D585UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012052
REPORT IS A COMBINATION OF REPORTS P990439 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D585UB35-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5226.0 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012052

CATALOG NUMBER: S123DIP-B775D585UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012052

CATALOG NUMBER: S123DIP-B775D585UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	66	66	66
1	100	96	92	88	94	90	86	83	79	76	74	68	66	65	59	57	56
2	91	84	77	72	85	78	73	68	69	65	61	60	57	54	52	49	47
3	83	74	66	60	78	69	62	57	61	55	51	53	49	46	46	43	40
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	35
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30
6	65	52	44	38	60	49	42	36	44	37	33	38	33	30	33	30	26
7	60	47	39	33	56	45	37	32	40	33	29	35	30	26	30	27	24
8	55	43	35	30	52	41	33	28	36	30	26	32	27	23	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19
10	48	36	29	24	45	34	27	23	31	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13235	13235	13235
5°	13268	12778	12759
10°	13150	12346	12219
15°	12967	11895	11631
20°	12757	11396	11047
25°	12486	10870	10424
30°	12190	10325	9768
35°	11879	9767	9117
40°	11552	9183	8475
45°	11195	8612	7806
50°	10832	7977	7134
55°	10364	7316	6452
60°	9882	6586	5728
65°	9430	5797	4971
70°	8779	4922	4090
75°	7844	3897	3175
80°	6775	2739	2245
85°	5283	1473	1124

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11195 cd/sqm

TEST NUMBER: P1012052

CATALOG NUMBER: S123DIP-B775D585UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.9	2.2
10°-20°	327.3	6.3
20°-30°	483.4	9.2
30°-40°	564.6	10.8
40°-50°	567.5	10.9
50°-60°	498.6	9.5
60°-70°	371.3	7.1
70°-80°	211.3	4.0
80°-90°	61.6	1.2
90°-100°	47.0	0.9
100°-110°	142.4	2.7
110°-120°	242.3	4.6
120°-130°	318.8	6.1
130°-140°	358.4	6.9
140°-150°	352.3	6.7
150°-160°	296.6	5.7
160°-170°	197.5	3.8
170°-180°	69.1	1.3
0°-30°	926.6	17.7
0°-40°	1491.2	28.5
0°-60°	2557.3	48.9
0°-90°	3201.6	61.3
90°-120°	431.8	8.3
90°-150°	1461.2	28.0
90°-180°	2024.0	38.7
0°-180°	5226.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1231	1225	1214	1224	1222	117
15°	1171	1167	1153	1162	1156	330
25°	1064	1057	1044	1044	1041	490
35°	920	913	900	893	888	575
45°	754	750	736	723	718	582
55°	572	571	557	546	540	512
65°	390	385	374	366	363	385
75°	206	202	199	194	190	220
85°	55	53	53	51	51	59
90°	1	6	14	16	17	6
95°	34	38	42	45	45	37
105°	129	130	136	136	137	138
115°	244	246	244	245	244	241
125°	357	359	358	355	353	318
135°	463	467	466	464	463	357
145°	562	563	565	564	562	351
155°	643	643	644	646	642	296
165°	701	699	699	702	698	198
175°	729	727	727	730	726	69
180°	731	731	731	731	731	

TEST NUMBER: P1012052

CATALOG NUMBER: S123DIP-B775D585UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1229.6	1229.6	1229.6	1229.6	1229.6
2.5°	1234.8	1230.6	1219.0	1229.6	1228.5
5°	1230.6	1225.3	1213.7	1224.3	1222.2
7.5°	1221.1	1215.8	1204.2	1213.7	1212.6
10°	1208.4	1203.1	1189.4	1198.9	1196.8
12.5°	1191.5	1187.3	1174.6	1180.9	1179.9
15°	1171.4	1167.2	1153.4	1161.9	1155.6
17.5°	1149.2	1143.9	1130.2	1136.5	1134.4
20°	1123.8	1117.5	1103.7	1108.0	1104.8
22.5°	1095.3	1088.9	1075.2	1078.4	1074.1
25°	1063.6	1057.2	1043.5	1044.5	1041.4
27.5°	1030.8	1024.5	1009.7	1010.7	1007.5
30°	994.9	989.6	974.8	974.8	967.4
32.5°	958.9	951.5	940.9	933.5	930.4
35°	919.8	913.4	899.7	893.4	888.1
37.5°	880.7	872.2	858.5	851.1	847.9
40°	839.4	833.1	818.3	809.8	805.6
42.5°	798.2	790.8	776.0	767.5	763.3
45°	753.8	749.6	735.8	723.1	717.9
47.5°	710.5	704.1	691.4	678.7	674.5
50°	666.1	660.8	647.0	635.4	629.1
52.5°	619.5	616.4	601.6	592.0	585.7
55°	572.0	570.9	557.2	545.5	540.2
57.5°	527.6	523.3	512.8	502.2	495.8
60°	478.9	477.9	465.2	455.7	450.4
62.5°	435.6	432.4	419.7	410.2	407.0
65°	390.1	384.8	374.3	365.8	362.6
67.5°	341.5	337.3	328.8	321.4	317.2
70°	298.1	291.8	285.5	278.1	272.8
72.5°	252.7	248.4	241.0	234.7	232.6
75°	206.2	201.9	198.8	193.5	190.3
77.5°	164.9	162.8	158.6	154.4	154.4
80°	124.8	121.6	119.5	118.4	118.4
82.5°	85.6	85.6	85.6	83.5	82.5
85°	55.0	52.9	52.9	50.7	50.7
87.5°	27.5	24.3	23.3	22.2	22.2
90°	0.6	6.3	13.8	16.1	17.2
92.5°	17.2	20.7	24.1	25.8	24.7
95°	33.9	37.9	42.5	44.8	44.8
97.5°	55.7	58.5	62.0	64.9	64.3
100°	78.1	81.5	84.4	86.1	87.2
102.5°	103.9	105.6	109.6	111.3	110.8
105°	129.1	130.3	135.5	135.5	136.6
107.5°	159.0	159.6	161.9	163.6	163.0
110°	186.5	187.7	188.8	191.1	190.0

TEST NUMBER: P1012052

CATALOG NUMBER: S123DIP-B775D585UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	215.2	215.8	215.8	218.7	218.7
115°	243.9	245.6	244.5	245.1	244.5
117.5°	273.2	273.8	272.6	272.6	270.9
120°	300.2	303.6	300.7	300.2	299.0
122.5°	328.3	330.6	329.4	327.7	326.0
125°	357.0	358.7	357.6	355.3	353.0
127.5°	383.4	386.8	385.7	382.2	380.0
130°	409.8	414.4	412.7	410.4	406.4
132.5°	436.2	440.8	439.6	436.8	433.9
135°	463.2	466.6	466.0	463.7	462.6
137.5°	487.9	490.7	492.4	489.6	487.9
140°	513.7	516.6	517.1	516.6	512.5
142.5°	537.2	540.1	541.2	540.7	537.8
145°	561.9	563.0	564.8	564.2	561.9
147.5°	583.1	585.4	587.1	587.1	583.7
150°	605.5	606.7	607.8	607.8	604.4
152.5°	623.9	625.6	626.2	627.3	624.5
155°	643.4	643.4	644.0	646.3	642.2
157.5°	660.0	659.5	660.0	662.3	658.9
160°	675.5	674.4	674.4	677.3	675.0
162.5°	689.3	687.6	688.2	691.0	687.0
165°	700.8	699.1	699.1	702.5	698.5
167.5°	710.5	708.3	708.8	712.3	708.8
170°	718.6	716.3	716.3	720.3	716.3
172.5°	724.9	722.6	722.6	726.0	722.0
175°	728.9	726.6	726.6	730.1	726.0
177.5°	731.2	728.9	728.9	732.4	728.3
180°	730.6	730.6	730.6	730.6	730.6

(END OF REPORT)