

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012062

Luminaire Tested: S123DIP-B775D585UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012062
REPORT IS A COMBINATION OF REPORTS P990449 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D585UB40-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5285.9 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012062

CATALOG NUMBER: S123DIP-B775D585UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012062

CATALOG NUMBER: S123DIP-B775D585UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89		77	77	77		65
1	100	96	92	88	93	89	86	83	78	75	73		67	65	64		58
2	91	83	77	72	85	78	73	68	68	64	60		59	56	53		51
3	83	73	66	60	77	69	62	57	60	55	51		52	48	45		45
4	76	65	57	51	71	61	54	48	53	48	43		47	42	39		40
5	70	58	50	43	65	54	47	41	48	42	37		42	37	33		36
6	64	52	44	38	60	49	41	36	43	37	33		38	33	29		33
7	60	47	39	33	55	44	37	32	39	33	29		34	30	26		30
8	55	43	35	29	52	40	33	28	36	30	26		32	27	23		27
9	51	39	31	26	48	37	30	25	33	27	23		29	24	21		25
10	48	36	28	24	45	34	27	23	30	25	21		27	22	19		24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13103	13103	13103
5°	13135	12651	12631
10°	13018	12222	12097
15°	12837	11777	11514
20°	12630	11282	10937
25°	12361	10762	10320
30°	12067	10221	9670
35°	11760	9669	9025
40°	11437	9091	8391
45°	11083	8527	7728
50°	10723	7898	7063
55°	10259	7243	6387
60°	9783	6520	5671
65°	9336	5738	4922
70°	8693	4872	4048
75°	7764	3858	3143
80°	6705	2712	2223
85°	5225	1456	1113

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11083 cd/sqm

TEST NUMBER: P1012062

CATALOG NUMBER: S123DIP-B775D585UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.8	2.2
10°-20°	324.0	6.1
20°-30°	478.6	9.1
30°-40°	558.9	10.6
40°-50°	561.9	10.6
50°-60°	493.6	9.3
60°-70°	367.6	7.0
70°-80°	209.2	4.0
80°-90°	61.0	1.2
90°-100°	159.5	3.0
100°-110°	445.8	8.4
110°-120°	434.7	8.2
120°-130°	346.2	6.5
130°-140°	273.3	5.2
140°-150°	203.9	3.9
150°-160°	142.2	2.7
160°-170°	83.5	1.6
170°-180°	27.2	0.5
0°-30°	917.4	17.4
0°-40°	1476.3	27.9
0°-60°	2531.7	47.9
0°-90°	3169.6	60.0
90°-120°	1040.1	19.7
90°-150°	1863.4	35.3
90°-180°	2116.0	40.0
0°-180°	5285.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1217	1217	1217	1217	1217	
5°	1218	1213	1202	1212	1210	116
15°	1160	1156	1142	1150	1144	327
25°	1053	1047	1033	1034	1031	485
35°	911	904	891	884	879	570
45°	746	742	728	716	711	576
55°	566	565	552	540	535	507
65°	386	381	370	362	359	381
75°	204	200	197	192	188	218
85°	54	52	52	50	50	58
90°	1	7	14	16	16	5
95°	19	63	337	98	66	20
105°	66	97	457	799	723	70
115°	116	145	350	766	879	115
125°	162	191	326	591	693	144
135°	190	226	322	487	562	147
145°	216	248	318	399	439	136
155°	246	265	307	349	364	113
165°	269	276	294	312	318	76
175°	280	280	282	286	286	27
180°	281	281	281	281	281	

TEST NUMBER: P1012062

CATALOG NUMBER: S123DIP-B775D585UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1217.3	1217.3	1217.3	1217.3	1217.3
2.5°	1222.5	1218.3	1206.8	1217.3	1216.2
5°	1218.3	1213.1	1201.6	1212.0	1209.9
7.5°	1208.9	1203.7	1192.1	1201.6	1200.5
10°	1196.3	1191.1	1177.5	1186.9	1184.8
12.5°	1179.6	1175.4	1162.8	1169.1	1168.1
15°	1159.7	1155.5	1141.9	1150.3	1144.0
17.5°	1137.7	1132.5	1118.9	1125.2	1123.1
20°	1112.6	1106.3	1092.7	1096.9	1093.8
22.5°	1084.3	1078.1	1064.5	1067.6	1063.4
25°	1052.9	1046.7	1033.1	1034.1	1031.0
27.5°	1020.5	1014.2	999.6	1000.6	997.5
30°	984.9	979.7	965.0	965.0	957.7
32.5°	949.3	942.0	931.5	924.2	921.1
35°	910.6	904.3	890.7	884.4	879.2
37.5°	871.9	863.5	849.9	842.6	839.4
40°	831.0	824.8	810.1	801.7	797.6
42.5°	790.2	782.9	768.2	759.9	755.7
45°	746.3	742.1	728.5	715.9	710.7
47.5°	703.4	697.1	684.5	672.0	667.8
50°	659.4	654.2	640.6	629.0	622.8
52.5°	613.3	610.2	595.5	586.1	579.8
55°	566.2	565.2	551.6	540.1	534.8
57.5°	522.3	518.1	507.6	497.2	490.9
60°	474.1	473.1	460.5	451.1	445.9
62.5°	431.2	428.1	415.5	406.1	403.0
65°	386.2	381.0	370.5	362.1	359.0
67.5°	338.1	333.9	325.5	318.2	314.0
70°	295.2	288.9	282.6	275.3	270.0
72.5°	250.2	246.0	238.6	232.4	230.3
75°	204.1	199.9	196.8	191.5	188.4
77.5°	163.3	161.2	157.0	152.8	152.8
80°	123.5	120.4	118.3	117.2	117.2
82.5°	84.8	84.8	84.8	82.7	81.6
85°	54.4	52.3	52.3	50.2	50.2
87.5°	27.2	24.1	23.0	22.0	22.0
90°	1.1	6.8	14.2	15.9	16.5
92.5°	8.5	34.1	105.7	36.1	30.1
95°	19.3	62.8	337.0	98.3	65.9
97.5°	30.7	71.9	518.2	247.2	135.2
100°	42.0	79.2	538.1	517.0	356.3
102.5°	54.0	87.8	501.2	692.4	564.2
105°	65.9	97.4	456.8	798.9	722.8
107.5°	78.4	108.8	417.6	845.8	826.2
110°	92.1	120.4	385.3	847.2	885.3

TEST NUMBER: P1012062

CATALOG NUMBER: S123DIP-B775D585UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	104.6	132.6	363.7	815.1	897.2
115°	116.5	145.2	349.5	766.2	879.0
117.5°	128.4	157.1	339.8	714.0	839.3
120°	140.9	169.0	333.5	664.5	787.0
122.5°	151.7	180.4	329.6	625.6	738.1
125°	161.9	191.2	326.2	591.0	693.2
127.5°	169.9	201.4	324.5	562.6	654.6
130°	177.3	210.6	322.7	536.4	622.8
132.5°	183.0	218.8	322.2	512.0	591.5
135°	189.8	226.4	321.6	486.7	562.0
137.5°	196.0	232.7	320.5	462.8	530.7
140°	202.3	238.4	319.9	439.5	497.8
142.5°	209.1	243.4	318.8	418.2	467.1
145°	216.5	248.0	317.6	399.2	439.2
147.5°	223.9	252.8	315.9	384.4	415.4
150°	231.3	256.8	313.7	371.3	394.9
152.5°	238.7	261.1	310.8	360.0	377.9
155°	246.0	265.4	307.4	349.4	364.2
157.5°	251.7	269.0	304.6	339.2	351.2
160°	258.5	272.2	301.2	329.8	338.7
162.5°	263.7	274.4	297.7	321.0	327.3
165°	268.8	276.4	294.3	312.2	317.6
167.5°	272.7	278.2	290.9	304.5	308.0
170°	276.2	279.0	287.5	297.8	299.5
172.5°	278.4	279.8	284.7	291.8	291.5
175°	280.1	280.4	282.4	286.4	285.8
177.5°	281.3	280.7	280.7	283.0	281.8
180°	280.7	280.7	280.7	280.7	280.7

(END OF REPORT)