

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012069

Luminaire Tested: S123DIP-B775D585UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012069
REPORT IS A COMBINATION OF REPORTS P990456 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D585UB50-4F0-XX-W2A-F
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5319.0 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012069

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1012069

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63
1	99	95	91	87	92	89	85	82	77	74	72	66	64	62	56	54	53
2	91	83	77	71	84	77	72	67	67	63	59	58	55	52	49	47	45
3	83	73	65	59	77	68	62	56	59	54	50	51	47	44	43	41	38
4	76	65	56	50	70	60	53	48	53	47	43	45	41	38	39	35	33
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	29
6	64	52	43	37	59	48	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	22
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12668	12668	12668
5°	12699	12231	12212
10°	12587	11818	11695
15°	12412	11387	11133
20°	12211	10909	10574
25°	11951	10404	9978
30°	11668	9882	9350
35°	11370	9349	8726
40°	11058	8790	8112
45°	10715	8244	7471
50°	10367	7636	6828
55°	9920	7003	6176
60°	9459	6305	5482
65°	9026	5548	4759
70°	8405	4710	3915
75°	7505	3730	3040
80°	6482	2622	2149
85°	5052	1409	1077

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10715 cd/sqm

TEST NUMBER: P1012069

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.0	2.1
10°-20°	313.3	5.9
20°-30°	462.7	8.7
30°-40°	540.4	10.2
40°-50°	543.3	10.2
50°-60°	477.2	9.0
60°-70°	355.4	6.7
70°-80°	202.3	3.8
80°-90°	59.0	1.1
90°-100°	26.1	0.5
100°-110°	126.1	2.4
110°-120°	309.0	5.8
120°-130°	392.2	7.4
130°-140°	419.0	7.9
140°-150°	391.8	7.4
150°-160°	316.0	5.9
160°-170°	204.0	3.8
170°-180°	70.3	1.3
0°-30°	886.9	16.7
0°-40°	1427.3	26.8
0°-60°	2447.8	46.0
0°-90°	3064.5	57.6
90°-120°	461.1	8.7
90°-150°	1664.2	31.3
90°-180°	2255.0	42.4
0°-180°	5319.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1177	1177	1177	1177	1177	
5°	1178	1173	1162	1172	1170	112
15°	1121	1117	1104	1112	1106	316
25°	1018	1012	999	1000	997	469
35°	880	874	861	855	850	551
45°	722	718	704	692	687	557
55°	548	546	533	522	517	490
65°	373	368	358	350	347	368
75°	197	193	190	185	182	211
85°	53	51	51	49	49	56
90°	0	6	13	15	16	5
95°	34	11	17	21	21	40
105°	164	170	120	23	24	174
115°	307	310	315	321	323	303
125°	433	437	440	441	442	387
135°	539	542	544	546	544	415
145°	622	626	627	628	628	389
155°	685	684	685	687	684	316
165°	722	721	720	725	721	204
175°	740	737	737	741	737	70
180°	740	740	740	740	740	

TEST NUMBER: P1012069

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1176.9	1176.9	1176.9	1176.9	1176.9
2.5°	1182.0	1177.9	1166.8	1176.9	1175.9
5°	1177.9	1172.9	1161.7	1171.9	1169.8
7.5°	1168.8	1163.8	1152.6	1161.7	1160.7
10°	1156.7	1151.6	1138.5	1147.6	1145.5
12.5°	1140.5	1136.4	1124.3	1130.4	1129.4
15°	1121.3	1117.2	1104.1	1112.2	1106.1
17.5°	1100.0	1095.0	1081.8	1087.9	1085.8
20°	1075.7	1069.7	1056.5	1060.5	1057.5
22.5°	1048.4	1042.3	1029.2	1032.2	1028.2
25°	1018.0	1012.0	998.8	999.8	996.8
27.5°	986.7	980.6	966.4	967.4	964.4
30°	952.3	947.2	933.0	933.0	926.0
32.5°	917.9	910.8	900.7	893.6	890.5
35°	880.4	874.3	861.2	855.1	850.1
37.5°	843.0	834.9	821.7	814.6	811.6
40°	803.5	797.4	783.3	775.2	771.1
42.5°	764.0	757.0	742.8	734.7	730.6
45°	721.5	717.5	704.3	692.2	687.1
47.5°	680.0	674.0	661.8	649.7	645.6
50°	637.5	632.5	619.3	608.2	602.1
52.5°	593.0	590.0	575.8	566.7	560.6
55°	547.5	546.5	533.3	522.2	517.1
57.5°	505.0	500.9	490.8	480.7	474.6
60°	458.4	457.4	445.3	436.2	431.1
62.5°	416.9	413.9	401.8	392.6	389.6
65°	373.4	368.4	358.2	350.1	347.1
67.5°	326.9	322.8	314.7	307.6	303.6
70°	285.4	279.3	273.2	266.1	261.1
72.5°	241.9	237.8	230.7	224.7	222.6
75°	197.3	193.3	190.3	185.2	182.2
77.5°	157.9	155.8	151.8	147.7	147.7
80°	119.4	116.4	114.4	113.3	113.3
82.5°	82.0	82.0	82.0	79.9	78.9
85°	52.6	50.6	50.6	48.6	48.6
87.5°	26.3	23.3	22.3	21.3	21.3
90°	0.5	6.0	13.2	15.4	16.5
92.5°	12.6	9.3	14.3	18.1	18.7
95°	33.5	11.0	17.0	20.9	20.9
97.5°	61.0	45.6	17.6	22.0	22.5
100°	92.9	103.8	18.1	22.5	23.1
102.5°	129.1	136.3	40.7	22.5	23.6
105°	163.7	169.8	120.3	23.1	24.2
107.5°	200.5	205.5	213.7	129.1	57.1
110°	237.4	241.7	247.8	229.7	151.1

TEST NUMBER: P1012069

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	272.5	276.4	282.4	287.4	286.3
115°	307.1	310.4	315.4	320.9	323.1
117.5°	341.2	345.0	347.8	352.2	352.7
120°	372.5	377.5	379.1	383.5	383.5
122.5°	404.4	408.2	410.4	413.2	413.7
125°	432.9	437.3	439.5	440.6	441.7
127.5°	461.5	465.9	468.7	470.3	469.2
130°	487.9	492.3	494.5	496.7	495.6
132.5°	513.2	517.6	519.2	521.4	519.8
135°	539.0	542.3	544.5	546.1	544.5
137.5°	561.0	565.4	566.5	569.2	568.1
140°	582.9	586.2	587.9	590.1	589.0
142.5°	603.3	606.6	608.2	609.9	608.2
145°	622.0	625.8	626.9	628.0	628.0
147.5°	640.1	642.8	643.9	645.0	642.3
150°	656.6	658.2	659.3	660.4	658.8
152.5°	671.4	672.0	672.5	674.7	672.0
155°	685.1	684.0	684.6	687.3	684.0
157.5°	696.1	696.1	695.6	698.9	694.5
160°	706.0	705.5	704.9	708.2	704.4
162.5°	715.4	713.7	713.2	717.0	713.7
165°	722.5	720.9	720.3	724.7	720.9
167.5°	728.5	726.3	726.3	730.7	726.3
170°	733.5	731.3	731.3	735.7	731.3
172.5°	736.8	734.0	734.6	739.0	734.0
175°	739.5	736.8	737.3	741.2	736.8
177.5°	740.6	737.9	738.4	742.8	737.3
180°	739.5	739.5	739.5	739.5	739.5

(END OF REPORT)