

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012440

Luminaire Tested: S123RDIP-B340D1195UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012440
REPORT IS A COMBINATION OF REPORTS P993163 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D1195UB27-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5317.0 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012440

CATALOG NUMBER: S123RDIP-B340D1195UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012440

CATALOG NUMBER: S123RDIP-B340D1195UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69		50	50	50		32
1	92	88	84	81	82	78	75	73	60	58	56		44	42	41		28
2	84	77	71	66	74	69	64	60	53	50	47		38	36	35		25
3	77	68	61	55	68	60	55	50	47	43	40		34	32	29		22
4	70	60	52	47	62	53	47	42	42	37	34		30	28	25		20
5	64	53	45	40	57	48	41	36	37	32	29		27	24	22		18
6	59	48	40	34	52	43	36	31	33	29	25		25	21	19		16
7	54	43	35	30	48	38	32	27	30	25	22		22	19	17		15
8	50	39	31	26	45	35	28	24	27	23	19		20	17	15		14
9	47	35	28	23	42	32	26	21	25	20	17		19	16	13		13
10	44	32	25	21	39	29	23	19	23	19	15		17	14	12		12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5970	5970	5970
5°	5979	5759	5743
10°	5933	5542	5433
15°	5856	5274	5093
20°	5754	4984	4714
25°	5650	4681	4354
30°	5517	4359	3929
35°	5379	4043	3541
40°	5249	3700	3114
45°	5084	3364	2729
50°	4901	3006	2331
55°	4711	2622	1966
60°	4529	2229	1596
65°	4296	1826	1246
70°	3999	1381	891
75°	3576	935	706
80°	3051	649	495
85°	2286	351	259

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5084 cd/sqm

TEST NUMBER: P1012440

CATALOG NUMBER: S123RDIP-B340D1195UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.1	1.0
10°-20°	145.0	2.7
20°-30°	208.8	3.9
30°-40°	235.2	4.4
40°-50°	225.0	4.2
50°-60°	184.1	3.5
60°-70°	124.2	2.3
70°-80°	62.3	1.2
80°-90°	19.4	0.4
90°-100°	94.3	1.8
100°-110°	285.6	5.4
110°-120°	486.1	9.1
120°-130°	639.5	12.0
130°-140°	718.9	13.5
140°-150°	706.7	13.3
150°-160°	595.0	11.2
160°-170°	396.1	7.4
170°-180°	138.7	2.6
0°-30°	406.0	7.6
0°-40°	641.2	12.1
0°-60°	1050.3	19.8
0°-90°	1256.1	23.6
90°-120°	866.0	16.3
90°-150°	2931.1	55.1
90°-180°	4061.0	76.4
0°-180°	5317.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	555	555	555	555	555	
5°	555	552	547	551	550	53
15°	529	524	511	509	506	149
25°	481	470	449	440	435	221
35°	416	400	372	353	345	261
45°	342	322	287	262	251	264
55°	260	238	200	174	165	233
65°	178	153	118	96	91	176
75°	94	72	48	43	42	100
85°	24	14	13	12	12	26
90°	1	13	28	32	34	7
95°	68	76	85	90	90	75
105°	259	261	272	272	274	277
115°	489	493	490	492	490	484
125°	716	720	717	713	708	639
135°	929	936	935	930	928	716
145°	1127	1129	1133	1132	1127	704
155°	1291	1291	1292	1296	1288	594
165°	1406	1402	1402	1409	1401	396
175°	1462	1458	1458	1464	1456	139
180°	1466	1466	1466	1466	1466	

TEST NUMBER: P1012440

CATALOG NUMBER: S123RDIP-B340D1195UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	554.6	554.6	554.6	554.6	554.6
2.5°	556.9	555.1	549.7	554.6	553.7
5°	554.6	552.4	547.0	551.0	550.1
7.5°	550.6	548.3	541.6	544.3	542.9
10°	545.2	542.0	533.9	534.4	532.1
12.5°	537.5	533.9	523.6	523.1	520.4
15°	529.0	524.0	511.4	509.2	506.0
17.5°	518.6	513.2	497.5	493.0	488.5
20°	506.9	499.7	482.7	476.8	471.4
22.5°	493.9	485.4	466.9	459.3	454.3
25°	481.3	470.1	449.4	439.9	435.0
27.5°	466.0	453.9	431.4	418.8	411.1
30°	450.3	436.8	411.6	396.3	389.1
32.5°	434.5	418.8	391.8	374.7	367.1
35°	416.5	400.3	372.4	353.1	345.0
37.5°	398.5	381.0	351.8	330.2	320.3
40°	381.4	361.7	329.7	306.3	296.0
42.5°	362.1	342.3	309.0	282.9	273.9
45°	342.3	322.1	287.4	261.8	251.0
47.5°	323.0	300.5	266.3	238.4	229.0
50°	301.4	280.2	243.8	215.9	205.6
52.5°	282.0	258.6	222.7	193.4	184.4
55°	260.0	238.0	199.7	173.6	164.6
57.5°	240.2	216.4	177.7	152.9	145.3
60°	219.5	194.8	157.4	133.1	125.5
62.5°	198.8	174.1	136.7	114.3	106.2
65°	177.7	152.9	117.9	95.8	90.9
67.5°	156.5	131.3	97.2	80.5	75.1
70°	135.8	111.6	80.1	64.3	59.4
72.5°	115.2	91.3	63.4	51.3	49.9
75°	94.0	72.4	47.7	43.2	42.3
77.5°	74.7	54.9	37.3	34.6	33.7
80°	56.2	37.8	28.3	27.0	26.1
82.5°	38.7	23.4	20.2	18.9	18.9
85°	23.8	13.9	12.6	11.7	11.7
87.5°	10.8	5.8	5.8	5.4	4.9
90°	1.2	12.7	27.6	32.2	34.5
92.5°	34.5	41.4	48.4	51.8	49.5
95°	67.9	76.0	85.2	89.8	89.8
97.5°	111.7	117.4	124.3	130.1	128.9
100°	156.6	163.5	169.2	172.7	175.0
102.5°	208.4	211.8	219.9	223.4	222.2
105°	259.0	261.3	271.7	271.7	274.0
107.5°	318.9	320.1	324.7	328.1	327.0
110°	374.2	376.5	378.8	383.4	381.1

TEST NUMBER: P1012440

CATALOG NUMBER: S123RDIP-B340D1195UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	431.7	432.9	432.9	438.6	438.6
115°	489.3	492.8	490.5	491.6	490.5
117.5°	548.0	549.2	546.9	546.9	543.4
120°	602.1	609.0	603.3	602.1	599.8
122.5°	658.5	663.1	660.8	657.4	653.9
125°	716.1	719.6	717.3	712.7	708.0
127.5°	769.1	776.0	773.7	766.8	762.2
130°	822.0	831.2	827.8	823.2	815.1
132.5°	875.0	884.2	881.9	876.1	870.4
135°	929.1	936.0	934.9	930.2	927.9
137.5°	978.6	984.4	987.8	982.1	978.6
140°	1030.4	1036.2	1037.3	1036.2	1028.1
142.5°	1077.6	1083.4	1085.7	1084.5	1078.8
145°	1127.1	1129.4	1132.9	1131.7	1127.1
147.5°	1169.7	1174.3	1177.8	1177.8	1170.9
150°	1214.6	1216.9	1219.2	1219.2	1212.3
152.5°	1251.5	1254.9	1256.1	1258.4	1252.6
155°	1290.6	1290.6	1291.8	1296.4	1288.3
157.5°	1324.0	1322.8	1324.0	1328.6	1321.7
160°	1355.1	1352.8	1352.8	1358.5	1353.9
162.5°	1382.7	1379.2	1380.4	1386.2	1378.1
165°	1405.7	1402.3	1402.3	1409.2	1401.1
167.5°	1425.3	1420.7	1421.8	1428.8	1421.8
170°	1441.4	1436.8	1436.8	1444.9	1436.8
172.5°	1454.1	1449.5	1449.5	1456.4	1448.3
175°	1462.1	1457.5	1457.5	1464.4	1456.4
177.5°	1466.7	1462.1	1462.1	1469.1	1461.0
180°	1465.6	1465.6	1465.6	1465.6	1465.6

(END OF REPORT)