

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012453

Luminaire Tested: S123RDIP-B340D1195UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012453
REPORT IS A COMBINATION OF REPORTS P993186 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D1195UB35-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5615.1 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012453

CATALOG NUMBER: S123RDIP-B340D1195UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012453

CATALOG NUMBER: S123RDIP-B340D1195UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	26
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22
3	76	67	61	55	67	60	54	50	46	42	39	34	31	29	22	20	19
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	19	18	17
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	11
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	13	12	10
9	47	35	28	23	41	32	25	21	25	20	17	18	15	13	12	11	9
10	43	32	25	21	39	29	23	19	23	18	15	17	14	12	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6046	6046	6046
5°	6056	5833	5817
10°	6008	5613	5502
15°	5930	5342	5158
20°	5828	5047	4774
25°	5723	4741	4409
30°	5587	4415	3979
35°	5449	4095	3587
40°	5316	3747	3154
45°	5149	3407	2764
50°	4963	3044	2361
55°	4771	2656	1991
60°	4587	2257	1616
65°	4349	1849	1261
70°	4052	1398	901
75°	3621	947	714
80°	3089	658	501
85°	2315	356	262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5149 cd/sqm

TEST NUMBER: P1012453

CATALOG NUMBER: S123RDIP-B340D1195UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.8	0.9
10°-20°	146.9	2.6
20°-30°	211.5	3.8
30°-40°	238.2	4.2
40°-50°	227.8	4.1
50°-60°	186.5	3.3
60°-70°	125.7	2.2
70°-80°	63.1	1.1
80°-90°	19.7	0.4
90°-100°	327.3	5.8
100°-110°	914.9	16.3
110°-120°	892.1	15.9
120°-130°	710.4	12.7
130°-140°	560.8	10.0
140°-150°	418.4	7.5
150°-160°	291.8	5.2
160°-170°	171.5	3.1
170°-180°	55.8	1.0
0°-30°	411.2	7.3
0°-40°	649.4	11.6
0°-60°	1063.7	18.9
0°-90°	1272.2	22.7
90°-120°	2134.3	38.0
90°-150°	3823.8	68.1
90°-180°	4343.0	77.3
0°-180°	5615.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	562	562	562	562	562	
5°	562	559	554	558	557	53
15°	536	531	518	516	512	151
25°	488	476	455	446	440	224
35°	422	406	377	358	349	264
45°	347	326	291	265	254	268
55°	263	241	202	176	167	236
65°	180	155	119	97	92	178
75°	95	73	48	44	43	101
85°	24	14	13	12	12	26
90°	2	14	29	33	34	5
95°	40	129	691	202	135	42
105°	135	200	938	1639	1483	144
115°	239	298	717	1572	1804	237
125°	332	392	669	1213	1422	295
135°	389	465	660	999	1153	301
145°	444	509	652	819	901	278
155°	505	545	631	717	747	232
165°	552	567	604	641	652	155
175°	575	575	580	588	586	55
180°	576	576	576	576	576	

TEST NUMBER: P1012453

CATALOG NUMBER: S123RDIP-B340D1195UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	561.7	561.7	561.7	561.7	561.7
2.5°	564.0	562.2	556.7	561.7	560.8
5°	561.7	559.4	554.0	558.1	557.2
7.5°	557.6	555.3	548.5	551.2	549.9
10°	552.1	549.0	540.8	541.2	538.9
12.5°	544.4	540.8	530.3	529.8	527.1
15°	535.7	530.7	518.0	515.7	512.5
17.5°	525.3	519.8	503.9	499.3	494.7
20°	513.4	506.1	488.8	482.9	477.4
22.5°	500.2	491.6	472.9	465.1	460.1
25°	487.5	476.1	455.1	445.5	440.5
27.5°	472.0	459.7	436.9	424.1	416.4
30°	456.0	442.4	416.8	401.4	394.1
32.5°	440.1	424.1	396.8	379.5	371.7
35°	421.9	405.5	377.2	357.6	349.4
37.5°	403.6	385.9	356.3	334.4	324.4
40°	386.3	366.3	333.9	310.2	299.8
42.5°	366.7	346.7	313.0	286.5	277.4
45°	346.7	326.2	291.1	265.1	254.2
47.5°	327.1	304.3	269.7	241.4	231.9
50°	305.2	283.8	246.9	218.7	208.2
52.5°	285.6	261.9	225.5	195.9	186.8
55°	263.3	241.0	202.3	175.8	166.7
57.5°	243.3	219.1	179.9	154.9	147.1
60°	222.3	197.3	159.4	134.8	127.1
62.5°	201.4	176.3	138.5	115.7	107.5
65°	179.9	154.9	119.4	97.0	92.0
67.5°	158.5	133.0	98.4	81.5	76.1
70°	137.6	113.0	81.1	65.1	60.1
72.5°	116.6	92.5	64.2	51.9	50.6
75°	95.2	73.3	48.3	43.7	42.8
77.5°	75.6	55.6	37.8	35.1	34.2
80°	56.9	38.3	28.7	27.3	26.4
82.5°	39.2	23.7	20.5	19.1	19.1
85°	24.1	14.1	12.8	11.8	11.8
87.5°	10.9	5.9	5.9	5.5	5.0
90°	2.3	14.0	29.2	32.6	33.8
92.5°	17.5	70.0	216.9	74.0	61.8
95°	39.6	128.8	691.4	201.7	135.3
97.5°	63.0	147.5	1063.4	507.2	277.5
100°	86.3	162.6	1104.2	1061.1	731.1
102.5°	110.8	180.1	1028.4	1420.8	1157.9
105°	135.3	200.0	937.5	1639.4	1483.2
107.5°	160.9	223.3	857.0	1735.6	1695.4
110°	188.9	247.2	790.6	1738.5	1816.6

TEST NUMBER: P1012453

CATALOG NUMBER: S123RDIP-B340D1195UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	214.5	272.2	746.2	1672.6	1841.1
115°	239.0	298.0	717.1	1572.4	1803.8
117.5°	263.5	322.4	697.3	1465.1	1722.2
120°	289.2	346.9	684.4	1363.6	1614.9
122.5°	311.3	370.2	676.3	1283.8	1514.7
125°	332.3	392.4	669.3	1212.6	1422.5
127.5°	348.6	413.4	665.8	1154.4	1343.2
130°	363.8	432.0	662.3	1100.8	1278.0
132.5°	375.5	449.0	661.1	1050.6	1213.8
135°	389.4	464.6	660.0	998.7	1153.2
137.5°	402.3	477.5	657.6	949.8	1089.1
140°	415.1	489.2	656.5	901.9	1021.4
142.5°	429.1	499.6	654.1	858.2	958.5
145°	444.3	509.0	651.8	819.1	901.3
147.5°	459.4	518.8	648.3	788.8	852.4
150°	474.6	527.0	643.6	762.0	810.4
152.5°	489.7	535.8	637.8	738.6	775.4
155°	504.9	544.6	630.8	717.1	747.4
157.5°	516.5	552.1	625.0	696.1	720.6
160°	530.5	558.6	618.0	676.9	694.9
162.5°	541.0	563.2	611.0	658.8	671.6
165°	551.5	567.2	604.0	640.7	651.8
167.5°	559.7	570.8	597.0	625.0	632.0
170°	566.7	572.5	590.0	611.0	614.5
172.5°	571.3	574.2	584.2	598.8	598.2
175°	574.8	575.4	579.5	587.7	586.5
177.5°	577.2	576.0	576.0	580.7	578.3
180°	576.0	576.0	576.0	576.0	576.0

(END OF REPORT)