

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012095

Luminaire Tested: S123DIP-B775D805UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012095
REPORT IS A COMBINATION OF REPORTS P990500 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D805UB35-4F0-XX-W2A-F4
Description: Define 3 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6058.6 lumens
Efficiency: N/A
Efficacy: 106.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012095

CATALOG NUMBER: S123DIP-B775D805UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012095

CATALOG NUMBER: S123DIP-B775D805UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	49
2	90	82	76	71	83	76	71	66	65	61	58	55	52	49	46	43	42
3	82	72	65	59	75	67	61	55	57	52	48	49	45	42	40	38	35
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	27
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23
7	58	46	38	32	54	43	36	31	37	32	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13235	13235	13235
5°	13268	12778	12759
10°	13150	12346	12219
15°	12967	11895	11631
20°	12757	11396	11047
25°	12486	10870	10424
30°	12190	10325	9768
35°	11879	9767	9117
40°	11552	9183	8475
45°	11195	8612	7806
50°	10832	7977	7134
55°	10364	7316	6452
60°	9882	6586	5728
65°	9430	5797	4971
70°	8779	4922	4090
75°	7844	3897	3175
80°	6775	2739	2245
85°	5283	1473	1124

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11195 cd/sqm

TEST NUMBER: P1012095

CATALOG NUMBER: S123DIP-B775D805UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.9	1.9
10°-20°	327.3	5.4
20°-30°	483.4	8.0
30°-40°	564.6	9.3
40°-50°	567.5	9.4
50°-60°	498.6	8.2
60°-70°	371.3	6.1
70°-80°	211.3	3.5
80°-90°	62.2	1.0
90°-100°	215.3	3.6
100°-110°	601.8	9.9
110°-120°	586.8	9.7
120°-130°	467.2	7.7
130°-140°	368.8	6.1
140°-150°	275.2	4.5
150°-160°	192.0	3.2
160°-170°	112.8	1.9
170°-180°	36.7	0.6
0°-30°	926.6	15.3
0°-40°	1491.2	24.6
0°-60°	2557.3	42.2
0°-90°	3202.1	52.9
90°-120°	1403.9	23.2
90°-150°	2515.1	41.5
90°-180°	2857.0	47.2
0°-180°	6058.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1231	1225	1214	1224	1222	117
15°	1171	1167	1153	1162	1156	330
25°	1064	1057	1044	1044	1041	490
35°	920	913	900	893	888	575
45°	754	750	736	723	718	582
55°	572	571	557	546	540	512
65°	390	385	374	366	363	385
75°	206	202	199	194	190	220
85°	55	53	53	51	51	59
90°	2	9	19	21	22	6
95°	26	85	455	133	89	28
105°	89	132	617	1078	976	94
115°	157	196	472	1034	1186	156
125°	219	258	440	798	936	194
135°	256	306	434	657	758	198
145°	292	335	429	539	593	183
155°	332	358	415	472	492	153
165°	363	373	397	421	429	102
175°	378	378	381	386	386	36
180°	379	379	379	379	379	

TEST NUMBER: P1012095

CATALOG NUMBER: S123DIP-B775D805UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1229.6	1229.6	1229.6	1229.6	1229.6
2.5°	1234.8	1230.6	1219.0	1229.6	1228.5
5°	1230.6	1225.3	1213.7	1224.3	1222.2
7.5°	1221.1	1215.8	1204.2	1213.7	1212.6
10°	1208.4	1203.1	1189.4	1198.9	1196.8
12.5°	1191.5	1187.3	1174.6	1180.9	1179.9
15°	1171.4	1167.2	1153.4	1161.9	1155.6
17.5°	1149.2	1143.9	1130.2	1136.5	1134.4
20°	1123.8	1117.5	1103.7	1108.0	1104.8
22.5°	1095.3	1088.9	1075.2	1078.4	1074.1
25°	1063.6	1057.2	1043.5	1044.5	1041.4
27.5°	1030.8	1024.5	1009.7	1010.7	1007.5
30°	994.9	989.6	974.8	974.8	967.4
32.5°	958.9	951.5	940.9	933.5	930.4
35°	919.8	913.4	899.7	893.4	888.1
37.5°	880.7	872.2	858.5	851.1	847.9
40°	839.4	833.1	818.3	809.8	805.6
42.5°	798.2	790.8	776.0	767.5	763.3
45°	753.8	749.6	735.8	723.1	717.9
47.5°	710.5	704.1	691.4	678.7	674.5
50°	666.1	660.8	647.0	635.4	629.1
52.5°	619.5	616.4	601.6	592.0	585.7
55°	572.0	570.9	557.2	545.5	540.2
57.5°	527.6	523.3	512.8	502.2	495.8
60°	478.9	477.9	465.2	455.7	450.4
62.5°	435.6	432.4	419.7	410.2	407.0
65°	390.1	384.8	374.3	365.8	362.6
67.5°	341.5	337.3	328.8	321.4	317.2
70°	298.1	291.8	285.5	278.1	272.8
72.5°	252.7	248.4	241.0	234.7	232.6
75°	206.2	201.9	198.8	193.5	190.3
77.5°	164.9	162.8	158.6	154.4	154.4
80°	124.8	121.6	119.5	118.4	118.4
82.5°	85.6	85.6	85.6	83.5	82.5
85°	55.0	52.9	52.9	50.7	50.7
87.5°	27.5	24.3	23.3	22.2	22.2
90°	1.5	9.2	19.2	21.4	22.2
92.5°	11.5	46.0	142.7	48.7	40.6
95°	26.1	84.8	454.8	132.7	89.0
97.5°	41.4	97.0	699.5	333.6	182.5
100°	56.8	107.0	726.3	698.0	480.9
102.5°	72.9	118.5	676.4	934.5	761.6
105°	89.0	131.5	616.6	1078.4	975.6
107.5°	105.8	146.8	563.7	1141.6	1115.1
110°	124.2	162.6	520.0	1143.6	1194.9



TEST NUMBER: P1012095

CATALOG NUMBER: S123DIP-B775D805UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.1	179.0	490.8	1100.2	1211.0
115°	157.2	196.0	471.7	1034.2	1186.5
117.5°	173.3	212.0	458.6	963.6	1132.8
120°	190.2	228.2	450.2	897.0	1062.2
122.5°	204.8	243.6	444.8	844.4	996.3
125°	218.6	258.0	440.2	797.6	935.7
127.5°	229.3	271.8	437.9	759.3	883.5
130°	239.3	284.2	435.6	724.0	840.6
132.5°	247.0	295.2	434.9	691.0	798.4
135°	256.2	305.6	434.1	656.8	758.5
137.5°	264.6	314.1	432.6	624.7	716.3
140°	273.0	321.7	431.8	593.2	671.8
142.5°	282.2	328.6	430.3	564.5	630.4
145°	292.2	334.8	428.7	538.8	592.8
147.5°	302.2	341.3	426.4	518.8	560.6
150°	312.1	346.7	423.4	501.2	533.0
152.5°	322.1	352.4	419.5	485.8	510.0
155°	332.1	358.2	414.9	471.7	491.6
157.5°	339.8	363.2	411.1	457.8	474.0
160°	349.0	367.4	406.5	445.2	457.1
162.5°	355.9	370.4	401.9	433.3	441.8
165°	362.8	373.1	397.3	421.4	428.7
167.5°	368.1	375.4	392.7	411.0	415.7
170°	372.7	376.6	388.1	401.8	404.2
172.5°	375.8	377.7	384.2	393.8	393.4
175°	378.1	378.5	381.2	386.5	385.8
177.5°	379.6	378.9	378.9	381.9	380.4
180°	378.9	378.9	378.9	378.9	378.9

(END OF REPORT)