

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012459

Luminaire Tested: S123RDIP-B340D1195UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012459
REPORT IS A COMBINATION OF REPORTS P993192 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D1195UB40-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5559.0 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012459

CATALOG NUMBER: S123RDIP-B340D1195UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012459

CATALOG NUMBER: S123RDIP-B340D1195UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	31	31	23
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	26	26	26	19
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22	22	22	16
3	76	67	61	55	67	60	54	50	46	42	39	34	31	29	22	20	19	19	19	14
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	19	18	17	17	17	12
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15	15	15	11
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	13	13	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	11	11	11	8
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	13	12	10	10	10	8
9	47	35	28	23	41	32	25	21	25	20	17	18	15	13	12	11	9	9	9	7
10	43	32	25	21	39	29	23	19	23	18	15	17	14	12	11	10	8	8	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5985	5985	5985
5°	5994	5773	5756
10°	5947	5555	5446
15°	5870	5288	5106
20°	5769	4995	4725
25°	5664	4692	4364
30°	5529	4370	3938
35°	5392	4053	3550
40°	5263	3709	3121
45°	5095	3372	2736
50°	4913	3013	2337
55°	4722	2629	1971
60°	4540	2234	1600
65°	4305	1829	1249
70°	4011	1384	892
75°	3583	937	707
80°	3062	651	497
85°	2296	351	259

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5095 cd/sqm

TEST NUMBER: P1012459

CATALOG NUMBER: S123RDIP-B340D1195UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.3	0.9
10°-20°	145.4	2.6
20°-30°	209.3	3.8
30°-40°	235.7	4.2
40°-50°	225.5	4.1
50°-60°	184.6	3.3
60°-70°	124.4	2.2
70°-80°	62.4	1.1
80°-90°	19.5	0.4
90°-100°	324.1	5.8
100°-110°	905.8	16.3
110°-120°	883.3	15.9
120°-130°	703.3	12.7
130°-140°	555.2	10.0
140°-150°	414.2	7.5
150°-160°	289.0	5.2
160°-170°	169.8	3.1
170°-180°	55.2	1.0
0°-30°	407.0	7.3
0°-40°	642.7	11.6
0°-60°	1052.8	18.9
0°-90°	1259.2	22.7
90°-120°	2113.2	38.0
90°-150°	3785.9	68.1
90°-180°	4300.0	77.4
0°-180°	5559.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	556	556	556	556	556	
5°	556	554	548	552	551	53
15°	530	525	513	510	507	149
25°	482	471	450	441	436	222
35°	418	401	373	354	346	261
45°	343	323	288	262	252	265
55°	261	238	200	174	165	234
65°	178	153	118	96	91	176
75°	94	73	48	43	42	100
85°	24	14	13	12	12	26
90°	2	14	29	32	34	4
95°	39	128	685	200	134	42
105°	134	198	928	1623	1468	142
115°	237	295	710	1557	1786	234
125°	329	388	663	1201	1408	292
135°	386	460	653	989	1142	298
145°	440	504	645	811	892	276
155°	500	539	625	710	740	230
165°	546	562	598	634	645	154
175°	569	570	574	582	581	54
180°	570	570	570	570	570	

TEST NUMBER: P1012459

CATALOG NUMBER: S123RDIP-B340D1195UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	556.0	556.0	556.0	556.0	556.0
2.5°	558.2	556.4	551.0	556.0	555.1
5°	556.0	553.7	548.3	552.3	551.4
7.5°	551.9	549.6	542.9	545.6	544.2
10°	546.5	543.3	535.2	535.7	533.4
12.5°	538.8	535.2	524.8	524.4	521.7
15°	530.3	525.3	512.7	510.4	507.3
17.5°	519.9	514.5	498.7	494.2	489.7
20°	508.2	500.9	483.8	477.9	472.5
22.5°	495.1	486.5	468.0	460.4	455.4
25°	482.5	471.2	450.4	441.0	436.0
27.5°	467.1	455.0	432.4	419.8	412.1
30°	451.3	437.8	412.6	397.2	390.0
32.5°	435.6	419.8	392.7	375.6	367.9
35°	417.5	401.3	373.3	354.0	345.8
37.5°	399.5	381.9	352.6	331.0	321.0
40°	382.4	362.5	330.5	307.1	296.7
42.5°	363.0	343.1	309.8	283.6	274.6
45°	343.1	322.8	288.1	262.4	251.6
47.5°	323.7	301.2	266.9	239.0	229.5
50°	302.1	280.9	244.4	216.4	206.1
52.5°	282.7	259.3	223.2	193.9	184.9
55°	260.6	238.5	200.2	174.0	165.0
57.5°	240.8	216.9	178.1	153.3	145.6
60°	220.0	195.2	157.8	133.5	125.8
62.5°	199.3	174.5	137.1	114.5	106.4
65°	178.1	153.3	118.1	96.0	91.1
67.5°	156.9	131.7	97.4	80.7	75.3
70°	136.2	111.8	80.3	64.5	59.5
72.5°	115.4	91.5	63.6	51.4	50.0
75°	94.2	72.6	47.8	43.3	42.4
77.5°	74.8	55.0	37.4	34.7	33.8
80°	56.4	37.9	28.4	27.1	26.2
82.5°	38.8	23.4	20.3	18.9	18.9
85°	23.9	14.0	12.6	11.7	11.7
87.5°	10.8	5.9	5.9	5.4	5.0
90°	2.3	13.8	28.9	32.4	33.5
92.5°	17.3	69.3	214.7	73.3	61.2
95°	39.3	127.6	684.6	199.7	133.9
97.5°	62.3	146.0	1052.9	502.2	274.8
100°	85.4	161.0	1093.3	1050.6	723.8
102.5°	109.7	178.4	1018.2	1406.7	1146.4
105°	133.9	198.0	928.2	1623.2	1468.5
107.5°	159.3	221.0	848.5	1718.4	1678.6
110°	187.0	244.8	782.7	1721.3	1798.6

TEST NUMBER: P1012459

CATALOG NUMBER: S123RDIP-B340D1195UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	212.4	269.6	738.8	1656.0	1822.9
115°	236.7	295.0	710.0	1556.8	1785.9
117.5°	260.9	319.2	690.4	1450.6	1705.1
120°	286.3	343.4	677.7	1350.1	1598.9
122.5°	308.2	366.6	669.6	1271.1	1499.6
125°	329.0	388.5	662.7	1200.6	1408.4
127.5°	345.2	409.2	659.2	1142.9	1329.9
130°	360.2	427.7	655.7	1089.8	1265.3
132.5°	371.7	444.5	654.6	1040.2	1201.8
135°	385.6	460.0	653.4	988.8	1141.8
137.5°	398.3	472.8	651.1	940.3	1078.3
140°	411.0	484.3	650.0	893.0	1011.3
142.5°	424.8	494.7	647.6	849.7	949.0
145°	439.8	503.9	645.3	811.0	892.4
147.5°	454.9	513.8	641.9	781.0	843.9
150°	469.9	521.8	637.3	754.4	802.3
152.5°	484.9	530.5	631.5	731.4	767.7
155°	499.9	539.1	624.6	710.0	740.0
157.5°	511.4	546.6	618.8	689.2	713.5
160°	525.3	553.0	611.9	670.2	688.1
162.5°	535.7	557.6	604.9	652.2	665.0
165°	546.1	561.7	598.0	634.4	645.3
167.5°	554.1	565.1	591.1	618.8	625.7
170°	561.1	566.8	584.2	605.0	608.4
172.5°	565.7	568.6	578.4	592.8	592.2
175°	569.1	569.7	573.8	581.8	580.7
177.5°	571.5	570.3	570.3	574.9	572.6
180°	570.3	570.3	570.3	570.3	570.3

(END OF REPORT)