

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012098

Luminaire Tested: S123DIP-B775D805UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012098
REPORT IS A COMBINATION OF REPORTS P990503 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D805UB40-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6083.0 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012098

CATALOG NUMBER: S123DIP-B775D805UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1012098

CATALOG NUMBER: S123DIP-B775D805UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	87	92	88	85	82	75	73	71	64	62	60	53	52	51
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	47	45	43
3	83	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32
5	69	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28
6	64	52	44	38	59	49	41	36	42	37	32	36	32	29	31	27	25
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20
9	51	39	32	27	48	37	30	25	32	27	23	28	23	20	24	20	18
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11626	11626	11626	11626
5°	11634	13396	11668	9998
10°	11560	16210	11572	8730
15°	11400	19225	11493	7859
20°	11263	22134	11287	7231
25°	11059	22692	11084	6904
30°	10913	18748	10913	6689
35°	10732	12538	10665	6500
40°	10515	9051	10385	6210
45°	10243	7170	9947	5850
50°	9583	6088	9241	5495
55°	8857	5351	8496	5100
60°	8120	4658	7688	4685
65°	7313	3989	6957	4132
70°	6473	3311	6040	3485
75°	5535	2497	5177	2689
80°	4376	1667	4034	1768
85°	3016	765	2411	696

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 18751 cd/sqm

TEST NUMBER: P1012098

CATALOG NUMBER: S123DIP-B775D805UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.2	1.7
10°-20°	341.2	5.6
20°-30°	574.1	9.4
30°-40°	648.8	10.7
40°-50°	581.1	9.6
50°-60°	469.1	7.7
60°-70°	326.9	5.4
70°-80°	171.6	2.8
80°-90°	43.2	0.7
90°-100°	203.5	3.3
100°-110°	595.8	9.8
110°-120°	581.8	9.6
120°-130°	463.4	7.6
130°-140°	365.6	6.0
140°-150°	272.7	4.5
150°-160°	190.1	3.1
160°-170°	111.7	1.8
170°-180°	36.3	0.6
0°-30°	1021.5	16.8
0°-40°	1670.3	27.5
0°-60°	2720.4	44.7
0°-90°	3262.1	53.6
90°-120°	1381.1	22.7
90°-150°	2482.7	40.8
90°-180°	2821.0	46.4
0°-180°	6083.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1080	1080	1080	1080	1080	
5°	1079	1283	1082	958	1079	102
15°	1030	1910	1038	781	1030	291
25°	942	2267	944	690	942	435
35°	831	1221	826	633	831	520
45°	690	659	670	538	690	528
55°	489	448	469	427	489	438
65°	302	291	288	301	302	301
75°	146	150	136	161	146	156
85°	31	34	25	31	31	36
90°	2	22	2	22	2	4
95°	26	88	26	88	26	27
105°	88	966	88	966	88	94
115°	156	1174	156	1174	156	154
125°	216	926	216	926	216	192
135°	254	751	254	751	254	196
145°	289	587	289	587	289	181
155°	329	487	329	487	329	151
165°	359	424	359	424	359	101
175°	374	382	374	382	374	36
180°	375	375	375	375	375	

TEST NUMBER: P1012098

CATALOG NUMBER: S123DIP-B775D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1
2.5°	1083.3	1091.6	1095.8	1102.1	1108.4	1117.8	1120.9	1126.2	1124.1	1128.3	1130.4
5°	1079.1	1093.7	1106.3	1122.0	1136.6	1147.1	1157.6	1174.3	1186.9	1189.0	1198.4
7.5°	1071.8	1092.7	1114.7	1136.6	1164.9	1181.7	1200.5	1223.5	1242.4	1272.7	1284.2
10°	1062.3	1091.6	1123.0	1153.4	1192.1	1218.3	1241.3	1280.0	1318.8	1350.2	1379.5
12.5°	1047.7	1084.3	1125.1	1170.1	1220.4	1250.7	1282.1	1333.4	1392.0	1440.2	1471.6
15°	1029.9	1075.9	1128.3	1176.4	1231.9	1288.4	1321.9	1379.5	1463.2	1508.2	1588.8
17.5°	1015.2	1062.3	1114.7	1190.0	1265.4	1321.9	1346.0	1451.7	1509.2	1584.6	1675.7
20°	992.2	1051.9	1118.9	1194.2	1291.5	1326.1	1375.3	1482.0	1553.2	1651.6	1763.6
22.5°	968.1	1032.0	1112.6	1191.1	1299.9	1336.6	1403.5	1488.3	1601.4	1698.7	1822.2
25°	942.0	1011.1	1092.7	1185.8	1292.6	1346.0	1408.8	1513.4	1635.9	1758.3	1872.4
27.5°	915.8	991.2	1075.9	1169.1	1272.7	1335.5	1398.3	1507.2	1664.2	1797.1	1942.6
30°	890.7	966.0	1050.8	1146.1	1254.9	1315.6	1375.3	1511.3	1686.1	1835.8	1982.3
32.5°	863.5	940.9	1029.9	1109.4	1219.3	1284.2	1351.2	1511.3	1699.7	1858.8	1992.8
35°	831.0	910.6	987.0	1066.5	1175.4	1247.6	1322.9	1500.9	1712.3	1866.2	1948.8
37.5°	799.6	869.8	935.7	1013.1	1127.2	1204.7	1291.5	1488.3	1706.0	1834.8	1857.8
40°	764.0	834.2	887.5	959.8	1080.1	1170.1	1258.1	1471.6	1678.8	1760.4	1693.5
42.5°	729.5	785.0	831.0	901.2	1032.0	1119.9	1215.1	1441.2	1625.4	1642.2	1491.5
45°	689.7	729.5	770.3	849.9	979.7	1069.7	1175.4	1397.3	1539.6	1491.5	1301.0
47.5°	638.4	674.0	719.0	792.3	924.2	1017.3	1117.8	1340.7	1415.1	1314.6	1106.3
50°	589.3	619.6	661.5	732.6	865.6	956.6	1063.4	1251.8	1288.4	1130.4	953.5
52.5°	540.1	563.1	603.9	675.1	808.0	895.9	993.3	1160.7	1139.8	970.2	813.2
55°	488.8	508.7	547.4	617.5	741.0	824.7	917.9	1048.7	994.3	833.1	707.5
57.5°	438.5	459.5	499.2	557.9	674.0	755.7	830.0	932.6	850.9	722.2	611.2
60°	393.5	411.3	441.7	499.2	605.0	670.9	738.9	809.0	741.0	616.5	531.7
62.5°	346.4	363.2	391.4	443.8	534.8	593.4	647.9	705.4	630.1	539.0	463.7
65°	302.5	316.1	342.2	390.4	464.7	512.9	556.8	596.6	535.9	452.1	395.6
67.5°	262.7	274.2	296.2	339.1	401.9	436.4	472.0	505.5	454.2	387.3	339.1
70°	219.8	229.2	249.1	280.5	330.7	366.3	392.5	417.6	371.6	318.2	285.7
72.5°	182.1	191.5	204.1	236.5	271.1	293.1	321.3	334.9	308.8	264.8	232.4
75°	145.5	152.8	164.3	185.3	217.7	232.4	250.1	260.6	236.5	207.2	187.3
77.5°	114.1	117.2	125.6	140.2	162.2	179.0	192.6	198.9	182.1	163.3	146.5
80°	80.6	84.8	91.1	103.6	120.4	125.6	134.0	141.3	130.8	114.1	103.6
82.5°	53.4	58.6	61.8	67.0	77.5	83.7	85.8	92.1	82.7	76.4	72.2
85°	31.4	33.5	34.5	37.7	42.9	46.1	49.2	50.2	48.1	47.1	42.9
87.5°	15.7	15.7	15.7	17.8	18.8	20.9	22.0	22.0	22.0	20.9	19.9
90°	1.5	3.0	4.6	6.8	8.4	9.2	9.9	12.1	14.4	16.7	19.0
92.5°	11.4	16.7	24.3	31.1	38.7	45.6	52.4	76.7	116.9	156.4	141.2
95°	25.8	28.1	36.4	49.3	69.1	83.9	98.7	163.2	276.3	400.8	450.2
97.5°	41.0	41.8	48.6	60.0	79.7	96.1	112.4	176.1	307.5	517.0	692.3
100°	56.2	56.9	62.2	72.9	91.1	105.9	120.7	173.8	286.2	485.9	718.9
102.5°	72.1	73.6	78.2	88.1	104.0	117.3	130.6	176.9	268.0	440.3	669.6
105°	88.1	90.3	94.9	104.0	118.4	130.2	142.0	183.0	261.1	404.6	610.4
107.5°	104.8	107.0	111.6	120.7	134.4	145.4	156.4	192.8	259.6	378.8	558.0
110°	123.0	125.3	129.1	137.4	150.3	161.0	171.6	205.7	263.4	365.1	514.7

TEST NUMBER: P1012098

CATALOG NUMBER: S123DIP-B775D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	139.7	142.0	145.8	154.1	167.0	177.2	187.5	218.6	271.0	357.6	485.9
115°	155.6	158.7	163.2	170.8	183.7	194.0	204.2	233.1	279.4	356.8	466.9
117.5°	171.6	175.4	179.2	186.0	200.4	209.9	219.4	248.2	290.0	357.6	454.0
120°	188.3	190.5	194.3	201.9	216.4	225.8	235.3	262.7	302.1	360.6	445.6
122.5°	202.7	205.0	208.8	217.1	230.8	241.0	251.3	277.8	313.5	365.9	440.3
125°	216.4	217.9	222.4	230.8	245.2	255.4	265.7	292.3	325.7	371.2	435.7
127.5°	227.0	229.3	234.6	242.9	258.9	269.2	279.4	305.2	335.5	377.3	433.5
130°	236.9	239.1	246.0	255.1	271.0	281.2	291.5	316.6	345.4	383.4	431.2
132.5°	244.4	247.5	255.1	266.5	282.4	292.2	302.1	326.4	354.5	387.9	430.4
135°	253.6	256.6	264.9	276.3	292.3	302.6	312.8	336.3	362.1	392.5	429.7
137.5°	261.9	264.9	273.3	285.4	301.4	310.9	320.4	343.1	368.2	395.5	428.2
140°	270.3	274.1	281.6	293.8	309.0	318.5	328.0	350.0	372.7	398.6	427.4
142.5°	279.4	282.4	290.8	301.4	316.6	325.3	334.0	355.3	377.3	400.8	425.9
145°	289.2	291.5	298.3	309.7	322.6	331.4	340.1	359.8	380.3	401.6	424.4
147.5°	299.1	300.6	307.5	317.3	330.2	337.8	345.4	363.6	382.6	401.6	422.1
150°	309.0	309.7	315.8	325.7	336.3	343.2	350.0	367.4	383.4	401.6	419.0
152.5°	318.8	318.8	324.9	333.3	342.4	348.8	355.3	369.7	384.9	399.3	415.3
155°	328.7	328.7	333.3	340.9	349.2	354.5	359.8	372.7	384.9	397.8	410.7
157.5°	336.3	337.1	340.9	347.7	355.3	359.5	363.6	374.3	385.6	395.5	406.9
160°	345.4	345.4	348.4	354.5	359.8	363.6	367.4	376.5	385.6	394.0	402.3
162.5°	352.2	352.2	354.5	359.1	363.6	366.6	369.7	377.3	384.9	391.0	397.8
165°	359.1	358.3	359.8	363.6	366.7	369.4	372.0	378.1	383.4	387.9	393.2
167.5°	364.4	363.6	364.4	367.4	369.7	371.6	373.5	378.1	382.6	384.9	388.7
170°	368.9	367.4	368.2	370.5	372.0	372.8	373.5	377.3	380.3	381.9	384.1
172.5°	372.0	371.2	371.2	372.7	373.5	373.9	374.3	377.3	379.6	379.6	380.3
175°	374.3	373.5	372.7	374.3	374.3	374.6	375.0	376.5	378.1	377.3	377.3
177.5°	375.8	375.0	374.3	375.0	375.0	375.0	375.0	375.8	377.3	375.8	375.0
180°	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0

TEST NUMBER: P1012098

CATALOG NUMBER: S123DIP-B775D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1
2.5°	1137.7	1139.8	1147.1	1152.3	1162.8	1161.8	1161.8	1160.7	1157.6	1162.8	1166.0
5°	1217.2	1235.0	1237.1	1260.1	1261.2	1270.6	1276.9	1271.7	1284.2	1283.2	1273.8
7.5°	1315.6	1339.7	1351.2	1373.2	1398.3	1392.0	1416.1	1420.3	1418.2	1428.7	1436.0
10°	1423.4	1465.3	1494.6	1535.4	1545.9	1552.2	1567.9	1581.5	1608.7	1587.7	1601.4
12.5°	1546.9	1577.3	1616.0	1680.9	1713.3	1734.3	1741.6	1751.0	1769.9	1758.3	1759.4
15°	1650.5	1691.4	1757.3	1837.9	1847.3	1873.5	1867.2	1923.7	1950.9	1910.1	1933.1
17.5°	1758.3	1812.8	1891.3	1961.4	2001.2	2019.0	2035.7	2090.1	2088.0	2081.8	2087.0
20°	1827.4	1916.4	2013.7	2106.9	2118.4	2132.0	2177.0	2200.0	2195.8	2213.6	2225.1
22.5°	1924.8	2019.0	2122.6	2184.3	2210.5	2226.2	2261.8	2276.4	2282.7	2286.9	2279.6
25°	2006.4	2106.9	2183.3	2237.7	2253.4	2261.8	2273.3	2277.5	2274.3	2267.0	2273.3
27.5°	2061.9	2142.5	2194.8	2219.9	2211.5	2197.9	2176.0	2161.3	2128.9	2113.2	2132.0
30°	2084.9	2120.5	2136.2	2094.3	2052.5	2019.0	1977.1	1899.6	1838.9	1856.7	1832.7
32.5°	2048.3	2025.2	1949.9	1842.1	1809.6	1755.2	1636.9	1545.9	1549.0	1500.9	1520.8
35°	1940.5	1835.8	1693.5	1530.2	1487.3	1458.0	1328.2	1308.3	1266.4	1221.4	1234.0
37.5°	1750.0	1597.2	1424.5	1304.1	1240.3	1176.4	1103.2	1059.2	1034.1	1015.2	1029.9
40°	1517.6	1331.3	1189.0	1081.2	1026.7	985.9	935.7	891.7	863.5	860.3	865.6
42.5°	1289.5	1132.5	1001.6	899.1	881.3	833.1	800.7	766.1	757.8	744.2	751.5
45°	1091.6	964.0	856.1	772.4	751.5	738.9	699.2	677.2	667.8	659.4	671.9
47.5°	948.3	814.3	735.8	685.5	664.6	643.7	621.7	607.0	599.7	600.8	599.7
50°	810.1	711.7	642.6	603.9	591.3	576.7	558.9	549.5	546.3	536.9	544.3
52.5°	697.1	625.9	577.7	541.1	531.7	521.2	506.6	501.3	494.0	491.9	491.9
55°	606.0	550.5	511.8	487.7	476.2	467.8	459.5	453.2	448.0	448.0	448.0
57.5°	534.8	486.7	458.4	437.5	433.3	424.9	415.5	415.5	408.2	407.1	410.3
60°	474.1	431.2	409.2	391.4	385.2	383.1	373.6	373.6	371.6	366.3	370.5
62.5°	412.4	381.0	362.1	348.5	342.2	342.2	334.9	329.7	329.7	330.7	328.6
65°	355.9	332.8	316.1	305.6	302.5	298.3	297.2	293.1	289.9	291.0	289.9
67.5°	305.6	287.8	276.3	267.9	262.7	260.6	257.5	257.5	255.4	256.4	251.2
70°	260.6	242.8	233.4	225.0	222.9	222.9	218.7	219.8	217.7	220.8	218.7
72.5°	214.6	201.0	193.6	190.5	188.4	187.3	185.3	183.2	182.1	184.2	183.2
75°	173.7	162.2	157.0	154.9	152.8	152.8	151.8	150.7	149.7	149.7	149.7
77.5°	135.0	127.7	121.4	123.5	120.4	121.4	118.3	118.3	119.3	118.3	118.3
80°	99.4	94.2	94.2	92.1	87.9	90.0	90.0	86.9	85.8	87.9	84.8
82.5°	65.9	64.9	62.8	61.8	59.7	60.7	59.7	58.6	57.6	59.7	57.6
85°	38.7	38.7	37.7	35.6	37.7	36.6	35.6	35.6	34.5	34.5	34.5
87.5°	19.9	17.8	17.8	16.7	17.8	15.7	16.7	15.7	14.7	15.7	14.7
90°	18.2	19.0	19.7	20.5	21.2	22.0	21.3	22.0	22.8	22.0	22.8
92.5°	105.5	75.2	58.5	50.9	48.2	45.5	44.0	41.0	41.8	40.2	41.8
95°	365.1	273.3	185.2	145.0	131.4	117.7	103.2	96.4	91.1	88.1	91.1
97.5°	715.9	627.8	473.7	373.5	330.2	287.0	236.1	207.2	189.0	180.7	189.0
100°	868.5	895.0	833.5	744.7	690.8	636.9	560.2	504.8	475.2	476.0	475.2
102.5°	876.1	983.9	996.8	954.2	925.0	895.8	840.4	799.4	775.8	753.8	775.8
105°	828.2	986.9	1062.8	1077.2	1067.4	1057.5	1022.6	993.7	969.4	965.6	969.4
107.5°	759.9	941.3	1060.5	1119.7	1130.0	1140.2	1135.7	1122.0	1112.1	1103.8	1112.1
110°	696.1	870.0	1009.7	1105.3	1131.9	1158.5	1179.7	1185.8	1184.3	1182.7	1184.3

TEST NUMBER: P1012098

CATALOG NUMBER: S123DIP-B775D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	640.7	799.4	942.9	1052.9	1089.0	1125.1	1168.3	1190.3	1197.9	1198.7	1197.9
115°	598.2	738.6	870.7	982.3	1023.7	1065.1	1122.0	1155.4	1170.6	1174.4	1170.6
117.5°	570.1	691.6	808.5	911.0	953.9	996.8	1056.0	1093.2	1115.9	1121.3	1115.9
120°	548.9	655.9	758.4	849.5	887.8	926.2	986.1	1028.6	1046.9	1051.4	1046.9
122.5°	531.4	627.8	718.2	800.9	835.8	870.7	922.4	959.6	980.1	986.1	980.1
125°	517.0	603.5	686.3	759.1	789.5	819.9	868.5	901.9	920.8	926.2	920.8
127.5°	503.3	581.5	656.7	723.5	751.6	779.6	823.7	852.5	870.0	874.5	870.0
130°	492.7	561.0	629.3	690.8	716.6	742.4	782.7	810.0	826.0	832.0	826.0
132.5°	482.8	542.0	603.5	659.7	684.0	708.3	745.5	772.8	786.5	790.3	786.5
135°	474.5	525.3	579.2	628.6	650.2	671.8	709.0	731.8	745.5	750.8	745.5
137.5°	466.9	509.4	554.9	599.0	618.4	637.7	669.6	693.1	704.5	709.0	704.5
140°	460.0	495.7	534.4	570.9	587.2	603.5	632.4	653.6	665.8	665.0	665.8
142.5°	454.0	482.8	514.7	545.1	558.8	572.4	595.9	614.1	624.8	624.0	624.8
145°	448.7	472.9	498.0	522.3	533.3	544.3	563.3	579.2	585.3	586.8	585.3
147.5°	443.3	464.6	485.1	505.6	513.6	521.5	536.7	548.1	554.2	554.9	554.2
150°	438.0	455.5	472.9	488.9	496.1	503.3	514.7	523.1	527.6	527.6	527.6
152.5°	432.0	447.1	461.6	475.2	480.9	486.6	495.0	502.6	504.8	504.8	504.8
155°	425.9	438.8	450.9	462.3	466.8	471.4	478.3	484.3	485.9	486.6	485.9
157.5°	419.0	429.7	440.3	449.4	453.2	457.0	463.1	467.6	469.2	469.2	469.2
160°	412.2	422.1	430.4	438.0	440.6	443.3	448.7	453.2	453.2	452.5	453.2
162.5°	405.4	413.0	419.8	426.6	428.9	431.2	434.2	438.0	438.0	437.3	438.0
165°	399.3	405.4	409.9	415.3	417.2	419.0	422.1	425.1	424.4	424.4	424.4
167.5°	393.2	398.6	402.3	405.4	406.9	408.4	409.9	412.2	411.5	411.5	411.5
170°	387.9	391.7	394.0	397.0	397.8	398.6	399.3	400.8	400.1	400.1	400.1
172.5°	382.6	385.6	387.2	389.4	389.8	390.2	390.2	391.7	390.2	389.4	390.2
175°	378.8	380.3	381.1	382.6	382.6	382.6	382.6	383.4	382.6	381.9	382.6
177.5°	375.8	376.5	377.3	378.1	378.1	378.1	377.3	378.1	376.5	376.5	376.5
180°	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0

TEST NUMBER: P1012098

CATALOG NUMBER: S123DIP-B775D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1
2.5°	1157.6	1160.7	1152.3	1150.3	1150.3	1154.4	1151.3	1123.0	1128.3	1122.0	1119.9
5°	1285.3	1279.0	1270.6	1266.4	1261.2	1246.5	1245.5	1213.1	1206.8	1185.8	1176.4
7.5°	1425.5	1420.3	1395.2	1392.0	1389.9	1376.3	1341.8	1307.2	1282.1	1258.1	1235.0
10°	1585.7	1570.0	1558.4	1535.4	1523.9	1505.1	1460.1	1427.6	1384.7	1348.1	1299.9
12.5°	1778.2	1760.4	1721.7	1705.0	1690.3	1638.0	1593.0	1556.3	1472.6	1447.5	1387.8
15°	1919.5	1881.9	1877.7	1841.0	1838.9	1781.4	1695.5	1655.8	1590.9	1498.8	1437.0
17.5°	2072.3	2038.8	2012.7	1968.7	1962.4	1908.0	1845.2	1747.9	1676.7	1588.8	1510.3
20°	2184.3	2166.5	2121.5	2103.7	2067.1	2021.1	1956.2	1835.8	1748.9	1661.0	1564.7
22.5°	2273.3	2255.5	2219.9	2195.8	2174.9	2115.3	2037.8	1935.2	1815.9	1700.8	1601.4
25°	2272.2	2267.0	2252.4	2240.8	2225.1	2181.2	2116.3	2017.9	1885.0	1758.3	1620.2
27.5°	2143.5	2158.2	2183.3	2195.8	2192.7	2186.4	2149.8	2067.1	1947.8	1797.1	1642.2
30°	1875.6	1928.9	1976.0	2038.8	2057.7	2103.7	2124.7	2077.6	1982.3	1842.1	1670.4
32.5°	1555.3	1632.8	1735.3	1769.9	1829.5	1918.5	2017.9	2035.7	1976.0	1868.2	1688.2
35°	1275.8	1339.7	1419.2	1473.7	1527.0	1671.5	1797.1	1905.9	1925.8	1854.6	1684.0
37.5°	1056.1	1101.1	1171.2	1217.2	1266.4	1389.9	1565.8	1707.1	1806.5	1808.6	1672.5
40°	897.0	916.9	977.6	1011.1	1058.1	1164.9	1321.9	1506.1	1651.6	1718.6	1642.2
42.5°	759.9	786.0	836.3	861.4	891.7	984.9	1088.5	1263.3	1443.3	1586.7	1585.7
45°	678.2	697.1	720.1	741.0	775.6	831.0	949.3	1080.1	1252.8	1415.1	1478.9
47.5°	606.0	623.8	646.8	653.1	676.1	728.5	800.7	914.8	1075.9	1237.1	1357.5
50°	545.3	560.0	575.6	587.2	597.6	640.5	695.0	791.3	920.0	1075.9	1225.6
52.5°	498.2	508.7	522.3	528.6	538.0	569.4	611.2	682.4	788.1	930.5	1075.9
55°	454.2	461.6	469.9	480.4	484.6	507.6	540.1	600.8	679.3	807.0	945.1
57.5°	413.4	416.6	421.8	428.1	433.3	453.2	481.5	522.3	591.3	689.7	820.6
60°	367.4	375.7	378.9	385.2	388.3	404.0	426.0	460.5	513.9	598.7	697.1
62.5°	328.6	333.9	339.1	342.2	349.6	354.8	372.6	404.0	448.0	510.8	599.7
65°	294.1	296.2	299.3	302.5	304.6	310.9	327.6	348.5	382.0	437.5	506.6
67.5°	254.3	256.4	260.6	261.7	263.8	272.1	281.5	299.3	327.6	369.5	426.0
70°	215.6	218.7	220.8	222.9	226.1	229.2	239.7	254.3	276.3	305.6	349.6
72.5°	182.1	185.3	185.3	187.3	186.3	190.5	201.0	211.4	226.1	250.1	288.9
75°	148.6	148.6	150.7	151.8	152.8	157.0	161.2	169.6	181.1	199.9	224.0
77.5°	117.2	116.2	118.3	118.3	118.3	121.4	125.6	129.8	137.1	150.7	169.6
80°	85.8	85.8	87.9	89.0	86.9	87.9	90.0	94.2	99.4	108.9	119.3
82.5°	56.5	60.7	59.7	60.7	59.7	61.8	62.8	63.8	65.9	70.1	77.5
85°	34.5	34.5	34.5	35.6	34.5	35.6	35.6	35.6	36.6	38.7	41.9
87.5°	14.7	14.7	14.7	15.7	14.7	14.7	15.7	14.7	15.7	15.7	16.7
90°	22.0	21.3	22.0	21.2	20.5	19.7	19.0	18.2	19.0	16.7	14.4
92.5°	41.0	44.0	45.5	48.2	50.9	58.5	75.2	105.5	141.2	156.4	116.9
95°	96.4	103.2	117.7	131.4	145.0	185.2	273.3	365.1	450.2	400.8	276.3
97.5°	207.2	236.1	287.0	330.2	373.5	473.7	627.8	715.9	692.3	517.0	307.5
100°	504.8	560.2	636.9	690.8	744.7	833.5	895.0	868.5	718.9	485.9	286.2
102.5°	799.4	840.4	895.8	925.0	954.2	996.8	983.9	876.1	669.6	440.3	268.0
105°	993.7	1022.6	1057.5	1067.4	1077.2	1062.8	986.9	828.2	610.4	404.6	261.1
107.5°	1122.0	1135.7	1140.2	1130.0	1119.7	1060.5	941.3	759.9	558.0	378.8	259.6
110°	1185.8	1179.7	1158.5	1131.9	1105.3	1009.7	870.0	696.1	514.7	365.1	263.4

TEST NUMBER: P1012098

CATALOG NUMBER: S123DIP-B775D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1190.3	1168.3	1125.1	1089.0	1052.9	942.9	799.4	640.7	485.9	357.6	271.0
115°	1155.4	1122.0	1065.1	1023.7	982.3	870.7	738.6	598.2	466.9	356.8	279.4
117.5°	1093.2	1056.0	996.8	953.9	911.0	808.5	691.6	570.1	454.0	357.6	290.0
120°	1028.6	986.1	926.2	887.8	849.5	758.4	655.9	548.9	445.6	360.6	302.1
122.5°	959.6	922.4	870.7	835.8	800.9	718.2	627.8	531.4	440.3	365.9	313.5
125°	901.9	868.5	819.9	789.5	759.1	686.3	603.5	517.0	435.7	371.2	325.7
127.5°	852.5	823.7	779.6	751.6	723.5	656.7	581.5	503.3	433.5	377.3	335.5
130°	810.0	782.7	742.4	716.6	690.8	629.3	561.0	492.7	431.2	383.4	345.4
132.5°	772.8	745.5	708.3	684.0	659.7	603.5	542.0	482.8	430.4	387.9	354.5
135°	731.8	709.0	671.8	650.2	628.6	579.2	525.3	474.5	429.7	392.5	362.1
137.5°	693.1	669.6	637.7	618.4	599.0	554.9	509.4	466.9	428.2	395.5	368.2
140°	653.6	632.4	603.5	587.2	570.9	534.4	495.7	460.0	427.4	398.6	372.7
142.5°	614.1	595.9	572.4	558.8	545.1	514.7	482.8	454.0	425.9	400.8	377.3
145°	579.2	563.3	544.3	533.3	522.3	498.0	472.9	448.7	424.4	401.6	380.3
147.5°	548.1	536.7	521.5	513.6	505.6	485.1	464.6	443.3	422.1	401.6	382.6
150°	523.1	514.7	503.3	496.1	488.9	472.9	455.5	438.0	419.0	401.6	383.4
152.5°	502.6	495.0	486.6	480.9	475.2	461.6	447.1	432.0	415.3	399.3	384.9
155°	484.3	478.3	471.4	466.8	462.3	450.9	438.8	425.9	410.7	397.8	384.9
157.5°	467.6	463.1	457.0	453.2	449.4	440.3	429.7	419.0	406.9	395.5	385.6
160°	453.2	448.7	443.3	440.6	438.0	430.4	422.1	412.2	402.3	394.0	385.6
162.5°	438.0	434.2	431.2	428.9	426.6	419.8	413.0	405.4	397.8	391.0	384.9
165°	425.1	422.1	419.0	417.2	415.3	409.9	405.4	399.3	393.2	387.9	383.4
167.5°	412.2	409.9	408.4	406.9	405.4	402.3	398.6	393.2	388.7	384.9	382.6
170°	400.8	399.3	398.6	397.8	397.0	394.0	391.7	387.9	384.1	381.9	380.3
172.5°	391.7	390.2	390.2	389.8	389.4	387.2	385.6	382.6	380.3	379.6	379.6
175°	383.4	382.6	382.6	382.6	382.6	381.1	380.3	378.8	377.3	377.3	378.1
177.5°	378.1	377.3	378.1	378.1	378.1	377.3	376.5	375.8	375.0	375.8	377.3
180°	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0

TEST NUMBER: P1012098

CATALOG NUMBER: S123DIP-B775D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1
2.5°	1109.4	1106.3	1106.3	1104.2	1097.9	1086.4	1085.4	1087.5	1081.2	1074.9	1065.5
5°	1163.9	1144.0	1137.7	1131.4	1118.9	1097.9	1089.5	1082.2	1070.7	1057.1	1042.4
7.5°	1209.9	1181.7	1173.3	1161.8	1136.6	1107.3	1088.5	1072.8	1057.1	1038.3	1020.5
10°	1267.5	1226.7	1206.8	1190.0	1155.5	1114.7	1086.4	1063.4	1038.3	1015.2	992.2
12.5°	1332.4	1266.4	1260.1	1219.3	1179.6	1118.9	1084.3	1050.8	1017.3	989.1	965.0
15°	1386.8	1314.6	1288.4	1261.2	1184.8	1109.4	1075.9	1038.3	999.5	969.2	933.6
17.5°	1421.3	1361.7	1306.2	1269.6	1190.0	1123.0	1058.1	1015.2	974.4	932.6	903.2
20°	1463.2	1376.3	1328.2	1279.0	1200.5	1112.6	1047.7	994.3	944.1	906.4	870.8
22.5°	1505.1	1387.8	1348.1	1294.7	1202.6	1102.1	1028.8	975.5	917.9	880.2	841.5
25°	1500.9	1404.6	1338.6	1293.6	1181.7	1092.7	1006.9	944.1	890.7	842.5	803.8
27.5°	1504.0	1385.7	1318.8	1266.4	1167.0	1079.1	983.8	917.9	862.4	812.2	771.4
30°	1505.1	1357.5	1298.9	1236.1	1139.8	1046.6	957.7	890.7	832.1	777.7	741.0
32.5°	1501.9	1334.5	1261.2	1204.7	1096.9	1015.2	927.3	856.1	796.5	746.3	711.7
35°	1494.6	1307.2	1222.5	1151.3	1052.9	970.2	899.1	825.8	762.0	715.9	676.1
37.5°	1474.7	1277.9	1181.7	1111.5	1001.6	917.9	855.1	794.4	732.6	678.2	644.7
40°	1460.1	1238.2	1140.8	1064.4	946.2	864.5	812.2	754.6	693.9	644.7	612.3
42.5°	1426.6	1200.5	1099.0	1007.9	891.7	808.0	758.8	712.8	660.4	612.3	583.0
45°	1372.1	1159.7	1047.7	955.6	832.1	752.5	707.5	669.8	623.8	577.7	548.4
47.5°	1295.7	1101.1	993.3	901.2	773.5	692.9	647.9	619.6	583.0	544.3	519.1
50°	1213.1	1037.2	937.8	846.7	716.9	638.4	594.5	568.3	544.3	508.7	484.6
52.5°	1105.2	969.2	873.9	787.1	656.2	580.9	542.2	523.3	498.2	473.1	452.1
55°	1000.6	881.3	802.8	720.1	596.6	526.5	488.8	468.9	454.2	433.3	416.6
57.5°	879.2	799.6	727.4	652.1	541.1	477.3	441.7	417.6	408.2	398.8	383.1
60°	767.2	706.5	647.9	585.1	483.5	426.0	391.4	372.6	363.2	356.9	346.4
62.5°	664.6	617.5	567.3	517.0	424.9	372.6	346.4	327.6	319.2	318.2	308.8
65°	566.2	532.7	491.9	442.7	370.5	324.5	299.3	287.8	278.4	278.4	271.1
67.5°	467.8	444.8	412.4	377.8	321.3	278.4	255.4	244.9	239.7	239.7	234.4
70°	389.3	373.6	344.3	314.0	264.8	232.4	214.6	205.1	202.0	203.0	198.9
72.5°	316.1	299.3	275.3	253.3	216.7	192.6	180.0	169.6	164.3	165.4	164.3
75°	244.9	236.5	215.6	198.9	169.6	152.8	141.3	136.1	131.9	132.9	130.8
77.5°	184.2	171.6	160.1	148.6	130.8	117.2	107.8	102.6	99.4	99.4	99.4
80°	125.6	123.5	114.1	107.8	93.2	82.7	75.4	74.3	71.2	71.2	71.2
82.5°	81.6	76.4	71.2	67.0	58.6	52.3	49.2	47.1	46.1	45.0	47.1
85°	45.0	41.9	39.8	35.6	32.4	29.3	26.2	25.1	24.1	25.1	24.1
87.5°	17.8	14.7	14.7	13.6	12.6	11.5	11.5	9.4	9.4	8.4	8.4
90°	12.1	9.9	9.2	8.4	6.8	4.6	3.0	1.5	3.0	4.6	6.8
92.5°	76.7	52.4	45.6	38.7	31.1	24.3	16.7	11.4	16.7	24.3	31.1
95°	163.2	98.7	83.9	69.1	49.3	36.4	28.1	25.8	28.1	36.4	49.3
97.5°	176.1	112.4	96.1	79.7	60.0	48.6	41.8	41.0	41.8	48.6	60.0
100°	173.8	120.7	105.9	91.1	72.9	62.2	56.9	56.2	56.9	62.2	72.9
102.5°	176.9	130.6	117.3	104.0	88.1	78.2	73.6	72.1	73.6	78.2	88.1
105°	183.0	142.0	130.2	118.4	104.0	94.9	90.3	88.1	90.3	94.9	104.0
107.5°	192.8	156.4	145.4	134.4	120.7	111.6	107.0	104.8	107.0	111.6	120.7
110°	205.7	171.6	161.0	150.3	137.4	129.1	125.3	123.0	125.3	129.1	137.4

TEST NUMBER: P1012098

CATALOG NUMBER: S123DIP-B775D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	218.6	187.5	177.2	167.0	154.1	145.8	142.0	139.7	142.0	145.8	154.1
115°	233.1	204.2	194.0	183.7	170.8	163.2	158.7	155.6	158.7	163.2	170.8
117.5°	248.2	219.4	209.9	200.4	186.0	179.2	175.4	171.6	175.4	179.2	186.0
120°	262.7	235.3	225.8	216.4	201.9	194.3	190.5	188.3	190.5	194.3	201.9
122.5°	277.8	251.3	241.0	230.8	217.1	208.8	205.0	202.7	205.0	208.8	217.1
125°	292.3	265.7	255.4	245.2	230.8	222.4	217.9	216.4	217.9	222.4	230.8
127.5°	305.2	279.4	269.2	258.9	242.9	234.6	229.3	227.0	229.3	234.6	242.9
130°	316.6	291.5	281.2	271.0	255.1	246.0	239.1	236.9	239.1	246.0	255.1
132.5°	326.4	302.1	292.2	282.4	266.5	255.1	247.5	244.4	247.5	255.1	266.5
135°	336.3	312.8	302.6	292.3	276.3	264.9	256.6	253.6	256.6	264.9	276.3
137.5°	343.1	320.4	310.9	301.4	285.4	273.3	264.9	261.9	264.9	273.3	285.4
140°	350.0	328.0	318.5	309.0	293.8	281.6	274.1	270.3	274.1	281.6	293.8
142.5°	355.3	334.0	325.3	316.6	301.4	290.8	282.4	279.4	282.4	290.8	301.4
145°	359.8	340.1	331.4	322.6	309.7	298.3	291.5	289.2	291.5	298.3	309.7
147.5°	363.6	345.4	337.8	330.2	317.3	307.5	300.6	299.1	300.6	307.5	317.3
150°	367.4	350.0	343.2	336.3	325.7	315.8	309.7	309.0	309.7	315.8	325.7
152.5°	369.7	355.3	348.8	342.4	333.3	324.9	318.8	318.8	318.8	324.9	333.3
155°	372.7	359.8	354.5	349.2	340.9	333.3	328.7	328.7	328.7	333.3	340.9
157.5°	374.3	363.6	359.5	355.3	347.7	340.9	337.1	336.3	337.1	340.9	347.7
160°	376.5	367.4	363.6	359.8	354.5	348.4	345.4	345.4	345.4	348.4	354.5
162.5°	377.3	369.7	366.6	363.6	359.1	354.5	352.2	352.2	352.2	354.5	359.1
165°	378.1	372.0	369.4	366.7	363.6	359.8	358.3	359.1	358.3	359.8	363.6
167.5°	378.1	373.5	371.6	369.7	367.4	364.4	363.6	364.4	363.6	364.4	367.4
170°	377.3	373.5	372.8	372.0	370.5	368.2	367.4	368.9	367.4	368.2	370.5
172.5°	377.3	374.3	373.9	373.5	372.7	371.2	371.2	372.0	371.2	371.2	372.7
175°	376.5	375.0	374.6	374.3	374.3	372.7	373.5	374.3	373.5	372.7	374.3
177.5°	375.8	375.0	375.0	375.0	375.0	374.3	375.0	375.8	375.0	374.3	375.0
180°	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0

TEST NUMBER: P1012098

CATALOG NUMBER: S123DIP-B775D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1
2.5°	1063.4	1062.3	1064.4	1058.1	1047.7	1042.4	1027.8	1024.7	1023.6	1024.7	1025.7
5°	1034.1	1033.0	1029.9	1019.4	1006.9	997.4	979.7	978.6	972.3	966.0	969.2
7.5°	1005.8	1001.6	995.4	981.7	965.0	954.5	939.9	929.4	921.0	915.8	911.6
10°	977.6	971.3	965.0	947.2	926.3	910.6	892.8	884.4	875.0	870.8	866.6
12.5°	940.9	934.6	923.1	902.2	889.6	869.8	852.0	843.6	838.4	830.0	824.7
15°	911.6	899.1	892.8	870.8	844.6	842.5	810.1	808.0	797.5	797.5	789.2
17.5°	878.1	868.7	857.2	835.2	816.4	797.5	780.8	774.5	765.1	763.0	758.8
20°	845.7	833.1	828.9	807.0	787.1	764.0	746.3	740.0	735.8	731.6	734.7
22.5°	812.2	801.7	791.3	771.4	756.7	733.7	723.2	716.9	710.7	708.6	709.6
25°	779.7	770.3	759.9	740.0	724.3	705.4	696.0	692.9	689.7	689.7	688.7
27.5°	748.3	738.9	729.5	711.7	696.0	682.4	675.1	671.9	668.8	670.9	673.0
30°	715.9	707.5	699.2	683.5	670.9	658.3	654.1	652.1	651.0	656.2	656.2
32.5°	686.6	679.3	673.0	658.3	645.8	635.3	632.2	633.2	634.3	637.4	639.5
35°	656.2	651.0	644.7	632.2	621.7	612.3	613.3	613.3	615.4	620.7	624.8
37.5°	629.0	621.7	616.5	606.0	597.6	589.3	592.4	595.5	597.6	603.9	606.0
40°	596.6	593.4	589.3	578.8	571.5	570.4	571.5	573.6	577.7	580.9	584.0
42.5°	570.4	566.2	561.0	552.6	546.3	547.4	548.4	550.5	552.6	557.9	561.0
45°	541.1	538.0	533.8	526.5	521.2	522.3	523.3	523.3	525.4	531.7	533.8
47.5°	508.7	509.7	504.5	497.2	494.0	494.0	494.0	496.1	501.3	503.4	504.5
50°	477.3	475.2	474.1	466.8	464.7	463.7	464.7	465.8	473.1	472.0	475.2
52.5°	443.8	443.8	442.7	438.5	435.4	435.4	433.3	438.5	440.6	442.7	445.9
55°	411.3	408.2	407.1	405.0	400.9	399.8	401.9	408.2	410.3	412.4	415.5
57.5°	375.7	375.7	373.6	370.5	370.5	370.5	370.5	374.7	377.8	379.9	386.2
60°	343.3	339.1	336.0	336.0	336.0	334.9	341.2	341.2	347.5	348.5	350.6
62.5°	304.6	302.5	300.4	301.4	300.4	302.5	304.6	308.8	309.8	312.9	316.1
65°	267.9	267.9	265.8	272.1	267.9	267.9	273.2	273.2	275.3	278.4	282.6
67.5°	232.4	233.4	231.3	231.3	233.4	234.4	235.5	239.7	240.7	244.9	250.1
70°	195.7	197.8	198.9	196.8	198.9	201.0	203.0	204.1	208.3	210.4	213.5
72.5°	163.3	165.4	162.2	163.3	164.3	166.4	167.5	169.6	171.6	177.9	180.0
75°	130.8	129.8	128.7	132.9	130.8	135.0	136.1	136.1	138.2	143.4	145.5
77.5°	100.5	100.5	101.5	99.4	102.6	101.5	102.6	105.7	108.9	108.9	117.2
80°	70.1	72.2	72.2	72.2	73.3	74.3	72.2	77.5	78.5	78.5	81.6
82.5°	45.0	46.1	45.0	47.1	47.1	49.2	48.1	49.2	51.3	53.4	54.4
85°	24.1	24.1	26.2	26.2	25.1	26.2	25.1	26.2	28.3	28.3	29.3
87.5°	8.4	8.4	8.4	8.4	9.4	8.4	9.4	9.4	8.4	8.4	11.5
90°	8.4	9.2	9.9	12.1	14.4	16.7	19.0	18.2	19.0	19.7	20.5
92.5°	38.7	45.6	52.4	76.7	116.9	156.4	141.2	105.5	75.2	58.5	50.9
95°	69.1	83.9	98.7	163.2	276.3	400.8	450.2	365.1	273.3	185.2	145.0
97.5°	79.7	96.1	112.4	176.1	307.5	517.0	692.3	715.9	627.8	473.7	373.5
100°	91.1	105.9	120.7	173.8	286.2	485.9	718.9	868.5	895.0	833.5	744.7
102.5°	104.0	117.3	130.6	176.9	268.0	440.3	669.6	876.1	983.9	996.8	954.2
105°	118.4	130.2	142.0	183.0	261.1	404.6	610.4	828.2	986.9	1062.8	1077.2
107.5°	134.4	145.4	156.4	192.8	259.6	378.8	558.0	759.9	941.3	1060.5	1119.7
110°	150.3	161.0	171.6	205.7	263.4	365.1	514.7	696.1	870.0	1009.7	1105.3

TEST NUMBER: P1012098

CATALOG NUMBER: S123DIP-B775D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	167.0	177.2	187.5	218.6	271.0	357.6	485.9	640.7	799.4	942.9	1052.9
115°	183.7	194.0	204.2	233.1	279.4	356.8	466.9	598.2	738.6	870.7	982.3
117.5°	200.4	209.9	219.4	248.2	290.0	357.6	454.0	570.1	691.6	808.5	911.0
120°	216.4	225.8	235.3	262.7	302.1	360.6	445.6	548.9	655.9	758.4	849.5
122.5°	230.8	241.0	251.3	277.8	313.5	365.9	440.3	531.4	627.8	718.2	800.9
125°	245.2	255.4	265.7	292.3	325.7	371.2	435.7	517.0	603.5	686.3	759.1
127.5°	258.9	269.2	279.4	305.2	335.5	377.3	433.5	503.3	581.5	656.7	723.5
130°	271.0	281.2	291.5	316.6	345.4	383.4	431.2	492.7	561.0	629.3	690.8
132.5°	282.4	292.2	302.1	326.4	354.5	387.9	430.4	482.8	542.0	603.5	659.7
135°	292.3	302.6	312.8	336.3	362.1	392.5	429.7	474.5	525.3	579.2	628.6
137.5°	301.4	310.9	320.4	343.1	368.2	395.5	428.2	466.9	509.4	554.9	599.0
140°	309.0	318.5	328.0	350.0	372.7	398.6	427.4	460.0	495.7	534.4	570.9
142.5°	316.6	325.3	334.0	355.3	377.3	400.8	425.9	454.0	482.8	514.7	545.1
145°	322.6	331.4	340.1	359.8	380.3	401.6	424.4	448.7	472.9	498.0	522.3
147.5°	330.2	337.8	345.4	363.6	382.6	401.6	422.1	443.3	464.6	485.1	505.6
150°	336.3	343.2	350.0	367.4	383.4	401.6	419.0	438.0	455.5	472.9	488.9
152.5°	342.4	348.8	355.3	369.7	384.9	399.3	415.3	432.0	447.1	461.6	475.2
155°	349.2	354.5	359.8	372.7	384.9	397.8	410.7	425.9	438.8	450.9	462.3
157.5°	355.3	359.5	363.6	374.3	385.6	395.5	406.9	419.0	429.7	440.3	449.4
160°	359.8	363.6	367.4	376.5	385.6	394.0	402.3	412.2	422.1	430.4	438.0
162.5°	363.6	366.6	369.7	377.3	384.9	391.0	397.8	405.4	413.0	419.8	426.6
165°	366.7	369.4	372.0	378.1	383.4	387.9	393.2	399.3	405.4	409.9	415.3
167.5°	369.7	371.6	373.5	378.1	382.6	384.9	388.7	393.2	398.6	402.3	405.4
170°	372.0	372.8	373.5	377.3	380.3	381.9	384.1	387.9	391.7	394.0	397.0
172.5°	373.5	373.9	374.3	377.3	379.6	379.6	380.3	382.6	385.6	387.2	389.4
175°	374.3	374.6	375.0	376.5	378.1	377.3	377.3	378.8	380.3	381.1	382.6
177.5°	375.0	375.0	375.0	375.8	377.3	375.8	375.0	375.8	376.5	377.3	378.1
180°	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0

TEST NUMBER: P1012098

CATALOG NUMBER: S123DIP-B775D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1
2.5°	1024.7	1025.7	1021.5	1018.4	1026.7	1021.5	1021.5	1022.6	1020.5	1023.6	1022.6
5°	967.1	968.1	960.8	962.9	958.7	957.7	956.6	962.9	961.9	960.8	962.9
7.5°	910.6	910.6	907.4	905.3	905.3	902.2	906.4	905.3	907.4	907.4	910.6
10°	863.5	865.6	860.3	855.1	854.1	855.1	855.1	856.1	857.2	864.5	863.5
12.5°	824.7	821.6	820.6	817.4	812.2	810.1	808.0	819.5	816.4	816.4	816.4
15°	781.8	789.2	788.1	778.7	776.6	780.8	778.7	778.7	789.2	788.1	787.1
17.5°	758.8	756.7	754.6	749.4	750.4	749.4	750.4	750.4	756.7	756.7	756.7
20°	732.6	728.5	728.5	726.4	726.4	723.2	727.4	728.5	732.6	732.6	733.7
22.5°	709.6	706.5	706.5	705.4	707.5	703.3	707.5	708.6	708.6	711.7	711.7
25°	689.7	687.6	687.6	689.7	689.7	689.7	689.7	693.9	690.8	691.8	690.8
27.5°	671.9	673.0	674.0	675.1	674.0	675.1	676.1	678.2	679.3	678.2	676.1
30°	655.2	658.3	659.4	659.4	661.5	662.5	663.6	663.6	664.6	661.5	663.6
32.5°	642.6	642.6	644.7	645.8	647.9	648.9	648.9	651.0	650.0	646.8	647.9
35°	624.8	624.8	629.0	631.1	634.3	633.2	634.3	634.3	635.3	633.2	630.1
37.5°	607.0	609.1	609.1	613.3	614.4	615.4	614.4	616.5	615.4	613.3	612.3
40°	586.1	585.1	586.1	589.3	590.3	590.3	590.3	592.4	592.4	592.4	591.3
42.5°	560.0	563.1	562.0	565.2	564.1	564.1	566.2	568.3	569.4	566.2	567.3
45°	534.8	534.8	536.9	536.9	538.0	538.0	542.2	540.1	542.2	540.1	541.1
47.5°	507.6	508.7	508.7	509.7	511.8	513.9	511.8	512.9	512.9	513.9	511.8
50°	477.3	477.3	479.4	482.5	486.7	484.6	483.5	487.7	484.6	484.6	482.5
52.5°	445.9	449.0	450.1	453.2	456.3	457.4	458.4	456.3	457.4	454.2	455.3
55°	415.5	416.6	420.7	423.9	427.0	427.0	426.0	427.0	428.1	423.9	423.9
57.5°	385.2	388.3	392.5	392.5	396.7	396.7	395.6	395.6	396.7	393.5	392.5
60°	352.7	355.9	361.1	361.1	367.4	368.4	366.3	364.2	364.2	361.1	362.1
62.5°	318.2	321.3	324.5	329.7	333.9	331.8	336.0	331.8	332.8	326.6	326.6
65°	287.8	288.9	294.1	299.3	299.3	301.4	299.3	300.4	297.2	297.2	293.1
67.5°	252.2	252.2	257.5	262.7	267.9	267.9	267.9	264.8	264.8	261.7	261.7
70°	220.8	219.8	225.0	228.2	231.3	232.4	230.3	229.2	227.1	224.0	222.9
72.5°	182.1	184.2	189.4	191.5	196.8	195.7	201.0	194.7	194.7	189.4	188.4
75°	147.6	149.7	154.9	158.0	161.2	161.2	164.3	161.2	157.0	154.9	153.9
77.5°	117.2	116.2	120.4	125.6	126.6	125.6	127.7	126.6	122.5	122.5	120.4
80°	83.7	86.9	91.1	90.0	94.2	93.2	93.2	91.1	91.1	87.9	90.0
82.5°	55.5	58.6	59.7	58.6	59.7	61.8	62.8	61.8	61.8	59.7	60.7
85°	29.3	29.3	31.4	32.4	31.4	31.4	32.4	35.6	33.5	31.4	33.5
87.5°	9.4	8.4	8.4	9.4	8.4	8.4	9.4	9.4	10.5	10.5	10.5
90°	21.2	22.0	21.3	22.0	22.8	22.0	22.8	22.0	21.3	22.0	21.2
92.5°	48.2	45.5	44.0	41.0	41.8	40.2	41.8	41.0	44.0	45.5	48.2
95°	131.4	117.7	103.2	96.4	91.1	88.1	91.1	96.4	103.2	117.7	131.4
97.5°	330.2	287.0	236.1	207.2	189.0	180.7	189.0	207.2	236.1	287.0	330.2
100°	690.8	636.9	560.2	504.8	475.2	476.0	475.2	504.8	560.2	636.9	690.8
102.5°	925.0	895.8	840.4	799.4	775.8	753.8	775.8	799.4	840.4	895.8	925.0
105°	1067.4	1057.5	1022.6	993.7	969.4	965.6	969.4	993.7	1022.6	1057.5	1067.4
107.5°	1130.0	1140.2	1135.7	1122.0	1112.1	1103.8	1112.1	1122.0	1135.7	1140.2	1130.0
110°	1131.9	1158.5	1179.7	1185.8	1184.3	1182.7	1184.3	1185.8	1179.7	1158.5	1131.9

TEST NUMBER: P1012098

CATALOG NUMBER: S123DIP-B775D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1089.0	1125.1	1168.3	1190.3	1197.9	1198.7	1197.9	1190.3	1168.3	1125.1	1089.0
115°	1023.7	1065.1	1122.0	1155.4	1170.6	1174.4	1170.6	1155.4	1122.0	1065.1	1023.7
117.5°	953.9	996.8	1056.0	1093.2	1115.9	1121.3	1115.9	1093.2	1056.0	996.8	953.9
120°	887.8	926.2	986.1	1028.6	1046.9	1051.4	1046.9	1028.6	986.1	926.2	887.8
122.5°	835.8	870.7	922.4	959.6	980.1	986.1	980.1	959.6	922.4	870.7	835.8
125°	789.5	819.9	868.5	901.9	920.8	926.2	920.8	901.9	868.5	819.9	789.5
127.5°	751.6	779.6	823.7	852.5	870.0	874.5	870.0	852.5	823.7	779.6	751.6
130°	716.6	742.4	782.7	810.0	826.0	832.0	826.0	810.0	782.7	742.4	716.6
132.5°	684.0	708.3	745.5	772.8	786.5	790.3	786.5	772.8	745.5	708.3	684.0
135°	650.2	671.8	709.0	731.8	745.5	750.8	745.5	731.8	709.0	671.8	650.2
137.5°	618.4	637.7	669.6	693.1	704.5	709.0	704.5	693.1	669.6	637.7	618.4
140°	587.2	603.5	632.4	653.6	665.8	665.0	665.8	653.6	632.4	603.5	587.2
142.5°	558.8	572.4	595.9	614.1	624.8	624.0	624.8	614.1	595.9	572.4	558.8
145°	533.3	544.3	563.3	579.2	585.3	586.8	585.3	579.2	563.3	544.3	533.3
147.5°	513.6	521.5	536.7	548.1	554.2	554.9	554.2	548.1	536.7	521.5	513.6
150°	496.1	503.3	514.7	523.1	527.6	527.6	527.6	523.1	514.7	503.3	496.1
152.5°	480.9	486.6	495.0	502.6	504.8	504.8	504.8	502.6	495.0	486.6	480.9
155°	466.8	471.4	478.3	484.3	485.9	486.6	485.9	484.3	478.3	471.4	466.8
157.5°	453.2	457.0	463.1	467.6	469.2	469.2	469.2	467.6	463.1	457.0	453.2
160°	440.6	443.3	448.7	453.2	453.2	452.5	453.2	453.2	448.7	443.3	440.6
162.5°	428.9	431.2	434.2	438.0	438.0	437.3	438.0	438.0	434.2	431.2	428.9
165°	417.2	419.0	422.1	425.1	424.4	424.4	424.4	425.1	422.1	419.0	417.2
167.5°	406.9	408.4	409.9	412.2	411.5	411.5	411.5	412.2	409.9	408.4	406.9
170°	397.8	398.6	399.3	400.8	400.1	400.1	400.1	400.8	399.3	398.6	397.8
172.5°	389.8	390.2	390.2	391.7	390.2	389.4	390.2	391.7	390.2	390.2	389.8
175°	382.6	382.6	382.6	383.4	382.6	381.9	382.6	383.4	382.6	382.6	382.6
177.5°	378.1	378.1	377.3	378.1	376.5	376.5	376.5	378.1	377.3	378.1	378.1
180°	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0

TEST NUMBER: P1012098

CATALOG NUMBER: S123DIP-B775D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1	1080.1
2.5°	1025.7	1027.8	1028.8	1024.7	1021.5	1026.7	1034.1	1039.3	1043.5	1048.7	1051.9
5°	965.0	972.3	972.3	974.4	977.6	982.8	996.4	1005.8	1014.2	1020.5	1025.7
7.5°	913.7	918.9	922.1	927.3	932.6	939.9	955.6	969.2	981.7	989.1	997.4
10°	867.7	871.8	877.1	880.2	889.6	900.1	920.0	931.5	946.2	957.7	968.1
12.5°	823.7	838.4	841.5	840.4	848.8	860.3	880.2	898.0	913.7	925.2	936.7
15°	792.3	797.5	803.8	802.8	820.6	823.7	840.4	861.4	882.3	889.6	900.1
17.5°	757.8	766.1	772.4	775.6	780.8	792.3	808.0	823.7	850.9	852.0	879.2
20°	730.6	738.9	743.1	747.3	750.4	764.0	777.7	795.4	817.4	828.9	843.6
22.5°	712.8	716.9	720.1	723.2	727.4	734.7	751.5	771.4	786.0	798.6	808.0
25°	691.8	696.0	700.2	702.3	705.4	709.6	722.2	737.9	758.8	767.2	776.6
27.5°	677.2	677.2	679.3	679.3	683.5	687.6	697.1	711.7	728.5	738.9	751.5
30°	661.5	660.4	661.5	660.4	659.4	665.7	674.0	686.6	698.1	710.7	719.0
32.5°	645.8	644.7	644.7	645.8	641.6	644.7	648.9	660.4	673.0	679.3	688.7
35°	629.0	626.9	626.9	626.9	624.8	622.7	626.9	637.4	645.8	654.1	661.5
37.5°	612.3	609.1	609.1	607.0	605.0	601.8	601.8	610.2	621.7	624.8	634.3
40°	589.3	589.3	587.2	586.1	584.0	581.9	578.8	586.1	596.6	599.7	607.0
42.5°	566.2	563.1	562.0	562.0	562.0	558.9	556.8	562.0	568.3	573.6	577.7
45°	540.1	538.0	539.0	538.0	535.9	534.8	533.8	535.9	543.2	545.3	550.5
47.5°	511.8	510.8	510.8	509.7	508.7	509.7	505.5	510.8	512.9	514.9	519.1
50°	482.5	481.5	480.4	479.4	479.4	480.4	479.4	479.4	483.5	485.6	489.8
52.5°	453.2	450.1	450.1	449.0	449.0	446.9	449.0	450.1	452.1	454.2	456.3
55°	421.8	421.8	418.7	418.7	416.6	416.6	417.6	416.6	420.7	422.8	422.8
57.5°	391.4	387.3	388.3	386.2	384.1	383.1	383.1	385.2	387.3	387.3	389.3
60°	359.0	354.8	353.8	349.6	351.7	348.5	349.6	349.6	353.8	351.7	353.8
62.5°	326.6	321.3	318.2	316.1	316.1	317.1	315.0	314.0	316.1	318.2	322.4
65°	292.0	288.9	285.7	282.6	282.6	281.5	283.6	280.5	279.5	280.5	282.6
67.5°	256.4	253.3	250.1	247.0	248.1	244.9	242.8	246.0	243.9	244.9	247.0
70°	221.9	219.8	213.5	211.4	210.4	211.4	210.4	208.3	211.4	210.4	211.4
72.5°	187.3	185.3	182.1	176.9	176.9	175.8	174.8	174.8	173.7	173.7	173.7
75°	153.9	149.7	146.5	145.5	143.4	142.3	141.3	139.2	140.2	141.3	139.2
77.5°	119.3	114.1	113.0	113.0	109.9	109.9	110.9	109.9	108.9	108.9	108.9
80°	87.9	83.7	83.7	81.6	79.5	79.5	79.5	79.5	78.5	77.5	78.5
82.5°	56.5	55.5	54.4	54.4	56.5	52.3	54.4	53.4	52.3	52.3	51.3
85°	31.4	32.4	31.4	32.4	30.4	31.4	31.4	31.4	30.4	31.4	29.3
87.5°	11.5	11.5	11.5	12.6	12.6	12.6	12.6	12.6	13.6	12.6	12.6
90°	20.5	19.7	19.0	18.2	19.0	16.7	14.4	12.1	9.9	9.2	8.4
92.5°	50.9	58.5	75.2	105.5	141.2	156.4	116.9	76.7	52.4	45.6	38.7
95°	145.0	185.2	273.3	365.1	450.2	400.8	276.3	163.2	98.7	83.9	69.1
97.5°	373.5	473.7	627.8	715.9	692.3	517.0	307.5	176.1	112.4	96.1	79.7
100°	744.7	833.5	895.0	868.5	718.9	485.9	286.2	173.8	120.7	105.9	91.1
102.5°	954.2	996.8	983.9	876.1	669.6	440.3	268.0	176.9	130.6	117.3	104.0
105°	1077.2	1062.8	986.9	828.2	610.4	404.6	261.1	183.0	142.0	130.2	118.4
107.5°	1119.7	1060.5	941.3	759.9	558.0	378.8	259.6	192.8	156.4	145.4	134.4
110°	1105.3	1009.7	870.0	696.1	514.7	365.1	263.4	205.7	171.6	161.0	150.3

TEST NUMBER: P1012098

CATALOG NUMBER: S123DIP-B775D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1052.9	942.9	799.4	640.7	485.9	357.6	271.0	218.6	187.5	177.2	167.0
115°	982.3	870.7	738.6	598.2	466.9	356.8	279.4	233.1	204.2	194.0	183.7
117.5°	911.0	808.5	691.6	570.1	454.0	357.6	290.0	248.2	219.4	209.9	200.4
120°	849.5	758.4	655.9	548.9	445.6	360.6	302.1	262.7	235.3	225.8	216.4
122.5°	800.9	718.2	627.8	531.4	440.3	365.9	313.5	277.8	251.3	241.0	230.8
125°	759.1	686.3	603.5	517.0	435.7	371.2	325.7	292.3	265.7	255.4	245.2
127.5°	723.5	656.7	581.5	503.3	433.5	377.3	335.5	305.2	279.4	269.2	258.9
130°	690.8	629.3	561.0	492.7	431.2	383.4	345.4	316.6	291.5	281.2	271.0
132.5°	659.7	603.5	542.0	482.8	430.4	387.9	354.5	326.4	302.1	292.2	282.4
135°	628.6	579.2	525.3	474.5	429.7	392.5	362.1	336.3	312.8	302.6	292.3
137.5°	599.0	554.9	509.4	466.9	428.2	395.5	368.2	343.1	320.4	310.9	301.4
140°	570.9	534.4	495.7	460.0	427.4	398.6	372.7	350.0	328.0	318.5	309.0
142.5°	545.1	514.7	482.8	454.0	425.9	400.8	377.3	355.3	334.0	325.3	316.6
145°	522.3	498.0	472.9	448.7	424.4	401.6	380.3	359.8	340.1	331.4	322.6
147.5°	505.6	485.1	464.6	443.3	422.1	401.6	382.6	363.6	345.4	337.8	330.2
150°	488.9	472.9	455.5	438.0	419.0	401.6	383.4	367.4	350.0	343.2	336.3
152.5°	475.2	461.6	447.1	432.0	415.3	399.3	384.9	369.7	355.3	348.8	342.4
155°	462.3	450.9	438.8	425.9	410.7	397.8	384.9	372.7	359.8	354.5	349.2
157.5°	449.4	440.3	429.7	419.0	406.9	395.5	385.6	374.3	363.6	359.5	355.3
160°	438.0	430.4	422.1	412.2	402.3	394.0	385.6	376.5	367.4	363.6	359.8
162.5°	426.6	419.8	413.0	405.4	397.8	391.0	384.9	377.3	369.7	366.6	363.6
165°	415.3	409.9	405.4	399.3	393.2	387.9	383.4	378.1	372.0	369.4	366.7
167.5°	405.4	402.3	398.6	393.2	388.7	384.9	382.6	378.1	373.5	371.6	369.7
170°	397.0	394.0	391.7	387.9	384.1	381.9	380.3	377.3	373.5	372.8	372.0
172.5°	389.4	387.2	385.6	382.6	380.3	379.6	379.6	377.3	374.3	373.9	373.5
175°	382.6	381.1	380.3	378.8	377.3	377.3	378.1	376.5	375.0	374.6	374.3
177.5°	378.1	377.3	376.5	375.8	375.0	375.8	377.3	375.8	375.0	375.0	375.0
180°	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0

TEST NUMBER: P1012098

CATALOG NUMBER: S123DIP-B775D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1080.1	1080.1	1080.1	1080.1
2.5°	1057.1	1060.2	1070.7	1083.3
5°	1036.2	1044.5	1059.2	1079.1
7.5°	1013.1	1025.7	1046.6	1071.8
10°	987.0	1004.8	1030.9	1062.3
12.5°	958.7	981.7	1015.2	1047.7
15°	940.9	964.0	994.3	1029.9
17.5°	906.4	933.6	965.0	1015.2
20°	870.8	901.2	942.0	992.2
22.5°	843.6	876.0	914.8	968.1
25°	811.1	844.6	886.5	942.0
27.5°	776.6	810.1	857.2	915.8
30°	750.4	782.9	827.9	890.7
32.5°	719.0	750.4	797.5	863.5
35°	683.5	719.0	764.0	831.0
37.5°	656.2	688.7	735.8	799.6
40°	626.9	655.2	701.2	764.0
42.5°	595.5	626.9	666.7	729.5
45°	566.2	589.3	630.1	689.7
47.5°	534.8	561.0	592.4	638.4
50°	501.3	523.3	557.9	589.3
52.5°	468.9	486.7	516.0	540.1
55°	434.4	452.1	474.1	488.8
57.5°	401.9	414.5	429.1	438.5
60°	362.1	374.7	384.1	393.5
62.5°	326.6	336.0	341.2	346.4
65°	289.9	295.2	298.3	302.5
67.5°	250.1	255.4	256.4	262.7
70°	213.5	214.6	216.7	219.8
72.5°	179.0	181.1	180.0	182.1
75°	143.4	145.5	143.4	145.5
77.5°	108.9	110.9	110.9	114.1
80°	78.5	79.5	80.6	80.6
82.5°	51.3	54.4	52.3	53.4
85°	29.3	30.4	30.4	31.4
87.5°	13.6	14.7	13.6	15.7
90°	6.8	4.6	3.0	1.5
92.5°	31.1	24.3	16.7	11.4
95°	49.3	36.4	28.1	25.8
97.5°	60.0	48.6	41.8	41.0
100°	72.9	62.2	56.9	56.2
102.5°	88.1	78.2	73.6	72.1
105°	104.0	94.9	90.3	88.1
107.5°	120.7	111.6	107.0	104.8
110°	137.4	129.1	125.3	123.0

TEST NUMBER: P1012098

CATALOG NUMBER: S123DIP-B775D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	154.1	145.8	142.0	139.7
115°	170.8	163.2	158.7	155.6
117.5°	186.0	179.2	175.4	171.6
120°	201.9	194.3	190.5	188.3
122.5°	217.1	208.8	205.0	202.7
125°	230.8	222.4	217.9	216.4
127.5°	242.9	234.6	229.3	227.0
130°	255.1	246.0	239.1	236.9
132.5°	266.5	255.1	247.5	244.4
135°	276.3	264.9	256.6	253.6
137.5°	285.4	273.3	264.9	261.9
140°	293.8	281.6	274.1	270.3
142.5°	301.4	290.8	282.4	279.4
145°	309.7	298.3	291.5	289.2
147.5°	317.3	307.5	300.6	299.1
150°	325.7	315.8	309.7	309.0
152.5°	333.3	324.9	318.8	318.8
155°	340.9	333.3	328.7	328.7
157.5°	347.7	340.9	337.1	336.3
160°	354.5	348.4	345.4	345.4
162.5°	359.1	354.5	352.2	352.2
165°	363.6	359.8	358.3	359.1
167.5°	367.4	364.4	363.6	364.4
170°	370.5	368.2	367.4	368.9
172.5°	372.7	371.2	371.2	372.0
175°	374.3	372.7	373.5	374.3
177.5°	375.0	374.3	375.0	375.8
180°	375.0	375.0	375.0	375.0

(END OF REPORT)