

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012499

Luminaire Tested: S123RDIP-B340D585UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012499
REPORT IS A COMBINATION OF REPORTS P993244 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D585UB27-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3364.9 lumens
Efficiency: N/A
Efficacy: 118.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012499

CATALOG NUMBER: S123RDIP-B340D585UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012499

CATALOG NUMBER: S123RDIP-B340D585UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	44	44	37
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	40	39	38	38	38	32
2	87	80	74	69	79	73	68	63	59	56	53	47	44	42	35	34	32	32	32	27
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	28	28	28	23
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	28	26	24	24	24	20
5	67	55	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	21	21	18
6	61	50	42	36	56	46	39	34	38	32	29	30	26	24	23	21	19	19	19	16
7	57	45	37	32	51	41	34	30	34	29	25	27	24	21	21	19	17	17	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15	15	15	12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	14	14	14	11
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12	12	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5970	5970	5970
5°	5979	5759	5743
10°	5933	5542	5433
15°	5856	5274	5093
20°	5754	4984	4714
25°	5650	4681	4354
30°	5517	4359	3929
35°	5379	4043	3541
40°	5249	3700	3114
45°	5084	3364	2729
50°	4901	3006	2331
55°	4711	2622	1966
60°	4529	2229	1596
65°	4296	1826	1246
70°	3999	1381	891
75°	3576	935	706
80°	3051	649	495
85°	2286	351	259

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5084 cd/sqm

TEST NUMBER: P1012499

CATALOG NUMBER: S123RDIP-B340D585UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.1	1.5
10°-20°	145.0	4.3
20°-30°	208.8	6.2
30°-40°	235.2	7.0
40°-50°	225.0	6.7
50°-60°	184.1	5.5
60°-70°	124.2	3.7
70°-80°	62.3	1.9
80°-90°	17.8	0.5
90°-100°	159.1	4.7
100°-110°	444.6	13.2
110°-120°	433.5	12.9
120°-130°	345.2	10.3
130°-140°	272.5	8.1
140°-150°	203.3	6.0
150°-160°	141.8	4.2
160°-170°	83.3	2.5
170°-180°	27.1	0.8
0°-30°	406.0	12.1
0°-40°	641.2	19.1
0°-60°	1050.3	31.2
0°-90°	1254.5	37.3
90°-120°	1037.2	30.8
90°-150°	1858.1	55.2
90°-180°	2110.0	62.7
0°-180°	3364.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	555	555	555	555	555	
5°	555	552	547	551	550	53
15°	529	524	511	509	506	149
25°	481	470	449	440	435	221
35°	416	400	372	353	345	261
45°	342	322	287	262	251	264
55°	260	238	200	174	165	233
65°	178	153	118	96	91	176
75°	94	72	48	43	42	100
85°	24	14	13	12	12	26
90°	1	7	14	16	16	3
95°	19	63	336	98	66	20
105°	66	97	456	797	721	70
115°	116	145	348	764	876	115
125°	162	191	325	589	691	143
135°	189	226	321	485	560	146
145°	216	247	317	398	438	135
155°	245	265	306	348	363	113
165°	268	276	294	311	317	76
175°	279	280	282	286	285	27
180°	280	280	280	280	280	

TEST NUMBER: P1012499

CATALOG NUMBER: S123RDIP-B340D585UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	554.6	554.6	554.6	554.6	554.6
2.5°	556.9	555.1	549.7	554.6	553.7
5°	554.6	552.4	547.0	551.0	550.1
7.5°	550.6	548.3	541.6	544.3	542.9
10°	545.2	542.0	533.9	534.4	532.1
12.5°	537.5	533.9	523.6	523.1	520.4
15°	529.0	524.0	511.4	509.2	506.0
17.5°	518.6	513.2	497.5	493.0	488.5
20°	506.9	499.7	482.7	476.8	471.4
22.5°	493.9	485.4	466.9	459.3	454.3
25°	481.3	470.1	449.4	439.9	435.0
27.5°	466.0	453.9	431.4	418.8	411.1
30°	450.3	436.8	411.6	396.3	389.1
32.5°	434.5	418.8	391.8	374.7	367.1
35°	416.5	400.3	372.4	353.1	345.0
37.5°	398.5	381.0	351.8	330.2	320.3
40°	381.4	361.7	329.7	306.3	296.0
42.5°	362.1	342.3	309.0	282.9	273.9
45°	342.3	322.1	287.4	261.8	251.0
47.5°	323.0	300.5	266.3	238.4	229.0
50°	301.4	280.2	243.8	215.9	205.6
52.5°	282.0	258.6	222.7	193.4	184.4
55°	260.0	238.0	199.7	173.6	164.6
57.5°	240.2	216.4	177.7	152.9	145.3
60°	219.5	194.8	157.4	133.1	125.5
62.5°	198.8	174.1	136.7	114.3	106.2
65°	177.7	152.9	117.9	95.8	90.9
67.5°	156.5	131.3	97.2	80.5	75.1
70°	135.8	111.6	80.1	64.3	59.4
72.5°	115.2	91.3	63.4	51.3	49.9
75°	94.0	72.4	47.7	43.2	42.3
77.5°	74.7	54.9	37.3	34.6	33.7
80°	56.2	37.8	28.3	27.0	26.1
82.5°	38.7	23.4	20.2	18.9	18.9
85°	23.8	13.9	12.6	11.7	11.7
87.5°	10.8	5.8	5.8	5.4	4.9
90°	1.1	6.8	14.2	15.8	16.4
92.5°	8.5	34.0	105.4	36.0	30.0
95°	19.3	62.6	336.0	98.0	65.7
97.5°	30.6	71.7	516.7	246.5	134.9
100°	41.9	79.0	536.6	515.6	355.3
102.5°	53.8	87.6	499.7	690.4	562.6
105°	65.7	97.2	455.5	796.6	720.7
107.5°	78.2	108.5	416.5	843.4	823.8
110°	91.8	120.2	384.2	844.8	882.8

TEST NUMBER: P1012499

CATALOG NUMBER: S123RDIP-B340D585UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	104.3	132.4	362.6	812.8	894.7
115°	116.2	144.8	348.5	764.0	876.5
117.5°	128.1	156.6	338.8	711.9	836.9
120°	140.5	168.6	332.6	662.6	784.7
122.5°	151.3	179.8	328.6	623.8	736.0
125°	161.5	190.6	325.2	589.2	691.3
127.5°	169.4	200.8	323.5	561.0	652.7
130°	176.8	210.0	321.8	534.8	621.0
132.5°	182.4	218.2	321.3	510.5	589.8
135°	189.2	225.8	320.7	485.2	560.4
137.5°	195.5	232.0	319.6	461.4	529.2
140°	201.7	237.7	319.0	438.2	496.3
142.5°	208.5	242.8	317.9	417.0	465.7
145°	215.9	247.3	316.7	398.0	438.0
147.5°	223.2	252.2	315.0	383.4	414.2
150°	230.6	256.1	312.8	370.3	393.8
152.5°	238.0	260.4	309.9	359.0	376.8
155°	245.3	264.6	306.5	348.5	363.2
157.5°	251.0	268.3	303.7	338.2	350.2
160°	257.8	271.4	300.3	328.9	337.7
162.5°	262.9	273.6	296.9	320.1	326.4
165°	268.0	275.6	293.5	311.4	316.7
167.5°	272.0	277.4	290.1	303.7	307.1
170°	275.4	278.2	286.7	296.9	298.6
172.5°	277.6	279.0	283.9	291.0	290.7
175°	279.3	279.6	281.6	285.6	285.0
177.5°	280.5	279.9	279.9	282.2	281.0
180°	279.9	279.9	279.9	279.9	279.9

(END OF REPORT)