

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012131

Luminaire Tested: S123RDIP-B1000D1025UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012131
REPORT IS A COMBINATION OF REPORTS P992746 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D1025UB35-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7484.6 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012131

CATALOG NUMBER: S123RDIP-B1000D1025UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012131

CATALOG NUMBER: S123RDIP-B1000D1025UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	90	87	91	87	84	81	74	72	69	62	60	59	51	50	49
2	90	83	77	72	83	76	71	67	65	61	58	55	52	49	45	43	41
3	82	73	66	60	76	68	61	56	58	53	49	49	45	42	40	38	36
4	75	65	57	51	69	60	53	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	41	46	41	37	39	35	32	33	30	27
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	23	20	17
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18034	18034	18034
5°	18063	17396	17349
10°	17922	16742	16411
15°	17688	15933	15385
20°	17384	15054	14239
25°	17069	14140	13153
30°	16664	13168	11868
35°	16249	12214	10698
40°	15859	11177	9406
45°	15356	10163	8244
50°	14804	9081	7042
55°	14231	7922	5939
60°	13683	6734	4821
65°	12974	5514	3763
70°	12086	4170	2690
75°	10803	2823	2130
80°	9218	1962	1494
85°	6916	1058	782

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15356 cd/sqm

TEST NUMBER: P1012131

CATALOG NUMBER: S123RDIP-B1000D1025UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.5	2.1
10°-20°	438.1	5.9
20°-30°	630.8	8.4
30°-40°	710.4	9.5
40°-50°	679.5	9.1
50°-60°	556.3	7.4
60°-70°	375.0	5.0
70°-80°	188.1	2.5
80°-90°	51.9	0.7
90°-100°	278.6	3.7
100°-110°	778.8	10.4
110°-120°	759.4	10.1
120°-130°	604.7	8.1
130°-140°	477.3	6.4
140°-150°	356.1	4.8
150°-160°	248.4	3.3
160°-170°	145.9	1.9
170°-180°	47.5	0.6
0°-30°	1226.5	16.4
0°-40°	1936.9	25.9
0°-60°	3172.7	42.4
0°-90°	3787.8	50.6
90°-120°	1816.8	24.3
90°-150°	3255.0	43.5
90°-180°	3697.0	49.4
0°-180°	7484.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1675	1675	1675	1675	1675	
5°	1675	1669	1652	1664	1662	159
15°	1598	1583	1545	1538	1529	450
25°	1454	1420	1357	1329	1314	669
35°	1258	1209	1125	1067	1042	788
45°	1034	973	868	791	758	798
55°	785	719	603	524	497	704
65°	537	462	356	289	274	531
75°	284	219	144	130	128	303
85°	72	42	38	35	35	79
90°	2	12	25	28	29	7
95°	34	110	589	172	115	36
105°	115	170	798	1396	1262	122
115°	204	254	610	1338	1536	201
125°	283	334	570	1032	1211	251
135°	332	396	562	850	982	256
145°	378	433	555	697	767	237
155°	430	464	537	610	636	198
165°	470	483	514	545	555	132
175°	489	490	493	500	499	46
180°	490	490	490	490	490	

TEST NUMBER: P1012131

CATALOG NUMBER: S123RDIP-B1000D1025UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1675.4	1675.4	1675.4	1675.4	1675.4
2.5°	1682.2	1676.7	1660.4	1675.4	1672.7
5°	1675.4	1668.6	1652.3	1664.5	1661.8
7.5°	1663.2	1656.4	1636.0	1644.1	1640.1
10°	1646.9	1637.3	1612.9	1614.2	1607.4
12.5°	1623.8	1612.9	1581.6	1580.3	1572.1
15°	1597.9	1583.0	1544.9	1538.2	1528.6
17.5°	1566.7	1550.4	1502.8	1489.2	1475.6
20°	1531.4	1509.6	1458.0	1440.3	1424.0
22.5°	1492.0	1466.1	1410.4	1387.3	1372.4
25°	1453.9	1419.9	1357.4	1328.9	1314.0
27.5°	1407.7	1371.0	1303.1	1265.0	1241.9
30°	1360.1	1319.4	1243.3	1197.1	1175.4
32.5°	1312.6	1265.0	1183.5	1131.9	1108.8
35°	1258.2	1209.3	1125.1	1066.7	1042.2
37.5°	1203.9	1150.9	1062.6	997.4	967.5
40°	1152.3	1092.5	996.0	925.3	894.1
42.5°	1093.8	1034.0	933.5	854.7	827.5
45°	1034.0	972.9	868.3	790.8	758.2
47.5°	975.6	907.7	804.4	720.2	691.6
50°	910.4	846.5	736.5	652.2	621.0
52.5°	852.0	781.3	672.6	584.3	557.1
55°	785.4	718.8	603.3	524.5	497.3
57.5°	725.6	653.6	536.7	462.0	438.9
60°	663.1	588.4	475.6	402.2	379.1
62.5°	600.6	525.9	413.1	345.1	320.7
65°	536.7	462.0	356.0	289.4	274.5
67.5°	472.9	396.8	293.5	243.2	226.9
70°	410.4	337.0	241.9	194.3	179.4
72.5°	347.9	275.8	191.6	154.9	150.8
75°	284.0	218.8	144.0	130.4	127.7
77.5°	225.6	165.8	112.8	104.6	101.9
80°	169.8	114.1	85.6	81.5	78.8
82.5°	116.9	70.7	61.1	57.1	57.1
85°	72.0	42.1	38.0	35.3	35.3
87.5°	32.6	17.7	17.7	16.3	14.9
90°	2.0	11.9	24.8	27.8	28.8
92.5°	14.9	59.6	184.6	63.0	52.6
95°	33.7	109.6	588.6	171.7	115.1
97.5°	53.6	125.6	905.2	431.8	236.2
100°	73.4	138.4	940.0	903.2	622.3
102.5°	94.3	153.4	875.4	1209.4	985.6
105°	115.1	170.2	798.0	1395.5	1262.5
107.5°	137.0	190.1	729.5	1477.4	1443.2
110°	160.8	210.4	673.0	1480.0	1546.4

TEST NUMBER: P1012131

CATALOG NUMBER: S123RDIP-B1000D1025UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	182.6	231.8	635.2	1423.8	1567.3
115°	203.5	253.6	610.4	1338.5	1535.5
117.5°	224.3	274.4	593.6	1247.2	1466.0
120°	246.2	295.3	582.6	1160.8	1374.7
122.5°	265.0	315.1	575.7	1092.8	1289.3
125°	282.9	334.0	569.7	1032.3	1210.9
127.5°	296.8	351.9	566.8	982.6	1143.4
130°	309.7	367.7	563.8	937.0	1087.8
132.5°	319.6	382.1	562.8	894.3	1033.3
135°	331.5	395.5	561.8	850.1	981.6
137.5°	342.4	406.4	559.8	808.4	927.1
140°	353.4	416.4	558.8	767.8	869.5
142.5°	365.3	425.3	556.8	730.6	815.9
145°	378.2	433.2	554.8	697.3	767.3
147.5°	391.1	441.7	551.9	671.4	725.6
150°	404.0	448.6	547.9	648.7	689.8
152.5°	416.9	456.0	542.9	628.8	660.1
155°	429.8	463.6	537.0	610.4	636.2
157.5°	439.7	470.0	532.0	592.6	613.4
160°	451.6	475.4	526.1	576.2	591.6
162.5°	460.5	479.4	520.1	560.8	571.7
165°	469.5	482.9	514.1	545.4	554.8
167.5°	476.4	485.8	508.2	532.0	538.0
170°	482.4	487.4	502.2	520.1	523.1
172.5°	486.4	488.8	497.3	509.7	509.2
175°	489.3	489.8	493.3	500.3	499.3
177.5°	491.3	490.3	490.3	494.3	492.3
180°	490.3	490.3	490.3	490.3	490.3

(END OF REPORT)