

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012137

Luminaire Tested: S123RDIP-B1000D1025UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012137
REPORT IS A COMBINATION OF REPORTS P992752 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D1025UB40-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7409.5 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012137

CATALOG NUMBER: S123RDIP-B1000D1025UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012137

CATALOG NUMBER: S123RDIP-B1000D1025UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	90	87	91	87	84	81	74	72	69	62	60	59	51	50	49
2	90	83	77	72	83	76	71	67	65	61	58	55	52	49	45	43	41
3	82	73	66	60	76	68	61	56	58	53	49	49	45	42	40	38	36
4	75	65	57	51	69	60	53	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	41	46	41	37	39	35	32	33	30	27
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	23	20	17
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17853	17853	17853
5°	17882	17221	17174
10°	17741	16574	16247
15°	17511	15773	15231
20°	17209	14903	14096
25°	16897	13998	13021
30°	16498	13036	11749
35°	16086	12091	10591
40°	15699	11064	9311
45°	15203	10060	8161
50°	14655	8990	6971
55°	14088	7842	5880
60°	13544	6666	4773
65°	12843	5458	3725
70°	11962	4127	2663
75°	10693	2795	2109
80°	9126	1941	1479
85°	6849	1050	776

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15203 cd/sqm

TEST NUMBER: P1012137

CATALOG NUMBER: S123RDIP-B1000D1025UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.9	2.1
10°-20°	433.7	5.9
20°-30°	624.5	8.4
30°-40°	703.3	9.5
40°-50°	672.7	9.1
50°-60°	550.7	7.4
60°-70°	371.3	5.0
70°-80°	186.2	2.5
80°-90°	51.4	0.7
90°-100°	275.8	3.7
100°-110°	771.0	10.4
110°-120°	751.8	10.1
120°-130°	598.6	8.1
130°-140°	472.5	6.4
140°-150°	352.5	4.8
150°-160°	246.0	3.3
160°-170°	144.5	2.0
170°-180°	47.0	0.6
0°-30°	1214.2	16.4
0°-40°	1917.4	25.9
0°-60°	3140.8	42.4
0°-90°	3749.7	50.6
90°-120°	1798.6	24.3
90°-150°	3222.4	43.5
90°-180°	3660.0	49.4
0°-180°	7409.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1659	1659	1659	1659	1659	
5°	1659	1652	1636	1648	1645	157
15°	1582	1567	1529	1523	1513	446
25°	1439	1406	1344	1316	1301	662
35°	1246	1197	1114	1056	1032	780
45°	1024	963	860	783	751	790
55°	778	712	597	519	492	697
65°	531	457	352	286	272	526
75°	281	217	143	129	126	300
85°	71	42	38	35	35	78
90°	2	12	25	28	28	7
95°	33	109	583	170	114	35
105°	114	168	790	1382	1250	121
115°	201	251	604	1325	1520	199
125°	280	331	564	1022	1199	249
135°	328	392	556	842	972	254
145°	374	429	549	690	760	235
155°	426	459	532	604	630	196
165°	465	478	509	540	549	131
175°	484	485	488	495	494	46
180°	485	485	485	485	485	

TEST NUMBER: P1012137

CATALOG NUMBER: S123RDIP-B1000D1025UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1658.6	1658.6	1658.6	1658.6	1658.6
2.5°	1665.3	1659.9	1643.8	1658.6	1655.9
5°	1658.6	1651.8	1635.7	1647.8	1645.1
7.5°	1646.5	1639.7	1619.6	1627.6	1623.6
10°	1630.3	1620.9	1596.7	1598.0	1591.3
12.5°	1607.5	1596.7	1565.8	1564.4	1556.3
15°	1581.9	1567.1	1529.4	1522.7	1513.3
17.5°	1551.0	1534.8	1487.7	1474.3	1460.8
20°	1516.0	1494.5	1443.3	1425.9	1409.7
22.5°	1477.0	1451.4	1396.3	1373.4	1358.6
25°	1439.3	1405.7	1343.8	1315.6	1300.8
27.5°	1393.6	1357.3	1290.0	1252.3	1229.5
30°	1346.5	1306.1	1230.8	1185.1	1163.6
32.5°	1299.4	1252.3	1171.6	1120.5	1097.6
35°	1245.6	1197.2	1113.8	1055.9	1031.7
37.5°	1191.8	1139.3	1051.9	987.3	957.7
40°	1140.7	1081.5	986.0	916.0	885.1
42.5°	1082.8	1023.7	924.1	846.1	819.2
45°	1023.7	963.1	859.5	782.9	750.6
47.5°	965.8	898.6	796.3	712.9	684.7
50°	901.2	838.0	729.1	645.7	614.7
52.5°	843.4	773.5	665.8	578.4	551.5
55°	777.5	711.6	597.2	519.2	492.3
57.5°	718.3	647.0	531.3	457.4	434.5
60°	656.4	582.4	470.8	398.2	375.3
62.5°	594.6	520.6	408.9	341.7	317.5
65°	531.3	457.4	352.4	286.5	271.7
67.5°	468.1	392.8	290.6	240.8	224.6
70°	406.2	333.6	239.4	192.4	177.6
72.5°	344.4	273.1	189.7	153.3	149.3
75°	281.1	216.6	142.6	129.1	126.4
77.5°	223.3	164.1	111.6	103.6	100.9
80°	168.1	113.0	84.7	80.7	78.0
82.5°	115.7	69.9	60.5	56.5	56.5
85°	71.3	41.7	37.7	35.0	35.0
87.5°	32.3	17.5	17.5	16.1	14.8
90°	2.0	11.8	24.6	27.5	28.5
92.5°	14.7	59.0	182.8	62.4	52.1
95°	33.4	108.6	582.7	170.0	114.0
97.5°	53.1	124.3	896.1	427.4	233.9
100°	72.7	137.0	930.5	894.2	616.1
102.5°	93.3	151.8	866.7	1197.3	975.7
105°	114.0	168.5	790.0	1381.6	1249.9
107.5°	135.6	188.2	722.2	1462.6	1428.7
110°	159.2	208.4	666.2	1465.1	1530.9



TEST NUMBER: P1012137

CATALOG NUMBER: S123RDIP-B1000D1025UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	180.8	229.4	628.9	1409.6	1551.5
115°	201.4	251.0	604.3	1325.0	1520.1
117.5°	222.1	271.7	587.6	1234.6	1451.3
120°	243.7	292.3	576.8	1149.2	1360.9
122.5°	262.4	312.0	569.9	1081.9	1276.4
125°	280.0	330.6	564.0	1021.9	1198.8
127.5°	293.8	348.4	561.1	972.8	1132.0
130°	306.6	364.0	558.1	927.6	1076.9
132.5°	316.4	378.3	557.1	885.4	1022.9
135°	328.2	391.6	556.2	841.6	971.8
137.5°	339.0	402.4	554.2	800.3	917.8
140°	349.8	412.2	553.2	760.0	860.8
142.5°	361.6	421.0	551.2	723.2	807.7
145°	374.4	428.9	549.3	690.2	759.6
147.5°	387.1	437.2	546.3	664.8	718.3
150°	399.9	444.2	542.4	642.2	682.9
152.5°	412.7	451.6	537.5	622.5	653.4
155°	425.5	458.9	531.6	604.3	629.9
157.5°	435.3	465.3	526.7	586.6	607.3
160°	447.1	470.7	520.8	570.4	585.6
162.5°	455.9	474.6	514.9	555.2	566.0
165°	464.8	478.0	509.0	540.0	549.3
167.5°	471.7	481.0	503.1	526.7	532.6
170°	477.6	482.4	497.2	514.9	517.8
172.5°	481.5	483.9	492.3	504.6	504.1
175°	484.4	484.9	488.4	495.2	494.3
177.5°	486.4	485.4	485.4	489.3	487.4
180°	485.4	485.4	485.4	485.4	485.4

(END OF REPORT)