

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012524

Luminaire Tested: S123RDIP-B340D805UB27-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012524
REPORT IS A COMBINATION OF REPORTS P993279 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D805UB27-4F0-XX-W2A-A
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4416.0 lumens
Efficiency: N/A
Efficacy: 129.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012524

CATALOG NUMBER: S123RDIP-B340D805UB27-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1012524

CATALOG NUMBER: S123RDIP-B340D805UB27-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	94	90	86	83	84	80	77	75	64	61	60	48	47	46	34	33	32
2	85	79	73	68	76	71	66	62	56	53	50	42	40	39	30	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24
4	72	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21
5	66	55	47	41	59	50	43	38	40	35	31	30	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15
8	52	40	33	28	46	36	30	26	30	25	21	23	20	17	17	15	13
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12
10	45	33	27	22	40	30	24	20	25	20	17	19	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5654	5654	5654	5654
5°	5658	6512	5673	4831
10°	5609	7861	5633	4220
15°	5551	8922	5551	3721
20°	5437	9623	5468	3301
25°	5353	9143	5343	3012
30°	5256	6335	5245	2729
35°	5140	4067	5117	2516
40°	4994	2872	4970	2304
45°	4742	2299	4736	2097
50°	4431	1922	4417	1856
55°	4082	1585	4050	1574
60°	3739	1310	3702	1338
65°	3338	1049	3360	1135
70°	2965	729	3045	918
75°	2514	541	2617	706
80°	2003	358	2172	529
85°	1422	168	1556	328

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7549 cd/sqm

TEST NUMBER: P1012524

CATALOG NUMBER: S123RDIP-B340D805UB27-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.6	1.2
10°-20°	161.5	3.7
20°-30°	254.3	5.8
30°-40°	264.5	6.0
40°-50°	226.3	5.1
50°-60°	172.5	3.9
60°-70°	110.5	2.5
70°-80°	52.9	1.2
80°-90°	15.9	0.4
90°-100°	35.9	0.8
100°-110°	173.7	3.9
110°-120°	425.7	9.6
120°-130°	540.4	12.2
130°-140°	577.3	13.1
140°-150°	539.8	12.2
150°-160°	435.4	9.9
160°-170°	281.0	6.4
170°-180°	96.8	2.2
0°-30°	467.4	10.6
0°-40°	731.9	16.6
0°-60°	1130.6	25.6
0°-90°	1310.0	29.7
90°-120°	635.3	14.4
90°-150°	2292.7	51.9
90°-180°	3106.0	70.3
0°-180°	4416.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	525	525	525	525	525	
5°	525	624	526	463	525	50
15°	502	886	502	370	502	141
25°	456	913	455	301	456	210
35°	398	396	396	245	398	249
45°	319	211	319	193	319	246
55°	225	133	224	132	225	202
65°	138	76	139	83	138	138
75°	66	32	69	42	66	71
85°	15	8	16	15	15	17
90°	1	23	1	23	1	3
95°	46	29	46	29	46	55
105°	226	33	226	33	226	239
115°	423	445	423	445	423	418
125°	596	609	596	609	596	533
135°	742	750	742	750	742	572
145°	857	865	857	865	857	536
155°	944	942	944	942	944	435
165°	995	993	995	993	995	281
175°	1019	1015	1019	1015	1019	97
180°	1019	1019	1019	1019	1019	

TEST NUMBER: P1012524

CATALOG NUMBER: S123RDIP-B340D805UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	526.6	530.2	532.9	534.7	539.2	541.9	544.2	548.2	548.2	549.1	550.9
5°	524.8	532.5	537.9	545.1	554.5	559.0	565.3	570.7	578.4	582.4	586.5
7.5°	520.8	531.6	542.8	553.6	567.6	576.6	582.9	596.8	606.7	618.8	628.3
10°	515.4	530.2	544.6	561.3	580.2	593.6	603.1	621.5	640.4	657.5	671.9
12.5°	508.6	526.6	547.3	567.6	594.1	607.6	622.9	645.8	672.8	694.4	713.7
15°	501.5	522.1	545.5	570.3	603.5	622.4	644.5	672.4	702.5	733.5	760.1
17.5°	490.2	516.3	542.4	578.4	617.5	628.7	647.6	685.8	723.2	751.1	783.4
20°	479.0	508.2	541.0	573.4	615.7	641.8	659.3	699.8	739.8	773.5	804.6
22.5°	468.6	499.2	533.4	574.3	613.9	640.0	662.0	704.3	750.6	788.4	826.6
25°	456.0	489.3	527.1	565.8	613.9	633.7	658.0	707.0	756.0	799.6	846.8
27.5°	442.5	476.3	513.6	553.2	597.2	626.5	650.3	702.9	762.7	809.5	858.1
30°	429.0	463.7	499.7	535.2	584.7	612.5	640.0	698.0	766.3	819.9	857.2
32.5°	416.0	445.2	480.8	515.4	564.4	595.0	626.0	693.0	767.7	812.7	830.7
35°	398.0	428.6	457.4	494.3	543.7	573.9	610.3	692.6	761.8	789.7	780.7
37.5°	381.4	407.0	434.4	467.3	518.1	557.2	595.0	680.9	742.5	744.3	693.5
40°	362.9	384.1	407.0	441.6	496.5	535.2	576.1	662.9	707.4	680.9	591.4
42.5°	341.8	360.7	378.7	412.4	472.2	515.4	559.5	640.4	656.6	595.4	502.4
45°	319.3	334.6	351.2	386.8	446.6	489.3	533.4	605.8	589.2	502.8	414.2
47.5°	295.9	309.0	325.2	357.5	419.2	462.8	504.6	556.3	514.0	421.4	347.2
50°	272.5	282.9	298.6	331.9	391.3	430.8	469.5	503.3	443.9	361.6	286.9
52.5°	249.6	257.7	273.9	302.2	359.8	397.6	425.4	438.5	378.2	298.6	249.2
55°	225.3	234.3	245.1	273.9	331.0	358.9	377.3	376.9	314.8	253.2	206.0
57.5°	201.9	210.0	219.5	248.3	294.6	313.5	329.2	321.6	262.6	207.3	176.7
60°	181.2	185.7	196.1	220.4	255.4	271.6	280.6	267.6	214.5	174.9	146.2
62.5°	158.8	163.3	171.8	194.7	216.3	224.9	232.5	215.9	177.2	142.6	125.0
65°	138.1	143.9	149.3	167.8	179.4	189.8	188.9	174.9	138.5	116.0	101.6
67.5°	120.1	122.3	126.8	138.1	143.5	151.1	151.6	135.8	111.5	94.4	85.9
70°	100.7	103.0	106.1	111.5	115.1	116.9	116.0	102.1	84.1	73.8	66.1
72.5°	84.1	83.7	85.9	85.9	89.5	89.0	86.3	75.6	63.9	55.3	50.8
75°	66.1	66.6	67.0	66.1	64.8	63.0	60.7	52.6	45.0	40.9	36.9
77.5°	51.7	50.8	51.3	48.1	46.3	44.5	41.4	37.3	31.0	30.1	28.3
80°	36.9	36.4	36.0	34.6	30.6	28.8	26.5	24.3	22.9	22.0	21.6
82.5°	24.7	24.7	23.8	21.1	18.9	17.5	17.1	16.2	14.8	14.8	14.4
85°	14.8	14.4	13.5	10.8	9.4	9.4	9.4	9.4	8.5	8.5	8.1
87.5°	5.8	5.4	4.0	4.0	3.6	3.6	3.6	3.1	3.1	2.7	2.7
90°	0.8	2.5	4.1	5.8	7.5	8.3	9.4	11.6	13.8	16.0	18.2
92.5°	17.4	16.4	15.4	14.4	13.4	12.9	13.7	15.2	16.7	18.2	19.7
95°	46.2	39.3	32.4	25.5	18.6	15.1	16.0	17.9	19.8	21.6	23.5
97.5°	84.0	79.3	74.6	69.9	65.2	62.8	58.5	49.9	41.4	32.8	24.2
100°	127.9	131.3	134.7	138.0	141.4	143.1	130.0	103.7	77.5	51.2	25.0
102.5°	177.9	180.1	182.3	184.4	186.6	187.7	173.1	143.8	114.5	85.3	56.0
105°	225.6	227.4	229.3	231.1	233.0	233.9	226.3	211.2	196.1	180.9	165.8
107.5°	276.3	277.8	279.3	280.8	282.3	283.1	284.4	286.9	289.4	291.9	294.4
110°	327.0	328.3	329.7	331.0	332.3	333.0	333.9	335.8	337.7	339.5	341.4

TEST NUMBER: P1012524

CATALOG NUMBER: S123RDIP-B340D805UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	375.4	376.6	377.8	378.9	380.1	380.7	381.6	383.5	385.4	387.2	389.1
115°	423.1	424.1	425.1	426.2	427.2	427.7	428.5	430.0	431.5	433.0	434.5
117.5°	470.1	471.3	472.4	473.6	474.7	475.3	475.7	476.6	477.4	478.3	479.1
120°	513.2	514.7	516.2	517.7	519.2	520.0	520.3	520.8	521.3	521.8	522.3
122.5°	557.1	558.3	559.5	560.6	561.8	562.4	562.7	563.4	564.1	564.7	565.4
125°	596.5	597.8	599.2	600.5	601.8	602.5	602.8	603.5	604.2	604.8	605.5
127.5°	635.8	637.2	638.5	639.9	641.2	641.9	642.3	643.2	644.0	644.9	645.7
130°	672.2	673.5	674.9	676.2	677.5	678.2	678.5	679.2	679.9	680.5	681.2
132.5°	707.0	708.3	709.7	711.0	712.3	713.0	713.3	713.8	714.3	714.8	715.3
135°	742.5	743.5	744.5	745.6	746.6	747.1	747.4	748.1	748.8	749.4	750.1
137.5°	772.8	774.2	775.5	776.9	778.2	778.9	779.1	779.4	779.7	780.1	780.4
140°	803.1	804.1	805.1	806.1	807.1	807.6	807.9	808.4	808.9	809.4	809.9
142.5°	831.1	832.1	833.1	834.1	835.1	835.6	835.9	836.4	836.9	837.4	837.9
145°	856.8	858.0	859.2	860.3	861.5	862.1	862.3	862.6	863.0	863.3	863.7
147.5°	881.8	882.6	883.5	884.3	885.2	885.6	885.8	886.1	886.4	886.8	887.1
150°	904.5	905.0	905.5	906.0	906.5	906.8	907.0	907.3	907.6	908.0	908.3
152.5°	925.0	925.2	925.3	925.5	925.6	925.7	925.8	926.0	926.1	926.3	926.5
155°	943.9	943.6	943.2	942.9	942.6	942.4	942.5	942.6	942.8	942.9	943.1
157.5°	959.0	959.0	959.0	959.0	959.0	959.0	958.9	958.8	958.6	958.5	958.3
160°	972.6	972.4	972.3	972.1	972.0	971.9	971.8	971.6	971.5	971.3	971.1
162.5°	985.5	985.0	984.5	984.0	983.5	983.2	983.1	983.0	982.8	982.7	982.5
165°	995.4	994.9	994.4	993.9	993.4	993.1	993.0	992.8	992.7	992.5	992.3
167.5°	1003.7	1003.0	1002.4	1001.7	1001.0	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
170°	1010.5	1009.8	1009.2	1008.5	1007.8	1007.5	1007.5	1007.5	1007.5	1007.5	1007.5
172.5°	1015.0	1014.2	1013.4	1012.5	1011.7	1011.3	1011.4	1011.5	1011.7	1011.8	1012.0
175°	1018.8	1018.0	1017.1	1016.3	1015.4	1015.0	1015.1	1015.3	1015.4	1015.6	1015.8
177.5°	1020.3	1019.5	1018.7	1017.8	1017.0	1016.6	1016.7	1016.8	1017.0	1017.1	1017.3
180°	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8

TEST NUMBER: P1012524

CATALOG NUMBER: S123RDIP-B340D805UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	554.5	554.5	558.6	562.6	560.4	561.7	566.7	564.9	568.5	568.0	569.4
5°	596.3	601.3	605.3	613.9	615.2	613.9	622.4	624.7	628.7	623.8	626.0
7.5°	643.6	653.9	663.8	676.4	680.4	681.3	685.8	692.1	697.5	687.6	692.6
10°	689.4	705.2	725.4	736.7	746.6	750.2	753.8	757.8	764.1	769.9	765.4
12.5°	738.9	761.8	781.2	801.4	813.6	812.2	822.6	825.3	830.2	831.6	833.4
15°	779.4	811.8	823.9	854.0	856.7	865.7	877.4	887.8	889.1	886.4	886.4
17.5°	818.1	846.0	867.5	891.8	896.8	904.4	919.3	924.2	926.0	925.6	925.6
20°	849.5	868.0	904.4	924.7	932.7	942.6	953.0	959.3	960.6	962.4	959.7
22.5°	870.2	898.1	927.8	944.4	951.2	954.8	961.5	963.3	961.1	961.5	962.0
25°	886.4	913.9	931.8	936.3	935.9	931.4	926.5	917.9	917.0	913.4	906.2
27.5°	890.9	901.3	899.0	880.6	862.1	860.3	830.7	814.5	796.0	798.7	788.4
30°	866.6	853.1	821.2	774.4	755.1	723.6	690.3	655.7	642.2	627.4	654.8
32.5°	807.3	759.2	702.5	641.8	609.4	581.5	546.0	520.8	506.4	494.3	517.6
35°	717.8	642.7	567.6	510.0	483.5	458.3	425.0	412.4	394.4	396.2	398.5
37.5°	602.6	519.9	463.2	406.6	389.0	378.7	354.4	335.1	328.8	327.0	327.0
40°	494.7	426.8	376.4	331.9	318.4	309.9	290.5	281.5	274.8	273.0	275.2
42.5°	409.3	351.2	312.1	282.4	273.0	262.2	254.1	242.9	241.5	238.4	242.4
45°	343.6	293.2	264.0	242.4	234.3	230.3	221.3	214.5	211.8	211.4	214.5
47.5°	291.4	252.3	226.7	213.2	206.9	202.8	195.2	192.5	189.8	190.7	189.3
50°	244.7	215.4	198.8	186.6	182.6	178.5	173.6	170.9	169.5	169.5	169.1
52.5°	210.0	185.7	174.9	163.7	161.9	159.7	154.3	152.5	150.2	149.8	151.6
55°	179.9	163.3	152.5	145.7	143.9	139.4	137.2	134.9	133.6	132.7	133.1
57.5°	153.8	141.2	134.0	128.2	125.0	123.2	119.2	118.7	117.8	117.8	117.4
60°	132.2	123.2	114.7	111.1	108.8	106.6	106.1	103.4	102.1	103.0	102.5
62.5°	112.0	104.8	99.8	95.8	94.4	92.6	91.3	90.4	89.0	89.5	89.5
65°	93.5	87.7	84.1	80.5	80.1	78.3	77.8	76.9	76.9	76.5	77.4
67.5°	76.9	72.9	69.7	67.5	66.1	66.6	64.8	63.4	63.4	63.0	64.3
70°	61.2	58.9	55.8	53.1	51.3	51.3	49.0	48.6	48.6	48.6	48.1
72.5°	47.2	43.2	41.8	40.9	40.9	40.9	40.0	40.0	39.6	40.0	39.6
75°	35.1	34.6	33.7	33.3	33.3	32.8	32.4	32.4	32.4	32.4	32.4
77.5°	27.4	27.4	26.5	26.1	26.1	26.1	25.6	25.6	25.2	25.2	25.2
80°	20.2	20.2	19.3	19.3	19.3	18.9	18.9	18.9	19.3	18.9	18.9
82.5°	13.9	13.9	13.5	13.9	13.5	13.0	13.0	13.0	12.6	13.0	13.0
85°	8.1	8.1	7.6	7.2	7.6	7.6	7.2	7.6	7.2	7.6	7.2
87.5°	3.1	2.7	2.7	2.7	2.2	2.7	2.2	2.2	2.7	2.2	2.7
90°	18.9	19.5	20.2	20.9	21.2	21.4	21.7	22.0	22.4	22.7	22.4
92.5°	20.9	22.1	23.2	24.4	25.0	25.1	25.2	25.4	25.5	25.7	25.5
95°	24.7	25.9	27.0	28.2	28.8	28.8	28.8	28.8	28.8	28.8	28.8
97.5°	25.6	26.9	28.3	29.6	30.3	30.4	30.5	30.7	30.8	31.0	30.8
100°	26.3	27.7	29.0	30.3	31.0	31.1	31.3	31.4	31.6	31.8	31.6
102.5°	50.4	44.9	39.3	33.8	31.0	31.2	31.5	31.8	32.2	32.5	32.2
105°	136.0	106.2	76.5	46.7	31.8	32.0	32.3	32.6	33.0	33.3	33.0
107.5°	268.5	242.6	216.7	190.8	177.9	166.9	144.8	122.8	100.7	78.7	100.7
110°	335.8	330.3	324.7	319.2	316.4	304.4	280.3	256.3	232.2	208.2	232.2

TEST NUMBER: P1012524

CATALOG NUMBER: S123RDIP-B340D805UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	390.6	392.1	393.6	395.1	395.9	395.7	395.4	395.1	394.7	394.4	394.7
115°	436.2	437.8	439.5	441.2	442.0	442.3	443.0	443.7	444.4	445.1	444.4
117.5°	480.5	481.8	483.2	484.5	485.2	485.3	485.4	485.6	485.7	485.9	485.7
120°	523.6	525.0	526.3	527.6	528.3	528.3	528.3	528.3	528.3	528.3	528.3
122.5°	566.2	567.1	567.9	568.8	569.2	569.3	569.5	569.6	569.8	570.0	569.8
125°	605.9	606.2	606.6	606.9	607.1	607.3	607.6	607.9	608.3	608.6	608.3
127.5°	646.2	646.7	647.2	647.7	647.9	647.7	647.4	647.1	646.7	646.4	646.7
130°	681.9	682.6	683.3	684.0	684.3	684.1	683.8	683.4	683.1	682.7	683.1
132.5°	716.0	716.6	717.3	718.0	718.3	718.1	717.6	717.1	716.6	716.1	716.6
135°	750.6	751.1	751.6	752.1	752.4	752.1	751.6	751.1	750.6	750.1	750.6
137.5°	781.2	782.1	782.9	783.8	784.2	784.0	783.7	783.4	783.0	782.7	783.0
140°	810.6	811.2	811.9	812.6	812.9	812.7	812.4	812.1	811.7	811.4	811.7
142.5°	838.4	838.9	839.4	839.9	840.2	839.9	839.4	838.9	838.4	837.9	838.4
145°	864.0	864.4	864.7	865.0	865.2	865.2	865.2	865.2	865.2	865.2	865.2
147.5°	887.4	887.8	888.1	888.4	888.6	888.2	887.3	886.5	885.6	884.8	885.6
150°	908.6	909.0	909.3	909.6	909.8	909.6	909.1	908.6	908.1	907.6	908.1
152.5°	927.2	927.8	928.5	929.2	929.5	929.1	928.2	927.4	926.5	925.7	926.5
155°	943.9	944.8	945.6	946.5	946.9	946.4	945.4	944.4	943.4	942.4	943.4
157.5°	959.3	960.3	961.3	962.3	962.8	962.1	960.8	959.5	958.1	956.8	958.1
160°	972.1	973.1	974.2	975.2	975.7	975.1	973.9	972.8	971.6	970.4	971.6
162.5°	983.7	984.9	986.0	987.2	987.8	987.3	986.3	985.2	984.2	983.2	984.2
165°	993.7	995.0	996.4	997.7	998.4	997.8	996.6	995.5	994.3	993.1	994.3
167.5°	1002.0	1003.4	1004.7	1006.0	1006.7	1006.0	1004.7	1003.4	1002.0	1000.7	1002.0
170°	1008.8	1010.2	1011.5	1012.8	1013.5	1012.8	1011.5	1010.2	1008.8	1007.5	1008.8
172.5°	1013.4	1014.7	1016.1	1017.4	1018.1	1017.3	1015.8	1014.3	1012.8	1011.3	1012.8
175°	1017.0	1018.2	1019.3	1020.5	1021.1	1020.4	1019.1	1017.7	1016.4	1015.0	1016.4
177.5°	1018.7	1020.0	1021.4	1022.7	1023.4	1022.6	1020.9	1019.2	1017.5	1015.8	1017.5
180°	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8

TEST NUMBER: P1012524

CATALOG NUMBER: S123RDIP-B340D805UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	567.1	564.4	562.6	561.3	559.9	564.0	558.6	552.7	548.7	546.0	545.1
5°	626.5	620.6	615.7	611.6	612.5	612.5	603.1	592.7	583.8	578.8	573.4
7.5°	695.3	689.0	679.1	676.8	675.1	663.8	654.4	635.5	624.2	613.0	603.1
10°	763.6	755.6	746.1	743.0	738.5	724.5	710.1	685.8	671.9	651.2	638.2
12.5°	827.5	817.6	808.2	805.9	799.2	787.0	762.3	737.1	713.3	691.2	668.3
15°	881.0	878.3	863.9	854.9	840.1	823.5	818.1	783.9	753.8	730.8	689.4
17.5°	926.0	913.4	899.9	894.1	888.2	868.9	849.5	814.5	782.1	748.4	721.8
20°	962.0	948.0	938.6	930.1	927.4	905.3	874.7	843.7	808.2	770.4	735.8
22.5°	963.8	962.0	955.7	950.7	945.3	930.9	906.7	868.0	830.2	788.8	743.4
25°	926.5	923.8	941.7	937.2	940.8	935.4	922.4	890.0	846.0	797.4	751.5
27.5°	814.0	841.5	869.8	879.7	886.4	905.8	912.1	894.1	858.5	806.8	755.6
30°	661.1	697.5	743.4	768.1	787.0	823.0	869.8	875.6	859.0	817.6	754.7
32.5°	519.0	552.3	589.2	618.4	643.6	717.3	780.3	825.7	833.8	812.2	756.9
35°	418.3	432.6	467.7	495.6	529.8	592.7	667.0	740.3	789.7	792.4	750.2
37.5°	344.9	352.6	383.2	398.9	419.2	474.5	543.7	639.5	716.4	752.9	731.3
40°	285.6	303.1	320.7	329.7	344.0	382.3	448.8	523.9	619.3	686.7	702.0
42.5°	247.8	255.4	266.7	279.3	288.3	321.6	366.1	434.9	520.8	614.8	657.1
45°	218.6	221.3	233.0	241.1	250.5	273.9	305.4	362.9	438.5	531.1	603.1
47.5°	194.3	199.7	206.0	210.9	217.2	235.2	262.2	304.0	370.6	453.3	530.7
50°	172.7	175.8	183.9	186.2	190.7	203.3	224.0	255.9	310.8	376.9	456.9
52.5°	152.5	158.3	161.5	164.6	168.7	179.0	192.5	218.6	259.9	322.0	389.9
55°	136.7	138.5	143.0	145.7	148.9	156.1	167.8	187.1	219.5	268.9	333.3
57.5°	121.4	121.4	125.9	128.2	131.3	136.7	147.1	161.9	185.3	222.2	281.1
60°	105.2	105.7	109.3	112.0	112.9	118.3	126.8	138.5	156.5	183.5	231.6
62.5°	90.8	93.1	94.9	95.8	98.9	102.1	109.3	117.4	130.0	153.8	188.0
65°	78.7	79.2	80.5	81.4	82.8	86.3	91.7	97.1	107.9	125.5	153.4
67.5°	64.8	66.6	68.4	68.4	69.7	71.5	76.9	81.4	89.5	99.8	118.7
70°	48.6	49.5	52.2	53.5	55.3	58.5	61.2	63.9	70.2	77.8	92.2
72.5°	40.5	40.5	41.4	41.8	41.8	44.1	48.1	50.8	54.0	59.4	69.3
75°	32.4	32.4	33.7	33.3	34.2	35.1	35.5	37.3	39.1	43.2	49.0
77.5°	25.6	26.1	26.1	26.5	26.5	27.0	27.4	28.3	29.2	31.5	34.2
80°	18.9	19.3	19.3	19.8	19.8	20.2	20.7	21.1	22.0	22.9	24.3
82.5°	13.0	13.5	13.5	13.9	13.5	13.9	14.4	14.4	14.8	15.7	16.2
85°	7.6	7.6	8.1	7.6	7.6	7.6	8.1	8.1	8.5	9.9	9.9
87.5°	2.2	2.7	2.2	2.7	2.7	2.7	2.7	3.1	3.1	3.6	4.0
90°	22.0	21.7	21.4	21.2	20.9	20.2	19.5	18.9	18.2	16.0	13.8
92.5°	25.4	25.2	25.1	25.0	24.4	23.2	22.1	20.9	19.7	18.2	16.7
95°	28.8	28.8	28.8	28.8	28.2	27.0	25.9	24.7	23.5	21.6	19.8
97.5°	30.7	30.5	30.4	30.3	29.6	28.3	26.9	25.6	24.2	32.8	41.4
100°	31.4	31.3	31.1	31.0	30.3	29.0	27.7	26.3	25.0	51.2	77.5
102.5°	31.8	31.5	31.2	31.0	33.8	39.3	44.9	50.4	56.0	85.3	114.5
105°	32.6	32.3	32.0	31.8	46.7	76.5	106.2	136.0	165.8	180.9	196.1
107.5°	122.8	144.8	166.9	177.9	190.8	216.7	242.6	268.5	294.4	291.9	289.4
110°	256.3	280.3	304.4	316.4	319.2	324.7	330.3	335.8	341.4	339.5	337.7

TEST NUMBER: P1012524

CATALOG NUMBER: S123RDIP-B340D805UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	395.1	395.4	395.7	395.9	395.1	393.6	392.1	390.6	389.1	387.2	385.4
115°	443.7	443.0	442.3	442.0	441.2	439.5	437.8	436.2	434.5	433.0	431.5
117.5°	485.6	485.4	485.3	485.2	484.5	483.2	481.8	480.5	479.1	478.3	477.4
120°	528.3	528.3	528.3	528.3	527.6	526.3	525.0	523.6	522.3	521.8	521.3
122.5°	569.6	569.5	569.3	569.2	568.8	567.9	567.1	566.2	565.4	564.7	564.1
125°	607.9	607.6	607.3	607.1	606.9	606.6	606.2	605.9	605.5	604.8	604.2
127.5°	647.1	647.4	647.7	647.9	647.7	647.2	646.7	646.2	645.7	644.9	644.0
130°	683.4	683.8	684.1	684.3	684.0	683.3	682.6	681.9	681.2	680.5	679.9
132.5°	717.1	717.6	718.1	718.3	718.0	717.3	716.6	716.0	715.3	714.8	714.3
135°	751.1	751.6	752.1	752.4	752.1	751.6	751.1	750.6	750.1	749.4	748.8
137.5°	783.4	783.7	784.0	784.2	783.8	782.9	782.1	781.2	780.4	780.1	779.7
140°	812.1	812.4	812.7	812.9	812.6	811.9	811.2	810.6	809.9	809.4	808.9
142.5°	838.9	839.4	839.9	840.2	839.9	839.4	838.9	838.4	837.9	837.4	836.9
145°	865.2	865.2	865.2	865.2	865.0	864.7	864.4	864.0	863.7	863.3	863.0
147.5°	886.5	887.3	888.2	888.6	888.4	888.1	887.8	887.4	887.1	886.8	886.4
150°	908.6	909.1	909.6	909.8	909.6	909.3	909.0	908.6	908.3	908.0	907.6
152.5°	927.4	928.2	929.1	929.5	929.2	928.5	927.8	927.2	926.5	926.3	926.1
155°	944.4	945.4	946.4	946.9	946.5	945.6	944.8	943.9	943.1	942.9	942.8
157.5°	959.5	960.8	962.1	962.8	962.3	961.3	960.3	959.3	958.3	958.5	958.6
160°	972.8	973.9	975.1	975.7	975.2	974.2	973.1	972.1	971.1	971.3	971.5
162.5°	985.2	986.3	987.3	987.8	987.2	986.0	984.9	983.7	982.5	982.7	982.8
165°	995.5	996.6	997.8	998.4	997.7	996.4	995.0	993.7	992.3	992.5	992.7
167.5°	1003.4	1004.7	1006.0	1006.7	1006.0	1004.7	1003.4	1002.0	1000.7	1000.7	1000.7
170°	1010.2	1011.5	1012.8	1013.5	1012.8	1011.5	1010.2	1008.8	1007.5	1007.5	1007.5
172.5°	1014.3	1015.8	1017.3	1018.1	1017.4	1016.1	1014.7	1013.4	1012.0	1011.8	1011.7
175°	1017.7	1019.1	1020.4	1021.1	1020.5	1019.3	1018.2	1017.0	1015.8	1015.6	1015.4
177.5°	1019.2	1020.9	1022.6	1023.4	1022.7	1021.4	1020.0	1018.7	1017.3	1017.1	1017.0
180°	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8

TEST NUMBER: P1012524

CATALOG NUMBER: S123RDIP-B340D805UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	543.7	541.5	539.2	539.2	534.3	529.8	527.5	528.4	525.7	522.1	518.5
5°	567.6	558.6	556.8	551.8	545.1	535.6	530.7	526.2	520.8	513.6	506.9
7.5°	589.6	577.9	571.6	566.7	553.6	540.6	529.8	522.6	513.1	502.4	494.3
10°	618.4	596.8	590.1	578.8	560.4	541.9	529.3	517.6	504.6	492.0	481.2
12.5°	641.3	616.6	604.0	592.7	568.9	545.5	524.4	510.0	494.3	480.3	466.4
15°	667.4	639.5	617.5	604.0	573.9	545.5	521.7	501.5	483.9	466.8	454.7
17.5°	680.0	644.9	635.0	615.7	572.1	543.7	514.5	492.9	471.8	452.0	437.6
20°	699.8	658.9	634.1	621.1	582.4	540.6	506.4	481.7	459.6	438.5	423.2
22.5°	701.1	656.6	640.4	615.7	568.0	531.1	499.2	469.1	443.4	423.6	407.9
25°	698.0	652.6	630.1	610.3	570.7	525.7	484.8	455.1	429.9	407.0	388.6
27.5°	696.6	640.9	619.7	599.9	555.4	510.0	476.3	442.5	413.8	393.5	374.6
30°	694.8	628.3	602.6	579.7	538.8	497.9	457.4	428.1	400.7	375.1	356.2
32.5°	683.1	611.2	585.1	560.8	516.7	475.8	443.9	412.9	383.2	359.3	342.2
35°	679.5	595.4	561.3	535.2	492.0	455.6	421.9	396.2	368.3	344.5	324.3
37.5°	669.2	579.3	542.4	509.1	464.1	429.5	404.8	379.1	352.1	326.5	310.3
40°	651.2	560.4	518.5	484.4	438.0	403.0	380.0	361.1	334.6	311.7	291.9
42.5°	624.7	541.0	496.1	460.1	408.8	376.0	357.1	339.1	316.6	292.8	276.6
45°	594.1	515.4	473.6	433.5	381.4	349.4	329.7	318.9	298.2	277.9	259.0
47.5°	552.3	488.9	447.5	406.1	353.0	322.0	306.3	295.5	281.1	259.0	243.8
50°	499.7	454.7	415.6	378.7	325.2	295.5	279.7	271.6	259.5	243.8	228.9
52.5°	441.2	415.1	382.7	348.5	296.8	268.9	254.5	248.3	239.3	224.4	211.8
55°	382.3	371.0	349.0	315.3	267.1	244.2	231.6	223.5	216.8	206.0	195.2
57.5°	329.7	324.3	309.0	282.9	242.4	218.6	207.8	202.4	197.0	188.9	178.1
60°	275.2	281.1	265.3	252.3	215.4	194.7	185.3	179.4	176.7	169.5	162.8
62.5°	228.0	233.4	224.4	214.5	188.4	170.0	164.2	158.8	157.0	150.7	143.9
65°	185.3	192.0	185.3	179.9	164.2	148.9	141.7	139.0	137.2	133.1	127.7
67.5°	147.5	154.3	151.1	144.4	139.4	126.8	122.8	120.1	119.2	116.0	111.5
70°	111.1	120.5	121.4	117.4	112.9	107.0	104.3	103.4	101.2	98.5	95.8
72.5°	80.1	90.8	91.3	91.3	88.6	88.6	85.9	84.6	84.6	81.9	78.7
75°	58.9	66.1	67.0	67.9	69.3	70.6	68.8	68.8	68.4	65.7	64.3
77.5°	39.1	45.4	47.7	50.8	52.6	52.6	53.5	54.4	53.5	52.2	51.3
80°	25.2	29.7	32.4	34.2	36.9	38.2	39.6	40.0	39.1	38.7	37.3
82.5°	16.6	18.0	19.3	21.6	24.7	27.0	27.0	26.5	27.4	27.0	26.5
85°	9.4	10.3	10.8	11.2	13.0	15.3	15.7	16.2	17.1	16.2	15.3
87.5°	3.6	4.0	4.0	4.0	4.9	5.4	6.7	8.5	8.1	7.2	7.2
90°	11.6	9.4	8.3	7.5	5.8	4.1	2.5	0.8	2.5	4.1	5.8
92.5°	15.2	13.7	12.9	13.4	14.4	15.4	16.4	17.4	16.4	15.4	14.4
95°	17.9	16.0	15.1	18.6	25.5	32.4	39.3	46.2	39.3	32.4	25.5
97.5°	49.9	58.5	62.8	65.2	69.9	74.6	79.3	84.0	79.3	74.6	69.9
100°	103.7	130.0	143.1	141.4	138.0	134.7	131.3	127.9	131.3	134.7	138.0
102.5°	143.8	173.1	187.7	186.6	184.4	182.3	180.1	177.9	180.1	182.3	184.4
105°	211.2	226.3	233.9	233.0	231.1	229.3	227.4	225.6	227.4	229.3	231.1
107.5°	286.9	284.4	283.1	282.3	280.8	279.3	277.8	276.3	277.8	279.3	280.8
110°	335.8	333.9	333.0	332.3	331.0	329.7	328.3	327.0	328.3	329.7	331.0

TEST NUMBER: P1012524

CATALOG NUMBER: S123RDIP-B340D805UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	383.5	381.6	380.7	380.1	378.9	377.8	376.6	375.4	376.6	377.8	378.9
115°	430.0	428.5	427.7	427.2	426.2	425.1	424.1	423.1	424.1	425.1	426.2
117.5°	476.6	475.7	475.3	474.7	473.6	472.4	471.3	470.1	471.3	472.4	473.6
120°	520.8	520.3	520.0	519.2	517.7	516.2	514.7	513.2	514.7	516.2	517.7
122.5°	563.4	562.7	562.4	561.8	560.6	559.5	558.3	557.1	558.3	559.5	560.6
125°	603.5	602.8	602.5	601.8	600.5	599.2	597.8	596.5	597.8	599.2	600.5
127.5°	643.2	642.3	641.9	641.2	639.9	638.5	637.2	635.8	637.2	638.5	639.9
130°	679.2	678.5	678.2	677.5	676.2	674.9	673.5	672.2	673.5	674.9	676.2
132.5°	713.8	713.3	713.0	712.3	711.0	709.7	708.3	707.0	708.3	709.7	711.0
135°	748.1	747.4	747.1	746.6	745.6	744.5	743.5	742.5	743.5	744.5	745.6
137.5°	779.4	779.1	778.9	778.2	776.9	775.5	774.2	772.8	774.2	775.5	776.9
140°	808.4	807.9	807.6	807.1	806.1	805.1	804.1	803.1	804.1	805.1	806.1
142.5°	836.4	835.9	835.6	835.1	834.1	833.1	832.1	831.1	832.1	833.1	834.1
145°	862.6	862.3	862.1	861.5	860.3	859.2	858.0	856.8	858.0	859.2	860.3
147.5°	886.1	885.8	885.6	885.2	884.3	883.5	882.6	881.8	882.6	883.5	884.3
150°	907.3	907.0	906.8	906.5	906.0	905.5	905.0	904.5	905.0	905.5	906.0
152.5°	926.0	925.8	925.7	925.6	925.5	925.3	925.2	925.0	925.2	925.3	925.5
155°	942.6	942.5	942.4	942.6	942.9	943.2	943.6	943.9	943.6	943.2	942.9
157.5°	958.8	958.9	959.0	959.0	959.0	959.0	959.0	959.0	959.0	959.0	959.0
160°	971.6	971.8	971.9	972.0	972.1	972.3	972.4	972.6	972.4	972.3	972.1
162.5°	983.0	983.1	983.2	983.5	984.0	984.5	985.0	985.5	985.0	984.5	984.0
165°	992.8	993.0	993.1	993.4	993.9	994.4	994.9	995.4	994.9	994.4	993.9
167.5°	1000.7	1000.7	1000.7	1001.0	1001.7	1002.4	1003.0	1003.7	1003.0	1002.4	1001.7
170°	1007.5	1007.5	1007.5	1007.8	1008.5	1009.2	1009.8	1010.5	1009.8	1009.2	1008.5
172.5°	1011.5	1011.4	1011.3	1011.7	1012.5	1013.4	1014.2	1015.0	1014.2	1013.4	1012.5
175°	1015.3	1015.1	1015.0	1015.4	1016.3	1017.1	1018.0	1018.8	1018.0	1017.1	1016.3
177.5°	1016.8	1016.7	1016.6	1017.0	1017.8	1018.7	1019.5	1020.3	1019.5	1018.7	1017.8
180°	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8

TEST NUMBER: P1012524

CATALOG NUMBER: S123RDIP-B340D805UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	518.5	516.3	515.4	513.1	507.7	504.2	500.1	497.4	497.9	495.6	497.0
5°	502.4	501.9	498.8	494.3	486.6	482.6	475.4	471.8	470.0	470.4	467.7
7.5°	488.9	484.8	482.6	475.4	468.2	459.6	453.8	450.6	447.9	445.2	443.4
10°	473.6	470.0	466.4	458.7	448.8	440.7	432.6	429.5	425.4	423.6	422.3
12.5°	457.4	455.1	450.6	441.6	430.4	422.8	413.3	411.5	406.1	402.5	401.6
15°	442.5	441.2	433.1	422.8	411.5	403.9	395.8	390.4	381.4	383.2	380.0
17.5°	426.8	421.0	416.0	402.1	396.7	385.0	375.5	372.8	366.5	362.5	358.4
20°	409.3	405.7	399.4	390.4	377.3	363.8	356.6	352.1	348.5	342.2	340.4
22.5°	392.6	388.1	382.7	371.0	359.8	348.5	338.6	334.6	330.1	325.6	322.9
25°	379.6	372.8	367.0	352.6	341.3	331.9	325.6	318.9	312.6	309.9	309.0
27.5°	359.3	355.3	349.4	336.0	325.6	315.3	309.4	304.9	298.2	295.0	292.3
30°	346.3	338.2	331.5	320.7	310.3	299.1	293.7	288.3	284.2	280.2	277.0
32.5°	328.8	322.5	317.1	306.3	295.9	285.6	279.7	271.6	269.4	266.2	262.6
35°	311.7	307.6	301.8	290.1	278.8	271.6	265.3	257.7	255.0	252.8	249.6
37.5°	295.5	289.6	285.6	274.3	264.4	255.9	251.0	244.7	242.9	240.2	237.9
40°	281.5	275.7	271.6	260.4	250.1	241.1	237.9	231.6	228.9	225.8	224.4
42.5°	265.8	260.8	255.4	247.4	236.6	227.6	221.3	217.7	214.1	212.7	210.0
45°	249.2	244.7	240.6	231.6	220.4	214.1	208.7	203.7	201.0	198.8	197.0
47.5°	234.8	230.7	225.3	215.4	206.4	200.6	195.2	190.2	187.5	184.8	182.6
50°	218.1	215.9	210.0	200.6	192.0	185.3	180.3	175.8	174.0	170.9	167.3
52.5°	203.3	199.2	194.3	186.6	179.0	170.9	164.2	161.5	158.3	156.5	153.4
55°	185.7	183.0	177.6	170.9	162.8	156.1	151.1	147.5	143.5	141.7	137.6
57.5°	170.9	166.0	163.3	154.7	147.1	140.3	136.7	133.1	128.6	125.9	124.1
60°	154.7	150.2	146.2	139.0	133.6	126.4	121.0	117.8	114.7	111.1	109.3
62.5°	139.0	135.4	130.4	124.6	117.8	112.0	107.9	103.4	101.6	98.0	96.7
65°	121.9	119.2	115.1	108.4	103.0	98.0	94.0	90.4	88.6	87.2	86.3
67.5°	106.6	103.0	100.3	94.4	88.6	84.6	82.3	80.1	77.8	76.5	75.1
70°	90.8	88.1	85.4	80.1	76.0	72.4	70.6	68.8	67.5	66.1	64.8
72.5°	74.7	73.3	70.6	67.0	63.9	61.2	59.8	57.6	56.2	54.0	53.1
75°	61.6	59.4	58.0	54.9	52.2	49.9	48.1	45.4	43.6	42.7	42.3
77.5°	48.6	47.7	45.9	43.2	41.8	39.6	36.9	36.0	35.1	35.1	34.6
80°	36.4	35.1	33.7	31.5	30.1	28.3	28.3	28.3	27.9	28.3	27.9
82.5°	24.7	23.8	22.9	21.6	21.1	21.1	21.6	21.6	21.6	21.6	21.6
85°	14.4	14.4	14.4	14.8	14.4	14.4	14.8	15.3	14.8	14.8	14.4
87.5°	6.7	6.7	7.2	7.2	7.6	7.6	7.6	7.6	7.6	7.6	8.1
90°	7.5	8.3	9.4	11.6	13.8	16.0	18.2	18.9	19.5	20.2	20.9
92.5°	13.4	12.9	13.7	15.2	16.7	18.2	19.7	20.9	22.1	23.2	24.4
95°	18.6	15.1	16.0	17.9	19.8	21.6	23.5	24.7	25.9	27.0	28.2
97.5°	65.2	62.8	58.5	49.9	41.4	32.8	24.2	25.6	26.9	28.3	29.6
100°	141.4	143.1	130.0	103.7	77.5	51.2	25.0	26.3	27.7	29.0	30.3
102.5°	186.6	187.7	173.1	143.8	114.5	85.3	56.0	50.4	44.9	39.3	33.8
105°	233.0	233.9	226.3	211.2	196.1	180.9	165.8	136.0	106.2	76.5	46.7
107.5°	282.3	283.1	284.4	286.9	289.4	291.9	294.4	268.5	242.6	216.7	190.8
110°	332.3	333.0	333.9	335.8	337.7	339.5	341.4	335.8	330.3	324.7	319.2

TEST NUMBER: P1012524

CATALOG NUMBER: S123RDIP-B340D805UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	380.1	380.7	381.6	383.5	385.4	387.2	389.1	390.6	392.1	393.6	395.1
115°	427.2	427.7	428.5	430.0	431.5	433.0	434.5	436.2	437.8	439.5	441.2
117.5°	474.7	475.3	475.7	476.6	477.4	478.3	479.1	480.5	481.8	483.2	484.5
120°	519.2	520.0	520.3	520.8	521.3	521.8	522.3	523.6	525.0	526.3	527.6
122.5°	561.8	562.4	562.7	563.4	564.1	564.7	565.4	566.2	567.1	567.9	568.8
125°	601.8	602.5	602.8	603.5	604.2	604.8	605.5	605.9	606.2	606.6	606.9
127.5°	641.2	641.9	642.3	643.2	644.0	644.9	645.7	646.2	646.7	647.2	647.7
130°	677.5	678.2	678.5	679.2	679.9	680.5	681.2	681.9	682.6	683.3	684.0
132.5°	712.3	713.0	713.3	713.8	714.3	714.8	715.3	716.0	716.6	717.3	718.0
135°	746.6	747.1	747.4	748.1	748.8	749.4	750.1	750.6	751.1	751.6	752.1
137.5°	778.2	778.9	779.1	779.4	779.7	780.1	780.4	781.2	782.1	782.9	783.8
140°	807.1	807.6	807.9	808.4	808.9	809.4	809.9	810.6	811.2	811.9	812.6
142.5°	835.1	835.6	835.9	836.4	836.9	837.4	837.9	838.4	838.9	839.4	839.9
145°	861.5	862.1	862.3	862.6	863.0	863.3	863.7	864.0	864.4	864.7	865.0
147.5°	885.2	885.6	885.8	886.1	886.4	886.8	887.1	887.4	887.8	888.1	888.4
150°	906.5	906.8	907.0	907.3	907.6	908.0	908.3	908.6	909.0	909.3	909.6
152.5°	925.6	925.7	925.8	926.0	926.1	926.3	926.5	927.2	927.8	928.5	929.2
155°	942.6	942.4	942.5	942.6	942.8	942.9	943.1	943.9	944.8	945.6	946.5
157.5°	959.0	959.0	958.9	958.8	958.6	958.5	958.3	959.3	960.3	961.3	962.3
160°	972.0	971.9	971.8	971.6	971.5	971.3	971.1	972.1	973.1	974.2	975.2
162.5°	983.5	983.2	983.1	983.0	982.8	982.7	982.5	983.7	984.9	986.0	987.2
165°	993.4	993.1	993.0	992.8	992.7	992.5	992.3	993.7	995.0	996.4	997.7
167.5°	1001.0	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1002.0	1003.4	1004.7	1006.0
170°	1007.8	1007.5	1007.5	1007.5	1007.5	1007.5	1007.5	1008.8	1010.2	1011.5	1012.8
172.5°	1011.7	1011.3	1011.4	1011.5	1011.7	1011.8	1012.0	1013.4	1014.7	1016.1	1017.4
175°	1015.4	1015.0	1015.1	1015.3	1015.4	1015.6	1015.8	1017.0	1018.2	1019.3	1020.5
177.5°	1017.0	1016.6	1016.7	1016.8	1017.0	1017.1	1017.3	1018.7	1020.0	1021.4	1022.7
180°	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8

TEST NUMBER: P1012524

CATALOG NUMBER: S123RDIP-B340D805UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	496.5	497.0	495.6	492.9	492.5	493.4	496.1	495.2	492.9	497.0	493.4
5°	469.1	466.8	465.9	466.8	464.1	462.8	465.5	464.1	465.5	465.9	467.3
7.5°	442.5	443.0	440.3	440.7	437.1	438.0	438.0	438.0	439.4	440.3	442.1
10°	419.6	420.5	417.4	417.8	415.1	413.3	414.7	417.4	417.4	417.4	418.3
12.5°	401.2	397.1	394.9	394.4	391.3	390.4	393.1	394.0	396.2	396.2	397.6
15°	378.2	377.3	375.5	375.5	367.9	369.7	370.6	373.7	378.2	374.6	375.5
17.5°	357.5	355.3	353.0	352.1	351.2	348.5	352.1	351.7	354.4	354.8	356.2
20°	339.1	337.3	332.8	333.3	334.2	330.1	332.4	332.4	335.1	337.8	340.9
22.5°	321.1	319.3	317.1	318.0	315.3	314.4	314.4	316.6	319.8	322.0	321.6
25°	307.2	304.0	302.7	301.3	300.0	300.9	299.5	301.8	304.0	305.4	304.0
27.5°	291.4	290.1	287.4	286.0	283.8	284.7	285.6	287.4	288.7	288.7	290.1
30°	276.1	274.3	273.4	272.1	272.1	270.3	270.7	272.5	273.9	275.2	277.0
32.5°	261.3	259.9	258.6	258.6	257.7	257.2	256.8	259.5	259.5	262.2	262.2
35°	249.2	246.9	246.9	244.7	245.6	245.1	244.2	246.0	246.5	248.3	247.8
37.5°	235.7	235.7	234.8	232.5	230.7	231.2	233.4	233.4	234.8	234.3	235.7
40°	222.2	221.3	221.3	219.9	219.5	219.0	219.5	219.9	222.2	221.7	222.2
42.5°	208.7	209.1	206.9	206.9	206.9	205.5	206.0	206.4	207.3	208.2	209.6
45°	195.6	194.7	194.3	193.4	192.5	192.9	192.5	194.3	193.8	194.7	196.1
47.5°	181.7	180.3	179.9	178.1	178.1	179.0	178.5	179.9	180.3	181.7	180.8
50°	168.2	166.4	165.1	165.5	162.8	163.7	163.7	165.1	166.4	166.9	167.8
52.5°	152.5	152.0	151.6	149.3	148.9	148.4	148.9	149.3	151.1	152.5	152.9
55°	137.2	136.7	134.0	133.1	131.8	131.8	132.7	133.1	136.3	136.7	138.5
57.5°	123.2	121.9	118.7	118.3	118.3	118.3	116.9	118.7	119.6	121.9	121.9
60°	107.9	107.9	105.2	105.2	105.7	105.2	105.2	105.7	105.7	107.5	108.4
62.5°	95.8	95.3	95.3	94.4	94.0	94.4	94.0	94.0	94.4	95.8	97.1
65°	85.0	84.6	84.1	83.7	82.8	82.8	83.2	84.1	84.1	85.0	85.4
67.5°	74.7	74.7	73.8	73.8	73.3	72.9	73.3	72.9	74.7	74.7	75.1
70°	64.3	63.9	62.5	62.1	60.7	61.2	61.2	62.5	63.0	63.9	64.8
72.5°	51.7	51.7	50.8	49.9	50.4	49.5	49.5	49.9	49.9	51.3	51.7
75°	42.7	41.8	41.4	41.8	41.4	42.3	41.4	41.4	42.3	42.3	42.3
77.5°	35.1	35.1	34.6	34.6	35.1	34.6	35.1	35.1	35.1	34.6	35.1
80°	28.8	28.3	28.3	28.3	27.9	27.9	27.9	27.9	27.9	27.9	27.9
82.5°	21.6	21.6	21.1	21.6	21.6	21.1	21.6	21.1	21.1	21.6	21.6
85°	14.4	15.3	14.4	14.4	14.8	14.8	15.3	14.8	15.3	14.4	14.8
87.5°	7.6	8.1	8.1	7.6	7.6	8.1	8.1	8.1	8.5	7.6	8.1
90°	21.2	21.4	21.7	22.0	22.4	22.7	22.4	22.0	21.7	21.4	21.2
92.5°	25.0	25.1	25.2	25.4	25.5	25.7	25.5	25.4	25.2	25.1	25.0
95°	28.8	28.8	28.8	28.8	28.8	28.8	28.8	28.8	28.8	28.8	28.8
97.5°	30.3	30.4	30.5	30.7	30.8	31.0	30.8	30.7	30.5	30.4	30.3
100°	31.0	31.1	31.3	31.4	31.6	31.8	31.6	31.4	31.3	31.1	31.0
102.5°	31.0	31.2	31.5	31.8	32.2	32.5	32.2	31.8	31.5	31.2	31.0
105°	31.8	32.0	32.3	32.6	33.0	33.3	33.0	32.6	32.3	32.0	31.8
107.5°	177.9	166.9	144.8	122.8	100.7	78.7	100.7	122.8	144.8	166.9	177.9
110°	316.4	304.4	280.3	256.3	232.2	208.2	232.2	256.3	280.3	304.4	316.4

TEST NUMBER: P1012524

CATALOG NUMBER: S123RDIP-B340D805UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	395.9	395.7	395.4	395.1	394.7	394.4	394.7	395.1	395.4	395.7	395.9
115°	442.0	442.3	443.0	443.7	444.4	445.1	444.4	443.7	443.0	442.3	442.0
117.5°	485.2	485.3	485.4	485.6	485.7	485.9	485.7	485.6	485.4	485.3	485.2
120°	528.3	528.3	528.3	528.3	528.3	528.3	528.3	528.3	528.3	528.3	528.3
122.5°	569.2	569.3	569.5	569.6	569.8	570.0	569.8	569.6	569.5	569.3	569.2
125°	607.1	607.3	607.6	607.9	608.3	608.6	608.3	607.9	607.6	607.3	607.1
127.5°	647.9	647.7	647.4	647.1	646.7	646.4	646.7	647.1	647.4	647.7	647.9
130°	684.3	684.1	683.8	683.4	683.1	682.7	683.1	683.4	683.8	684.1	684.3
132.5°	718.3	718.1	717.6	717.1	716.6	716.1	716.6	717.1	717.6	718.1	718.3
135°	752.4	752.1	751.6	751.1	750.6	750.1	750.6	751.1	751.6	752.1	752.4
137.5°	784.2	784.0	783.7	783.4	783.0	782.7	783.0	783.4	783.7	784.0	784.2
140°	812.9	812.7	812.4	812.1	811.7	811.4	811.7	812.1	812.4	812.7	812.9
142.5°	840.2	839.9	839.4	838.9	838.4	837.9	838.4	838.9	839.4	839.9	840.2
145°	865.2	865.2	865.2	865.2	865.2	865.2	865.2	865.2	865.2	865.2	865.2
147.5°	888.6	888.2	887.3	886.5	885.6	884.8	885.6	886.5	887.3	888.2	888.6
150°	909.8	909.6	909.1	908.6	908.1	907.6	908.1	908.6	909.1	909.6	909.8
152.5°	929.5	929.1	928.2	927.4	926.5	925.7	926.5	927.4	928.2	929.1	929.5
155°	946.9	946.4	945.4	944.4	943.4	942.4	943.4	944.4	945.4	946.4	946.9
157.5°	962.8	962.1	960.8	959.5	958.1	956.8	958.1	959.5	960.8	962.1	962.8
160°	975.7	975.1	973.9	972.8	971.6	970.4	971.6	972.8	973.9	975.1	975.7
162.5°	987.8	987.3	986.3	985.2	984.2	983.2	984.2	985.2	986.3	987.3	987.8
165°	998.4	997.8	996.6	995.5	994.3	993.1	994.3	995.5	996.6	997.8	998.4
167.5°	1006.7	1006.0	1004.7	1003.4	1002.0	1000.7	1002.0	1003.4	1004.7	1006.0	1006.7
170°	1013.5	1012.8	1011.5	1010.2	1008.8	1007.5	1008.8	1010.2	1011.5	1012.8	1013.5
172.5°	1018.1	1017.3	1015.8	1014.3	1012.8	1011.3	1012.8	1014.3	1015.8	1017.3	1018.1
175°	1021.1	1020.4	1019.1	1017.7	1016.4	1015.0	1016.4	1017.7	1019.1	1020.4	1021.1
177.5°	1023.4	1022.6	1020.9	1019.2	1017.5	1015.8	1017.5	1019.2	1020.9	1022.6	1023.4
180°	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8

TEST NUMBER: P1012524

CATALOG NUMBER: S123RDIP-B340D805UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3	525.3
2.5°	497.0	498.8	497.0	493.4	497.0	499.2	501.5	505.1	506.9	506.9	509.5
5°	468.6	472.2	470.9	470.0	473.6	475.8	479.4	483.9	488.9	492.0	495.6
7.5°	443.4	445.7	447.9	447.9	451.5	456.5	461.9	467.3	473.6	478.1	480.8
10°	421.4	423.2	424.5	426.3	431.7	437.1	444.3	451.1	456.5	461.4	465.9
12.5°	400.3	403.0	406.1	407.5	411.5	418.3	425.0	433.1	441.6	446.6	451.1
15°	380.0	381.4	385.0	389.0	392.6	399.8	408.4	416.9	424.1	431.7	435.8
17.5°	359.3	359.8	369.2	367.0	378.7	385.4	389.9	398.0	409.7	416.0	422.3
20°	339.1	343.6	347.6	349.9	356.2	363.8	376.9	383.2	392.6	398.5	403.9
22.5°	323.4	330.1	330.1	335.5	338.6	345.8	355.3	367.4	377.8	381.8	389.5
25°	309.4	312.6	318.0	319.8	325.6	331.9	338.2	351.2	362.5	367.9	373.3
27.5°	291.4	295.5	302.7	302.7	310.3	317.1	324.7	333.3	344.5	352.1	358.0
30°	277.5	281.5	284.7	289.6	292.8	299.1	312.6	318.9	328.8	335.5	342.7
32.5°	264.4	267.6	270.3	275.7	279.3	286.5	293.7	304.9	313.5	319.8	327.4
35°	250.1	253.2	256.8	260.8	266.2	273.0	279.7	289.2	297.7	303.6	309.9
37.5°	236.6	238.8	244.2	246.9	251.4	257.7	266.2	276.1	283.8	288.3	294.6
40°	223.5	225.3	229.4	234.3	237.5	242.4	251.4	259.9	269.4	274.8	279.7
42.5°	209.6	211.8	215.4	220.4	225.3	230.7	235.7	245.6	254.1	258.6	264.0
45°	197.4	198.8	201.5	206.4	211.4	215.4	223.1	232.1	240.2	243.8	249.6
47.5°	183.0	184.4	188.4	190.7	196.1	201.5	209.1	218.1	225.3	228.9	234.3
50°	168.2	169.5	172.2	177.2	180.8	186.6	193.4	201.0	210.0	215.0	218.1
52.5°	153.8	156.5	158.8	162.8	167.3	173.1	179.4	186.6	194.3	199.2	202.8
55°	139.4	141.7	144.4	146.6	152.0	157.4	164.6	171.3	178.1	182.6	186.6
57.5°	123.2	126.4	129.1	133.6	137.6	142.1	150.2	155.6	163.7	166.9	170.4
60°	109.3	112.4	114.7	118.3	121.9	127.7	133.1	139.9	146.6	150.7	155.2
62.5°	97.6	98.9	100.3	103.9	107.5	112.9	118.3	125.0	132.2	134.5	138.1
65°	85.9	87.2	89.5	92.6	95.3	98.5	104.3	109.7	116.5	120.1	121.4
67.5°	76.0	77.4	77.8	80.1	82.3	85.9	89.0	94.4	100.7	103.0	105.7
70°	64.8	67.0	67.5	69.3	70.2	72.4	76.0	80.1	85.0	89.0	91.3
72.5°	51.7	54.9	55.8	58.5	59.8	62.1	64.8	67.9	71.1	72.9	74.7
75°	42.3	43.2	43.6	45.9	48.1	51.3	52.6	54.4	57.1	59.4	61.2
77.5°	35.1	35.5	36.0	36.0	36.4	38.2	40.9	43.2	45.0	45.9	47.2
80°	28.3	27.9	27.9	28.3	28.3	28.3	29.2	32.4	33.3	35.5	35.1
82.5°	22.0	21.1	21.6	21.1	21.1	21.1	21.1	21.6	21.6	22.9	23.8
85°	14.4	14.8	14.4	14.4	13.9	14.4	13.9	13.9	13.5	13.5	13.0
87.5°	7.6	8.1	7.6	7.6	7.2	7.6	7.2	7.2	6.7	6.7	5.8
90°	20.9	20.2	19.5	18.9	18.2	16.0	13.8	11.6	9.4	8.3	7.5
92.5°	24.4	23.2	22.1	20.9	19.7	18.2	16.7	15.2	13.7	12.9	13.4
95°	28.2	27.0	25.9	24.7	23.5	21.6	19.8	17.9	16.0	15.1	18.6
97.5°	29.6	28.3	26.9	25.6	24.2	32.8	41.4	49.9	58.5	62.8	65.2
100°	30.3	29.0	27.7	26.3	25.0	51.2	77.5	103.7	130.0	143.1	141.4
102.5°	33.8	39.3	44.9	50.4	56.0	85.3	114.5	143.8	173.1	187.7	186.6
105°	46.7	76.5	106.2	136.0	165.8	180.9	196.1	211.2	226.3	233.9	233.0
107.5°	190.8	216.7	242.6	268.5	294.4	291.9	289.4	286.9	284.4	283.1	282.3
110°	319.2	324.7	330.3	335.8	341.4	339.5	337.7	335.8	333.9	333.0	332.3

TEST NUMBER: P1012524

CATALOG NUMBER: S123RDIP-B340D805UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	395.1	393.6	392.1	390.6	389.1	387.2	385.4	383.5	381.6	380.7	380.1
115°	441.2	439.5	437.8	436.2	434.5	433.0	431.5	430.0	428.5	427.7	427.2
117.5°	484.5	483.2	481.8	480.5	479.1	478.3	477.4	476.6	475.7	475.3	474.7
120°	527.6	526.3	525.0	523.6	522.3	521.8	521.3	520.8	520.3	520.0	519.2
122.5°	568.8	567.9	567.1	566.2	565.4	564.7	564.1	563.4	562.7	562.4	561.8
125°	606.9	606.6	606.2	605.9	605.5	604.8	604.2	603.5	602.8	602.5	601.8
127.5°	647.7	647.2	646.7	646.2	645.7	644.9	644.0	643.2	642.3	641.9	641.2
130°	684.0	683.3	682.6	681.9	681.2	680.5	679.9	679.2	678.5	678.2	677.5
132.5°	718.0	717.3	716.6	716.0	715.3	714.8	714.3	713.8	713.3	713.0	712.3
135°	752.1	751.6	751.1	750.6	750.1	749.4	748.8	748.1	747.4	747.1	746.6
137.5°	783.8	782.9	782.1	781.2	780.4	780.1	779.7	779.4	779.1	778.9	778.2
140°	812.6	811.9	811.2	810.6	809.9	809.4	808.9	808.4	807.9	807.6	807.1
142.5°	839.9	839.4	838.9	838.4	837.9	837.4	836.9	836.4	835.9	835.6	835.1
145°	865.0	864.7	864.4	864.0	863.7	863.3	863.0	862.6	862.3	862.1	861.5
147.5°	888.4	888.1	887.8	887.4	887.1	886.8	886.4	886.1	885.8	885.6	885.2
150°	909.6	909.3	909.0	908.6	908.3	908.0	907.6	907.3	907.0	906.8	906.5
152.5°	929.2	928.5	927.8	927.2	926.5	926.3	926.1	926.0	925.8	925.7	925.6
155°	946.5	945.6	944.8	943.9	943.1	942.9	942.8	942.6	942.5	942.4	942.6
157.5°	962.3	961.3	960.3	959.3	958.3	958.5	958.6	958.8	958.9	959.0	959.0
160°	975.2	974.2	973.1	972.1	971.1	971.3	971.5	971.6	971.8	971.9	972.0
162.5°	987.2	986.0	984.9	983.7	982.5	982.7	982.8	983.0	983.1	983.2	983.5
165°	997.7	996.4	995.0	993.7	992.3	992.5	992.7	992.8	993.0	993.1	993.4
167.5°	1006.0	1004.7	1003.4	1002.0	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1001.0
170°	1012.8	1011.5	1010.2	1008.8	1007.5	1007.5	1007.5	1007.5	1007.5	1007.5	1007.8
172.5°	1017.4	1016.1	1014.7	1013.4	1012.0	1011.8	1011.7	1011.5	1011.4	1011.3	1011.7
175°	1020.5	1019.3	1018.2	1017.0	1015.8	1015.6	1015.4	1015.3	1015.1	1015.0	1015.4
177.5°	1022.7	1021.4	1020.0	1018.7	1017.3	1017.1	1017.0	1016.8	1016.7	1016.6	1017.0
180°	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8	1018.8

TEST NUMBER: P1012524

CATALOG NUMBER: S123RDIP-B340D805UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	525.3	525.3	525.3	525.3
2.5°	511.8	514.9	521.2	526.6
5°	501.0	506.0	515.4	524.8
7.5°	488.0	495.6	507.7	520.8
10°	475.4	485.3	500.1	515.4
12.5°	462.8	473.1	488.9	508.6
15°	447.9	458.7	477.6	501.5
17.5°	434.9	449.3	466.4	490.2
20°	421.0	431.7	453.8	479.0
22.5°	403.4	421.4	442.1	468.6
25°	389.5	405.2	425.9	456.0
27.5°	372.4	390.8	416.0	442.5
30°	358.4	373.7	397.1	429.0
32.5°	342.2	360.2	384.5	416.0
35°	327.9	343.1	366.1	398.0
37.5°	310.8	327.4	353.0	381.4
40°	295.9	312.1	336.4	362.9
42.5°	277.9	295.0	319.3	341.8
45°	263.5	279.3	298.6	319.3
47.5°	246.0	262.6	281.5	295.9
50°	230.3	245.6	260.4	272.5
52.5°	213.2	227.1	240.6	249.6
55°	197.4	208.2	219.0	225.3
57.5°	179.0	189.3	198.3	201.9
60°	162.8	171.3	177.2	181.2
62.5°	145.7	152.0	156.5	158.8
65°	129.1	133.6	135.8	138.1
67.5°	112.0	116.0	117.4	120.1
70°	94.0	98.5	99.4	100.7
72.5°	80.5	80.5	82.3	84.1
75°	64.3	65.2	66.1	66.1
77.5°	50.4	50.4	51.3	51.7
80°	36.9	37.3	37.3	36.9
82.5°	25.2	26.1	25.2	24.7
85°	13.9	15.7	14.8	14.8
87.5°	5.8	5.8	6.7	5.8
90°	5.8	4.1	2.5	0.8
92.5°	14.4	15.4	16.4	17.4
95°	25.5	32.4	39.3	46.2
97.5°	69.9	74.6	79.3	84.0
100°	138.0	134.7	131.3	127.9
102.5°	184.4	182.3	180.1	177.9
105°	231.1	229.3	227.4	225.6
107.5°	280.8	279.3	277.8	276.3
110°	331.0	329.7	328.3	327.0

TEST NUMBER: P1012524

CATALOG NUMBER: S123RDIP-B340D805UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	378.9	377.8	376.6	375.4
115°	426.2	425.1	424.1	423.1
117.5°	473.6	472.4	471.3	470.1
120°	517.7	516.2	514.7	513.2
122.5°	560.6	559.5	558.3	557.1
125°	600.5	599.2	597.8	596.5
127.5°	639.9	638.5	637.2	635.8
130°	676.2	674.9	673.5	672.2
132.5°	711.0	709.7	708.3	707.0
135°	745.6	744.5	743.5	742.5
137.5°	776.9	775.5	774.2	772.8
140°	806.1	805.1	804.1	803.1
142.5°	834.1	833.1	832.1	831.1
145°	860.3	859.2	858.0	856.8
147.5°	884.3	883.5	882.6	881.8
150°	906.0	905.5	905.0	904.5
152.5°	925.5	925.3	925.2	925.0
155°	942.9	943.2	943.6	943.9
157.5°	959.0	959.0	959.0	959.0
160°	972.1	972.3	972.4	972.6
162.5°	984.0	984.5	985.0	985.5
165°	993.9	994.4	994.9	995.4
167.5°	1001.7	1002.4	1003.0	1003.7
170°	1008.5	1009.2	1009.8	1010.5
172.5°	1012.5	1013.4	1014.2	1015.0
175°	1016.3	1017.1	1018.0	1018.8
177.5°	1017.8	1018.7	1019.5	1020.3
180°	1018.8	1018.8	1018.8	1018.8

(END OF REPORT)