

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012530

Luminaire Tested: S123RDIP-B340D805UB30-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012530
REPORT IS A COMBINATION OF REPORTS P993295 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D805UB30-4F0-XX-W2A-A
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4454.0 lumens
Efficiency: N/A
Efficacy: 130.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012530

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1012530

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	94	90	86	83	84	80	77	75	64	61	60	48	47	46	34	33	32
2	85	79	73	68	76	71	66	62	56	53	50	42	40	39	30	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24
4	72	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21
5	66	55	47	41	59	50	43	38	40	35	31	30	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15
8	52	40	33	28	46	36	30	26	30	25	21	23	20	17	17	15	13
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12
10	45	33	27	22	40	30	24	20	25	20	17	19	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5702	5702	5702	5702
5°	5707	6567	5721	4872
10°	5655	7927	5680	4255
15°	5598	8997	5598	3752
20°	5483	9704	5513	3329
25°	5399	9220	5389	3037
30°	5302	6389	5289	2753
35°	5184	4101	5159	2538
40°	5037	2896	5012	2324
45°	4782	2318	4775	2116
50°	4469	1939	4454	1872
55°	4117	1598	4084	1587
60°	3772	1321	3735	1349
65°	3365	1057	3387	1143
70°	2992	735	3072	925
75°	2537	546	2640	711
80°	2020	360	2193	533
85°	1441	171	1566	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7612 cd/sqm

TEST NUMBER: P1012530

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.0	1.2
10°-20°	162.8	3.7
20°-30°	256.5	5.8
30°-40°	266.7	6.0
40°-50°	228.2	5.1
50°-60°	173.9	3.9
60°-70°	111.4	2.5
70°-80°	53.4	1.2
80°-90°	16.1	0.4
90°-100°	36.3	0.8
100°-110°	175.2	3.9
110°-120°	429.3	9.6
120°-130°	545.1	12.2
130°-140°	582.3	13.1
140°-150°	544.5	12.2
150°-160°	439.2	9.9
160°-170°	283.4	6.4
170°-180°	97.7	2.2
0°-30°	471.3	10.6
0°-40°	738.0	16.6
0°-60°	1140.1	25.6
0°-90°	1321.1	29.7
90°-120°	640.8	14.4
90°-150°	2312.6	51.9
90°-180°	3133.0	70.3
0°-180°	4454.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	530	530	530	530	530	
5°	529	629	531	467	529	50
15°	506	894	506	373	506	142
25°	460	921	459	303	460	212
35°	401	400	400	247	401	251
45°	322	213	322	195	322	248
55°	227	134	225	133	227	204
65°	139	77	140	83	139	139
75°	67	33	69	43	67	72
85°	15	8	16	15	15	17
90°	1	23	1	23	1	3
95°	47	29	47	29	47	56
105°	228	34	228	34	228	241
115°	427	449	427	449	427	422
125°	602	614	602	614	602	538
135°	749	757	749	757	749	577
145°	864	873	864	873	864	541
155°	952	951	952	951	952	439
165°	1004	1002	1004	1002	1004	284
175°	1028	1024	1028	1024	1028	98
180°	1028	1028	1028	1028	1028	

TEST NUMBER: P1012530

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	531.1	534.7	537.4	539.2	543.8	546.5	548.8	552.8	552.8	553.7	555.6
5°	529.3	537.0	542.4	549.7	559.2	563.7	570.1	575.5	583.2	587.3	591.4
7.5°	525.2	536.1	547.4	558.3	572.3	581.4	587.8	601.8	611.8	624.0	633.6
10°	519.7	534.7	549.2	566.0	585.0	598.6	608.2	626.8	645.8	663.0	677.6
12.5°	512.9	531.1	551.9	572.3	599.1	612.7	628.1	651.2	678.5	700.2	719.7
15°	505.7	526.5	550.1	575.1	608.6	627.7	649.9	678.0	708.4	739.7	766.4
17.5°	494.3	520.6	546.9	583.2	622.7	634.0	653.1	691.6	729.3	757.4	790.0
20°	483.0	512.5	545.6	578.2	620.9	647.2	664.9	705.7	746.0	780.0	811.3
22.5°	472.6	503.4	537.9	579.1	619.0	645.4	667.6	710.2	756.9	795.0	833.6
25°	459.9	493.4	531.5	570.5	619.0	639.0	663.5	712.9	762.4	806.4	854.0
27.5°	446.3	480.3	517.9	557.8	602.3	631.7	655.8	708.8	769.2	816.3	865.3
30°	432.7	467.6	503.9	539.7	589.6	617.7	645.4	703.9	772.8	826.8	864.4
32.5°	419.5	449.0	484.8	519.7	569.2	600.0	631.3	698.9	774.2	819.5	837.6
35°	401.4	432.2	461.2	498.4	548.3	578.7	615.4	698.4	768.3	796.4	787.3
37.5°	384.6	410.4	438.1	471.2	522.5	561.9	600.0	686.6	748.8	750.6	699.3
40°	366.0	387.3	410.4	445.4	500.7	539.7	581.0	668.5	713.4	686.6	596.4
42.5°	344.7	363.7	381.9	415.9	476.2	519.7	564.2	645.8	662.1	600.5	506.6
45°	322.0	337.4	354.2	390.0	450.3	493.4	537.9	610.9	594.1	507.0	417.7
47.5°	298.4	311.6	327.9	360.5	422.7	466.7	508.8	561.0	518.4	424.9	350.1
50°	274.8	285.3	301.1	334.7	394.6	434.5	473.5	507.5	447.6	364.6	289.3
52.5°	251.7	259.9	276.2	304.8	362.8	400.9	429.0	442.2	381.4	301.1	251.2
55°	227.2	236.3	247.2	276.2	333.8	361.9	380.5	380.0	317.5	255.3	207.7
57.5°	203.6	211.8	221.3	250.3	297.1	316.1	332.0	324.3	264.9	209.1	178.2
60°	182.8	187.3	197.7	222.2	257.6	273.9	283.0	269.8	216.3	176.4	147.4
62.5°	160.1	164.6	173.2	196.4	218.1	226.8	234.5	217.7	178.7	143.8	126.1
65°	139.2	145.1	150.6	169.2	181.0	191.4	190.5	176.4	139.7	117.0	102.5
67.5°	121.1	123.4	127.9	139.2	144.7	152.4	152.8	137.0	112.5	95.2	86.6
70°	101.6	103.9	107.0	112.5	116.1	117.9	117.0	102.9	84.8	74.4	66.7
72.5°	84.8	84.4	86.6	86.6	90.2	89.8	87.1	76.2	64.4	55.8	51.2
75°	66.7	67.1	67.6	66.7	65.3	63.5	61.2	53.1	45.4	41.3	37.2
77.5°	52.2	51.2	51.7	48.5	46.7	44.9	41.7	37.6	31.3	30.4	28.6
80°	37.2	36.7	36.3	34.9	30.8	29.0	26.8	24.5	23.1	22.2	21.8
82.5°	24.9	24.9	24.0	21.3	19.0	17.7	17.2	16.3	15.0	15.0	14.5
85°	15.0	14.5	13.6	10.9	9.5	9.5	9.5	9.5	8.6	8.6	8.2
87.5°	5.9	5.4	4.1	4.1	3.6	3.6	3.6	3.2	3.2	2.7	2.7
90°	0.8	2.5	4.2	5.9	7.6	8.4	9.5	11.7	13.9	16.1	18.3
92.5°	17.6	16.6	15.6	14.5	13.5	13.0	13.8	15.3	16.8	18.4	19.9
95°	46.6	39.6	32.7	25.7	18.8	15.3	16.2	18.1	20.0	21.8	23.7
97.5°	84.7	80.0	75.2	70.5	65.8	63.4	59.1	50.4	41.7	33.1	24.4
100°	129.0	132.4	135.8	139.2	142.6	144.3	131.1	104.6	78.1	51.7	25.2
102.5°	179.4	181.6	183.8	186.0	188.2	189.3	174.5	145.0	115.5	86.0	56.5
105°	227.5	229.4	231.2	233.1	235.0	235.9	228.3	213.0	197.7	182.5	167.2
107.5°	278.7	280.2	281.7	283.2	284.7	285.5	286.8	289.3	291.9	294.4	297.0
110°	329.8	331.2	332.5	333.9	335.2	335.9	336.8	338.7	340.6	342.4	344.3

TEST NUMBER: P1012530

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	378.7	379.9	381.1	382.2	383.4	384.0	384.9	386.8	388.7	390.5	392.4
115°	426.8	427.8	428.8	429.9	430.9	431.4	432.2	433.7	435.2	436.7	438.2
117.5°	474.1	475.3	476.5	477.7	478.9	479.5	479.9	480.8	481.6	482.5	483.3
120°	517.7	519.2	520.7	522.2	523.7	524.5	524.8	525.3	525.8	526.3	526.8
122.5°	561.9	563.1	564.3	565.5	566.7	567.3	567.6	568.3	569.0	569.6	570.3
125°	601.6	603.0	604.3	605.7	607.0	607.7	608.0	608.7	609.4	610.1	610.8
127.5°	641.3	642.7	644.0	645.4	646.7	647.4	647.8	648.7	649.6	650.4	651.3
130°	678.0	679.4	680.7	682.1	683.4	684.1	684.4	685.1	685.8	686.5	687.2
132.5°	713.1	714.5	715.8	717.2	718.5	719.2	719.5	720.0	720.5	721.0	721.5
135°	749.0	750.0	751.0	752.1	753.1	753.6	753.9	754.6	755.3	755.9	756.6
137.5°	779.5	780.9	782.2	783.6	784.9	785.6	785.8	786.1	786.5	786.8	787.2
140°	810.1	811.1	812.1	813.2	814.2	814.7	814.9	815.4	815.9	816.4	816.9
142.5°	838.3	839.3	840.3	841.4	842.4	842.9	843.2	843.7	844.2	844.7	845.2
145°	864.3	865.5	866.7	867.8	869.0	869.6	869.8	870.1	870.5	870.8	871.2
147.5°	889.5	890.3	891.2	892.0	892.9	893.3	893.5	893.8	894.1	894.5	894.8
150°	912.4	912.9	913.4	913.9	914.4	914.7	914.9	915.2	915.5	915.9	916.2
152.5°	933.0	933.2	933.4	933.5	933.7	933.8	933.9	934.0	934.2	934.3	934.5
155°	952.1	951.8	951.4	951.1	950.8	950.6	950.7	950.8	951.0	951.1	951.3
157.5°	967.4	967.4	967.4	967.4	967.4	967.4	967.3	967.1	967.0	966.8	966.6
160°	981.1	980.9	980.7	980.6	980.4	980.3	980.2	980.1	979.9	979.8	979.6
162.5°	994.1	993.6	993.1	992.6	992.1	991.8	991.7	991.5	991.4	991.2	991.0
165°	1004.0	1003.5	1003.0	1002.5	1002.0	1001.7	1001.6	1001.5	1001.3	1001.2	1001.0
167.5°	1012.4	1011.7	1011.0	1010.3	1009.6	1009.3	1009.3	1009.3	1009.3	1009.3	1009.3
170°	1019.3	1018.6	1017.9	1017.2	1016.5	1016.2	1016.2	1016.2	1016.2	1016.2	1016.2
172.5°	1023.9	1023.0	1022.2	1021.3	1020.4	1020.0	1020.1	1020.3	1020.4	1020.6	1020.8
175°	1027.7	1026.9	1026.0	1025.2	1024.3	1023.9	1024.0	1024.1	1024.3	1024.4	1024.6
177.5°	1029.2	1028.4	1027.5	1026.7	1025.8	1025.4	1025.5	1025.6	1025.8	1025.9	1026.1
180°	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7

TEST NUMBER: P1012530

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	559.2	559.2	563.3	567.3	565.1	566.4	571.4	569.6	573.2	572.8	574.2
5°	601.4	606.4	610.4	619.0	620.4	619.0	627.7	629.9	634.0	629.0	631.3
7.5°	649.0	659.4	669.4	682.1	686.2	687.1	691.6	698.0	703.4	693.4	698.4
10°	695.2	711.1	731.5	742.9	752.8	756.5	760.1	764.2	770.5	776.4	771.9
12.5°	745.1	768.3	787.8	808.2	820.4	819.1	829.5	832.2	837.2	838.6	840.4
15°	785.9	818.6	830.8	861.2	863.9	873.0	884.8	895.2	896.6	893.9	893.9
17.5°	824.9	853.1	874.8	899.3	904.3	912.0	927.0	932.0	933.8	933.3	933.3
20°	856.7	875.3	912.0	932.4	940.6	950.6	961.0	967.4	968.7	970.5	967.8
22.5°	877.6	905.7	935.6	952.4	959.2	962.8	969.6	971.4	969.2	969.6	970.1
25°	893.9	921.5	939.7	944.2	943.8	939.2	934.2	925.6	924.7	921.1	913.8
27.5°	898.4	908.8	906.6	888.0	869.4	867.6	837.6	821.3	802.7	805.4	795.0
30°	873.9	860.3	828.1	781.0	761.5	729.7	696.1	661.2	647.6	632.7	660.3
32.5°	814.1	765.5	708.4	647.2	614.5	586.4	550.6	525.2	510.7	498.4	522.0
35°	723.8	648.1	572.3	514.3	487.5	462.1	428.6	415.9	397.7	399.5	401.8
37.5°	607.7	524.3	467.1	410.0	392.3	381.9	357.4	337.9	331.5	329.7	329.7
40°	498.9	430.4	379.6	334.7	321.1	312.5	293.0	283.9	277.1	275.3	277.6
42.5°	412.7	354.2	314.7	284.8	275.3	264.4	256.2	244.9	243.5	240.4	244.4
45°	346.5	295.7	266.2	244.4	236.3	232.2	223.1	216.3	213.6	213.2	216.3
47.5°	293.9	254.4	228.6	215.0	208.6	204.5	196.8	194.1	191.4	192.3	190.9
50°	246.7	217.2	200.5	188.2	184.1	180.0	175.1	172.3	171.0	171.0	170.5
52.5°	211.8	187.3	176.4	165.1	163.3	161.0	155.6	153.7	151.5	151.0	152.8
55°	181.4	164.6	153.7	146.9	145.1	140.6	138.3	136.1	134.7	133.8	134.2
57.5°	155.1	142.4	135.1	129.3	126.1	124.3	120.2	119.7	118.8	118.8	118.4
60°	133.3	124.3	115.6	112.0	109.8	107.5	107.0	104.3	102.9	103.9	103.4
62.5°	112.9	105.7	100.7	96.6	95.2	93.4	92.1	91.2	89.8	90.2	90.2
65°	94.3	88.4	84.8	81.2	80.7	78.9	78.5	77.6	77.6	77.1	78.0
67.5°	77.6	73.5	70.3	68.0	66.7	67.1	65.3	63.9	63.9	63.5	64.9
70°	61.7	59.4	56.2	53.5	51.7	51.7	49.4	49.0	49.0	49.0	48.5
72.5°	47.6	43.5	42.2	41.3	41.3	41.3	40.4	40.4	39.9	40.4	39.9
75°	35.4	34.9	34.0	33.6	33.6	33.1	32.7	32.7	32.7	32.7	32.7
77.5°	27.7	27.7	26.8	26.3	26.3	26.3	25.9	25.9	25.4	25.4	25.4
80°	20.4	20.4	19.5	19.5	19.5	19.0	19.0	19.0	19.5	19.0	19.0
82.5°	14.1	14.1	13.6	14.1	13.6	13.2	13.2	13.2	12.7	13.2	13.2
85°	8.2	8.2	7.7	7.3	7.7	7.7	7.3	7.7	7.3	7.7	7.3
87.5°	3.2	2.7	2.7	2.7	2.3	2.7	2.3	2.3	2.7	2.3	2.7
90°	19.0	19.7	20.4	21.1	21.4	21.6	21.9	22.2	22.6	22.9	22.6
92.5°	21.1	22.3	23.4	24.6	25.2	25.3	25.5	25.6	25.8	26.0	25.8
95°	24.9	26.1	27.2	28.4	29.0	29.0	29.0	29.0	29.0	29.0	29.0
97.5°	25.8	27.1	28.5	29.8	30.5	30.6	30.8	30.9	31.1	31.3	31.1
100°	26.6	27.9	29.3	30.6	31.3	31.4	31.6	31.7	31.9	32.1	31.9
102.5°	50.9	45.3	39.7	34.1	31.3	31.5	31.8	32.1	32.5	32.8	32.5
105°	137.2	107.2	77.1	47.1	32.1	32.3	32.6	32.9	33.3	33.6	33.3
107.5°	270.9	244.7	218.6	192.5	179.4	168.3	146.1	123.8	101.6	79.4	101.6
110°	338.7	333.1	327.5	321.9	319.1	307.0	282.7	258.5	234.2	210.0	234.2

TEST NUMBER: P1012530

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	393.9	395.5	397.0	398.5	399.3	399.1	398.8	398.5	398.1	397.8	398.1
115°	439.9	441.6	443.3	445.0	445.9	446.2	446.9	447.6	448.2	448.9	448.2
117.5°	484.7	486.0	487.4	488.7	489.4	489.5	489.7	489.8	490.0	490.2	490.0
120°	528.2	529.5	530.9	532.2	532.9	532.9	532.9	532.9	532.9	532.9	532.9
122.5°	571.2	572.0	572.9	573.8	574.2	574.3	574.4	574.6	574.7	574.9	574.7
125°	611.1	611.5	611.8	612.1	612.3	612.5	612.8	613.2	613.5	613.9	613.5
127.5°	651.8	652.3	652.8	653.3	653.6	653.4	653.1	652.7	652.4	652.0	652.4
130°	687.9	688.5	689.2	689.9	690.2	690.0	689.7	689.4	689.0	688.7	689.0
132.5°	722.2	722.9	723.6	724.3	724.6	724.3	723.8	723.3	722.8	722.3	722.8
135°	757.1	757.6	758.1	758.6	758.9	758.6	758.1	757.6	757.1	756.6	757.1
137.5°	788.0	788.9	789.7	790.6	791.0	790.8	790.5	790.2	789.8	789.5	789.8
140°	817.6	818.3	819.0	819.7	820.0	819.8	819.5	819.2	818.8	818.5	818.8
142.5°	845.7	846.2	846.7	847.2	847.5	847.2	846.7	846.2	845.7	845.2	845.7
145°	871.5	871.9	872.2	872.5	872.7	872.7	872.7	872.7	872.7	872.7	872.7
147.5°	895.2	895.5	895.9	896.2	896.4	896.0	895.1	894.2	893.4	892.5	893.4
150°	916.5	916.9	917.2	917.5	917.7	917.4	916.9	916.4	915.9	915.4	915.9
152.5°	935.2	935.9	936.6	937.3	937.6	937.2	936.3	935.5	934.6	933.8	934.6
155°	952.1	953.0	953.8	954.7	955.1	954.6	953.6	952.6	951.6	950.6	951.6
157.5°	967.6	968.6	969.7	970.7	971.2	970.5	969.2	967.8	966.5	965.1	966.5
160°	980.6	981.6	982.7	983.7	984.2	983.6	982.4	981.2	980.0	978.8	980.0
162.5°	992.2	993.4	994.6	995.8	996.4	995.9	994.9	993.8	992.8	991.8	992.8
165°	1002.4	1003.7	1005.1	1006.4	1007.1	1006.5	1005.3	1004.1	1002.9	1001.7	1002.9
167.5°	1010.7	1012.1	1013.4	1014.8	1015.5	1014.8	1013.4	1012.1	1010.7	1009.3	1010.7
170°	1017.6	1018.9	1020.3	1021.6	1022.3	1021.6	1020.3	1018.9	1017.6	1016.2	1017.6
172.5°	1022.2	1023.5	1024.9	1026.2	1026.9	1026.1	1024.6	1023.1	1021.5	1020.0	1021.5
175°	1025.8	1027.0	1028.2	1029.4	1030.0	1029.3	1028.0	1026.6	1025.3	1023.9	1025.3
177.5°	1027.5	1028.9	1030.2	1031.6	1032.3	1031.4	1029.7	1028.0	1026.3	1024.6	1026.3
180°	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7

TEST NUMBER: P1012530

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	571.9	569.2	567.3	566.0	564.6	568.7	563.3	557.4	553.3	550.6	549.7
5°	631.7	625.9	620.9	616.8	617.7	617.7	608.2	597.7	588.7	583.7	578.2
7.5°	701.1	694.8	684.8	682.5	680.7	669.4	659.9	640.8	629.5	618.1	608.2
10°	770.1	761.9	752.4	749.2	744.7	730.6	716.1	691.6	677.6	656.7	643.5
12.5°	834.5	824.5	815.0	812.7	805.9	793.7	768.7	743.3	719.3	697.1	673.9
15°	888.4	885.7	871.2	862.1	847.2	830.4	824.9	790.5	760.1	737.0	695.2
17.5°	933.8	921.1	907.5	901.6	895.7	876.2	856.7	821.3	788.7	754.7	727.9
20°	970.1	956.0	946.5	937.9	935.2	912.9	882.1	850.8	815.0	776.9	742.0
22.5°	971.9	970.1	963.7	958.7	953.3	938.8	914.3	875.3	837.2	795.5	749.7
25°	934.2	931.5	949.7	945.1	948.8	943.3	930.2	897.5	853.1	804.1	757.8
27.5°	820.9	848.5	877.1	887.1	893.9	913.4	919.7	901.6	865.8	813.6	761.9
30°	666.7	703.4	749.7	774.6	793.7	829.9	877.1	883.0	866.2	824.5	761.0
32.5°	523.4	556.9	594.1	623.6	649.0	723.4	786.9	832.7	840.8	819.1	763.3
35°	421.8	436.3	471.7	499.8	534.2	597.7	672.6	746.5	796.4	799.1	756.5
37.5°	347.8	355.6	386.4	402.3	422.7	478.5	548.3	644.9	722.5	759.2	737.4
40°	288.0	305.7	323.4	332.4	346.9	385.5	452.6	528.3	624.5	692.5	707.9
42.5°	249.9	257.6	268.9	281.6	290.7	324.3	369.2	438.6	525.2	620.0	662.6
45°	220.4	223.1	234.9	243.1	252.6	276.2	307.9	366.0	442.2	535.6	608.2
47.5°	195.9	201.4	207.7	212.7	219.0	237.2	264.4	306.6	373.7	457.1	535.1
50°	174.2	177.3	185.5	187.8	192.3	205.0	225.9	258.1	313.4	380.0	460.8
52.5°	153.7	159.6	162.8	166.0	170.1	180.5	194.1	220.4	262.1	324.7	393.2
55°	137.9	139.7	144.2	146.9	150.1	157.4	169.2	188.7	221.3	271.2	336.1
57.5°	122.4	122.4	127.0	129.3	132.4	137.9	148.3	163.3	186.8	224.0	283.4
60°	106.1	106.6	110.2	112.9	113.8	119.3	127.9	139.7	157.8	185.0	233.6
62.5°	91.6	93.9	95.7	96.6	99.8	102.9	110.2	118.4	131.1	155.1	189.6
65°	79.4	79.8	81.2	82.1	83.4	87.1	92.5	98.0	108.8	126.5	154.6
67.5°	65.3	67.1	68.9	68.9	70.3	72.1	77.6	82.1	90.2	100.7	119.7
70°	49.0	49.9	52.6	54.0	55.8	59.0	61.7	64.4	70.7	78.5	93.0
72.5°	40.8	40.8	41.7	42.2	42.2	44.4	48.5	51.2	54.4	59.9	69.8
75°	32.7	32.7	34.0	33.6	34.5	35.4	35.8	37.6	39.5	43.5	49.4
77.5°	25.9	26.3	26.3	26.8	26.8	27.2	27.7	28.6	29.5	31.7	34.5
80°	19.0	19.5	19.5	20.0	20.0	20.4	20.9	21.3	22.2	23.1	24.5
82.5°	13.2	13.6	13.6	14.1	13.6	14.1	14.5	14.5	15.0	15.9	16.3
85°	7.7	7.7	8.2	7.7	7.7	7.7	8.2	8.2	8.6	10.0	10.0
87.5°	2.3	2.7	2.3	2.7	2.7	2.7	2.7	3.2	3.2	3.6	4.1
90°	22.2	21.9	21.6	21.4	21.1	20.4	19.7	19.0	18.3	16.1	13.9
92.5°	25.6	25.5	25.3	25.2	24.6	23.4	22.3	21.1	19.9	18.4	16.8
95°	29.0	29.0	29.0	29.0	28.4	27.2	26.1	24.9	23.7	21.8	20.0
97.5°	30.9	30.8	30.6	30.5	29.8	28.5	27.1	25.8	24.4	33.1	41.7
100°	31.7	31.6	31.4	31.3	30.6	29.3	27.9	26.6	25.2	51.7	78.1
102.5°	32.1	31.8	31.5	31.3	34.1	39.7	45.3	50.9	56.5	86.0	115.5
105°	32.9	32.6	32.3	32.1	47.1	77.1	107.2	137.2	167.2	182.5	197.7
107.5°	123.8	146.1	168.3	179.4	192.5	218.6	244.7	270.9	297.0	294.4	291.9
110°	258.5	282.7	307.0	319.1	321.9	327.5	333.1	338.7	344.3	342.4	340.6

TEST NUMBER: P1012530

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	398.5	398.8	399.1	399.3	398.5	397.0	395.5	393.9	392.4	390.5	388.7
115°	447.6	446.9	446.2	445.9	445.0	443.3	441.6	439.9	438.2	436.7	435.2
117.5°	489.8	489.7	489.5	489.4	488.7	487.4	486.0	484.7	483.3	482.5	481.6
120°	532.9	532.9	532.9	532.9	532.2	530.9	529.5	528.2	526.8	526.3	525.8
122.5°	574.6	574.4	574.3	574.2	573.8	572.9	572.0	571.2	570.3	569.6	569.0
125°	613.2	612.8	612.5	612.3	612.1	611.8	611.5	611.1	610.8	610.1	609.4
127.5°	652.7	653.1	653.4	653.6	653.3	652.8	652.3	651.8	651.3	650.4	649.6
130°	689.4	689.7	690.0	690.2	689.9	689.2	688.5	687.9	687.2	686.5	685.8
132.5°	723.3	723.8	724.3	724.6	724.3	723.6	722.9	722.2	721.5	721.0	720.5
135°	757.6	758.1	758.6	758.9	758.6	758.1	757.6	757.1	756.6	755.9	755.3
137.5°	790.2	790.5	790.8	791.0	790.6	789.7	788.9	788.0	787.2	786.8	786.5
140°	819.2	819.5	819.8	820.0	819.7	819.0	818.3	817.6	816.9	816.4	815.9
142.5°	846.2	846.7	847.2	847.5	847.2	846.7	846.2	845.7	845.2	844.7	844.2
145°	872.7	872.7	872.7	872.7	872.5	872.2	871.9	871.5	871.2	870.8	870.5
147.5°	894.2	895.1	896.0	896.4	896.2	895.9	895.5	895.2	894.8	894.5	894.1
150°	916.4	916.9	917.4	917.7	917.5	917.2	916.9	916.5	916.2	915.9	915.5
152.5°	935.5	936.3	937.2	937.6	937.3	936.6	935.9	935.2	934.5	934.3	934.2
155°	952.6	953.6	954.6	955.1	954.7	953.8	953.0	952.1	951.3	951.1	951.0
157.5°	967.8	969.2	970.5	971.2	970.7	969.7	968.6	967.6	966.6	966.8	967.0
160°	981.2	982.4	983.6	984.2	983.7	982.7	981.6	980.6	979.6	979.8	979.9
162.5°	993.8	994.9	995.9	996.4	995.8	994.6	993.4	992.2	991.0	991.2	991.4
165°	1004.1	1005.3	1006.5	1007.1	1006.4	1005.1	1003.7	1002.4	1001.0	1001.2	1001.3
167.5°	1012.1	1013.4	1014.8	1015.5	1014.8	1013.4	1012.1	1010.7	1009.3	1009.3	1009.3
170°	1018.9	1020.3	1021.6	1022.3	1021.6	1020.3	1018.9	1017.6	1016.2	1016.2	1016.2
172.5°	1023.1	1024.6	1026.1	1026.9	1026.2	1024.9	1023.5	1022.2	1020.8	1020.6	1020.4
175°	1026.6	1028.0	1029.3	1030.0	1029.4	1028.2	1027.0	1025.8	1024.6	1024.4	1024.3
177.5°	1028.0	1029.7	1031.4	1032.3	1031.6	1030.2	1028.9	1027.5	1026.1	1025.9	1025.8
180°	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7

TEST NUMBER: P1012530

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	548.3	546.0	543.8	543.8	538.8	534.2	532.0	532.9	530.2	526.5	522.9
5°	572.3	563.3	561.5	556.5	549.7	540.1	535.1	530.6	525.2	517.9	511.1
7.5°	594.6	582.8	576.4	571.4	558.3	545.1	534.2	527.0	517.5	506.6	498.4
10°	623.6	601.8	595.0	583.7	565.1	546.5	533.8	522.0	508.8	496.1	485.3
12.5°	646.7	621.8	609.1	597.7	573.7	550.1	528.8	514.3	498.4	484.4	470.3
15°	673.0	644.9	622.7	609.1	578.7	550.1	526.1	505.7	488.0	470.7	458.5
17.5°	685.7	650.3	640.4	620.9	576.9	548.3	518.8	497.1	475.7	455.8	441.3
20°	705.7	664.4	639.5	626.3	587.3	545.1	510.7	485.7	463.5	442.2	426.8
22.5°	707.0	662.1	645.8	620.9	572.8	535.6	503.4	473.0	447.2	427.2	411.3
25°	703.9	658.1	635.4	615.4	575.5	530.2	488.9	459.0	433.6	410.4	391.8
27.5°	702.5	646.3	624.9	605.0	560.1	514.3	480.3	446.3	417.2	396.8	377.8
30°	700.7	633.6	607.7	584.6	543.3	502.0	461.2	431.7	404.1	378.2	359.2
32.5°	688.9	616.3	590.0	565.5	521.1	479.8	447.6	416.3	386.4	362.4	345.1
35°	685.3	600.5	566.0	539.7	496.1	459.4	425.4	399.5	371.4	347.4	327.0
37.5°	674.8	584.1	546.9	513.4	468.0	433.1	408.2	382.3	355.1	329.3	312.9
40°	656.7	565.1	522.9	488.4	441.7	406.4	383.2	364.2	337.4	314.3	294.3
42.5°	629.9	545.6	500.2	463.9	412.2	379.1	360.1	342.0	319.3	295.2	278.9
45°	599.1	519.7	477.6	437.2	384.6	352.4	332.4	321.5	300.7	280.3	261.2
47.5°	556.9	493.0	451.2	409.5	356.0	324.7	308.8	298.0	283.4	261.2	245.8
50°	503.9	458.5	419.0	381.9	327.9	298.0	282.1	273.9	261.7	245.8	230.8
52.5°	444.9	418.6	385.9	351.5	299.3	271.2	256.7	250.3	241.3	226.3	213.6
55°	385.5	374.2	351.9	317.9	269.4	246.3	233.6	225.4	218.6	207.7	196.8
57.5°	332.4	327.0	311.6	285.3	244.4	220.4	209.5	204.1	198.6	190.5	179.6
60°	277.6	283.4	267.6	254.4	217.2	196.4	186.8	181.0	178.2	171.0	164.2
62.5°	229.9	235.4	226.3	216.3	190.0	171.4	165.5	160.1	158.3	151.9	145.1
65°	186.8	193.7	186.8	181.4	165.5	150.1	142.9	140.1	138.3	134.2	128.8
67.5°	148.8	155.6	152.4	145.6	140.6	127.9	123.8	121.1	120.2	117.0	112.5
70°	112.0	121.5	122.4	118.4	113.8	107.9	105.2	104.3	102.0	99.3	96.6
72.5°	80.7	91.6	92.1	92.1	89.3	89.3	86.6	85.3	85.3	82.5	79.4
75°	59.4	66.7	67.6	68.5	69.8	71.2	69.4	69.4	68.9	66.2	64.9
77.5°	39.5	45.8	48.1	51.2	53.1	53.1	54.0	54.9	54.0	52.6	51.7
80°	25.4	29.9	32.7	34.5	37.2	38.5	39.9	40.4	39.5	39.0	37.6
82.5°	16.8	18.1	19.5	21.8	24.9	27.2	27.2	26.8	27.7	27.2	26.8
85°	9.5	10.4	10.9	11.3	13.2	15.4	15.9	16.3	17.2	16.3	15.4
87.5°	3.6	4.1	4.1	4.1	5.0	5.4	6.8	8.6	8.2	7.3	7.3
90°	11.7	9.5	8.4	7.6	5.9	4.2	2.5	0.8	2.5	4.2	5.9
92.5°	15.3	13.8	13.0	13.5	14.5	15.6	16.6	17.6	16.6	15.6	14.5
95°	18.1	16.2	15.3	18.8	25.7	32.7	39.6	46.6	39.6	32.7	25.7
97.5°	50.4	59.1	63.4	65.8	70.5	75.2	80.0	84.7	80.0	75.2	70.5
100°	104.6	131.1	144.3	142.6	139.2	135.8	132.4	129.0	132.4	135.8	139.2
102.5°	145.0	174.5	189.3	188.2	186.0	183.8	181.6	179.4	181.6	183.8	186.0
105°	213.0	228.3	235.9	235.0	233.1	231.2	229.4	227.5	229.4	231.2	233.1
107.5°	289.3	286.8	285.5	284.7	283.2	281.7	280.2	278.7	280.2	281.7	283.2
110°	338.7	336.8	335.9	335.2	333.9	332.5	331.2	329.8	331.2	332.5	333.9

TEST NUMBER: P1012530

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	386.8	384.9	384.0	383.4	382.2	381.1	379.9	378.7	379.9	381.1	382.2
115°	433.7	432.2	431.4	430.9	429.9	428.8	427.8	426.8	427.8	428.8	429.9
117.5°	480.8	479.9	479.5	478.9	477.7	476.5	475.3	474.1	475.3	476.5	477.7
120°	525.3	524.8	524.5	523.7	522.2	520.7	519.2	517.7	519.2	520.7	522.2
122.5°	568.3	567.6	567.3	566.7	565.5	564.3	563.1	561.9	563.1	564.3	565.5
125°	608.7	608.0	607.7	607.0	605.7	604.3	603.0	601.6	603.0	604.3	605.7
127.5°	648.7	647.8	647.4	646.7	645.4	644.0	642.7	641.3	642.7	644.0	645.4
130°	685.1	684.4	684.1	683.4	682.1	680.7	679.4	678.0	679.4	680.7	682.1
132.5°	720.0	719.5	719.2	718.5	717.2	715.8	714.5	713.1	714.5	715.8	717.2
135°	754.6	753.9	753.6	753.1	752.1	751.0	750.0	749.0	750.0	751.0	752.1
137.5°	786.1	785.8	785.6	784.9	783.6	782.2	780.9	779.5	780.9	782.2	783.6
140°	815.4	814.9	814.7	814.2	813.2	812.1	811.1	810.1	811.1	812.1	813.2
142.5°	843.7	843.2	842.9	842.4	841.4	840.3	839.3	838.3	839.3	840.3	841.4
145°	870.1	869.8	869.6	869.0	867.8	866.7	865.5	864.3	865.5	866.7	867.8
147.5°	893.8	893.5	893.3	892.9	892.0	891.2	890.3	889.5	890.3	891.2	892.0
150°	915.2	914.9	914.7	914.4	913.9	913.4	912.9	912.4	912.9	913.4	913.9
152.5°	934.0	933.9	933.8	933.7	933.5	933.4	933.2	933.0	933.2	933.4	933.5
155°	950.8	950.7	950.6	950.8	951.1	951.4	951.8	952.1	951.8	951.4	951.1
157.5°	967.1	967.3	967.4	967.4	967.4	967.4	967.4	967.4	967.4	967.4	967.4
160°	980.1	980.2	980.3	980.4	980.6	980.7	980.9	981.1	980.9	980.7	980.6
162.5°	991.5	991.7	991.8	992.1	992.6	993.1	993.6	994.1	993.6	993.1	992.6
165°	1001.5	1001.6	1001.7	1002.0	1002.5	1003.0	1003.5	1004.0	1003.5	1003.0	1002.5
167.5°	1009.3	1009.3	1009.3	1009.6	1010.3	1011.0	1011.7	1012.4	1011.7	1011.0	1010.3
170°	1016.2	1016.2	1016.2	1016.5	1017.2	1017.9	1018.6	1019.3	1018.6	1017.9	1017.2
172.5°	1020.3	1020.1	1020.0	1020.4	1021.3	1022.2	1023.0	1023.9	1023.0	1022.2	1021.3
175°	1024.1	1024.0	1023.9	1024.3	1025.2	1026.0	1026.9	1027.7	1026.9	1026.0	1025.2
177.5°	1025.6	1025.5	1025.4	1025.8	1026.7	1027.5	1028.4	1029.2	1028.4	1027.5	1026.7
180°	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7

TEST NUMBER: P1012530

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	522.9	520.6	519.7	517.5	512.0	508.4	504.3	501.6	502.0	499.8	501.1
5°	506.6	506.1	502.9	498.4	490.7	486.6	479.4	475.7	473.9	474.4	471.7
7.5°	493.0	488.9	486.6	479.4	472.1	463.5	457.6	454.4	451.7	449.0	447.2
10°	477.6	473.9	470.3	462.6	452.6	444.4	436.3	433.1	429.0	427.2	425.9
12.5°	461.2	459.0	454.4	445.4	434.0	426.3	416.8	415.0	409.5	405.9	405.0
15°	446.3	444.9	436.7	426.3	415.0	407.3	399.1	393.7	384.6	386.4	383.2
17.5°	430.4	424.5	419.5	405.4	400.0	388.2	378.7	376.0	369.6	365.5	361.5
20°	412.7	409.1	402.7	393.7	380.5	366.9	359.6	355.1	351.5	345.1	343.3
22.5°	395.9	391.4	385.9	374.2	362.8	351.5	341.5	337.4	332.9	328.3	325.6
25°	382.8	376.0	370.1	355.6	344.2	334.7	328.3	321.5	315.2	312.5	311.6
27.5°	362.4	358.3	352.4	338.8	328.3	317.9	312.0	307.5	300.7	297.5	294.8
30°	349.2	341.0	334.2	323.4	312.9	301.6	296.1	290.7	286.6	282.5	279.4
32.5°	331.5	325.2	319.7	308.8	298.4	288.0	282.1	273.9	271.7	268.5	264.9
35°	314.3	310.2	304.3	292.5	281.2	273.9	267.6	259.9	257.1	254.9	251.7
37.5°	298.0	292.1	288.0	276.6	266.7	258.1	253.1	246.7	244.9	242.2	239.9
40°	283.9	278.0	273.9	262.6	252.2	243.1	239.9	233.6	230.8	227.7	226.3
42.5°	268.0	263.0	257.6	249.4	238.5	229.5	223.1	219.5	215.9	214.5	211.8
45°	251.2	246.7	242.6	233.6	222.2	215.9	210.4	205.4	202.7	200.5	198.6
47.5°	236.7	232.7	227.2	217.2	208.2	202.3	196.8	191.8	189.1	186.4	184.1
50°	220.0	217.7	211.8	202.3	193.7	186.8	181.9	177.3	175.5	172.3	168.7
52.5°	205.0	200.9	195.9	188.2	180.5	172.3	165.5	162.8	159.6	157.8	154.6
55°	187.3	184.6	179.1	172.3	164.2	157.4	152.4	148.8	144.7	142.9	138.8
57.5°	172.3	167.3	164.6	156.0	148.3	141.5	137.9	134.2	129.7	127.0	125.2
60°	156.0	151.5	147.4	140.1	134.7	127.4	122.0	118.8	115.6	112.0	110.2
62.5°	140.1	136.5	131.5	125.6	118.8	112.9	108.8	104.3	102.5	98.9	97.5
65°	122.9	120.2	116.1	109.3	103.9	98.9	94.8	91.2	89.3	88.0	87.1
67.5°	107.5	103.9	101.1	95.2	89.3	85.3	83.0	80.7	78.5	77.1	75.7
70°	91.6	88.9	86.2	80.7	76.6	73.0	71.2	69.4	68.0	66.7	65.3
72.5°	75.3	73.9	71.2	67.6	64.4	61.7	60.3	58.1	56.7	54.4	53.5
75°	62.1	59.9	58.5	55.3	52.6	50.3	48.5	45.8	44.0	43.1	42.6
77.5°	49.0	48.1	46.3	43.5	42.2	39.9	37.2	36.3	35.4	35.4	34.9
80°	36.7	35.4	34.0	31.7	30.4	28.6	28.6	28.6	28.1	28.6	28.1
82.5°	24.9	24.0	23.1	21.8	21.3	21.3	21.8	21.8	21.8	21.8	21.8
85°	14.5	14.5	14.5	15.0	14.5	14.5	15.0	15.4	15.0	15.0	14.5
87.5°	6.8	6.8	7.3	7.3	7.7	7.7	7.7	7.7	7.7	7.7	8.2
90°	7.6	8.4	9.5	11.7	13.9	16.1	18.3	19.0	19.7	20.4	21.1
92.5°	13.5	13.0	13.8	15.3	16.8	18.4	19.9	21.1	22.3	23.4	24.6
95°	18.8	15.3	16.2	18.1	20.0	21.8	23.7	24.9	26.1	27.2	28.4
97.5°	65.8	63.4	59.1	50.4	41.7	33.1	24.4	25.8	27.1	28.5	29.8
100°	142.6	144.3	131.1	104.6	78.1	51.7	25.2	26.6	27.9	29.3	30.6
102.5°	188.2	189.3	174.5	145.0	115.5	86.0	56.5	50.9	45.3	39.7	34.1
105°	235.0	235.9	228.3	213.0	197.7	182.5	167.2	137.2	107.2	77.1	47.1
107.5°	284.7	285.5	286.8	289.3	291.9	294.4	297.0	270.9	244.7	218.6	192.5
110°	335.2	335.9	336.8	338.7	340.6	342.4	344.3	338.7	333.1	327.5	321.9

TEST NUMBER: P1012530

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	383.4	384.0	384.9	386.8	388.7	390.5	392.4	393.9	395.5	397.0	398.5
115°	430.9	431.4	432.2	433.7	435.2	436.7	438.2	439.9	441.6	443.3	445.0
117.5°	478.9	479.5	479.9	480.8	481.6	482.5	483.3	484.7	486.0	487.4	488.7
120°	523.7	524.5	524.8	525.3	525.8	526.3	526.8	528.2	529.5	530.9	532.2
122.5°	566.7	567.3	567.6	568.3	569.0	569.6	570.3	571.2	572.0	572.9	573.8
125°	607.0	607.7	608.0	608.7	609.4	610.1	610.8	611.1	611.5	611.8	612.1
127.5°	646.7	647.4	647.8	648.7	649.6	650.4	651.3	651.8	652.3	652.8	653.3
130°	683.4	684.1	684.4	685.1	685.8	686.5	687.2	687.9	688.5	689.2	689.9
132.5°	718.5	719.2	719.5	720.0	720.5	721.0	721.5	722.2	722.9	723.6	724.3
135°	753.1	753.6	753.9	754.6	755.3	755.9	756.6	757.1	757.6	758.1	758.6
137.5°	784.9	785.6	785.8	786.1	786.5	786.8	787.2	788.0	788.9	789.7	790.6
140°	814.2	814.7	814.9	815.4	815.9	816.4	816.9	817.6	818.3	819.0	819.7
142.5°	842.4	842.9	843.2	843.7	844.2	844.7	845.2	845.7	846.2	846.7	847.2
145°	869.0	869.6	869.8	870.1	870.5	870.8	871.2	871.5	871.9	872.2	872.5
147.5°	892.9	893.3	893.5	893.8	894.1	894.5	894.8	895.2	895.5	895.9	896.2
150°	914.4	914.7	914.9	915.2	915.5	915.9	916.2	916.5	916.9	917.2	917.5
152.5°	933.7	933.8	933.9	934.0	934.2	934.3	934.5	935.2	935.9	936.6	937.3
155°	950.8	950.6	950.7	950.8	951.0	951.1	951.3	952.1	953.0	953.8	954.7
157.5°	967.4	967.4	967.3	967.1	967.0	966.8	966.6	967.6	968.6	969.7	970.7
160°	980.4	980.3	980.2	980.1	979.9	979.8	979.6	980.6	981.6	982.7	983.7
162.5°	992.1	991.8	991.7	991.5	991.4	991.2	991.0	992.2	993.4	994.6	995.8
165°	1002.0	1001.7	1001.6	1001.5	1001.3	1001.2	1001.0	1002.4	1003.7	1005.1	1006.4
167.5°	1009.6	1009.3	1009.3	1009.3	1009.3	1009.3	1009.3	1010.7	1012.1	1013.4	1014.8
170°	1016.5	1016.2	1016.2	1016.2	1016.2	1016.2	1016.2	1017.6	1018.9	1020.3	1021.6
172.5°	1020.4	1020.0	1020.1	1020.3	1020.4	1020.6	1020.8	1022.2	1023.5	1024.9	1026.2
175°	1024.3	1023.9	1024.0	1024.1	1024.3	1024.4	1024.6	1025.8	1027.0	1028.2	1029.4
177.5°	1025.8	1025.4	1025.5	1025.6	1025.8	1025.9	1026.1	1027.5	1028.9	1030.2	1031.6
180°	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7

TEST NUMBER: P1012530

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	500.7	501.1	499.8	497.1	496.6	497.5	500.2	499.3	497.1	501.1	497.5
5°	473.0	470.7	469.8	470.7	468.0	466.7	469.4	468.0	469.4	469.8	471.2
7.5°	446.3	446.7	444.0	444.4	440.8	441.7	441.7	441.7	443.1	444.0	445.8
10°	423.1	424.0	420.9	421.3	418.6	416.8	418.1	420.9	420.9	420.9	421.8
12.5°	404.5	400.5	398.2	397.7	394.6	393.7	396.4	397.3	399.5	399.5	400.9
15°	381.4	380.5	378.7	378.7	371.0	372.8	373.7	376.9	381.4	377.8	378.7
17.5°	360.5	358.3	356.0	355.1	354.2	351.5	355.1	354.6	357.4	357.8	359.2
20°	342.0	340.1	335.6	336.1	337.0	332.9	335.1	335.1	337.9	340.6	343.8
22.5°	323.8	322.0	319.7	320.6	317.9	317.0	317.0	319.3	322.5	324.7	324.3
25°	309.8	306.6	305.2	303.9	302.5	303.4	302.0	304.3	306.6	307.9	306.6
27.5°	293.9	292.5	289.8	288.4	286.2	287.1	288.0	289.8	291.2	291.2	292.5
30°	278.5	276.6	275.7	274.4	274.4	272.6	273.0	274.8	276.2	277.6	279.4
32.5°	263.5	262.1	260.8	260.8	259.9	259.4	259.0	261.7	261.7	264.4	264.4
35°	251.2	249.0	249.0	246.7	247.6	247.2	246.3	248.1	248.5	250.3	249.9
37.5°	237.6	237.6	236.7	234.5	232.7	233.1	235.4	235.4	236.7	236.3	237.6
40°	224.0	223.1	223.1	221.8	221.3	220.9	221.3	221.8	224.0	223.6	224.0
42.5°	210.4	210.9	208.6	208.6	208.6	207.3	207.7	208.2	209.1	210.0	211.3
45°	197.3	196.4	195.9	195.0	194.1	194.6	194.1	195.9	195.5	196.4	197.7
47.5°	183.2	181.9	181.4	179.6	179.6	180.5	180.0	181.4	181.9	183.2	182.3
50°	169.6	167.8	166.4	166.9	164.2	165.1	165.1	166.4	167.8	168.3	169.2
52.5°	153.7	153.3	152.8	150.6	150.1	149.7	150.1	150.6	152.4	153.7	154.2
55°	138.3	137.9	135.1	134.2	132.9	132.9	133.8	134.2	137.4	137.9	139.7
57.5°	124.3	122.9	119.7	119.3	119.3	119.3	117.9	119.7	120.6	122.9	122.9
60°	108.8	108.8	106.1	106.1	106.6	106.1	106.1	106.6	106.6	108.4	109.3
62.5°	96.6	96.1	96.1	95.2	94.8	95.2	94.8	94.8	95.2	96.6	98.0
65°	85.7	85.3	84.8	84.4	83.4	83.4	83.9	84.8	84.8	85.7	86.2
67.5°	75.3	75.3	74.4	74.4	73.9	73.5	73.9	73.5	75.3	75.3	75.7
70°	64.9	64.4	63.0	62.6	61.2	61.7	61.7	63.0	63.5	64.4	65.3
72.5°	52.2	52.2	51.2	50.3	50.8	49.9	49.9	50.3	50.3	51.7	52.2
75°	43.1	42.2	41.7	42.2	41.7	42.6	41.7	41.7	42.6	42.6	42.6
77.5°	35.4	35.4	34.9	34.9	35.4	34.9	35.4	35.4	35.4	34.9	35.4
80°	29.0	28.6	28.6	28.6	28.1	28.1	28.1	28.1	28.1	28.1	28.1
82.5°	21.8	21.8	21.3	21.8	21.8	21.3	21.8	21.3	21.3	21.8	21.8
85°	14.5	15.4	14.5	14.5	15.0	15.0	15.4	15.0	15.4	14.5	15.0
87.5°	7.7	8.2	8.2	7.7	7.7	8.2	8.2	8.2	8.6	7.7	8.2
90°	21.4	21.6	21.9	22.2	22.6	22.9	22.6	22.2	21.9	21.6	21.4
92.5°	25.2	25.3	25.5	25.6	25.8	26.0	25.8	25.6	25.5	25.3	25.2
95°	29.0	29.0	29.0	29.0	29.0	29.0	29.0	29.0	29.0	29.0	29.0
97.5°	30.5	30.6	30.8	30.9	31.1	31.3	31.1	30.9	30.8	30.6	30.5
100°	31.3	31.4	31.6	31.7	31.9	32.1	31.9	31.7	31.6	31.4	31.3
102.5°	31.3	31.5	31.8	32.1	32.5	32.8	32.5	32.1	31.8	31.5	31.3
105°	32.1	32.3	32.6	32.9	33.3	33.6	33.3	32.9	32.6	32.3	32.1
107.5°	179.4	168.3	146.1	123.8	101.6	79.4	101.6	123.8	146.1	168.3	179.4
110°	319.1	307.0	282.7	258.5	234.2	210.0	234.2	258.5	282.7	307.0	319.1

TEST NUMBER: P1012530

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	399.3	399.1	398.8	398.5	398.1	397.8	398.1	398.5	398.8	399.1	399.3
115°	445.9	446.2	446.9	447.6	448.2	448.9	448.2	447.6	446.9	446.2	445.9
117.5°	489.4	489.5	489.7	489.8	490.0	490.2	490.0	489.8	489.7	489.5	489.4
120°	532.9	532.9	532.9	532.9	532.9	532.9	532.9	532.9	532.9	532.9	532.9
122.5°	574.2	574.3	574.4	574.6	574.7	574.9	574.7	574.6	574.4	574.3	574.2
125°	612.3	612.5	612.8	613.2	613.5	613.9	613.5	613.2	612.8	612.5	612.3
127.5°	653.6	653.4	653.1	652.7	652.4	652.0	652.4	652.7	653.1	653.4	653.6
130°	690.2	690.0	689.7	689.4	689.0	688.7	689.0	689.4	689.7	690.0	690.2
132.5°	724.6	724.3	723.8	723.3	722.8	722.3	722.8	723.3	723.8	724.3	724.6
135°	758.9	758.6	758.1	757.6	757.1	756.6	757.1	757.6	758.1	758.6	758.9
137.5°	791.0	790.8	790.5	790.2	789.8	789.5	789.8	790.2	790.5	790.8	791.0
140°	820.0	819.8	819.5	819.2	818.8	818.5	818.8	819.2	819.5	819.8	820.0
142.5°	847.5	847.2	846.7	846.2	845.7	845.2	845.7	846.2	846.7	847.2	847.5
145°	872.7	872.7	872.7	872.7	872.7	872.7	872.7	872.7	872.7	872.7	872.7
147.5°	896.4	896.0	895.1	894.2	893.4	892.5	893.4	894.2	895.1	896.0	896.4
150°	917.7	917.4	916.9	916.4	915.9	915.4	915.9	916.4	916.9	917.4	917.7
152.5°	937.6	937.2	936.3	935.5	934.6	933.8	934.6	935.5	936.3	937.2	937.6
155°	955.1	954.6	953.6	952.6	951.6	950.6	951.6	952.6	953.6	954.6	955.1
157.5°	971.2	970.5	969.2	967.8	966.5	965.1	966.5	967.8	969.2	970.5	971.2
160°	984.2	983.6	982.4	981.2	980.0	978.8	980.0	981.2	982.4	983.6	984.2
162.5°	996.4	995.9	994.9	993.8	992.8	991.8	992.8	993.8	994.9	995.9	996.4
165°	1007.1	1006.5	1005.3	1004.1	1002.9	1001.7	1002.9	1004.1	1005.3	1006.5	1007.1
167.5°	1015.5	1014.8	1013.4	1012.1	1010.7	1009.3	1010.7	1012.1	1013.4	1014.8	1015.5
170°	1022.3	1021.6	1020.3	1018.9	1017.6	1016.2	1017.6	1018.9	1020.3	1021.6	1022.3
172.5°	1026.9	1026.1	1024.6	1023.1	1021.5	1020.0	1021.5	1023.1	1024.6	1026.1	1026.9
175°	1030.0	1029.3	1028.0	1026.6	1025.3	1023.9	1025.3	1026.6	1028.0	1029.3	1030.0
177.5°	1032.3	1031.4	1029.7	1028.0	1026.3	1024.6	1026.3	1028.0	1029.7	1031.4	1032.3
180°	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7

TEST NUMBER: P1012530

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	501.1	502.9	501.1	497.5	501.1	503.4	505.7	509.3	511.1	511.1	513.8
5°	472.6	476.2	474.8	473.9	477.6	479.8	483.4	488.0	493.0	496.1	499.8
7.5°	447.2	449.4	451.7	451.7	455.3	460.3	465.8	471.2	477.6	482.1	484.8
10°	424.9	426.8	428.1	429.9	435.4	440.8	448.1	454.9	460.3	465.3	469.8
12.5°	403.6	406.4	409.5	410.9	415.0	421.8	428.6	436.7	445.4	450.3	454.9
15°	383.2	384.6	388.2	392.3	395.9	403.2	411.8	420.4	427.7	435.4	439.5
17.5°	362.4	362.8	372.3	370.1	381.9	388.7	393.2	401.4	413.2	419.5	425.9
20°	342.0	346.5	350.6	352.8	359.2	366.9	380.0	386.4	395.9	401.8	407.3
22.5°	326.1	332.9	332.9	338.3	341.5	348.8	358.3	370.5	381.0	385.0	392.7
25°	312.0	315.2	320.6	322.5	328.3	334.7	341.0	354.2	365.5	371.0	376.4
27.5°	293.9	298.0	305.2	305.2	312.9	319.7	327.4	336.1	347.4	355.1	361.0
30°	279.8	283.9	287.1	292.1	295.2	301.6	315.2	321.5	331.5	338.3	345.6
32.5°	266.7	269.8	272.6	278.0	281.6	288.9	296.1	307.5	316.1	322.5	330.2
35°	252.2	255.3	259.0	263.0	268.5	275.3	282.1	291.6	300.2	306.1	312.5
37.5°	238.5	240.8	246.3	249.0	253.5	259.9	268.5	278.5	286.2	290.7	297.1
40°	225.4	227.2	231.3	236.3	239.5	244.4	253.5	262.1	271.7	277.1	282.1
42.5°	211.3	213.6	217.2	222.2	227.2	232.7	237.6	247.6	256.2	260.8	266.2
45°	199.1	200.5	203.2	208.2	213.2	217.2	224.9	234.0	242.2	245.8	251.7
47.5°	184.6	185.9	190.0	192.3	197.7	203.2	210.9	220.0	227.2	230.8	236.3
50°	169.6	171.0	173.7	178.7	182.3	188.2	195.0	202.7	211.8	216.8	220.0
52.5°	155.1	157.8	160.1	164.2	168.7	174.6	181.0	188.2	195.9	200.9	204.5
55°	140.6	142.9	145.6	147.8	153.3	158.7	166.0	172.8	179.6	184.1	188.2
57.5°	124.3	127.4	130.2	134.7	138.8	143.3	151.5	156.9	165.1	168.3	171.9
60°	110.2	113.4	115.6	119.3	122.9	128.8	134.2	141.0	147.8	151.9	156.5
62.5°	98.4	99.8	101.1	104.8	108.4	113.8	119.3	126.1	133.3	135.6	139.2
65°	86.6	88.0	90.2	93.4	96.1	99.3	105.2	110.7	117.5	121.1	122.4
67.5°	76.6	78.0	78.5	80.7	83.0	86.6	89.8	95.2	101.6	103.9	106.6
70°	65.3	67.6	68.0	69.8	70.7	73.0	76.6	80.7	85.7	89.8	92.1
72.5°	52.2	55.3	56.2	59.0	60.3	62.6	65.3	68.5	71.7	73.5	75.3
75°	42.6	43.5	44.0	46.3	48.5	51.7	53.1	54.9	57.6	59.9	61.7
77.5°	35.4	35.8	36.3	36.3	36.7	38.5	41.3	43.5	45.4	46.3	47.6
80°	28.6	28.1	28.1	28.6	28.6	28.6	29.5	32.7	33.6	35.8	35.4
82.5°	22.2	21.3	21.8	21.3	21.3	21.3	21.3	21.8	21.8	23.1	24.0
85°	14.5	15.0	14.5	14.5	14.1	14.5	14.1	14.1	13.6	13.6	13.2
87.5°	7.7	8.2	7.7	7.7	7.3	7.7	7.3	7.3	6.8	6.8	5.9
90°	21.1	20.4	19.7	19.0	18.3	16.1	13.9	11.7	9.5	8.4	7.6
92.5°	24.6	23.4	22.3	21.1	19.9	18.4	16.8	15.3	13.8	13.0	13.5
95°	28.4	27.2	26.1	24.9	23.7	21.8	20.0	18.1	16.2	15.3	18.8
97.5°	29.8	28.5	27.1	25.8	24.4	33.1	41.7	50.4	59.1	63.4	65.8
100°	30.6	29.3	27.9	26.6	25.2	51.7	78.1	104.6	131.1	144.3	142.6
102.5°	34.1	39.7	45.3	50.9	56.5	86.0	115.5	145.0	174.5	189.3	188.2
105°	47.1	77.1	107.2	137.2	167.2	182.5	197.7	213.0	228.3	235.9	235.0
107.5°	192.5	218.6	244.7	270.9	297.0	294.4	291.9	289.3	286.8	285.5	284.7
110°	321.9	327.5	333.1	338.7	344.3	342.4	340.6	338.7	336.8	335.9	335.2

TEST NUMBER: P1012530

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	398.5	397.0	395.5	393.9	392.4	390.5	388.7	386.8	384.9	384.0	383.4
115°	445.0	443.3	441.6	439.9	438.2	436.7	435.2	433.7	432.2	431.4	430.9
117.5°	488.7	487.4	486.0	484.7	483.3	482.5	481.6	480.8	479.9	479.5	478.9
120°	532.2	530.9	529.5	528.2	526.8	526.3	525.8	525.3	524.8	524.5	523.7
122.5°	573.8	572.9	572.0	571.2	570.3	569.6	569.0	568.3	567.6	567.3	566.7
125°	612.1	611.8	611.5	611.1	610.8	610.1	609.4	608.7	608.0	607.7	607.0
127.5°	653.3	652.8	652.3	651.8	651.3	650.4	649.6	648.7	647.8	647.4	646.7
130°	689.9	689.2	688.5	687.9	687.2	686.5	685.8	685.1	684.4	684.1	683.4
132.5°	724.3	723.6	722.9	722.2	721.5	721.0	720.5	720.0	719.5	719.2	718.5
135°	758.6	758.1	757.6	757.1	756.6	755.9	755.3	754.6	753.9	753.6	753.1
137.5°	790.6	789.7	788.9	788.0	787.2	786.8	786.5	786.1	785.8	785.6	784.9
140°	819.7	819.0	818.3	817.6	816.9	816.4	815.9	815.4	814.9	814.7	814.2
142.5°	847.2	846.7	846.2	845.7	845.2	844.7	844.2	843.7	843.2	842.9	842.4
145°	872.5	872.2	871.9	871.5	871.2	870.8	870.5	870.1	869.8	869.6	869.0
147.5°	896.2	895.9	895.5	895.2	894.8	894.5	894.1	893.8	893.5	893.3	892.9
150°	917.5	917.2	916.9	916.5	916.2	915.9	915.5	915.2	914.9	914.7	914.4
152.5°	937.3	936.6	935.9	935.2	934.5	934.3	934.2	934.0	933.9	933.8	933.7
155°	954.7	953.8	953.0	952.1	951.3	951.1	951.0	950.8	950.7	950.6	950.8
157.5°	970.7	969.7	968.6	967.6	966.6	966.8	967.0	967.1	967.3	967.4	967.4
160°	983.7	982.7	981.6	980.6	979.6	979.8	979.9	980.1	980.2	980.3	980.4
162.5°	995.8	994.6	993.4	992.2	991.0	991.2	991.4	991.5	991.7	991.8	992.1
165°	1006.4	1005.1	1003.7	1002.4	1001.0	1001.2	1001.3	1001.5	1001.6	1001.7	1002.0
167.5°	1014.8	1013.4	1012.1	1010.7	1009.3	1009.3	1009.3	1009.3	1009.3	1009.3	1009.6
170°	1021.6	1020.3	1018.9	1017.6	1016.2	1016.2	1016.2	1016.2	1016.2	1016.2	1016.5
172.5°	1026.2	1024.9	1023.5	1022.2	1020.8	1020.6	1020.4	1020.3	1020.1	1020.0	1020.4
175°	1029.4	1028.2	1027.0	1025.8	1024.6	1024.4	1024.3	1024.1	1024.0	1023.9	1024.3
177.5°	1031.6	1030.2	1028.9	1027.5	1026.1	1025.9	1025.8	1025.6	1025.5	1025.4	1025.8
180°	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7	1027.7

TEST NUMBER: P1012530

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	529.7	529.7	529.7	529.7
2.5°	516.1	519.3	525.6	531.1
5°	505.2	510.2	519.7	529.3
7.5°	492.1	499.8	512.0	525.2
10°	479.4	489.3	504.3	519.7
12.5°	466.7	477.1	493.0	512.9
15°	451.7	462.6	481.6	505.7
17.5°	438.6	453.1	470.3	494.3
20°	424.5	435.4	457.6	483.0
22.5°	406.8	424.9	445.8	472.6
25°	392.7	408.6	429.5	459.9
27.5°	375.5	394.1	419.5	446.3
30°	361.5	376.9	400.5	432.7
32.5°	345.1	363.3	387.8	419.5
35°	330.6	346.0	369.2	401.4
37.5°	313.4	330.2	356.0	384.6
40°	298.4	314.7	339.2	366.0
42.5°	280.3	297.5	322.0	344.7
45°	265.8	281.6	301.1	322.0
47.5°	248.1	264.9	283.9	298.4
50°	232.2	247.6	262.6	274.8
52.5°	215.0	229.0	242.6	251.7
55°	199.1	210.0	220.9	227.2
57.5°	180.5	190.9	200.0	203.6
60°	164.2	172.8	178.7	182.8
62.5°	146.9	153.3	157.8	160.1
65°	130.2	134.7	137.0	139.2
67.5°	112.9	117.0	118.4	121.1
70°	94.8	99.3	100.2	101.6
72.5°	81.2	81.2	83.0	84.8
75°	64.9	65.8	66.7	66.7
77.5°	50.8	50.8	51.7	52.2
80°	37.2	37.6	37.6	37.2
82.5°	25.4	26.3	25.4	24.9
85°	14.1	15.9	15.0	15.0
87.5°	5.9	5.9	6.8	5.9
90°	5.9	4.2	2.5	0.8
92.5°	14.5	15.6	16.6	17.6
95°	25.7	32.7	39.6	46.6
97.5°	70.5	75.2	80.0	84.7
100°	139.2	135.8	132.4	129.0
102.5°	186.0	183.8	181.6	179.4
105°	233.1	231.2	229.4	227.5
107.5°	283.2	281.7	280.2	278.7
110°	333.9	332.5	331.2	329.8

TEST NUMBER: P1012530

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	382.2	381.1	379.9	378.7
115°	429.9	428.8	427.8	426.8
117.5°	477.7	476.5	475.3	474.1
120°	522.2	520.7	519.2	517.7
122.5°	565.5	564.3	563.1	561.9
125°	605.7	604.3	603.0	601.6
127.5°	645.4	644.0	642.7	641.3
130°	682.1	680.7	679.4	678.0
132.5°	717.2	715.8	714.5	713.1
135°	752.1	751.0	750.0	749.0
137.5°	783.6	782.2	780.9	779.5
140°	813.2	812.1	811.1	810.1
142.5°	841.4	840.3	839.3	838.3
145°	867.8	866.7	865.5	864.3
147.5°	892.0	891.2	890.3	889.5
150°	913.9	913.4	912.9	912.4
152.5°	933.5	933.4	933.2	933.0
155°	951.1	951.4	951.8	952.1
157.5°	967.4	967.4	967.4	967.4
160°	980.6	980.7	980.9	981.1
162.5°	992.6	993.1	993.6	994.1
165°	1002.5	1003.0	1003.5	1004.0
167.5°	1010.3	1011.0	1011.7	1012.4
170°	1017.2	1017.9	1018.6	1019.3
172.5°	1021.3	1022.2	1023.0	1023.9
175°	1025.2	1026.0	1026.9	1027.7
177.5°	1026.7	1027.5	1028.4	1029.2
180°	1027.7	1027.7	1027.7	1027.7

(END OF REPORT)