

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012166

Luminaire Tested: S123RDIP-B1000D1195UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012166
REPORT IS A COMBINATION OF REPORTS P992791 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D1195UB40-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7822.0 lumens
Efficiency: N/A
Efficacy: 95.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012166

CATALOG NUMBER: S123RDIP-B1000D1195UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012166

CATALOG NUMBER: S123RDIP-B1000D1195UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54
1	98	93	90	86	90	86	83	80	73	70	68	60	58	57	48	47	46
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40
3	82	72	65	59	75	67	61	56	57	52	48	47	44	41	38	36	34
4	75	64	56	51	69	59	53	47	50	45	41	42	38	35	34	32	30
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	51	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	18
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17
10	47	35	28	24	44	33	27	22	29	24	20	24	20	18	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17853	17853	17853
5°	17882	17221	17174
10°	17741	16574	16247
15°	17511	15773	15231
20°	17209	14903	14096
25°	16897	13998	13021
30°	16498	13036	11749
35°	16086	12091	10591
40°	15699	11064	9311
45°	15203	10060	8161
50°	14655	8990	6971
55°	14088	7842	5880
60°	13544	6666	4773
65°	12843	5458	3725
70°	11962	4127	2663
75°	10693	2795	2109
80°	9126	1941	1479
85°	6849	1050	776

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15203 cd/sqm

TEST NUMBER: P1012166

CATALOG NUMBER: S123RDIP-B1000D1195UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.9	2.0
10°-20°	433.7	5.5
20°-30°	624.5	8.0
30°-40°	703.3	9.0
40°-50°	672.7	8.6
50°-60°	550.7	7.0
60°-70°	371.3	4.7
70°-80°	186.2	2.4
80°-90°	51.8	0.7
90°-100°	94.6	1.2
100°-110°	286.3	3.7
110°-120°	487.4	6.2
120°-130°	641.3	8.2
130°-140°	720.8	9.2
140°-150°	708.6	9.1
150°-160°	596.6	7.6
160°-170°	397.2	5.1
170°-180°	139.1	1.8
0°-30°	1214.2	15.5
0°-40°	1917.4	24.5
0°-60°	3140.8	40.2
0°-90°	3750.1	47.9
90°-120°	868.4	11.1
90°-150°	2939.0	37.6
90°-180°	4072.0	52.1
0°-180°	7822.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1659	1659	1659	1659	1659	
5°	1659	1652	1636	1648	1645	157
15°	1582	1567	1529	1523	1513	446
25°	1439	1406	1344	1316	1301	662
35°	1246	1197	1114	1056	1032	780
45°	1024	963	860	783	751	790
55°	778	712	597	519	492	697
65°	531	457	352	286	272	526
75°	281	217	143	129	126	300
85°	71	42	38	35	35	78
90°	1	13	28	32	35	9
95°	68	76	85	90	90	75
105°	260	262	272	272	275	278
115°	491	494	492	493	492	486
125°	718	722	719	715	710	640
135°	932	938	937	933	930	718
145°	1130	1132	1136	1135	1130	706
155°	1294	1294	1295	1300	1292	596
165°	1410	1406	1406	1413	1405	398
175°	1466	1462	1462	1468	1460	139
180°	1470	1470	1470	1470	1470	

TEST NUMBER: P1012166

CATALOG NUMBER: S123RDIP-B1000D1195UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1658.6	1658.6	1658.6	1658.6	1658.6
2.5°	1665.3	1659.9	1643.8	1658.6	1655.9
5°	1658.6	1651.8	1635.7	1647.8	1645.1
7.5°	1646.5	1639.7	1619.6	1627.6	1623.6
10°	1630.3	1620.9	1596.7	1598.0	1591.3
12.5°	1607.5	1596.7	1565.8	1564.4	1556.3
15°	1581.9	1567.1	1529.4	1522.7	1513.3
17.5°	1551.0	1534.8	1487.7	1474.3	1460.8
20°	1516.0	1494.5	1443.3	1425.9	1409.7
22.5°	1477.0	1451.4	1396.3	1373.4	1358.6
25°	1439.3	1405.7	1343.8	1315.6	1300.8
27.5°	1393.6	1357.3	1290.0	1252.3	1229.5
30°	1346.5	1306.1	1230.8	1185.1	1163.6
32.5°	1299.4	1252.3	1171.6	1120.5	1097.6
35°	1245.6	1197.2	1113.8	1055.9	1031.7
37.5°	1191.8	1139.3	1051.9	987.3	957.7
40°	1140.7	1081.5	986.0	916.0	885.1
42.5°	1082.8	1023.7	924.1	846.1	819.2
45°	1023.7	963.1	859.5	782.9	750.6
47.5°	965.8	898.6	796.3	712.9	684.7
50°	901.2	838.0	729.1	645.7	614.7
52.5°	843.4	773.5	665.8	578.4	551.5
55°	777.5	711.6	597.2	519.2	492.3
57.5°	718.3	647.0	531.3	457.4	434.5
60°	656.4	582.4	470.8	398.2	375.3
62.5°	594.6	520.6	408.9	341.7	317.5
65°	531.3	457.4	352.4	286.5	271.7
67.5°	468.1	392.8	290.6	240.8	224.6
70°	406.2	333.6	239.4	192.4	177.6
72.5°	344.4	273.1	189.7	153.3	149.3
75°	281.1	216.6	142.6	129.1	126.4
77.5°	223.3	164.1	111.6	103.6	100.9
80°	168.1	113.0	84.7	80.7	78.0
82.5°	115.7	69.9	60.5	56.5	56.5
85°	71.3	41.7	37.7	35.0	35.0
87.5°	32.3	17.5	17.5	16.1	14.8
90°	1.2	12.7	27.7	32.3	34.6
92.5°	34.6	41.6	48.5	51.9	49.6
95°	68.1	76.2	85.4	90.0	90.0
97.5°	112.0	117.7	124.7	130.4	129.3
100°	157.0	163.9	169.7	173.2	175.5
102.5°	208.9	212.4	220.5	224.0	222.8
105°	259.7	262.1	272.4	272.4	274.7
107.5°	319.8	320.9	325.5	329.0	327.9
110°	375.2	377.5	379.8	384.4	382.1

TEST NUMBER: P1012166

CATALOG NUMBER: S123RDIP-B1000D1195UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	432.9	434.1	434.1	439.8	439.8
115°	490.6	494.1	491.8	492.9	491.8
117.5°	549.5	550.7	548.3	548.3	544.9
120°	603.8	610.7	604.9	603.8	601.4
122.5°	660.3	664.9	662.6	659.2	655.7
125°	718.0	721.5	719.2	714.6	710.0
127.5°	771.1	778.1	775.8	768.8	764.2
130°	824.2	833.5	830.0	825.4	817.3
132.5°	877.4	886.6	884.3	878.5	872.7
135°	931.6	938.5	937.4	932.8	930.5
137.5°	981.2	987.0	990.5	984.7	981.2
140°	1033.2	1039.0	1040.1	1039.0	1030.9
142.5°	1080.5	1086.3	1088.6	1087.5	1081.7
145°	1130.2	1132.5	1135.9	1134.8	1130.2
147.5°	1172.9	1177.5	1181.0	1181.0	1174.0
150°	1217.9	1220.2	1222.5	1222.5	1215.6
152.5°	1254.8	1258.3	1259.5	1261.8	1256.0
155°	1294.1	1294.1	1295.2	1299.9	1291.8
157.5°	1327.6	1326.4	1327.6	1332.2	1325.3
160°	1358.7	1356.4	1356.4	1362.2	1357.6
162.5°	1386.4	1383.0	1384.1	1389.9	1381.8
165°	1409.5	1406.1	1406.1	1413.0	1404.9
167.5°	1429.2	1424.5	1425.7	1432.6	1425.7
170°	1445.3	1440.7	1440.7	1448.8	1440.7
172.5°	1458.0	1453.4	1453.4	1460.3	1452.2
175°	1466.1	1461.5	1461.5	1468.4	1460.3
177.5°	1470.7	1466.1	1466.1	1473.0	1464.9
180°	1469.6	1469.6	1469.6	1469.6	1469.6

(END OF REPORT)