

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012534

Luminaire Tested: S123RDIP-B340D805UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012534
REPORT IS A COMBINATION OF REPORTS P993299 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D805UB30-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3958.0 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012534

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012534

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	40	40	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	34	34	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	29	29	23
3	78	69	62	57	70	63	57	52	50	46	42	39	36	33	28	26	25	25	25	20
4	72	61	54	48	64	56	49	44	45	40	36	34	31	29	25	23	21	21	21	17
5	66	55	47	41	59	49	43	38	40	35	31	31	28	25	23	20	19	19	19	15
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	21	18	17	17	17	13
7	56	44	36	31	50	40	33	29	33	28	24	25	22	19	19	16	15	15	15	12
8	52	40	33	27	47	36	30	25	30	25	21	23	20	17	17	15	13	13	13	11
9	48	36	29	24	43	33	27	23	27	22	19	21	18	15	16	14	12	12	12	10
10	45	33	26	22	40	30	24	20	25	20	17	20	16	14	15	13	11	11	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6018	6018	6018
5°	6028	5804	5789
10°	5980	5586	5477
15°	5902	5316	5134
20°	5801	5023	4752
25°	5695	4719	4388
30°	5561	4394	3960
35°	5423	4075	3570
40°	5292	3729	3138
45°	5124	3391	2751
50°	4940	3029	2350
55°	4749	2643	1981
60°	4566	2247	1609
65°	4329	1840	1256
70°	4032	1391	897
75°	3606	943	711
80°	3078	656	499
85°	2305	354	262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5124 cd/sqm

TEST NUMBER: P1012534

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.6	1.3
10°-20°	146.2	3.7
20°-30°	210.5	5.3
30°-40°	237.1	6.0
40°-50°	226.7	5.7
50°-60°	185.6	4.7
60°-70°	125.1	3.2
70°-80°	62.8	1.6
80°-90°	18.5	0.5
90°-100°	62.6	1.6
100°-110°	189.4	4.8
110°-120°	322.4	8.1
120°-130°	424.1	10.7
130°-140°	476.7	12.0
140°-150°	468.7	11.8
150°-160°	394.6	10.0
160°-170°	262.7	6.6
170°-180°	92.0	2.3
0°-30°	409.2	10.3
0°-40°	646.3	16.3
0°-60°	1058.7	26.7
0°-90°	1265.0	32.0
90°-120°	574.3	14.5
90°-150°	1943.8	49.1
90°-180°	2693.0	68.0
0°-180°	3958.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	559	559	559	559	559	
5°	559	557	551	555	554	53
15°	533	528	516	513	510	150
25°	485	474	453	443	438	223
35°	420	404	375	356	348	263
45°	345	325	290	264	253	266
55°	262	240	201	175	166	235
65°	179	154	119	97	92	177
75°	95	73	48	44	43	101
85°	24	14	13	12	12	26
90°	1	8	18	21	23	5
95°	45	50	56	60	60	50
105°	172	173	180	180	182	184
115°	324	327	325	326	325	321
125°	475	477	476	473	470	424
135°	616	621	620	617	615	475
145°	747	749	751	750	747	467
155°	856	856	857	860	854	394
165°	932	930	930	934	929	263
175°	970	967	967	971	966	92
180°	972	972	972	972	972	

TEST NUMBER: P1012534

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	559.1	559.1	559.1	559.1	559.1
2.5°	561.3	559.5	554.1	559.1	558.1
5°	559.1	556.8	551.3	555.4	554.5
7.5°	555.0	552.7	545.9	548.6	547.3
10°	549.5	546.4	538.2	538.6	536.4
12.5°	541.8	538.2	527.8	527.3	524.6
15°	533.2	528.2	515.5	513.3	510.1
17.5°	522.8	517.3	501.5	496.9	492.4
20°	511.0	503.7	486.5	480.6	475.2
22.5°	497.8	489.2	470.6	462.9	457.9
25°	485.1	473.8	453.0	443.4	438.4
27.5°	469.7	457.5	434.8	422.1	414.4
30°	453.9	440.3	414.9	399.5	392.2
32.5°	438.0	422.1	394.9	377.7	370.0
35°	419.9	403.5	375.4	355.9	347.8
37.5°	401.7	384.0	354.6	332.8	322.8
40°	384.5	364.5	332.3	308.8	298.3
42.5°	365.0	345.0	311.5	285.2	276.1
45°	345.0	324.6	289.7	263.9	253.0
47.5°	325.5	302.9	268.4	240.3	230.8
50°	303.8	282.5	245.7	217.6	207.2
52.5°	284.3	260.7	224.4	195.0	185.9
55°	262.1	239.9	201.3	175.0	165.9
57.5°	242.1	218.1	179.1	154.2	146.5
60°	221.3	196.3	158.7	134.2	126.5
62.5°	200.4	175.5	137.8	115.2	107.0
65°	179.1	154.2	118.8	96.6	91.6
67.5°	157.8	132.4	97.9	81.2	75.7
70°	136.9	112.4	80.7	64.8	59.8
72.5°	116.1	92.0	63.9	51.7	50.3
75°	94.8	73.0	48.1	43.5	42.6
77.5°	75.3	55.3	37.6	34.9	34.0
80°	56.7	38.1	28.6	27.2	26.3
82.5°	39.0	23.6	20.4	19.0	19.0
85°	24.0	14.1	12.7	11.8	11.8
87.5°	10.9	5.9	5.9	5.4	5.0
90°	0.8	8.4	18.3	21.4	22.9
92.5°	22.9	27.5	32.1	34.4	32.8
95°	45.0	50.4	56.5	59.6	59.6
97.5°	74.1	77.9	82.5	86.3	85.5
100°	103.8	108.4	112.2	114.5	116.0
102.5°	138.2	140.5	145.8	148.1	147.3
105°	171.8	173.3	180.2	180.2	181.7
107.5°	211.5	212.2	215.3	217.6	216.8
110°	248.1	249.7	251.2	254.2	252.7

TEST NUMBER: P1012534

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	286.3	287.1	287.1	290.9	290.9
115°	324.5	326.8	325.2	326.0	325.2
117.5°	363.4	364.2	362.6	362.6	360.4
120°	399.3	403.9	400.1	399.3	397.8
122.5°	436.7	439.8	438.2	435.9	433.7
125°	474.9	477.2	475.6	472.6	469.5
127.5°	510.0	514.6	513.1	508.5	505.4
130°	545.1	551.2	548.9	545.9	540.5
132.5°	580.2	586.3	584.8	581.0	577.2
135°	616.1	620.7	619.9	616.9	615.4
137.5°	648.9	652.8	655.1	651.2	648.9
140°	683.3	687.1	687.9	687.1	681.8
142.5°	714.6	718.4	720.0	719.2	715.4
145°	747.4	749.0	751.3	750.5	747.4
147.5°	775.7	778.7	781.0	781.0	776.4
150°	805.5	807.0	808.5	808.5	803.9
152.5°	829.9	832.2	832.9	834.5	830.7
155°	855.8	855.8	856.6	859.7	854.3
157.5°	878.0	877.2	878.0	881.0	876.5
160°	898.6	897.1	897.1	900.9	897.8
162.5°	916.9	914.6	915.4	919.2	913.9
165°	932.2	929.9	929.9	934.5	929.1
167.5°	945.2	942.1	942.9	947.5	942.9
170°	955.9	952.8	952.8	958.2	952.8
172.5°	964.3	961.2	961.2	965.8	960.4
175°	969.6	966.6	966.6	971.1	965.8
177.5°	972.7	969.6	969.6	974.2	968.8
180°	971.9	971.9	971.9	971.9	971.9

(END OF REPORT)