

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012167

Luminaire Tested: S123RDIP-B1000D1195UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012167
REPORT IS A COMBINATION OF REPORTS P992792 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D1195UB40-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8050.0 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012167

CATALOG NUMBER: S123RDIP-B1000D1195UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012167

CATALOG NUMBER: S123RDIP-B1000D1195UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53
1	97	93	89	86	89	86	83	80	72	70	67	59	58	56	47	46	45
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	35	33
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29
5	68	57	49	43	63	53	46	41	45	39	35	37	33	30	30	28	25
6	63	51	43	38	58	48	40	35	40	35	31	34	30	27	28	25	22
7	58	46	39	33	54	43	36	31	37	31	27	31	27	24	25	22	20
8	54	42	34	29	50	39	32	28	34	28	24	28	24	21	23	20	18
9	50	38	31	26	46	36	29	25	31	26	22	26	22	19	22	19	16
10	47	35	28	23	43	33	27	22	28	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17853	17853	17853
5°	17882	17221	17174
10°	17741	16574	16247
15°	17511	15773	15231
20°	17209	14903	14096
25°	16897	13998	13021
30°	16498	13036	11749
35°	16086	12091	10591
40°	15699	11064	9311
45°	15203	10060	8161
50°	14655	8990	6971
55°	14088	7842	5880
60°	13544	6666	4773
65°	12843	5458	3725
70°	11962	4127	2663
75°	10693	2795	2109
80°	9126	1941	1479
85°	6849	1050	776

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15203 cd/sqm

TEST NUMBER: P1012167

CATALOG NUMBER: S123RDIP-B1000D1195UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.9	1.9
10°-20°	433.7	5.4
20°-30°	624.5	7.8
30°-40°	703.3	8.7
40°-50°	672.7	8.4
50°-60°	550.7	6.8
60°-70°	371.3	4.6
70°-80°	186.2	2.3
80°-90°	51.9	0.6
90°-100°	324.1	4.0
100°-110°	905.8	11.3
110°-120°	883.3	11.0
120°-130°	703.3	8.7
130°-140°	555.2	6.9
140°-150°	414.2	5.1
150°-160°	289.0	3.6
160°-170°	169.8	2.1
170°-180°	55.2	0.7
0°-30°	1214.2	15.1
0°-40°	1917.4	23.8
0°-60°	3140.8	39.0
0°-90°	3750.2	46.6
90°-120°	2113.2	26.3
90°-150°	3785.9	47.0
90°-180°	4300.0	53.4
0°-180°	8050.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1659	1659	1659	1659	1659	
5°	1659	1652	1636	1648	1645	157
15°	1582	1567	1529	1523	1513	446
25°	1439	1406	1344	1316	1301	662
35°	1246	1197	1114	1056	1032	780
45°	1024	963	860	783	751	790
55°	778	712	597	519	492	697
65°	531	457	352	286	272	526
75°	281	217	143	129	126	300
85°	71	42	38	35	35	78
90°	2	14	29	32	34	7
95°	39	128	685	200	134	42
105°	134	198	928	1623	1468	142
115°	237	295	710	1557	1786	234
125°	329	388	663	1201	1408	292
135°	386	460	653	989	1142	298
145°	440	504	645	811	892	276
155°	500	539	625	710	740	230
165°	546	562	598	634	645	154
175°	569	570	574	582	581	54
180°	570	570	570	570	570	

TEST NUMBER: P1012167

CATALOG NUMBER: S123RDIP-B1000D1195UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1658.6	1658.6	1658.6	1658.6	1658.6
2.5°	1665.3	1659.9	1643.8	1658.6	1655.9
5°	1658.6	1651.8	1635.7	1647.8	1645.1
7.5°	1646.5	1639.7	1619.6	1627.6	1623.6
10°	1630.3	1620.9	1596.7	1598.0	1591.3
12.5°	1607.5	1596.7	1565.8	1564.4	1556.3
15°	1581.9	1567.1	1529.4	1522.7	1513.3
17.5°	1551.0	1534.8	1487.7	1474.3	1460.8
20°	1516.0	1494.5	1443.3	1425.9	1409.7
22.5°	1477.0	1451.4	1396.3	1373.4	1358.6
25°	1439.3	1405.7	1343.8	1315.6	1300.8
27.5°	1393.6	1357.3	1290.0	1252.3	1229.5
30°	1346.5	1306.1	1230.8	1185.1	1163.6
32.5°	1299.4	1252.3	1171.6	1120.5	1097.6
35°	1245.6	1197.2	1113.8	1055.9	1031.7
37.5°	1191.8	1139.3	1051.9	987.3	957.7
40°	1140.7	1081.5	986.0	916.0	885.1
42.5°	1082.8	1023.7	924.1	846.1	819.2
45°	1023.7	963.1	859.5	782.9	750.6
47.5°	965.8	898.6	796.3	712.9	684.7
50°	901.2	838.0	729.1	645.7	614.7
52.5°	843.4	773.5	665.8	578.4	551.5
55°	777.5	711.6	597.2	519.2	492.3
57.5°	718.3	647.0	531.3	457.4	434.5
60°	656.4	582.4	470.8	398.2	375.3
62.5°	594.6	520.6	408.9	341.7	317.5
65°	531.3	457.4	352.4	286.5	271.7
67.5°	468.1	392.8	290.6	240.8	224.6
70°	406.2	333.6	239.4	192.4	177.6
72.5°	344.4	273.1	189.7	153.3	149.3
75°	281.1	216.6	142.6	129.1	126.4
77.5°	223.3	164.1	111.6	103.6	100.9
80°	168.1	113.0	84.7	80.7	78.0
82.5°	115.7	69.9	60.5	56.5	56.5
85°	71.3	41.7	37.7	35.0	35.0
87.5°	32.3	17.5	17.5	16.1	14.8
90°	2.3	13.8	28.9	32.4	33.5
92.5°	17.3	69.3	214.7	73.3	61.2
95°	39.3	127.6	684.6	199.7	133.9
97.5°	62.3	146.0	1052.9	502.2	274.8
100°	85.4	161.0	1093.3	1050.6	723.8
102.5°	109.7	178.4	1018.2	1406.7	1146.4
105°	133.9	198.0	928.2	1623.2	1468.5
107.5°	159.3	221.0	848.5	1718.4	1678.6
110°	187.0	244.8	782.7	1721.3	1798.6

TEST NUMBER: P1012167

CATALOG NUMBER: S123RDIP-B1000D1195UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	212.4	269.6	738.8	1656.0	1822.9
115°	236.7	295.0	710.0	1556.8	1785.9
117.5°	260.9	319.2	690.4	1450.6	1705.1
120°	286.3	343.4	677.7	1350.1	1598.9
122.5°	308.2	366.6	669.6	1271.1	1499.6
125°	329.0	388.5	662.7	1200.6	1408.4
127.5°	345.2	409.2	659.2	1142.9	1329.9
130°	360.2	427.7	655.7	1089.8	1265.3
132.5°	371.7	444.5	654.6	1040.2	1201.8
135°	385.6	460.0	653.4	988.8	1141.8
137.5°	398.3	472.8	651.1	940.3	1078.3
140°	411.0	484.3	650.0	893.0	1011.3
142.5°	424.8	494.7	647.6	849.7	949.0
145°	439.8	503.9	645.3	811.0	892.4
147.5°	454.9	513.8	641.9	781.0	843.9
150°	469.9	521.8	637.3	754.4	802.3
152.5°	484.9	530.5	631.5	731.4	767.7
155°	499.9	539.1	624.6	710.0	740.0
157.5°	511.4	546.6	618.8	689.2	713.5
160°	525.3	553.0	611.9	670.2	688.1
162.5°	535.7	557.6	604.9	652.2	665.0
165°	546.1	561.7	598.0	634.4	645.3
167.5°	554.1	565.1	591.1	618.8	625.7
170°	561.1	566.8	584.2	605.0	608.4
172.5°	565.7	568.6	578.4	592.8	592.2
175°	569.1	569.7	573.8	581.8	580.7
177.5°	571.5	570.3	570.3	574.9	572.6
180°	570.3	570.3	570.3	570.3	570.3

(END OF REPORT)