

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012536

Luminaire Tested: S123RDIP-B340D805UB35-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012536
REPORT IS A COMBINATION OF REPORTS P993301 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D805UB35-4F0-XX-W2A-A
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4474.0 lumens
Efficiency: N/A
Efficacy: 131.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012536

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1012536

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	94	90	86	83	84	80	77	75	64	61	60	48	47	46	34	33	32
2	85	79	73	68	76	71	66	62	56	53	50	42	40	39	30	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24
4	72	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21
5	66	55	47	41	59	50	43	38	40	35	31	30	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15
8	52	40	33	28	46	36	30	26	30	25	21	23	20	17	17	15	13
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12
10	45	33	27	22	40	30	24	20	25	20	17	19	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5727	5727	5727	5727
5°	5732	6597	5747	4894
10°	5681	7964	5707	4275
15°	5623	9037	5623	3769
20°	5508	9748	5538	3344
25°	5424	9262	5412	3051
30°	5325	6417	5314	2765
35°	5207	4120	5184	2549
40°	5061	2909	5034	2334
45°	4804	2328	4797	2125
50°	4490	1948	4475	1880
55°	4135	1605	4102	1594
60°	3788	1326	3751	1356
65°	3382	1061	3404	1149
70°	3004	738	3086	930
75°	2549	547	2651	714
80°	2030	362	2199	535
85°	1441	171	1575	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7647 cd/sqm

TEST NUMBER: P1012536

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.3	1.2
10°-20°	163.6	3.7
20°-30°	257.6	5.8
30°-40°	267.9	6.0
40°-50°	229.2	5.1
50°-60°	174.7	3.9
60°-70°	111.9	2.5
70°-80°	53.6	1.2
80°-90°	16.2	0.4
90°-100°	36.4	0.8
100°-110°	176.0	3.9
110°-120°	431.3	9.6
120°-130°	547.5	12.2
130°-140°	584.9	13.1
140°-150°	546.9	12.2
150°-160°	441.1	9.9
160°-170°	284.7	6.4
170°-180°	98.1	2.2
0°-30°	473.5	10.6
0°-40°	741.4	16.6
0°-60°	1145.3	25.6
0°-90°	1327.1	29.7
90°-120°	643.7	14.4
90°-150°	2323.0	51.9
90°-180°	3147.0	70.3
0°-180°	4474.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	532	532	532	532	532	
5°	532	632	533	469	532	50
15°	508	898	508	374	508	143
25°	462	925	461	305	462	213
35°	403	401	401	248	403	252
45°	324	214	323	195	324	249
55°	228	134	226	134	228	205
65°	140	77	141	84	140	140
75°	67	33	70	43	67	72
85°	15	8	16	15	15	17
90°	1	23	1	23	1	3
95°	47	29	47	29	47	56
105°	228	34	228	34	228	242
115°	429	451	429	451	429	423
125°	604	617	604	617	604	540
135°	752	760	752	760	752	579
145°	868	877	868	877	868	544
155°	956	955	956	955	956	441
165°	1008	1006	1008	1006	1008	285
175°	1032	1028	1032	1028	1032	98
180°	1032	1032	1032	1032	1032	

TEST NUMBER: P1012536

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1
2.5°	533.5	537.1	539.9	541.7	546.2	549.0	551.3	555.4	555.4	556.3	558.1
5°	531.7	539.4	544.9	552.2	561.7	566.3	572.7	578.1	585.9	590.0	594.1
7.5°	527.6	538.5	549.9	560.8	574.9	584.1	590.4	604.6	614.6	626.9	636.4
10°	522.1	537.1	551.7	568.6	587.7	601.4	610.9	629.6	648.7	666.1	680.6
12.5°	515.3	533.5	554.4	574.9	601.8	615.5	631.0	654.2	681.5	703.4	723.0
15°	508.0	528.9	552.6	577.7	611.4	630.5	652.8	681.1	711.6	743.0	769.9
17.5°	496.6	523.0	549.4	585.9	625.5	636.9	656.0	694.8	732.6	760.8	793.6
20°	485.2	514.8	548.1	580.9	623.7	650.1	667.9	708.9	749.4	783.6	815.0
22.5°	474.7	505.7	540.3	581.8	621.9	648.3	670.6	713.4	760.4	798.6	837.4
25°	462.0	495.7	533.9	573.1	621.9	641.9	666.5	716.2	765.8	810.0	857.9
27.5°	448.3	482.5	520.3	560.4	605.0	634.6	658.8	712.1	772.7	820.0	869.2
30°	434.6	469.7	506.1	542.1	592.3	620.5	648.3	707.1	776.3	830.5	868.3
32.5°	421.4	451.0	487.0	522.1	571.8	602.7	634.2	702.0	777.7	823.2	841.5
35°	403.2	434.2	463.3	500.7	550.8	581.3	618.2	701.6	771.8	800.0	790.9
37.5°	386.3	412.3	440.1	473.3	524.8	564.5	602.7	689.7	752.2	754.0	702.5
40°	367.7	389.1	412.3	447.4	503.0	542.1	583.6	671.5	716.6	689.7	599.1
42.5°	346.2	365.4	383.6	417.8	478.4	522.1	566.7	648.7	665.1	603.2	508.9
45°	323.5	339.0	355.8	391.8	452.4	495.7	540.3	613.7	596.8	509.3	419.6
47.5°	299.8	313.0	329.4	362.2	424.6	468.8	511.2	563.6	520.7	426.9	351.7
50°	276.1	286.6	302.5	336.2	396.4	436.4	475.6	509.8	449.7	366.3	290.7
52.5°	252.8	261.0	277.4	306.1	364.5	402.7	431.0	444.2	383.1	302.5	252.4
55°	228.2	237.4	248.3	277.4	335.3	363.6	382.2	381.8	318.9	256.5	208.7
57.5°	204.6	212.8	222.3	251.5	298.4	317.5	333.5	325.7	266.1	210.0	179.0
60°	183.6	188.2	198.6	223.2	258.8	275.2	284.3	271.1	217.3	177.2	148.1
62.5°	160.8	165.4	174.0	197.3	219.1	227.8	235.5	218.7	179.5	144.4	126.7
65°	139.9	145.8	151.3	169.9	181.8	192.3	191.3	177.2	140.3	117.5	103.0
67.5°	121.6	123.9	128.5	139.9	145.3	153.1	153.5	137.6	113.0	95.7	87.0
70°	102.0	104.3	107.5	113.0	116.6	118.5	117.5	103.4	85.2	74.7	67.0
72.5°	85.2	84.7	87.0	87.0	90.7	90.2	87.5	76.5	64.7	56.0	51.5
75°	67.0	67.4	67.9	67.0	65.6	63.8	61.5	53.3	45.6	41.5	37.4
77.5°	52.4	51.5	51.9	48.7	46.9	45.1	41.9	37.8	31.4	30.5	28.7
80°	37.4	36.9	36.4	35.1	31.0	29.2	26.9	24.6	23.2	22.3	21.9
82.5°	25.1	25.1	24.1	21.4	19.1	17.8	17.3	16.4	15.0	15.0	14.6
85°	15.0	14.6	13.7	10.9	9.6	9.6	9.6	9.6	8.7	8.7	8.2
87.5°	5.9	5.5	4.1	4.1	3.6	3.6	3.6	3.2	3.2	2.7	2.7
90°	0.8	2.5	4.2	5.9	7.6	8.4	9.5	11.7	14.0	16.2	18.4
92.5°	17.6	16.6	15.6	14.5	13.5	13.0	13.8	15.3	16.8	18.4	19.9
95°	46.8	39.8	32.8	25.8	18.8	15.3	16.2	18.1	20.0	21.9	23.8
97.5°	85.1	80.3	75.6	70.8	66.1	63.7	59.3	50.6	41.9	33.2	24.5
100°	129.6	133.0	136.4	139.8	143.2	144.9	131.6	105.0	78.5	51.9	25.3
102.5°	180.2	182.4	184.6	186.9	189.1	190.2	175.4	145.7	116.1	86.4	56.8
105°	228.5	230.4	232.3	234.2	236.1	237.0	229.3	214.0	198.7	183.3	168.0
107.5°	279.9	281.4	283.0	284.5	286.0	286.8	288.1	290.6	293.2	295.7	298.3
110°	331.3	332.7	334.0	335.4	336.7	337.4	338.3	340.2	342.1	344.0	345.9

TEST NUMBER: P1012536

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	380.4	381.6	382.8	384.0	385.2	385.8	386.7	388.6	390.5	392.3	394.2
115°	428.7	429.7	430.7	431.8	432.8	433.3	434.1	435.6	437.1	438.7	440.2
117.5°	476.3	477.5	478.7	479.8	481.0	481.6	482.0	482.9	483.8	484.6	485.5
120°	520.0	521.5	523.1	524.6	526.1	526.9	527.2	527.7	528.2	528.7	529.2
122.5°	564.4	565.6	566.8	568.0	569.2	569.8	570.1	570.8	571.5	572.2	572.9
125°	604.3	605.7	607.1	608.4	609.8	610.5	610.8	611.5	612.2	612.8	613.5
127.5°	644.2	645.6	646.9	648.3	649.6	650.3	650.7	651.6	652.5	653.3	654.2
130°	681.0	682.4	683.8	685.1	686.5	687.2	687.5	688.2	688.9	689.5	690.2
132.5°	716.3	717.7	719.0	720.4	721.7	722.4	722.7	723.2	723.7	724.2	724.7
135°	752.3	753.3	754.3	755.4	756.4	756.9	757.2	757.9	758.6	759.3	760.0
137.5°	783.0	784.4	785.8	787.1	788.5	789.2	789.4	789.7	790.0	790.4	790.7
140°	813.7	814.7	815.7	816.8	817.8	818.3	818.6	819.1	819.6	820.1	820.6
142.5°	842.1	843.1	844.1	845.2	846.2	846.7	847.0	847.5	848.0	848.5	849.0
145°	868.1	869.3	870.5	871.7	872.9	873.5	873.7	874.0	874.3	874.7	875.0
147.5°	893.5	894.3	895.2	896.0	896.9	897.3	897.5	897.8	898.1	898.5	898.8
150°	916.5	917.0	917.5	918.0	918.5	918.8	919.0	919.3	919.6	920.0	920.3
152.5°	937.2	937.4	937.5	937.7	937.8	937.9	938.0	938.2	938.3	938.5	938.7
155°	956.3	956.0	955.6	955.3	955.0	954.8	954.9	955.1	955.2	955.4	955.6
157.5°	971.7	971.7	971.7	971.7	971.7	971.7	971.6	971.4	971.3	971.1	970.9
160°	985.5	985.3	985.1	985.0	984.8	984.7	984.6	984.4	984.3	984.1	983.9
162.5°	998.5	998.0	997.5	997.0	996.5	996.2	996.1	996.0	995.8	995.7	995.5
165°	1008.5	1008.0	1007.5	1007.0	1006.5	1006.2	1006.1	1005.9	1005.8	1005.6	1005.4
167.5°	1016.9	1016.2	1015.6	1014.9	1014.2	1013.9	1013.9	1013.9	1013.9	1013.9	1013.9
170°	1023.8	1023.1	1022.5	1021.8	1021.1	1020.8	1020.8	1020.8	1020.8	1020.8	1020.8
172.5°	1028.4	1027.6	1026.7	1025.9	1025.0	1024.6	1024.7	1024.9	1025.0	1025.2	1025.4
175°	1032.3	1031.4	1030.6	1029.7	1028.8	1028.4	1028.5	1028.7	1028.8	1029.0	1029.2
177.5°	1033.8	1033.0	1032.1	1031.3	1030.4	1030.0	1030.1	1030.2	1030.4	1030.5	1030.7
180°	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3

TEST NUMBER: P1012536

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1
2.5°	561.7	561.7	565.8	569.9	567.7	569.0	574.0	572.2	575.9	575.4	576.8
5°	604.1	609.1	613.2	621.9	623.2	621.9	630.5	632.8	636.9	631.9	634.2
7.5°	651.9	662.4	672.4	685.2	689.3	690.2	694.8	701.1	706.6	696.6	701.6
10°	698.4	714.3	734.8	746.2	756.3	759.9	763.6	767.7	774.0	780.0	775.4
12.5°	748.5	771.8	791.3	811.8	824.1	822.8	833.3	836.0	841.0	842.4	844.2
15°	789.5	822.3	834.6	865.1	867.9	877.0	888.8	899.3	900.7	897.9	897.9
17.5°	828.7	856.9	878.8	903.4	908.4	916.2	931.2	936.2	938.0	937.6	937.6
20°	860.6	879.3	916.2	936.7	944.9	954.9	965.4	971.8	973.1	974.9	972.2
22.5°	881.5	909.8	939.9	956.7	963.6	967.2	974.0	975.9	973.6	974.0	974.5
25°	897.9	925.7	944.0	948.5	948.1	943.5	938.5	929.8	928.9	925.3	918.0
27.5°	902.5	913.0	910.7	892.0	873.3	871.5	841.5	825.1	806.4	809.1	798.6
30°	877.9	864.2	831.9	784.5	764.9	733.0	699.3	664.2	650.6	635.5	663.3
32.5°	817.8	769.0	711.6	650.1	617.3	589.1	553.1	527.6	513.0	500.7	524.4
35°	727.1	651.0	574.9	516.6	489.7	464.2	430.5	417.8	399.5	401.4	403.6
37.5°	610.5	526.6	469.2	411.8	394.1	383.6	359.0	339.4	333.0	331.2	331.2
40°	501.1	432.3	381.3	336.2	322.6	313.9	294.3	285.2	278.4	276.5	278.8
42.5°	414.6	355.8	316.2	286.1	276.5	265.6	257.4	246.0	244.6	241.5	245.6
45°	348.1	297.0	267.4	245.6	237.4	233.3	224.1	217.3	214.6	214.1	217.3
47.5°	295.2	255.6	229.6	215.9	209.6	205.5	197.7	195.0	192.3	193.2	191.8
50°	247.8	218.2	201.4	189.1	185.0	180.9	175.9	173.1	171.8	171.8	171.3
52.5°	212.8	188.2	177.2	165.8	164.0	161.7	156.3	154.4	152.2	151.7	153.5
55°	182.2	165.4	154.4	147.6	145.8	141.2	139.0	136.7	135.3	134.4	134.9
57.5°	155.8	143.1	135.8	129.8	126.7	124.8	120.7	120.3	119.4	119.4	118.9
60°	133.9	124.8	116.2	112.5	110.3	108.0	107.5	104.8	103.4	104.3	103.9
62.5°	113.4	106.1	101.1	97.0	95.7	93.8	92.5	91.6	90.2	90.7	90.7
65°	94.8	88.8	85.2	81.5	81.1	79.3	78.8	77.9	77.9	77.4	78.4
67.5°	77.9	73.8	70.6	68.3	67.0	67.4	65.6	64.2	64.2	63.8	65.1
70°	62.0	59.7	56.5	53.8	51.9	51.9	49.7	49.2	49.2	49.2	48.7
72.5°	47.8	43.7	42.4	41.5	41.5	41.5	40.5	40.5	40.1	40.5	40.1
75°	35.5	35.1	34.2	33.7	33.7	33.3	32.8	32.8	32.8	32.8	32.8
77.5°	27.8	27.8	26.9	26.4	26.4	26.4	26.0	26.0	25.5	25.5	25.5
80°	20.5	20.5	19.6	19.6	19.6	19.1	19.1	19.1	19.6	19.1	19.1
82.5°	14.1	14.1	13.7	14.1	13.7	13.2	13.2	13.2	12.8	13.2	13.2
85°	8.2	8.2	7.7	7.3	7.7	7.7	7.3	7.7	7.3	7.7	7.3
87.5°	3.2	2.7	2.7	2.7	2.3	2.7	2.3	2.3	2.7	2.3	2.7
90°	19.1	19.8	20.5	21.2	21.5	21.7	22.0	22.3	22.7	23.0	22.7
92.5°	21.1	22.3	23.5	24.7	25.3	25.4	25.6	25.7	25.9	26.1	25.9
95°	25.0	26.2	27.3	28.5	29.1	29.1	29.1	29.1	29.1	29.1	29.1
97.5°	25.9	27.3	28.6	30.0	30.7	30.8	30.9	31.1	31.2	31.4	31.2
100°	26.7	28.0	29.4	30.7	31.4	31.5	31.7	31.8	32.0	32.2	32.0
102.5°	51.2	45.5	39.9	34.2	31.4	31.6	31.9	32.3	32.6	33.0	32.6
105°	137.8	107.6	77.5	47.3	32.2	32.4	32.7	33.0	33.4	33.7	33.4
107.5°	272.1	245.8	219.6	193.3	180.2	169.0	146.7	124.4	102.1	79.8	102.1
110°	340.3	334.7	329.0	323.4	320.6	308.4	284.0	259.7	235.3	210.9	235.3

TEST NUMBER: P1012536

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	395.7	397.3	398.8	400.3	401.1	400.9	400.6	400.3	399.9	399.6	399.9
115°	441.9	443.6	445.3	447.0	447.9	448.2	448.9	449.6	450.2	450.9	450.2
117.5°	486.9	488.2	489.6	490.9	491.6	491.7	491.9	492.0	492.2	492.4	492.2
120°	530.6	531.9	533.3	534.6	535.3	535.3	535.3	535.3	535.3	535.3	535.3
122.5°	573.7	574.6	575.4	576.3	576.7	576.8	577.0	577.1	577.3	577.5	577.3
125°	613.9	614.2	614.6	614.9	615.1	615.3	615.6	615.9	616.3	616.6	616.3
127.5°	654.7	655.2	655.7	656.2	656.5	656.3	656.0	655.6	655.3	654.9	655.3
130°	690.9	691.6	692.3	693.0	693.3	693.1	692.8	692.5	692.1	691.8	692.1
132.5°	725.4	726.1	726.8	727.5	727.8	727.5	727.0	726.5	726.0	725.5	726.0
135°	760.5	761.0	761.5	762.0	762.3	762.0	761.5	761.0	760.5	760.0	760.5
137.5°	791.5	792.4	793.2	794.1	794.5	794.3	794.0	793.7	793.3	793.0	793.3
140°	821.3	822.0	822.7	823.4	823.7	823.5	823.2	822.8	822.5	822.1	822.5
142.5°	849.5	850.0	850.5	851.0	851.3	851.0	850.5	850.0	849.5	849.0	849.5
145°	875.4	875.7	876.1	876.4	876.6	876.6	876.6	876.6	876.6	876.6	876.6
147.5°	899.2	899.5	899.9	900.2	900.4	900.0	899.1	898.2	897.4	896.5	897.4
150°	920.6	921.0	921.3	921.6	921.8	921.5	921.0	920.5	920.0	919.5	920.0
152.5°	939.4	940.1	940.8	941.5	941.8	941.4	940.5	939.6	938.8	937.9	938.8
155°	956.4	957.3	958.1	959.0	959.4	958.9	957.9	956.8	955.8	954.8	955.8
157.5°	971.9	972.9	974.0	975.0	975.5	974.8	973.5	972.1	970.8	969.4	970.8
160°	984.9	985.9	987.0	988.0	988.5	987.9	986.7	985.6	984.4	983.2	984.4
162.5°	996.7	997.9	999.0	1000.2	1000.8	1000.3	999.3	998.2	997.2	996.2	997.2
165°	1006.8	1008.2	1009.5	1010.9	1011.6	1011.0	1009.8	1008.6	1007.4	1006.2	1007.4
167.5°	1015.3	1016.6	1018.0	1019.3	1020.0	1019.3	1018.0	1016.6	1015.3	1013.9	1015.3
170°	1022.2	1023.5	1024.9	1026.2	1026.9	1026.2	1024.9	1023.5	1022.2	1020.8	1022.2
172.5°	1026.8	1028.1	1029.5	1030.8	1031.5	1030.7	1029.2	1027.7	1026.1	1024.6	1026.1
175°	1030.4	1031.6	1032.8	1034.0	1034.6	1033.9	1032.5	1031.2	1029.8	1028.4	1029.8
177.5°	1032.1	1033.5	1034.8	1036.2	1036.9	1036.0	1034.3	1032.6	1030.9	1029.2	1030.9
180°	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3

TEST NUMBER: P1012536

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1
2.5°	574.5	571.8	569.9	568.6	567.2	571.3	565.8	559.9	555.8	553.1	552.2
5°	634.6	628.7	623.7	619.6	620.5	620.5	610.9	600.5	591.3	586.3	580.9
7.5°	704.3	697.9	687.9	685.6	683.8	672.4	662.9	643.7	632.3	621.0	610.9
10°	773.6	765.4	755.8	752.6	748.1	733.9	719.4	694.8	680.6	659.7	646.5
12.5°	838.3	828.2	818.7	816.4	809.6	797.3	772.2	746.7	722.5	700.2	677.0
15°	892.5	889.7	875.2	866.1	851.0	834.2	828.7	794.1	763.6	740.3	698.4
17.5°	938.0	925.3	911.6	905.7	899.8	880.2	860.6	825.1	792.3	758.1	731.2
20°	974.5	960.4	950.8	942.1	939.4	917.1	886.1	854.7	818.7	780.4	745.3
22.5°	976.3	974.5	968.1	963.1	957.6	943.0	918.4	879.3	841.0	799.1	753.1
25°	938.5	935.8	954.0	949.4	953.1	947.6	934.4	901.6	856.9	807.7	761.3
27.5°	824.6	852.4	881.1	891.1	897.9	917.5	923.9	905.7	869.7	817.3	765.4
30°	669.7	706.6	753.1	778.1	797.3	833.7	881.1	887.0	870.2	828.2	764.5
32.5°	525.7	559.5	596.8	626.4	651.9	726.6	790.4	836.4	844.6	822.8	766.7
35°	423.7	438.3	473.8	502.0	536.7	600.5	675.6	749.9	800.0	802.7	759.9
37.5°	349.4	357.2	388.2	404.1	424.6	480.6	550.8	647.8	725.7	762.6	740.8
40°	289.3	307.1	324.8	333.9	348.5	387.2	454.7	530.7	627.3	695.7	711.2
42.5°	251.0	258.8	270.2	282.9	292.0	325.7	370.8	440.5	527.6	622.8	665.6
45°	221.4	224.1	236.0	244.2	253.8	277.4	309.3	367.7	444.2	538.0	610.9
47.5°	196.8	202.3	208.7	213.7	220.0	238.3	265.6	308.0	375.4	459.2	537.6
50°	174.9	178.1	186.3	188.6	193.2	205.9	226.9	259.2	314.8	381.8	462.9
52.5°	154.4	160.4	163.6	166.7	170.8	181.3	195.0	221.4	263.3	326.2	395.0
55°	138.5	140.3	144.9	147.6	150.8	158.1	169.9	189.5	222.3	272.4	337.6
57.5°	123.0	123.0	127.6	129.8	133.0	138.5	149.0	164.0	187.7	225.1	284.7
60°	106.6	107.1	110.7	113.4	114.4	119.8	128.5	140.3	158.5	185.9	234.6
62.5°	92.0	94.3	96.1	97.0	100.2	103.4	110.7	118.9	131.7	155.8	190.4
65°	79.7	80.2	81.5	82.5	83.8	87.5	92.9	98.4	109.3	127.1	155.4
67.5°	65.6	67.4	69.2	69.2	70.6	72.4	77.9	82.5	90.7	101.1	120.3
70°	49.2	50.1	52.8	54.2	56.0	59.2	62.0	64.7	71.1	78.8	93.4
72.5°	41.0	41.0	41.9	42.4	42.4	44.6	48.7	51.5	54.7	60.1	70.2
75°	32.8	32.8	34.2	33.7	34.6	35.5	36.0	37.8	39.6	43.7	49.7
77.5°	26.0	26.4	26.4	26.9	26.9	27.3	27.8	28.7	29.6	31.9	34.6
80°	19.1	19.6	19.6	20.0	20.0	20.5	21.0	21.4	22.3	23.2	24.6
82.5°	13.2	13.7	13.7	14.1	13.7	14.1	14.6	14.6	15.0	15.9	16.4
85°	7.7	7.7	8.2	7.7	7.7	7.7	8.2	8.2	8.7	10.0	10.0
87.5°	2.3	2.7	2.3	2.7	2.7	2.7	2.7	3.2	3.2	3.6	4.1
90°	22.3	22.0	21.7	21.5	21.2	20.5	19.8	19.1	18.4	16.2	14.0
92.5°	25.7	25.6	25.4	25.3	24.7	23.5	22.3	21.1	19.9	18.4	16.8
95°	29.1	29.1	29.1	29.1	28.5	27.3	26.2	25.0	23.8	21.9	20.0
97.5°	31.1	30.9	30.8	30.7	30.0	28.6	27.3	25.9	24.5	33.2	41.9
100°	31.8	31.7	31.5	31.4	30.7	29.4	28.0	26.7	25.3	51.9	78.5
102.5°	32.3	31.9	31.6	31.4	34.2	39.9	45.5	51.2	56.8	86.4	116.1
105°	33.0	32.7	32.4	32.2	47.3	77.5	107.6	137.8	168.0	183.3	198.7
107.5°	124.4	146.7	169.0	180.2	193.3	219.6	245.8	272.1	298.3	295.7	293.2
110°	259.7	284.0	308.4	320.6	323.4	329.0	334.7	340.3	345.9	344.0	342.1

TEST NUMBER: P1012536

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	400.3	400.6	400.9	401.1	400.3	398.8	397.3	395.7	394.2	392.3	390.5
115°	449.6	448.9	448.2	447.9	447.0	445.3	443.6	441.9	440.2	438.7	437.1
117.5°	492.0	491.9	491.7	491.6	490.9	489.6	488.2	486.9	485.5	484.6	483.8
120°	535.3	535.3	535.3	535.3	534.6	533.3	531.9	530.6	529.2	528.7	528.2
122.5°	577.1	577.0	576.8	576.7	576.3	575.4	574.6	573.7	572.9	572.2	571.5
125°	615.9	615.6	615.3	615.1	614.9	614.6	614.2	613.9	613.5	612.8	612.2
127.5°	655.6	656.0	656.3	656.5	656.2	655.7	655.2	654.7	654.2	653.3	652.5
130°	692.5	692.8	693.1	693.3	693.0	692.3	691.6	690.9	690.2	689.5	688.9
132.5°	726.5	727.0	727.5	727.8	727.5	726.8	726.1	725.4	724.7	724.2	723.7
135°	761.0	761.5	762.0	762.3	762.0	761.5	761.0	760.5	760.0	759.3	758.6
137.5°	793.7	794.0	794.3	794.5	794.1	793.2	792.4	791.5	790.7	790.4	790.0
140°	822.8	823.2	823.5	823.7	823.4	822.7	822.0	821.3	820.6	820.1	819.6
142.5°	850.0	850.5	851.0	851.3	851.0	850.5	850.0	849.5	849.0	848.5	848.0
145°	876.6	876.6	876.6	876.6	876.4	876.1	875.7	875.4	875.0	874.7	874.3
147.5°	898.2	899.1	900.0	900.4	900.2	899.9	899.5	899.2	898.8	898.5	898.1
150°	920.5	921.0	921.5	921.8	921.6	921.3	921.0	920.6	920.3	920.0	919.6
152.5°	939.6	940.5	941.4	941.8	941.5	940.8	940.1	939.4	938.7	938.5	938.3
155°	956.8	957.9	958.9	959.4	959.0	958.1	957.3	956.4	955.6	955.4	955.2
157.5°	972.1	973.5	974.8	975.5	975.0	974.0	972.9	971.9	970.9	971.1	971.3
160°	985.6	986.7	987.9	988.5	988.0	987.0	985.9	984.9	983.9	984.1	984.3
162.5°	998.2	999.3	1000.3	1000.8	1000.2	999.0	997.9	996.7	995.5	995.7	995.8
165°	1008.6	1009.8	1011.0	1011.6	1010.9	1009.5	1008.2	1006.8	1005.4	1005.6	1005.8
167.5°	1016.6	1018.0	1019.3	1020.0	1019.3	1018.0	1016.6	1015.3	1013.9	1013.9	1013.9
170°	1023.5	1024.9	1026.2	1026.9	1026.2	1024.9	1023.5	1022.2	1020.8	1020.8	1020.8
172.5°	1027.7	1029.2	1030.7	1031.5	1030.8	1029.5	1028.1	1026.8	1025.4	1025.2	1025.0
175°	1031.2	1032.5	1033.9	1034.6	1034.0	1032.8	1031.6	1030.4	1029.2	1029.0	1028.8
177.5°	1032.6	1034.3	1036.0	1036.9	1036.2	1034.8	1033.5	1032.1	1030.7	1030.5	1030.4
180°	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3

TEST NUMBER: P1012536

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1
2.5°	550.8	548.5	546.2	546.2	541.2	536.7	534.4	535.3	532.6	528.9	525.3
5°	574.9	565.8	564.0	559.0	552.2	542.6	537.6	533.0	527.6	520.3	513.4
7.5°	597.3	585.4	579.0	574.0	560.8	547.6	536.7	529.4	519.8	508.9	500.7
10°	626.4	604.6	597.7	586.3	567.7	549.0	536.2	524.4	511.2	498.4	487.5
12.5°	649.7	624.6	611.8	600.5	576.3	552.6	531.2	516.6	500.7	486.6	472.4
15°	676.1	647.8	625.5	611.8	581.3	552.6	528.5	508.0	490.2	472.9	460.6
17.5°	688.8	653.3	643.3	623.7	579.5	550.8	521.2	499.3	477.9	457.9	443.3
20°	708.9	667.4	642.4	629.2	590.0	547.6	513.0	487.9	465.6	444.2	428.7
22.5°	710.2	665.1	648.7	623.7	575.4	538.0	505.7	475.2	449.2	429.2	413.2
25°	707.1	661.0	638.3	618.2	578.1	532.6	491.1	461.0	435.5	412.3	393.6
27.5°	705.7	649.2	627.8	607.7	562.6	516.6	482.5	448.3	419.1	398.6	379.5
30°	703.9	636.4	610.5	587.2	545.8	504.3	463.3	433.7	405.9	380.0	360.8
32.5°	692.0	619.1	592.7	568.1	523.5	482.0	449.7	418.2	388.2	364.0	346.7
35°	688.4	603.2	568.6	542.1	498.4	461.5	427.3	401.4	373.1	349.0	328.5
37.5°	677.9	586.8	549.4	515.7	470.2	435.1	410.0	384.1	356.7	330.8	314.3
40°	659.7	567.7	525.3	490.7	443.7	408.2	385.0	365.8	339.0	315.7	295.7
42.5°	632.8	548.1	502.5	466.1	414.1	380.9	361.7	343.5	320.7	296.6	280.2
45°	601.8	522.1	479.7	439.2	386.3	354.0	333.9	323.0	302.0	281.5	262.4
47.5°	559.5	495.2	453.3	411.4	357.6	326.2	310.2	299.3	284.7	262.4	246.9
50°	506.1	460.6	421.0	383.6	329.4	299.3	283.4	275.2	262.9	246.9	231.9
52.5°	446.9	420.5	387.7	353.1	300.7	272.4	257.9	251.5	242.4	227.3	214.6
55°	387.2	375.9	353.5	319.4	270.6	247.4	234.6	226.4	219.6	208.7	197.7
57.5°	333.9	328.5	313.0	286.6	245.6	221.4	210.5	205.0	199.5	191.3	180.4
60°	278.8	284.7	268.8	255.6	218.2	197.3	187.7	181.8	179.0	171.8	164.9
62.5°	231.0	236.4	227.3	217.3	190.9	172.2	166.3	160.8	159.0	152.6	145.8
65°	187.7	194.5	187.7	182.2	166.3	150.8	143.5	140.8	139.0	134.9	129.4
67.5°	149.4	156.3	153.1	146.2	141.2	128.5	124.4	121.6	120.7	117.5	113.0
70°	112.5	122.1	123.0	118.9	114.4	108.4	105.7	104.8	102.5	99.8	97.0
72.5°	81.1	92.0	92.5	92.5	89.7	89.7	87.0	85.6	85.6	82.9	79.7
75°	59.7	67.0	67.9	68.8	70.2	71.5	69.7	69.7	69.2	66.5	65.1
77.5°	39.6	46.0	48.3	51.5	53.3	53.3	54.2	55.1	54.2	52.8	51.9
80°	25.5	30.1	32.8	34.6	37.4	38.7	40.1	40.5	39.6	39.2	37.8
82.5°	16.9	18.2	19.6	21.9	25.1	27.3	27.3	26.9	27.8	27.3	26.9
85°	9.6	10.5	10.9	11.4	13.2	15.5	15.9	16.4	17.3	16.4	15.5
87.5°	3.6	4.1	4.1	4.1	5.0	5.5	6.8	8.7	8.2	7.3	7.3
90°	11.7	9.5	8.4	7.6	5.9	4.2	2.5	0.8	2.5	4.2	5.9
92.5°	15.3	13.8	13.0	13.5	14.5	15.6	16.6	17.6	16.6	15.6	14.5
95°	18.1	16.2	15.3	18.8	25.8	32.8	39.8	46.8	39.8	32.8	25.8
97.5°	50.6	59.3	63.7	66.1	70.8	75.6	80.3	85.1	80.3	75.6	70.8
100°	105.0	131.6	144.9	143.2	139.8	136.4	133.0	129.6	133.0	136.4	139.8
102.5°	145.7	175.4	190.2	189.1	186.9	184.6	182.4	180.2	182.4	184.6	186.9
105°	214.0	229.3	237.0	236.1	234.2	232.3	230.4	228.5	230.4	232.3	234.2
107.5°	290.6	288.1	286.8	286.0	284.5	283.0	281.4	279.9	281.4	283.0	284.5
110°	340.2	338.3	337.4	336.7	335.4	334.0	332.7	331.3	332.7	334.0	335.4

TEST NUMBER: P1012536

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	388.6	386.7	385.8	385.2	384.0	382.8	381.6	380.4	381.6	382.8	384.0
115°	435.6	434.1	433.3	432.8	431.8	430.7	429.7	428.7	429.7	430.7	431.8
117.5°	482.9	482.0	481.6	481.0	479.8	478.7	477.5	476.3	477.5	478.7	479.8
120°	527.7	527.2	526.9	526.1	524.6	523.1	521.5	520.0	521.5	523.1	524.6
122.5°	570.8	570.1	569.8	569.2	568.0	566.8	565.6	564.4	565.6	566.8	568.0
125°	611.5	610.8	610.5	609.8	608.4	607.1	605.7	604.3	605.7	607.1	608.4
127.5°	651.6	650.7	650.3	649.6	648.3	646.9	645.6	644.2	645.6	646.9	648.3
130°	688.2	687.5	687.2	686.5	685.1	683.8	682.4	681.0	682.4	683.8	685.1
132.5°	723.2	722.7	722.4	721.7	720.4	719.0	717.7	716.3	717.7	719.0	720.4
135°	757.9	757.2	756.9	756.4	755.4	754.3	753.3	752.3	753.3	754.3	755.4
137.5°	789.7	789.4	789.2	788.5	787.1	785.8	784.4	783.0	784.4	785.8	787.1
140°	819.1	818.6	818.3	817.8	816.8	815.7	814.7	813.7	814.7	815.7	816.8
142.5°	847.5	847.0	846.7	846.2	845.2	844.1	843.1	842.1	843.1	844.1	845.2
145°	874.0	873.7	873.5	872.9	871.7	870.5	869.3	868.1	869.3	870.5	871.7
147.5°	897.8	897.5	897.3	896.9	896.0	895.2	894.3	893.5	894.3	895.2	896.0
150°	919.3	919.0	918.8	918.5	918.0	917.5	917.0	916.5	917.0	917.5	918.0
152.5°	938.2	938.0	937.9	937.8	937.7	937.5	937.4	937.2	937.4	937.5	937.7
155°	955.1	954.9	954.8	955.0	955.3	955.6	956.0	956.3	956.0	955.6	955.3
157.5°	971.4	971.6	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
160°	984.4	984.6	984.7	984.8	985.0	985.1	985.3	985.5	985.3	985.1	985.0
162.5°	996.0	996.1	996.2	996.5	997.0	997.5	998.0	998.5	998.0	997.5	997.0
165°	1005.9	1006.1	1006.2	1006.5	1007.0	1007.5	1008.0	1008.5	1008.0	1007.5	1007.0
167.5°	1013.9	1013.9	1013.9	1014.2	1014.9	1015.6	1016.2	1016.9	1016.2	1015.6	1014.9
170°	1020.8	1020.8	1020.8	1021.1	1021.8	1022.5	1023.1	1023.8	1023.1	1022.5	1021.8
172.5°	1024.9	1024.7	1024.6	1025.0	1025.9	1026.7	1027.6	1028.4	1027.6	1026.7	1025.9
175°	1028.7	1028.5	1028.4	1028.8	1029.7	1030.6	1031.4	1032.3	1031.4	1030.6	1029.7
177.5°	1030.2	1030.1	1030.0	1030.4	1031.3	1032.1	1033.0	1033.8	1033.0	1032.1	1031.3
180°	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3

TEST NUMBER: P1012536

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1
2.5°	525.3	523.0	522.1	519.8	514.3	510.7	506.6	503.9	504.3	502.0	503.4
5°	508.9	508.4	505.2	500.7	492.9	488.8	481.5	477.9	476.1	476.5	473.8
7.5°	495.2	491.1	488.8	481.5	474.3	465.6	459.7	456.5	453.8	451.0	449.2
10°	479.7	476.1	472.4	464.7	454.7	446.5	438.3	435.1	431.0	429.2	427.8
12.5°	463.3	461.0	456.5	447.4	436.0	428.2	418.7	416.9	411.4	407.7	406.8
15°	448.3	446.9	438.7	428.2	416.9	409.1	400.9	395.4	386.3	388.2	385.0
17.5°	432.3	426.4	421.4	407.3	401.8	390.0	380.4	377.7	371.3	367.2	363.1
20°	414.6	410.9	404.6	395.4	382.2	368.6	361.3	356.7	353.1	346.7	344.9
22.5°	397.7	393.2	387.7	375.9	364.5	353.1	343.1	339.0	334.4	329.8	327.1
25°	384.5	377.7	371.8	357.2	345.8	336.2	329.8	323.0	316.6	313.9	313.0
27.5°	364.0	359.9	354.0	340.3	329.8	319.4	313.4	308.9	302.0	298.9	296.1
30°	350.8	342.6	335.8	324.8	314.3	303.0	297.5	292.0	287.9	283.8	280.6
32.5°	333.0	326.7	321.2	310.2	299.8	289.3	283.4	275.2	272.9	269.7	266.1
35°	315.7	311.6	305.7	293.8	282.5	275.2	268.8	261.0	258.3	256.0	252.8
37.5°	299.3	293.4	289.3	277.9	267.9	259.2	254.2	247.8	246.0	243.3	241.0
40°	285.2	279.3	275.2	263.8	253.3	244.2	241.0	234.6	231.9	228.7	227.3
42.5°	269.2	264.2	258.8	250.6	239.6	230.5	224.1	220.5	216.9	215.5	212.8
45°	252.4	247.8	243.7	234.6	223.2	216.9	211.4	206.4	203.6	201.4	199.5
47.5°	237.8	233.7	228.2	218.2	209.1	203.2	197.7	192.7	190.0	187.2	185.0
50°	221.0	218.7	212.8	203.2	194.5	187.7	182.7	178.1	176.3	173.1	169.5
52.5°	205.9	201.8	196.8	189.1	181.3	173.1	166.3	163.6	160.4	158.5	155.4
55°	188.2	185.4	180.0	173.1	164.9	158.1	153.1	149.4	145.3	143.5	139.4
57.5°	173.1	168.1	165.4	156.7	149.0	142.1	138.5	134.9	130.3	127.6	125.7
60°	156.7	152.2	148.1	140.8	135.3	128.0	122.6	119.4	116.2	112.5	110.7
62.5°	140.8	137.1	132.1	126.2	119.4	113.4	109.3	104.8	103.0	99.3	97.9
65°	123.5	120.7	116.6	109.8	104.3	99.3	95.2	91.6	89.7	88.4	87.5
67.5°	108.0	104.3	101.6	95.7	89.7	85.6	83.4	81.1	78.8	77.4	76.1
70°	92.0	89.3	86.6	81.1	77.0	73.3	71.5	69.7	68.3	67.0	65.6
72.5°	75.6	74.3	71.5	67.9	64.7	62.0	60.6	58.3	56.9	54.7	53.8
75°	62.4	60.1	58.8	55.6	52.8	50.6	48.7	46.0	44.2	43.3	42.8
77.5°	49.2	48.3	46.5	43.7	42.4	40.1	37.4	36.4	35.5	35.5	35.1
80°	36.9	35.5	34.2	31.9	30.5	28.7	28.7	28.7	28.2	28.7	28.2
82.5°	25.1	24.1	23.2	21.9	21.4	21.4	21.9	21.9	21.9	21.9	21.9
85°	14.6	14.6	14.6	15.0	14.6	14.6	15.0	15.5	15.0	15.0	14.6
87.5°	6.8	6.8	7.3	7.3	7.7	7.7	7.7	7.7	7.7	7.7	8.2
90°	7.6	8.4	9.5	11.7	14.0	16.2	18.4	19.1	19.8	20.5	21.2
92.5°	13.5	13.0	13.8	15.3	16.8	18.4	19.9	21.1	22.3	23.5	24.7
95°	18.8	15.3	16.2	18.1	20.0	21.9	23.8	25.0	26.2	27.3	28.5
97.5°	66.1	63.7	59.3	50.6	41.9	33.2	24.5	25.9	27.3	28.6	30.0
100°	143.2	144.9	131.6	105.0	78.5	51.9	25.3	26.7	28.0	29.4	30.7
102.5°	189.1	190.2	175.4	145.7	116.1	86.4	56.8	51.2	45.5	39.9	34.2
105°	236.1	237.0	229.3	214.0	198.7	183.3	168.0	137.8	107.6	77.5	47.3
107.5°	286.0	286.8	288.1	290.6	293.2	295.7	298.3	272.1	245.8	219.6	193.3
110°	336.7	337.4	338.3	340.2	342.1	344.0	345.9	340.3	334.7	329.0	323.4

TEST NUMBER: P1012536

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	385.2	385.8	386.7	388.6	390.5	392.3	394.2	395.7	397.3	398.8	400.3
115°	432.8	433.3	434.1	435.6	437.1	438.7	440.2	441.9	443.6	445.3	447.0
117.5°	481.0	481.6	482.0	482.9	483.8	484.6	485.5	486.9	488.2	489.6	490.9
120°	526.1	526.9	527.2	527.7	528.2	528.7	529.2	530.6	531.9	533.3	534.6
122.5°	569.2	569.8	570.1	570.8	571.5	572.2	572.9	573.7	574.6	575.4	576.3
125°	609.8	610.5	610.8	611.5	612.2	612.8	613.5	613.9	614.2	614.6	614.9
127.5°	649.6	650.3	650.7	651.6	652.5	653.3	654.2	654.7	655.2	655.7	656.2
130°	686.5	687.2	687.5	688.2	688.9	689.5	690.2	690.9	691.6	692.3	693.0
132.5°	721.7	722.4	722.7	723.2	723.7	724.2	724.7	725.4	726.1	726.8	727.5
135°	756.4	756.9	757.2	757.9	758.6	759.3	760.0	760.5	761.0	761.5	762.0
137.5°	788.5	789.2	789.4	789.7	790.0	790.4	790.7	791.5	792.4	793.2	794.1
140°	817.8	818.3	818.6	819.1	819.6	820.1	820.6	821.3	822.0	822.7	823.4
142.5°	846.2	846.7	847.0	847.5	848.0	848.5	849.0	849.5	850.0	850.5	851.0
145°	872.9	873.5	873.7	874.0	874.3	874.7	875.0	875.4	875.7	876.1	876.4
147.5°	896.9	897.3	897.5	897.8	898.1	898.5	898.8	899.2	899.5	899.9	900.2
150°	918.5	918.8	919.0	919.3	919.6	920.0	920.3	920.6	921.0	921.3	921.6
152.5°	937.8	937.9	938.0	938.2	938.3	938.5	938.7	939.4	940.1	940.8	941.5
155°	955.0	954.8	954.9	955.1	955.2	955.4	955.6	956.4	957.3	958.1	959.0
157.5°	971.7	971.7	971.6	971.4	971.3	971.1	970.9	971.9	972.9	974.0	975.0
160°	984.8	984.7	984.6	984.4	984.3	984.1	983.9	984.9	985.9	987.0	988.0
162.5°	996.5	996.2	996.1	996.0	995.8	995.7	995.5	996.7	997.9	999.0	1000.2
165°	1006.5	1006.2	1006.1	1005.9	1005.8	1005.6	1005.4	1006.8	1008.2	1009.5	1010.9
167.5°	1014.2	1013.9	1013.9	1013.9	1013.9	1013.9	1013.9	1015.3	1016.6	1018.0	1019.3
170°	1021.1	1020.8	1020.8	1020.8	1020.8	1020.8	1020.8	1022.2	1023.5	1024.9	1026.2
172.5°	1025.0	1024.6	1024.7	1024.9	1025.0	1025.2	1025.4	1026.8	1028.1	1029.5	1030.8
175°	1028.8	1028.4	1028.5	1028.7	1028.8	1029.0	1029.2	1030.4	1031.6	1032.8	1034.0
177.5°	1030.4	1030.0	1030.1	1030.2	1030.4	1030.5	1030.7	1032.1	1033.5	1034.8	1036.2
180°	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3

TEST NUMBER: P1012536

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1
2.5°	503.0	503.4	502.0	499.3	498.9	499.8	502.5	501.6	499.3	503.4	499.8
5°	475.2	472.9	472.0	472.9	470.2	468.8	471.5	470.2	471.5	472.0	473.3
7.5°	448.3	448.7	446.0	446.5	442.8	443.7	443.7	443.7	445.1	446.0	447.8
10°	425.1	426.0	422.8	423.2	420.5	418.7	420.0	422.8	422.8	422.8	423.7
12.5°	406.4	402.3	400.0	399.5	396.4	395.4	398.2	399.1	401.4	401.4	402.7
15°	383.1	382.2	380.4	380.4	372.7	374.5	375.4	378.6	383.1	379.5	380.4
17.5°	362.2	359.9	357.6	356.7	355.8	353.1	356.7	356.3	359.0	359.5	360.8
20°	343.5	341.7	337.1	337.6	338.5	334.4	336.7	336.7	339.4	342.1	345.3
22.5°	325.3	323.5	321.2	322.1	319.4	318.4	318.4	320.7	323.9	326.2	325.7
25°	311.2	308.0	306.6	305.2	303.9	304.8	303.4	305.7	308.0	309.3	308.0
27.5°	295.2	293.8	291.1	289.7	287.5	288.4	289.3	291.1	292.5	292.5	293.8
30°	279.7	277.9	277.0	275.6	275.6	273.8	274.3	276.1	277.4	278.8	280.6
32.5°	264.7	263.3	262.0	262.0	261.0	260.6	260.1	262.9	262.9	265.6	265.6
35°	252.4	250.1	250.1	247.8	248.7	248.3	247.4	249.2	249.7	251.5	251.0
37.5°	238.7	238.7	237.8	235.5	233.7	234.2	236.4	236.4	237.8	237.4	238.7
40°	225.1	224.1	224.1	222.8	222.3	221.9	222.3	222.8	225.1	224.6	225.1
42.5°	211.4	211.8	209.6	209.6	209.6	208.2	208.7	209.1	210.0	210.9	212.3
45°	198.2	197.3	196.8	195.9	195.0	195.4	195.0	196.8	196.4	197.3	198.6
47.5°	184.1	182.7	182.2	180.4	180.4	181.3	180.9	182.2	182.7	184.1	183.1
50°	170.4	168.6	167.2	167.7	164.9	165.8	165.8	167.2	168.6	169.0	169.9
52.5°	154.4	154.0	153.5	151.3	150.8	150.3	150.8	151.3	153.1	154.4	154.9
55°	139.0	138.5	135.8	134.9	133.5	133.5	134.4	134.9	138.0	138.5	140.3
57.5°	124.8	123.5	120.3	119.8	119.8	119.8	118.5	120.3	121.2	123.5	123.5
60°	109.3	109.3	106.6	106.6	107.1	106.6	106.6	107.1	107.1	108.9	109.8
62.5°	97.0	96.6	96.6	95.7	95.2	95.7	95.2	95.2	95.7	97.0	98.4
65°	86.1	85.6	85.2	84.7	83.8	83.8	84.3	85.2	85.2	86.1	86.6
67.5°	75.6	75.6	74.7	74.7	74.3	73.8	74.3	73.8	75.6	75.6	76.1
70°	65.1	64.7	63.3	62.9	61.5	62.0	62.0	63.3	63.8	64.7	65.6
72.5°	52.4	52.4	51.5	50.6	51.0	50.1	50.1	50.6	50.6	51.9	52.4
75°	43.3	42.4	41.9	42.4	41.9	42.8	41.9	41.9	42.8	42.8	42.8
77.5°	35.5	35.5	35.1	35.1	35.5	35.1	35.5	35.5	35.5	35.1	35.5
80°	29.2	28.7	28.7	28.7	28.2	28.2	28.2	28.2	28.2	28.2	28.2
82.5°	21.9	21.9	21.4	21.9	21.9	21.4	21.9	21.4	21.4	21.9	21.9
85°	14.6	15.5	14.6	14.6	15.0	15.0	15.5	15.0	15.5	14.6	15.0
87.5°	7.7	8.2	8.2	7.7	7.7	8.2	8.2	8.2	8.7	7.7	8.2
90°	21.5	21.7	22.0	22.3	22.7	23.0	22.7	22.3	22.0	21.7	21.5
92.5°	25.3	25.4	25.6	25.7	25.9	26.1	25.9	25.7	25.6	25.4	25.3
95°	29.1	29.1	29.1	29.1	29.1	29.1	29.1	29.1	29.1	29.1	29.1
97.5°	30.7	30.8	30.9	31.1	31.2	31.4	31.2	31.1	30.9	30.8	30.7
100°	31.4	31.5	31.7	31.8	32.0	32.2	32.0	31.8	31.7	31.5	31.4
102.5°	31.4	31.6	31.9	32.3	32.6	33.0	32.6	32.3	31.9	31.6	31.4
105°	32.2	32.4	32.7	33.0	33.4	33.7	33.4	33.0	32.7	32.4	32.2
107.5°	180.2	169.0	146.7	124.4	102.1	79.8	102.1	124.4	146.7	169.0	180.2
110°	320.6	308.4	284.0	259.7	235.3	210.9	235.3	259.7	284.0	308.4	320.6

TEST NUMBER: P1012536

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	401.1	400.9	400.6	400.3	399.9	399.6	399.9	400.3	400.6	400.9	401.1
115°	447.9	448.2	448.9	449.6	450.2	450.9	450.2	449.6	448.9	448.2	447.9
117.5°	491.6	491.7	491.9	492.0	492.2	492.4	492.2	492.0	491.9	491.7	491.6
120°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3
122.5°	576.7	576.8	577.0	577.1	577.3	577.5	577.3	577.1	577.0	576.8	576.7
125°	615.1	615.3	615.6	615.9	616.3	616.6	616.3	615.9	615.6	615.3	615.1
127.5°	656.5	656.3	656.0	655.6	655.3	654.9	655.3	655.6	656.0	656.3	656.5
130°	693.3	693.1	692.8	692.5	692.1	691.8	692.1	692.5	692.8	693.1	693.3
132.5°	727.8	727.5	727.0	726.5	726.0	725.5	726.0	726.5	727.0	727.5	727.8
135°	762.3	762.0	761.5	761.0	760.5	760.0	760.5	761.0	761.5	762.0	762.3
137.5°	794.5	794.3	794.0	793.7	793.3	793.0	793.3	793.7	794.0	794.3	794.5
140°	823.7	823.5	823.2	822.8	822.5	822.1	822.5	822.8	823.2	823.5	823.7
142.5°	851.3	851.0	850.5	850.0	849.5	849.0	849.5	850.0	850.5	851.0	851.3
145°	876.6	876.6	876.6	876.6	876.6	876.6	876.6	876.6	876.6	876.6	876.6
147.5°	900.4	900.0	899.1	898.2	897.4	896.5	897.4	898.2	899.1	900.0	900.4
150°	921.8	921.5	921.0	920.5	920.0	919.5	920.0	920.5	921.0	921.5	921.8
152.5°	941.8	941.4	940.5	939.6	938.8	937.9	938.8	939.6	940.5	941.4	941.8
155°	959.4	958.9	957.9	956.8	955.8	954.8	955.8	956.8	957.9	958.9	959.4
157.5°	975.5	974.8	973.5	972.1	970.8	969.4	970.8	972.1	973.5	974.8	975.5
160°	988.5	987.9	986.7	985.6	984.4	983.2	984.4	985.6	986.7	987.9	988.5
162.5°	1000.8	1000.3	999.3	998.2	997.2	996.2	997.2	998.2	999.3	1000.3	1000.8
165°	1011.6	1011.0	1009.8	1008.6	1007.4	1006.2	1007.4	1008.6	1009.8	1011.0	1011.6
167.5°	1020.0	1019.3	1018.0	1016.6	1015.3	1013.9	1015.3	1016.6	1018.0	1019.3	1020.0
170°	1026.9	1026.2	1024.9	1023.5	1022.2	1020.8	1022.2	1023.5	1024.9	1026.2	1026.9
172.5°	1031.5	1030.7	1029.2	1027.7	1026.1	1024.6	1026.1	1027.7	1029.2	1030.7	1031.5
175°	1034.6	1033.9	1032.5	1031.2	1029.8	1028.4	1029.8	1031.2	1032.5	1033.9	1034.6
177.5°	1036.9	1036.0	1034.3	1032.6	1030.9	1029.2	1030.9	1032.6	1034.3	1036.0	1036.9
180°	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3

TEST NUMBER: P1012536

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1
2.5°	503.4	505.2	503.4	499.8	503.4	505.7	508.0	511.6	513.4	513.4	516.2
5°	474.7	478.4	477.0	476.1	479.7	482.0	485.6	490.2	495.2	498.4	502.0
7.5°	449.2	451.5	453.8	453.8	457.4	462.4	467.9	473.3	479.7	484.3	487.0
10°	426.9	428.7	430.1	431.9	437.4	442.8	450.1	456.9	462.4	467.4	472.0
12.5°	405.5	408.2	411.4	412.8	416.9	423.7	430.5	438.7	447.4	452.4	456.9
15°	385.0	386.3	390.0	394.1	397.7	405.0	413.7	422.3	429.6	437.4	441.5
17.5°	364.0	364.5	374.0	371.8	383.6	390.4	395.0	403.2	415.0	421.4	427.8
20°	343.5	348.1	352.2	354.4	360.8	368.6	381.8	388.2	397.7	403.6	409.1
22.5°	327.6	334.4	334.4	339.9	343.1	350.3	359.9	372.2	382.7	386.8	394.5
25°	313.4	316.6	322.1	323.9	329.8	336.2	342.6	355.8	367.2	372.7	378.1
27.5°	295.2	299.3	306.6	306.6	314.3	321.2	328.9	337.6	349.0	356.7	362.6
30°	281.1	285.2	288.4	293.4	296.6	303.0	316.6	323.0	333.0	339.9	347.2
32.5°	267.9	271.1	273.8	279.3	282.9	290.2	297.5	308.9	317.5	323.9	331.7
35°	253.3	256.5	260.1	264.2	269.7	276.5	283.4	292.9	301.6	307.5	313.9
37.5°	239.6	241.9	247.4	250.1	254.7	261.0	269.7	279.7	287.5	292.0	298.4
40°	226.4	228.2	232.3	237.4	240.5	245.6	254.7	263.3	272.9	278.4	283.4
42.5°	212.3	214.6	218.2	223.2	228.2	233.7	238.7	248.7	257.4	262.0	267.4
45°	200.0	201.4	204.1	209.1	214.1	218.2	226.0	235.1	243.3	246.9	252.8
47.5°	185.4	186.8	190.9	193.2	198.6	204.1	211.8	221.0	228.2	231.9	237.4
50°	170.4	171.8	174.5	179.5	183.1	189.1	195.9	203.6	212.8	217.8	221.0
52.5°	155.8	158.5	160.8	164.9	169.5	175.4	181.8	189.1	196.8	201.8	205.5
55°	141.2	143.5	146.2	148.5	154.0	159.5	166.7	173.6	180.4	185.0	189.1
57.5°	124.8	128.0	130.8	135.3	139.4	144.0	152.2	157.6	165.8	169.0	172.7
60°	110.7	113.9	116.2	119.8	123.5	129.4	134.9	141.7	148.5	152.6	157.2
62.5°	98.9	100.2	101.6	105.2	108.9	114.4	119.8	126.7	133.9	136.2	139.9
65°	87.0	88.4	90.7	93.8	96.6	99.8	105.7	111.2	118.0	121.6	123.0
67.5°	77.0	78.4	78.8	81.1	83.4	87.0	90.2	95.7	102.0	104.3	107.1
70°	65.6	67.9	68.3	70.2	71.1	73.3	77.0	81.1	86.1	90.2	92.5
72.5°	52.4	55.6	56.5	59.2	60.6	62.9	65.6	68.8	72.0	73.8	75.6
75°	42.8	43.7	44.2	46.5	48.7	51.9	53.3	55.1	57.9	60.1	62.0
77.5°	35.5	36.0	36.4	36.4	36.9	38.7	41.5	43.7	45.6	46.5	47.8
80°	28.7	28.2	28.2	28.7	28.7	28.7	29.6	32.8	33.7	36.0	35.5
82.5°	22.3	21.4	21.9	21.4	21.4	21.4	21.4	21.9	21.9	23.2	24.1
85°	14.6	15.0	14.6	14.6	14.1	14.6	14.1	14.1	13.7	13.7	13.2
87.5°	7.7	8.2	7.7	7.7	7.3	7.7	7.3	7.3	6.8	6.8	5.9
90°	21.2	20.5	19.8	19.1	18.4	16.2	14.0	11.7	9.5	8.4	7.6
92.5°	24.7	23.5	22.3	21.1	19.9	18.4	16.8	15.3	13.8	13.0	13.5
95°	28.5	27.3	26.2	25.0	23.8	21.9	20.0	18.1	16.2	15.3	18.8
97.5°	30.0	28.6	27.3	25.9	24.5	33.2	41.9	50.6	59.3	63.7	66.1
100°	30.7	29.4	28.0	26.7	25.3	51.9	78.5	105.0	131.6	144.9	143.2
102.5°	34.2	39.9	45.5	51.2	56.8	86.4	116.1	145.7	175.4	190.2	189.1
105°	47.3	77.5	107.6	137.8	168.0	183.3	198.7	214.0	229.3	237.0	236.1
107.5°	193.3	219.6	245.8	272.1	298.3	295.7	293.2	290.6	288.1	286.8	286.0
110°	323.4	329.0	334.7	340.3	345.9	344.0	342.1	340.2	338.3	337.4	336.7

TEST NUMBER: P1012536

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	400.3	398.8	397.3	395.7	394.2	392.3	390.5	388.6	386.7	385.8	385.2
115°	447.0	445.3	443.6	441.9	440.2	438.7	437.1	435.6	434.1	433.3	432.8
117.5°	490.9	489.6	488.2	486.9	485.5	484.6	483.8	482.9	482.0	481.6	481.0
120°	534.6	533.3	531.9	530.6	529.2	528.7	528.2	527.7	527.2	526.9	526.1
122.5°	576.3	575.4	574.6	573.7	572.9	572.2	571.5	570.8	570.1	569.8	569.2
125°	614.9	614.6	614.2	613.9	613.5	612.8	612.2	611.5	610.8	610.5	609.8
127.5°	656.2	655.7	655.2	654.7	654.2	653.3	652.5	651.6	650.7	650.3	649.6
130°	693.0	692.3	691.6	690.9	690.2	689.5	688.9	688.2	687.5	687.2	686.5
132.5°	727.5	726.8	726.1	725.4	724.7	724.2	723.7	723.2	722.7	722.4	721.7
135°	762.0	761.5	761.0	760.5	760.0	759.3	758.6	757.9	757.2	756.9	756.4
137.5°	794.1	793.2	792.4	791.5	790.7	790.4	790.0	789.7	789.4	789.2	788.5
140°	823.4	822.7	822.0	821.3	820.6	820.1	819.6	819.1	818.6	818.3	817.8
142.5°	851.0	850.5	850.0	849.5	849.0	848.5	848.0	847.5	847.0	846.7	846.2
145°	876.4	876.1	875.7	875.4	875.0	874.7	874.3	874.0	873.7	873.5	872.9
147.5°	900.2	899.9	899.5	899.2	898.8	898.5	898.1	897.8	897.5	897.3	896.9
150°	921.6	921.3	921.0	920.6	920.3	920.0	919.6	919.3	919.0	918.8	918.5
152.5°	941.5	940.8	940.1	939.4	938.7	938.5	938.3	938.2	938.0	937.9	937.8
155°	959.0	958.1	957.3	956.4	955.6	955.4	955.2	955.1	954.9	954.8	955.0
157.5°	975.0	974.0	972.9	971.9	970.9	971.1	971.3	971.4	971.6	971.7	971.7
160°	988.0	987.0	985.9	984.9	983.9	984.1	984.3	984.4	984.6	984.7	984.8
162.5°	1000.2	999.0	997.9	996.7	995.5	995.7	995.8	996.0	996.1	996.2	996.5
165°	1010.9	1009.5	1008.2	1006.8	1005.4	1005.6	1005.8	1005.9	1006.1	1006.2	1006.5
167.5°	1019.3	1018.0	1016.6	1015.3	1013.9	1013.9	1013.9	1013.9	1013.9	1013.9	1014.2
170°	1026.2	1024.9	1023.5	1022.2	1020.8	1020.8	1020.8	1020.8	1020.8	1020.8	1021.1
172.5°	1030.8	1029.5	1028.1	1026.8	1025.4	1025.2	1025.0	1024.9	1024.7	1024.6	1025.0
175°	1034.0	1032.8	1031.6	1030.4	1029.2	1029.0	1028.8	1028.7	1028.5	1028.4	1028.8
177.5°	1036.2	1034.8	1033.5	1032.1	1030.7	1030.5	1030.4	1030.2	1030.1	1030.0	1030.4
180°	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3	1032.3

TEST NUMBER: P1012536

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	532.1	532.1	532.1	532.1
2.5°	518.4	521.6	528.0	533.5
5°	507.5	512.5	522.1	531.7
7.5°	494.3	502.0	514.3	527.6
10°	481.5	491.6	506.6	522.1
12.5°	468.8	479.3	495.2	515.3
15°	453.8	464.7	483.8	508.0
17.5°	440.5	455.1	472.4	496.6
20°	426.4	437.4	459.7	485.2
22.5°	408.7	426.9	447.8	474.7
25°	394.5	410.5	431.4	462.0
27.5°	377.2	395.9	421.4	448.3
30°	363.1	378.6	402.3	434.6
32.5°	346.7	364.9	389.5	421.4
35°	332.1	347.6	370.8	403.2
37.5°	314.8	331.7	357.6	386.3
40°	299.8	316.2	340.8	367.7
42.5°	281.5	298.9	323.5	346.2
45°	267.0	282.9	302.5	323.5
47.5°	249.2	266.1	285.2	299.8
50°	233.3	248.7	263.8	276.1
52.5°	215.9	230.1	243.7	252.8
55°	200.0	210.9	221.9	228.2
57.5°	181.3	191.8	200.9	204.6
60°	164.9	173.6	179.5	183.6
62.5°	147.6	154.0	158.5	160.8
65°	130.8	135.3	137.6	139.9
67.5°	113.4	117.5	118.9	121.6
70°	95.2	99.8	100.7	102.0
72.5°	81.5	81.5	83.4	85.2
75°	65.1	66.1	67.0	67.0
77.5°	51.0	51.0	51.9	52.4
80°	37.4	37.8	37.8	37.4
82.5°	25.5	26.4	25.5	25.1
85°	14.1	15.9	15.0	15.0
87.5°	5.9	5.9	6.8	5.9
90°	5.9	4.2	2.5	0.8
92.5°	14.5	15.6	16.6	17.6
95°	25.8	32.8	39.8	46.8
97.5°	70.8	75.6	80.3	85.1
100°	139.8	136.4	133.0	129.6
102.5°	186.9	184.6	182.4	180.2
105°	234.2	232.3	230.4	228.5
107.5°	284.5	283.0	281.4	279.9
110°	335.4	334.0	332.7	331.3

TEST NUMBER: P1012536

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	384.0	382.8	381.6	380.4
115°	431.8	430.7	429.7	428.7
117.5°	479.8	478.7	477.5	476.3
120°	524.6	523.1	521.5	520.0
122.5°	568.0	566.8	565.6	564.4
125°	608.4	607.1	605.7	604.3
127.5°	648.3	646.9	645.6	644.2
130°	685.1	683.8	682.4	681.0
132.5°	720.4	719.0	717.7	716.3
135°	755.4	754.3	753.3	752.3
137.5°	787.1	785.8	784.4	783.0
140°	816.8	815.7	814.7	813.7
142.5°	845.2	844.1	843.1	842.1
145°	871.7	870.5	869.3	868.1
147.5°	896.0	895.2	894.3	893.5
150°	918.0	917.5	917.0	916.5
152.5°	937.7	937.5	937.4	937.2
155°	955.3	955.6	956.0	956.3
157.5°	971.7	971.7	971.7	971.7
160°	985.0	985.1	985.3	985.5
162.5°	997.0	997.5	998.0	998.5
165°	1007.0	1007.5	1008.0	1008.5
167.5°	1014.9	1015.6	1016.2	1016.9
170°	1021.8	1022.5	1023.1	1023.8
172.5°	1025.9	1026.7	1027.6	1028.4
175°	1029.7	1030.6	1031.4	1032.3
177.5°	1031.3	1032.1	1033.0	1033.8
180°	1032.3	1032.3	1032.3	1032.3

(END OF REPORT)