

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012184

Luminaire Tested: S123RDIP-B1000D365UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012184
REPORT IS A COMBINATION OF REPORTS P992819 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D365UB30-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5024.0 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012184

CATALOG NUMBER: S123RDIP-B1000D365UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012184

CATALOG NUMBER: S123RDIP-B1000D365UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79
1	104	100	96	92	99	95	92	88	86	84	81	78	76	74	71	69	68
2	95	88	81	76	90	84	78	73	76	72	68	69	66	63	63	60	58
3	87	77	70	64	83	74	67	62	68	62	58	62	57	54	56	53	50
4	80	69	61	55	76	66	59	53	60	54	50	55	50	47	50	47	43
5	74	62	54	47	70	59	52	46	54	48	43	50	45	41	46	41	38
6	68	56	48	42	65	54	46	40	49	43	38	45	40	36	42	37	34
7	63	51	43	37	60	49	41	36	45	39	34	41	36	32	38	34	30
8	59	46	38	33	56	45	37	32	41	35	30	38	33	29	35	31	27
9	55	42	35	30	52	41	34	29	38	32	27	35	30	26	33	28	25
10	52	39	32	27	49	38	31	26	35	29	25	33	27	24	30	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17957	17957	17957
5°	17987	17322	17276
10°	17845	16671	16343
15°	17614	15866	15321
20°	17310	14990	14179
25°	16997	14081	13097
30°	16594	13112	11818
35°	16180	12162	10653
40°	15791	11130	9366
45°	15292	10120	8209
50°	14741	9043	7011
55°	14171	7889	5914
60°	13625	6705	4801
65°	12921	5491	3747
70°	12033	4151	2678
75°	10758	2811	2122
80°	9180	1953	1489
85°	6887	1055	780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15292 cd/sqm

TEST NUMBER: P1012184

CATALOG NUMBER: S123RDIP-B1000D365UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.8	3.1
10°-20°	436.3	8.7
20°-30°	628.2	12.5
30°-40°	707.4	14.1
40°-50°	676.7	13.5
50°-60°	553.9	11.0
60°-70°	373.5	7.4
70°-80°	187.3	3.7
80°-90°	49.9	1.0
90°-100°	29.1	0.6
100°-110°	88.2	1.8
110°-120°	150.1	3.0
120°-130°	197.5	3.9
130°-140°	222.0	4.4
140°-150°	218.2	4.3
150°-160°	183.7	3.7
160°-170°	122.3	2.4
170°-180°	42.8	0.9
0°-30°	1221.3	24.3
0°-40°	1928.7	38.4
0°-60°	3159.3	62.9
0°-90°	3770.0	75.0
90°-120°	267.5	5.3
90°-150°	905.2	18.0
90°-180°	1254.0	25.0
0°-180°	5024.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1668	1668	1668	1668	1668	
5°	1668	1662	1645	1658	1655	158
15°	1591	1576	1538	1532	1522	448
25°	1448	1414	1352	1323	1308	666
35°	1253	1204	1120	1062	1038	784
45°	1030	969	865	788	755	795
55°	782	716	601	522	495	701
65°	534	460	354	288	273	529
75°	283	218	143	130	127	301
85°	72	42	38	35	35	79
90°	0	4	8	10	11	6
95°	21	24	26	28	28	23
105°	80	81	84	84	85	86
115°	151	152	152	152	152	150
125°	221	222	222	220	219	197
135°	287	289	289	287	287	221
145°	348	349	350	350	348	217
155°	398	398	399	400	398	183
165°	434	433	433	435	433	122
175°	452	450	450	452	450	43
180°	453	453	453	453	453	

TEST NUMBER: P1012184

CATALOG NUMBER: S123RDIP-B1000D365UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1668.3	1668.3	1668.3	1668.3	1668.3
2.5°	1675.1	1669.7	1653.4	1668.3	1665.6
5°	1668.3	1661.5	1645.3	1657.5	1654.8
7.5°	1656.1	1649.4	1629.1	1637.2	1633.1
10°	1639.9	1630.4	1606.1	1607.4	1600.7
12.5°	1616.9	1606.1	1574.9	1573.6	1565.5
15°	1591.2	1576.3	1538.4	1531.6	1522.2
17.5°	1560.1	1543.8	1496.5	1482.9	1469.4
20°	1524.9	1503.2	1451.8	1434.2	1418.0
22.5°	1485.6	1459.9	1404.5	1381.5	1366.6
25°	1447.8	1413.9	1351.7	1323.3	1308.4
27.5°	1401.8	1365.2	1297.6	1259.7	1236.7
30°	1354.4	1313.8	1238.0	1192.0	1170.4
32.5°	1307.0	1259.7	1178.5	1127.1	1104.1
35°	1252.9	1204.2	1120.3	1062.1	1037.8
37.5°	1198.8	1146.0	1058.1	993.1	963.4
40°	1147.4	1087.8	991.8	921.4	890.3
42.5°	1089.2	1029.7	929.5	851.1	824.0
45°	1029.7	968.8	864.6	787.5	755.0
47.5°	971.5	903.8	801.0	717.1	688.7
50°	906.5	842.9	733.4	649.5	618.3
52.5°	848.4	778.0	669.8	581.8	554.7
55°	782.1	715.8	600.8	522.3	495.2
57.5°	722.5	650.8	534.5	460.0	437.0
60°	660.3	585.9	473.6	400.5	377.5
62.5°	598.0	523.6	411.3	343.7	319.3
65°	534.5	460.0	354.5	288.2	273.3
67.5°	470.9	395.1	292.3	242.2	226.0
70°	408.6	335.6	240.8	193.5	178.6
72.5°	346.4	274.7	190.8	154.2	150.2
75°	282.8	217.8	143.4	129.9	127.2
77.5°	224.6	165.1	112.3	104.2	101.5
80°	169.1	113.7	85.2	81.2	78.5
82.5°	116.4	70.4	60.9	56.8	56.8
85°	71.7	41.9	37.9	35.2	35.2
87.5°	32.5	17.6	17.6	16.2	14.9
90°	0.4	3.9	8.5	10.0	10.7
92.5°	10.7	12.8	14.9	16.0	15.3
95°	21.0	23.5	26.3	27.7	27.7
97.5°	34.5	36.3	38.4	40.2	39.8
100°	48.4	50.5	52.3	53.3	54.0
102.5°	64.4	65.4	67.9	69.0	68.6
105°	80.0	80.7	83.9	83.9	84.6
107.5°	98.5	98.8	100.3	101.3	101.0
110°	115.5	116.3	117.0	118.4	117.7



TEST NUMBER: P1012184

CATALOG NUMBER: S123RDIP-B1000D365UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	133.3	133.7	133.7	135.5	135.5
115°	151.1	152.2	151.5	151.8	151.5
117.5°	169.2	169.6	168.9	168.9	167.8
120°	185.9	188.1	186.3	185.9	185.2
122.5°	203.4	204.8	204.1	203.0	201.9
125°	221.1	222.2	221.5	220.1	218.7
127.5°	237.5	239.6	238.9	236.8	235.4
130°	253.8	256.7	255.6	254.2	251.7
132.5°	270.2	273.0	272.3	270.6	268.8
135°	286.9	289.0	288.7	287.3	286.6
137.5°	302.2	304.0	305.0	303.3	302.2
140°	318.2	320.0	320.3	320.0	317.5
142.5°	332.8	334.6	335.3	334.9	333.1
145°	348.1	348.8	349.8	349.5	348.1
147.5°	361.2	362.6	363.7	363.7	361.6
150°	375.1	375.8	376.5	376.5	374.4
152.5°	386.5	387.5	387.9	388.6	386.8
155°	398.5	398.5	398.9	400.3	397.8
157.5°	408.9	408.5	408.9	410.3	408.1
160°	418.5	417.7	417.7	419.5	418.1
162.5°	427.0	425.9	426.3	428.1	425.6
165°	434.1	433.0	433.0	435.2	432.7
167.5°	440.1	438.7	439.1	441.2	439.1
170°	445.1	443.7	443.7	446.2	443.7
172.5°	449.0	447.6	447.6	449.7	447.3
175°	451.5	450.1	450.1	452.2	449.7
177.5°	452.9	451.5	451.5	453.7	451.2
180°	452.6	452.6	452.6	452.6	452.6

(END OF REPORT)