

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012556

Luminaire Tested: S123RDIP-B560D1025UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012556
REPORT IS A COMBINATION OF REPORTS P993323 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D1025UB27-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5565.0 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012556

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012556

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	95	91	87	84	86	83	80	77	67	65	63	53	52	51	40	39	38
2	87	80	74	69	79	73	68	63	59	56	53	47	45	43	36	34	33
3	79	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	28
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	29	26	24
5	67	56	48	42	60	51	44	39	42	37	33	34	30	27	26	23	21
6	62	50	42	36	56	46	39	34	38	33	29	30	27	24	23	21	19
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	21	19	17
8	53	41	33	28	48	38	31	26	31	26	23	25	22	19	20	17	15
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10038	10038	10038
5°	10055	9684	9658
10°	9977	9319	9136
15°	9846	8869	8564
20°	9677	8380	7926
25°	9501	7871	7321
30°	9277	7330	6607
35°	9045	6799	5956
40°	8827	6221	5236
45°	8548	5657	4590
50°	8241	5055	3920
55°	7922	4409	3306
60°	7616	3748	2683
65°	7223	3070	2095
70°	6726	2320	1496
75°	6014	1572	1186
80°	5130	1093	833
85°	3852	590	437

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8548 cd/sqm

TEST NUMBER: P1012556

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	1.6
10°-20°	243.9	4.4
20°-30°	351.2	6.3
30°-40°	395.5	7.1
40°-50°	378.3	6.8
50°-60°	309.7	5.6
60°-70°	208.8	3.8
70°-80°	104.7	1.9
80°-90°	30.0	0.5
90°-100°	80.3	1.4
100°-110°	243.0	4.4
110°-120°	413.6	7.4
120°-130°	544.2	9.8
130°-140°	611.7	11.0
140°-150°	601.3	10.8
150°-160°	506.3	9.1
160°-170°	337.0	6.1
170°-180°	118.0	2.1
0°-30°	682.7	12.3
0°-40°	1078.2	19.4
0°-60°	1766.1	31.7
0°-90°	2109.6	37.9
90°-120°	736.9	13.2
90°-150°	2494.0	44.8
90°-180°	3455.0	62.1
0°-180°	5565.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	933	933	933	933	933	
5°	933	929	920	927	925	88
15°	890	881	860	856	851	251
25°	809	790	756	740	731	372
35°	700	673	626	594	580	438
45°	576	542	483	440	422	444
55°	437	400	336	292	277	392
65°	299	257	198	161	153	296
75°	158	122	80	73	71	168
85°	40	23	21	20	20	44
90°	1	11	24	27	29	7
95°	58	65	72	76	76	64
105°	220	222	231	231	233	236
115°	416	419	417	418	417	412
125°	609	612	610	606	602	543
135°	791	796	796	792	790	609
145°	959	961	964	963	959	599
155°	1098	1098	1099	1103	1096	506
165°	1196	1193	1193	1199	1192	337
175°	1244	1240	1240	1246	1239	118
180°	1247	1247	1247	1247	1247	

TEST NUMBER: P1012556

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	932.6	932.6	932.6	932.6	932.6
2.5°	936.4	933.4	924.3	932.6	931.1
5°	932.6	928.9	919.8	926.6	925.1
7.5°	925.8	922.1	910.7	915.2	913.0
10°	916.8	911.5	897.8	898.6	894.8
12.5°	903.9	897.8	880.4	879.7	875.2
15°	889.5	881.2	860.0	856.2	850.9
17.5°	872.1	863.1	836.6	829.0	821.4
20°	852.5	840.4	811.6	801.8	792.7
22.5°	830.5	816.2	785.1	772.3	764.0
25°	809.3	790.4	755.6	739.8	731.4
27.5°	783.6	763.2	725.4	704.2	691.3
30°	757.2	734.5	692.1	666.4	654.3
32.5°	730.7	704.2	658.8	630.1	617.2
35°	700.4	673.2	626.3	593.8	580.2
37.5°	670.2	640.7	591.5	555.2	538.6
40°	641.4	608.1	554.4	515.1	497.7
42.5°	608.9	575.6	519.6	475.8	460.6
45°	575.6	541.6	483.3	440.2	422.1
47.5°	543.1	505.3	447.8	400.9	385.0
50°	506.8	471.2	410.0	363.1	345.7
52.5°	474.3	434.9	374.4	325.3	310.1
55°	437.2	400.1	335.8	292.0	276.8
57.5°	403.9	363.8	298.8	257.2	244.3
60°	369.1	327.5	264.7	223.9	211.0
62.5°	334.3	292.7	229.9	192.1	178.5
65°	298.8	257.2	198.2	161.1	152.8
67.5°	263.2	220.9	163.4	135.4	126.3
70°	228.4	187.6	134.6	108.2	99.8
72.5°	193.6	153.5	106.7	86.2	84.0
75°	158.1	121.8	80.2	72.6	71.1
77.5°	125.6	92.3	62.8	58.2	56.7
80°	94.5	63.5	47.7	45.4	43.9
82.5°	65.1	39.3	34.0	31.8	31.8
85°	40.1	23.4	21.2	19.7	19.7
87.5°	18.2	9.8	9.8	9.1	8.3
90°	1.0	10.8	23.5	27.4	29.4
92.5°	29.4	35.3	41.1	44.1	42.1
95°	57.8	64.7	72.5	76.4	76.4
97.5°	95.0	99.9	105.8	110.7	109.7
100°	133.2	139.1	144.0	146.9	148.9
102.5°	177.3	180.2	187.1	190.0	189.1
105°	220.4	222.4	231.2	231.2	233.1
107.5°	271.4	272.3	276.3	279.2	278.2
110°	318.4	320.3	322.3	326.2	324.3

TEST NUMBER: P1012556

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	367.4	368.3	368.3	373.2	373.2
115°	416.3	419.3	417.3	418.3	417.3
117.5°	466.3	467.3	465.3	465.3	462.4
120°	512.3	518.2	513.3	512.3	510.4
122.5°	560.3	564.3	562.3	559.4	556.4
125°	609.3	612.3	610.3	606.4	602.5
127.5°	654.4	660.3	658.3	652.4	648.5
130°	699.4	707.3	704.3	700.4	693.6
132.5°	744.5	752.3	750.4	745.5	740.6
135°	790.6	796.4	795.5	791.5	789.6
137.5°	832.7	837.6	840.5	835.6	832.7
140°	876.8	881.7	882.6	881.7	874.8
142.5°	916.9	921.8	923.8	922.8	917.9
145°	959.0	961.0	963.9	963.0	959.0
147.5°	995.3	999.2	1002.2	1002.2	996.3
150°	1033.5	1035.5	1037.4	1037.4	1031.5
152.5°	1064.8	1067.8	1068.8	1070.7	1065.8
155°	1098.2	1098.2	1099.1	1103.1	1096.2
157.5°	1126.6	1125.6	1126.6	1130.5	1124.6
160°	1153.0	1151.1	1151.1	1156.0	1152.0
162.5°	1176.5	1173.6	1174.6	1179.5	1172.6
165°	1196.1	1193.2	1193.2	1199.1	1192.2
167.5°	1212.8	1208.9	1209.8	1215.7	1209.8
170°	1226.5	1222.6	1222.6	1229.4	1222.6
172.5°	1237.3	1233.3	1233.3	1239.2	1232.4
175°	1244.1	1240.2	1240.2	1246.1	1239.2
177.5°	1248.0	1244.1	1244.1	1250.0	1243.1
180°	1247.1	1247.1	1247.1	1247.1	1247.1

(END OF REPORT)