

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012190

Luminaire Tested: S123RDIP-B1000D365UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012190
REPORT IS A COMBINATION OF REPORTS P992825 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D365UB35-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5045.0 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012190

CATALOG NUMBER: S123RDIP-B1000D365UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012190

CATALOG NUMBER: S123RDIP-B1000D365UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79
1	104	100	96	92	99	95	92	88	86	84	81	78	76	74	71	69	68
2	95	88	81	76	90	84	78	73	76	72	68	69	66	63	63	60	58
3	87	77	70	64	83	74	67	62	68	62	58	62	57	54	56	53	50
4	80	69	61	55	76	66	59	53	60	54	50	55	50	47	50	47	43
5	74	62	54	47	70	59	52	46	54	48	43	50	45	41	46	41	38
6	68	56	48	42	65	54	46	40	49	43	38	45	40	36	42	37	34
7	63	51	43	37	60	49	41	36	45	39	34	41	36	32	38	34	30
8	59	46	38	33	56	45	37	32	41	35	30	38	33	29	35	31	27
9	55	42	35	30	52	41	34	29	38	32	27	35	30	26	33	28	25
10	52	39	32	27	49	38	31	26	35	29	25	33	27	24	30	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18034	18034	18034
5°	18063	17396	17349
10°	17922	16742	16411
15°	17688	15933	15385
20°	17384	15054	14239
25°	17069	14140	13153
30°	16664	13168	11868
35°	16249	12214	10698
40°	15859	11177	9406
45°	15356	10163	8244
50°	14804	9081	7042
55°	14231	7922	5939
60°	13683	6734	4821
65°	12974	5514	3763
70°	12086	4170	2690
75°	10803	2823	2130
80°	9218	1962	1494
85°	6916	1058	782

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15356 cd/sqm

TEST NUMBER: P1012190

CATALOG NUMBER: S123RDIP-B1000D365UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.5	3.1
10°-20°	438.1	8.7
20°-30°	630.8	12.5
30°-40°	710.4	14.1
40°-50°	679.5	13.5
50°-60°	556.3	11.0
60°-70°	375.0	7.4
70°-80°	188.1	3.7
80°-90°	50.1	1.0
90°-100°	29.3	0.6
100°-110°	88.5	1.8
110°-120°	150.7	3.0
120°-130°	198.3	3.9
130°-140°	222.9	4.4
140°-150°	219.1	4.3
150°-160°	184.5	3.7
160°-170°	122.8	2.4
170°-180°	43.0	0.9
0°-30°	1226.5	24.3
0°-40°	1936.9	38.4
0°-60°	3172.7	62.9
0°-90°	3786.0	75.0
90°-120°	268.5	5.3
90°-150°	908.8	18.0
90°-180°	1259.0	25.0
0°-180°	5045.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1675	1675	1675	1675	1675	
5°	1675	1669	1652	1664	1662	159
15°	1598	1583	1545	1538	1529	450
25°	1454	1420	1357	1329	1314	669
35°	1258	1209	1125	1067	1042	788
45°	1034	973	868	791	758	798
55°	785	719	603	524	497	704
65°	537	462	356	289	274	531
75°	284	219	144	130	128	303
85°	72	42	38	35	35	79
90°	0	4	9	10	11	6
95°	21	24	26	28	28	23
105°	80	81	84	84	85	86
115°	152	153	152	152	152	150
125°	222	223	222	221	220	198
135°	288	290	290	288	288	222
145°	350	350	351	351	350	218
155°	400	400	400	402	399	184
165°	436	435	435	437	434	123
175°	453	452	452	454	452	43
180°	454	454	454	454	454	

TEST NUMBER: P1012190

CATALOG NUMBER: S123RDIP-B1000D365UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1675.4	1675.4	1675.4	1675.4	1675.4
2.5°	1682.2	1676.7	1660.4	1675.4	1672.7
5°	1675.4	1668.6	1652.3	1664.5	1661.8
7.5°	1663.2	1656.4	1636.0	1644.1	1640.1
10°	1646.9	1637.3	1612.9	1614.2	1607.4
12.5°	1623.8	1612.9	1581.6	1580.3	1572.1
15°	1597.9	1583.0	1544.9	1538.2	1528.6
17.5°	1566.7	1550.4	1502.8	1489.2	1475.6
20°	1531.4	1509.6	1458.0	1440.3	1424.0
22.5°	1492.0	1466.1	1410.4	1387.3	1372.4
25°	1453.9	1419.9	1357.4	1328.9	1314.0
27.5°	1407.7	1371.0	1303.1	1265.0	1241.9
30°	1360.1	1319.4	1243.3	1197.1	1175.4
32.5°	1312.6	1265.0	1183.5	1131.9	1108.8
35°	1258.2	1209.3	1125.1	1066.7	1042.2
37.5°	1203.9	1150.9	1062.6	997.4	967.5
40°	1152.3	1092.5	996.0	925.3	894.1
42.5°	1093.8	1034.0	933.5	854.7	827.5
45°	1034.0	972.9	868.3	790.8	758.2
47.5°	975.6	907.7	804.4	720.2	691.6
50°	910.4	846.5	736.5	652.2	621.0
52.5°	852.0	781.3	672.6	584.3	557.1
55°	785.4	718.8	603.3	524.5	497.3
57.5°	725.6	653.6	536.7	462.0	438.9
60°	663.1	588.4	475.6	402.2	379.1
62.5°	600.6	525.9	413.1	345.1	320.7
65°	536.7	462.0	356.0	289.4	274.5
67.5°	472.9	396.8	293.5	243.2	226.9
70°	410.4	337.0	241.9	194.3	179.4
72.5°	347.9	275.8	191.6	154.9	150.8
75°	284.0	218.8	144.0	130.4	127.7
77.5°	225.6	165.8	112.8	104.6	101.9
80°	169.8	114.1	85.6	81.5	78.8
82.5°	116.9	70.7	61.1	57.1	57.1
85°	72.0	42.1	38.0	35.3	35.3
87.5°	32.6	17.7	17.7	16.3	14.9
90°	0.4	3.9	8.6	10.0	10.7
92.5°	10.7	12.9	15.0	16.1	15.3
95°	21.1	23.6	26.4	27.8	27.8
97.5°	34.6	36.4	38.6	40.3	40.0
100°	48.5	50.7	52.5	53.5	54.3
102.5°	64.6	65.7	68.2	69.2	68.9
105°	80.3	81.0	84.2	84.2	85.0
107.5°	98.9	99.2	100.7	101.7	101.4
110°	116.0	116.7	117.4	118.9	118.1

TEST NUMBER: P1012190

CATALOG NUMBER: S123RDIP-B1000D365UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	133.9	134.2	134.2	136.0	136.0
115°	151.7	152.8	152.1	152.4	152.1
117.5°	169.9	170.3	169.5	169.5	168.5
120°	186.7	188.8	187.0	186.7	186.0
122.5°	204.2	205.6	204.9	203.8	202.7
125°	222.0	223.1	222.4	220.9	219.5
127.5°	238.4	240.6	239.9	237.7	236.3
130°	254.9	257.7	256.6	255.2	252.7
132.5°	271.3	274.1	273.4	271.6	269.9
135°	288.1	290.2	289.8	288.4	287.7
137.5°	303.4	305.2	306.3	304.5	303.4
140°	319.5	321.3	321.6	321.3	318.8
142.5°	334.1	335.9	336.6	336.2	334.5
145°	349.5	350.2	351.2	350.9	349.5
147.5°	362.7	364.1	365.2	365.2	363.0
150°	376.6	377.3	378.0	378.0	375.9
152.5°	388.0	389.1	389.4	390.1	388.4
155°	400.1	400.1	400.5	401.9	399.4
157.5°	410.5	410.1	410.5	411.9	409.8
160°	420.1	419.4	419.4	421.2	419.8
162.5°	428.7	427.6	428.0	429.8	427.3
165°	435.8	434.8	434.8	436.9	434.4
167.5°	441.9	440.5	440.8	443.0	440.8
170°	446.9	445.5	445.5	448.0	445.5
172.5°	450.8	449.4	449.4	451.5	449.0
175°	453.3	451.9	451.9	454.0	451.5
177.5°	454.7	453.3	453.3	455.5	453.0
180°	454.4	454.4	454.4	454.4	454.4

(END OF REPORT)