

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012563

Luminaire Tested: S123RDIP-B560D1025UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012563
REPORT IS A COMBINATION OF REPORTS P993340 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D1025UB30-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5808.5 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012563

CATALOG NUMBER: S123RDIP-B560D1025UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012563

CATALOG NUMBER: S123RDIP-B560D1025UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	91	87	84	86	83	79	77	67	65	63	52	51	50	39	38	37
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	35	33	32
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	27
4	73	62	55	49	65	57	50	45	46	42	38	37	33	31	28	26	24
5	67	55	48	42	60	51	44	39	41	36	33	33	29	27	25	23	21
6	61	50	42	36	55	45	39	34	37	32	28	30	26	23	23	20	18
7	57	45	37	32	51	41	34	29	34	29	25	27	23	21	21	18	16
8	53	41	33	28	48	37	31	26	31	26	22	25	21	18	19	17	15
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10125	10125	10125
5°	10141	9766	9740
10°	10061	9399	9214
15°	9930	8946	8638
20°	9759	8451	7994
25°	9583	7939	7384
30°	9356	7393	6663
35°	9123	6857	6006
40°	8903	6275	5281
45°	8621	5706	4629
50°	8311	5098	3953
55°	7989	4447	3335
60°	7682	3780	2706
65°	7284	3096	2113
70°	6785	2341	1510
75°	6063	1586	1196
80°	5179	1103	838
85°	3881	596	439

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8621 cd/sqm

TEST NUMBER: P1012563

CATALOG NUMBER: S123RDIP-B560D1025UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.4	1.5
10°-20°	246.0	4.2
20°-30°	354.2	6.1
30°-40°	398.8	6.9
40°-50°	381.5	6.6
50°-60°	312.3	5.4
60°-70°	210.6	3.6
70°-80°	105.6	1.8
80°-90°	30.3	0.5
90°-100°	277.4	4.8
100°-110°	775.4	13.3
110°-120°	756.1	13.0
120°-130°	602.1	10.4
130°-140°	475.2	8.2
140°-150°	354.6	6.1
150°-160°	247.4	4.3
160°-170°	145.3	2.5
170°-180°	47.3	0.8
0°-30°	688.6	11.9
0°-40°	1087.4	18.7
0°-60°	1781.2	30.7
0°-90°	2127.7	36.6
90°-120°	1809.0	31.1
90°-150°	3240.9	55.8
90°-180°	3681.0	63.4
0°-180°	5808.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	941	941	941	941	941	
5°	941	937	928	934	933	89
15°	897	889	867	864	858	253
25°	816	797	762	746	738	375
35°	706	679	632	599	585	442
45°	580	546	488	444	426	448
55°	441	404	339	294	279	395
65°	301	259	200	162	154	298
75°	159	123	81	73	72	170
85°	40	24	21	20	20	44
90°	2	12	25	28	29	5
95°	34	109	586	171	115	36
105°	115	170	795	1389	1257	122
115°	203	252	608	1333	1529	201
125°	282	332	567	1028	1206	250
135°	330	394	559	846	977	255
145°	376	431	552	694	764	236
155°	428	462	535	608	634	197
165°	467	481	512	543	552	132
175°	487	488	491	498	497	46
180°	488	488	488	488	488	

TEST NUMBER: P1012563

CATALOG NUMBER: S123RDIP-B560D1025UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	940.6	940.6	940.6	940.6	940.6
2.5°	944.4	941.4	932.2	940.6	939.1
5°	940.6	936.8	927.6	934.5	933.0
7.5°	933.7	929.9	918.5	923.1	920.8
10°	924.6	919.2	905.5	906.3	902.5
12.5°	911.6	905.5	888.0	887.2	882.6
15°	897.1	888.7	867.4	863.6	858.2
17.5°	879.6	870.4	843.7	836.1	828.5
20°	859.7	847.5	818.5	808.6	799.5
22.5°	837.6	823.1	791.8	778.9	770.5
25°	816.3	797.2	762.1	746.1	737.7
27.5°	790.3	769.7	731.6	710.2	697.3
30°	763.6	740.7	698.0	672.1	659.9
32.5°	736.9	710.2	664.5	635.5	622.5
35°	706.4	678.9	631.6	598.8	585.1
37.5°	675.9	646.1	596.6	559.9	543.2
40°	646.9	613.3	559.2	519.5	502.0
42.5°	614.1	580.5	524.1	479.8	464.6
45°	580.5	546.2	487.5	444.0	425.7
47.5°	547.7	509.6	451.6	404.3	388.3
50°	511.1	475.3	413.5	366.2	348.6
52.5°	478.3	438.6	377.6	328.0	312.8
55°	440.9	403.6	338.7	294.5	279.2
57.5°	407.4	366.9	301.3	259.4	246.4
60°	372.3	330.3	267.0	225.8	212.8
62.5°	337.2	295.2	231.9	193.8	180.0
65°	301.3	259.4	199.9	162.5	154.1
67.5°	265.5	222.8	164.8	136.6	127.4
70°	230.4	189.2	135.8	109.1	100.7
72.5°	195.3	154.9	107.6	87.0	84.7
75°	159.4	122.8	80.9	73.2	71.7
77.5°	126.6	93.1	63.3	58.7	57.2
80°	95.4	64.1	48.1	45.8	44.2
82.5°	65.6	39.7	34.3	32.0	32.0
85°	40.4	23.6	21.4	19.8	19.8
87.5°	18.3	9.9	9.9	9.2	8.4
90°	2.0	11.9	24.7	27.7	28.7
92.5°	14.8	59.3	183.8	62.8	52.4
95°	33.6	109.2	586.0	171.0	114.6
97.5°	53.4	125.0	901.3	429.9	235.2
100°	73.1	137.8	935.9	899.4	619.6
102.5°	93.9	152.7	871.6	1204.2	981.3
105°	114.6	169.5	794.6	1389.4	1257.1
107.5°	136.4	189.2	726.4	1471.1	1436.9
110°	160.1	209.5	670.0	1473.5	1539.7

TEST NUMBER: P1012563

CATALOG NUMBER: S123RDIP-B560D1025UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	181.8	230.8	632.5	1417.6	1560.5
115°	202.6	252.5	607.8	1332.6	1528.8
117.5°	223.3	273.2	591.0	1241.8	1459.7
120°	245.1	294.0	580.1	1155.8	1368.7
122.5°	263.9	313.8	573.2	1088.0	1283.8
125°	281.7	332.5	567.3	1027.8	1205.7
127.5°	295.5	350.4	564.3	978.4	1138.5
130°	308.3	366.2	561.3	932.9	1083.1
132.5°	318.2	380.5	560.3	890.4	1028.8
135°	330.1	393.8	559.4	846.4	977.4
137.5°	341.0	404.6	557.4	804.9	923.0
140°	351.8	414.6	556.4	764.4	865.7
142.5°	363.7	423.4	554.4	727.4	812.4
145°	376.5	431.4	552.4	694.2	763.9
147.5°	389.4	439.8	549.5	668.6	722.4
150°	402.2	446.7	545.5	645.8	686.8
152.5°	415.1	454.1	540.6	626.1	657.2
155°	427.9	461.5	534.6	607.8	633.5
157.5°	437.8	468.0	529.7	590.0	610.7
160°	449.7	473.4	523.8	573.7	589.0
162.5°	458.6	477.4	517.8	558.3	569.2
165°	467.4	480.8	511.9	543.0	552.4
167.5°	474.4	483.8	506.0	529.7	535.6
170°	480.3	485.2	500.1	517.8	520.8
172.5°	484.2	486.7	495.1	507.5	507.0
175°	487.2	487.7	491.2	498.1	497.1
177.5°	489.2	488.2	488.2	492.2	490.2
180°	488.2	488.2	488.2	488.2	488.2

(END OF REPORT)