

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012568

Luminaire Tested: S123RDIP-B560D1025UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012568
REPORT IS A COMBINATION OF REPORTS P993345 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D1025UB35-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5637.0 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012568

CATALOG NUMBER: S123RDIP-B560D1025UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012568

CATALOG NUMBER: S123RDIP-B560D1025UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38		
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32		
2	87	80	74	69	79	73	68	63	59	56	53	47	45	43	36	34	33	28		
3	79	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	28	24		
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	29	26	24	20		
5	67	56	48	42	60	51	44	39	42	37	33	34	30	27	26	23	21	18		
6	62	50	42	36	56	46	39	34	38	33	29	30	27	24	23	21	19	16		
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	21	19	17	14		
8	53	41	33	28	48	38	31	26	31	26	23	25	22	19	20	17	15	13		
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14	11		
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10168	10168	10168
5°	10184	9808	9781
10°	10104	9440	9253
15°	9972	8983	8675
20°	9801	8487	8028
25°	9623	7972	7415
30°	9396	7425	6691
35°	9161	6886	6032
40°	8940	6301	5303
45°	8658	5730	4648
50°	8347	5119	3970
55°	8023	4466	3349
60°	7715	3796	2718
65°	7315	3108	2122
70°	6814	2351	1516
75°	6090	1592	1201
80°	5201	1107	842
85°	3900	599	441

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8658 cd/sqm

TEST NUMBER: P1012568

CATALOG NUMBER: S123RDIP-B560D1025UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.8	1.6
10°-20°	247.0	4.4
20°-30°	355.7	6.3
30°-40°	400.5	7.1
40°-50°	383.1	6.8
50°-60°	313.6	5.6
60°-70°	211.5	3.8
70°-80°	106.1	1.9
80°-90°	30.4	0.5
90°-100°	81.3	1.4
100°-110°	246.1	4.4
110°-120°	419.0	7.4
120°-130°	551.2	9.8
130°-140°	619.6	11.0
140°-150°	609.2	10.8
150°-160°	512.8	9.1
160°-170°	341.4	6.1
170°-180°	119.6	2.1
0°-30°	691.5	12.3
0°-40°	1092.0	19.4
0°-60°	1788.8	31.7
0°-90°	2136.7	37.9
90°-120°	746.5	13.2
90°-150°	2526.5	44.8
90°-180°	3500.0	62.1
0°-180°	5637.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	945	945	945	945	945	
5°	945	941	932	938	937	90
15°	901	892	871	867	862	254
25°	820	801	765	749	741	377
35°	709	682	634	601	588	444
45°	583	548	490	446	428	450
55°	443	405	340	296	280	397
65°	303	260	201	163	155	299
75°	160	123	81	74	72	171
85°	41	24	22	20	20	44
90°	1	11	24	28	30	7
95°	58	66	73	77	77	65
105°	223	225	234	234	236	239
115°	422	425	423	424	423	417
125°	617	620	618	614	610	550
135°	801	807	806	802	800	617
145°	972	974	976	976	972	607
155°	1112	1112	1113	1117	1110	512
165°	1212	1209	1209	1215	1208	342
175°	1260	1256	1256	1262	1255	120
180°	1263	1263	1263	1263	1263	

TEST NUMBER: P1012568

CATALOG NUMBER: S123RDIP-B560D1025UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	944.6	944.6	944.6	944.6	944.6
2.5°	948.4	945.4	936.2	944.6	943.1
5°	944.6	940.8	931.6	938.5	936.9
7.5°	937.7	933.9	922.4	927.0	924.7
10°	928.5	923.1	909.4	910.1	906.3
12.5°	915.5	909.4	891.7	891.0	886.4
15°	900.9	892.5	871.0	867.2	861.9
17.5°	883.3	874.1	847.3	839.6	832.0
20°	863.4	851.1	822.0	812.1	802.9
22.5°	841.2	826.6	795.2	782.2	773.8
25°	819.7	800.6	765.3	749.2	740.8
27.5°	793.7	773.0	734.7	713.2	700.2
30°	766.9	743.9	701.0	674.9	662.7
32.5°	740.0	713.2	667.3	638.2	625.1
35°	709.4	681.8	634.3	601.4	587.6
37.5°	678.8	648.9	599.1	562.3	545.5
40°	649.6	615.9	561.5	521.7	504.1
42.5°	616.7	583.0	526.3	481.9	466.6
45°	583.0	548.5	489.5	445.9	427.5
47.5°	550.1	511.7	453.5	406.0	389.9
50°	513.3	477.3	415.2	367.7	350.1
52.5°	480.3	440.5	379.2	329.4	314.1
55°	442.8	405.3	340.1	295.7	280.4
57.5°	409.1	368.5	302.6	260.5	247.4
60°	373.9	331.7	268.1	226.8	213.7
62.5°	338.6	296.5	232.9	194.6	180.8
65°	302.6	260.5	200.7	163.2	154.8
67.5°	266.6	223.7	165.5	137.1	127.9
70°	231.4	190.0	136.4	109.6	101.1
72.5°	196.1	155.5	108.0	87.3	85.0
75°	160.1	123.3	81.2	73.5	72.0
77.5°	127.2	93.5	63.6	59.0	57.5
80°	95.8	64.4	48.3	46.0	44.4
82.5°	65.9	39.8	34.5	32.2	32.2
85°	40.6	23.7	21.5	19.9	19.9
87.5°	18.4	10.0	10.0	9.2	8.4
90°	1.0	10.9	23.8	27.8	29.8
92.5°	29.8	35.7	41.7	44.7	42.7
95°	58.5	65.5	73.4	77.4	77.4
97.5°	96.3	101.2	107.2	112.1	111.1
100°	135.0	140.9	145.9	148.9	150.8
102.5°	179.6	182.6	189.5	192.5	191.5
105°	223.3	225.3	234.2	234.2	236.2
107.5°	274.9	275.9	279.8	282.8	281.8
110°	322.5	324.5	326.5	330.5	328.5

TEST NUMBER: P1012568

CATALOG NUMBER: S123RDIP-B560D1025UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	372.1	373.1	373.1	378.1	378.1
115°	421.8	424.7	422.7	423.7	422.7
117.5°	472.4	473.4	471.4	471.4	468.4
120°	519.0	525.0	520.0	519.0	517.0
122.5°	567.6	571.6	569.6	566.6	563.7
125°	617.3	620.2	618.2	614.3	610.3
127.5°	662.9	668.9	666.9	660.9	656.9
130°	708.6	716.5	713.5	709.5	702.6
132.5°	754.2	762.1	760.2	755.2	750.2
135°	800.8	806.8	805.8	801.8	799.8
137.5°	843.5	848.5	851.5	846.5	843.5
140°	888.2	893.1	894.1	893.1	886.2
142.5°	928.9	933.8	935.8	934.8	929.8
145°	971.5	973.5	976.5	975.5	971.5
147.5°	1008.2	1012.2	1015.2	1015.2	1009.2
150°	1046.9	1048.9	1050.9	1050.9	1045.0
152.5°	1078.7	1081.7	1082.7	1084.7	1079.7
155°	1112.4	1112.4	1113.4	1117.4	1110.5
157.5°	1141.2	1140.2	1141.2	1145.2	1139.2
160°	1168.0	1166.0	1166.0	1171.0	1167.0
162.5°	1191.8	1188.9	1189.8	1194.8	1187.9
165°	1211.7	1208.7	1208.7	1214.7	1207.7
167.5°	1228.6	1224.6	1225.6	1231.5	1225.6
170°	1242.4	1238.5	1238.5	1245.4	1238.5
172.5°	1253.4	1249.4	1249.4	1255.3	1248.4
175°	1260.3	1256.3	1256.3	1262.3	1255.3
177.5°	1264.3	1260.3	1260.3	1266.3	1259.3
180°	1263.3	1263.3	1263.3	1263.3	1263.3

(END OF REPORT)