

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012224

Luminaire Tested: S123RDIP-B1000D585UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012224
REPORT IS A COMBINATION OF REPORTS P992871 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D585UB40-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5753.0 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012224

CATALOG NUMBER: S123RDIP-B1000D585UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012224

CATALOG NUMBER: S123RDIP-B1000D585UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70
1	102	97	94	90	95	92	88	85	81	79	76	72	70	68	63	61	60
2	93	86	79	74	87	81	75	71	72	68	64	63	60	57	56	53	51
3	85	76	68	62	80	71	65	60	64	58	54	56	52	49	50	47	44
4	78	67	59	53	73	64	57	51	57	51	47	51	46	42	45	41	38
5	72	60	52	46	67	57	50	44	51	45	41	46	41	37	40	37	34
6	66	54	46	40	62	51	44	39	46	40	36	41	36	33	37	33	30
7	62	49	41	36	58	47	39	34	42	36	32	38	33	29	34	30	27
8	57	45	37	32	54	43	36	31	39	33	28	35	30	26	31	27	24
9	53	41	34	28	50	39	32	27	35	30	26	32	27	24	29	25	22
10	50	38	31	26	47	36	29	25	33	27	23	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17853	17853	17853
5°	17882	17221	17174
10°	17741	16574	16247
15°	17511	15773	15231
20°	17209	14903	14096
25°	16897	13998	13021
30°	16498	13036	11749
35°	16086	12091	10591
40°	15699	11064	9311
45°	15203	10060	8161
50°	14655	8990	6971
55°	14088	7842	5880
60°	13544	6666	4773
65°	12843	5458	3725
70°	11962	4127	2663
75°	10693	2795	2109
80°	9126	1941	1479
85°	6849	1050	776

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15203 cd/sqm

TEST NUMBER: P1012224

CATALOG NUMBER: S123RDIP-B1000D585UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.9	2.7
10°-20°	433.7	7.5
20°-30°	624.5	10.9
30°-40°	703.3	12.2
40°-50°	672.7	11.7
50°-60°	550.7	9.6
60°-70°	371.3	6.5
70°-80°	186.2	3.2
80°-90°	50.2	0.9
90°-100°	46.6	0.8
100°-110°	141.0	2.5
110°-120°	240.0	4.2
120°-130°	315.7	5.5
130°-140°	354.8	6.2
140°-150°	348.8	6.1
150°-160°	293.7	5.1
160°-170°	195.5	3.4
170°-180°	68.5	1.2
0°-30°	1214.2	21.1
0°-40°	1917.4	33.3
0°-60°	3140.8	54.6
0°-90°	3748.5	65.2
90°-120°	427.5	7.4
90°-150°	1446.8	25.1
90°-180°	2004.0	34.8
0°-180°	5753.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1659	1659	1659	1659	1659	
5°	1659	1652	1636	1648	1645	157
15°	1582	1567	1529	1523	1513	446
25°	1439	1406	1344	1316	1301	662
35°	1246	1197	1114	1056	1032	780
45°	1024	963	860	783	751	790
55°	778	712	597	519	492	697
65°	531	457	352	286	272	526
75°	281	217	143	129	126	300
85°	71	42	38	35	35	78
90°	1	6	14	16	17	7
95°	34	38	42	44	44	37
105°	128	129	134	134	135	137
115°	242	243	242	243	242	239
125°	354	355	354	352	350	315
135°	459	462	461	459	458	353
145°	556	558	559	559	556	347
155°	637	637	638	640	636	293
165°	694	692	692	696	692	196
175°	722	719	719	723	719	69
180°	723	723	723	723	723	

TEST NUMBER: P1012224

CATALOG NUMBER: S123RDIP-B1000D585UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1658.6	1658.6	1658.6	1658.6	1658.6
2.5°	1665.3	1659.9	1643.8	1658.6	1655.9
5°	1658.6	1651.8	1635.7	1647.8	1645.1
7.5°	1646.5	1639.7	1619.6	1627.6	1623.6
10°	1630.3	1620.9	1596.7	1598.0	1591.3
12.5°	1607.5	1596.7	1565.8	1564.4	1556.3
15°	1581.9	1567.1	1529.4	1522.7	1513.3
17.5°	1551.0	1534.8	1487.7	1474.3	1460.8
20°	1516.0	1494.5	1443.3	1425.9	1409.7
22.5°	1477.0	1451.4	1396.3	1373.4	1358.6
25°	1439.3	1405.7	1343.8	1315.6	1300.8
27.5°	1393.6	1357.3	1290.0	1252.3	1229.5
30°	1346.5	1306.1	1230.8	1185.1	1163.6
32.5°	1299.4	1252.3	1171.6	1120.5	1097.6
35°	1245.6	1197.2	1113.8	1055.9	1031.7
37.5°	1191.8	1139.3	1051.9	987.3	957.7
40°	1140.7	1081.5	986.0	916.0	885.1
42.5°	1082.8	1023.7	924.1	846.1	819.2
45°	1023.7	963.1	859.5	782.9	750.6
47.5°	965.8	898.6	796.3	712.9	684.7
50°	901.2	838.0	729.1	645.7	614.7
52.5°	843.4	773.5	665.8	578.4	551.5
55°	777.5	711.6	597.2	519.2	492.3
57.5°	718.3	647.0	531.3	457.4	434.5
60°	656.4	582.4	470.8	398.2	375.3
62.5°	594.6	520.6	408.9	341.7	317.5
65°	531.3	457.4	352.4	286.5	271.7
67.5°	468.1	392.8	290.6	240.8	224.6
70°	406.2	333.6	239.4	192.4	177.6
72.5°	344.4	273.1	189.7	153.3	149.3
75°	281.1	216.6	142.6	129.1	126.4
77.5°	223.3	164.1	111.6	103.6	100.9
80°	168.1	113.0	84.7	80.7	78.0
82.5°	115.7	69.9	60.5	56.5	56.5
85°	71.3	41.7	37.7	35.0	35.0
87.5°	32.3	17.5	17.5	16.1	14.8
90°	0.6	6.3	13.6	15.9	17.0
92.5°	17.0	20.5	23.9	25.6	24.4
95°	33.5	37.5	42.1	44.3	44.3
97.5°	55.1	58.0	61.4	64.2	63.6
100°	77.3	80.7	83.5	85.2	86.4
102.5°	102.9	104.6	108.5	110.2	109.7
105°	127.9	129.0	134.1	134.1	135.3
107.5°	157.4	158.0	160.3	162.0	161.4
110°	184.7	185.8	187.0	189.2	188.1



TEST NUMBER: P1012224

CATALOG NUMBER: S123RDIP-B1000D585UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	213.1	213.7	213.7	216.5	216.5
115°	241.5	243.2	242.1	242.7	242.1
117.5°	270.5	271.1	269.9	269.9	268.2
120°	297.2	300.6	297.8	297.2	296.1
122.5°	325.1	327.3	326.2	324.5	322.8
125°	353.5	355.2	354.0	351.8	349.5
127.5°	379.6	383.0	381.9	378.5	376.2
130°	405.8	410.3	408.6	406.3	402.3
132.5°	431.9	436.4	435.3	432.5	429.6
135°	458.6	462.0	461.4	459.2	458.0
137.5°	483.0	485.9	487.6	484.7	483.0
140°	508.6	511.5	512.0	511.5	507.5
142.5°	531.9	534.8	535.9	535.3	532.5
145°	556.3	557.5	559.2	558.6	556.3
147.5°	577.4	579.6	581.4	581.4	577.9
150°	599.5	600.7	601.8	601.8	598.4
152.5°	617.7	619.4	620.0	621.1	618.3
155°	637.0	637.0	637.6	639.9	635.9
157.5°	653.5	653.0	653.5	655.8	652.4
160°	668.9	667.7	667.7	670.6	668.3
162.5°	682.5	680.8	681.4	684.2	680.2
165°	693.9	692.2	692.2	695.6	691.6
167.5°	703.5	701.3	701.8	705.2	701.8
170°	711.5	709.2	709.2	713.2	709.2
172.5°	717.7	715.5	715.5	718.9	714.9
175°	721.7	719.4	719.4	722.9	718.9
177.5°	724.0	721.7	721.7	725.1	721.1
180°	723.4	723.4	723.4	723.4	723.4

(END OF REPORT)