

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012587

Luminaire Tested: S123RDIP-B560D1195UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012587
REPORT IS A COMBINATION OF REPORTS P993364 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D1195UB27-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6397.9 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012587

CATALOG NUMBER: S123RDIP-B560D1195UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012587

CATALOG NUMBER: S123RDIP-B560D1195UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	35
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	29
3	78	69	62	57	70	63	57	52	51	46	43	39	36	34	29	27	25
4	72	61	54	48	64	56	49	44	45	40	37	35	32	29	26	24	22
5	66	55	47	41	59	50	43	38	40	35	32	31	28	25	23	21	19
6	61	49	41	36	55	45	38	33	36	31	28	28	25	22	21	19	17
7	56	44	37	31	50	40	34	29	33	28	24	26	22	20	19	17	15
8	52	40	33	28	47	37	30	25	30	25	21	24	20	17	18	15	14
9	48	37	29	24	44	33	27	23	27	23	19	22	18	16	16	14	12
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10038	10038	10038
5°	10055	9684	9658
10°	9977	9319	9136
15°	9846	8869	8564
20°	9677	8380	7926
25°	9501	7871	7321
30°	9277	7330	6607
35°	9045	6799	5956
40°	8827	6221	5236
45°	8548	5657	4590
50°	8241	5055	3920
55°	7922	4409	3306
60°	7616	3748	2683
65°	7223	3070	2095
70°	6726	2320	1496
75°	6014	1572	1186
80°	5130	1093	833
85°	3852	590	437

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8548 cd/sqm

TEST NUMBER: P1012587

CATALOG NUMBER: S123RDIP-B560D1195UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	1.4
10°-20°	243.9	3.8
20°-30°	351.2	5.5
30°-40°	395.5	6.2
40°-50°	378.3	5.9
50°-60°	309.7	4.8
60°-70°	208.8	3.3
70°-80°	104.7	1.6
80°-90°	30.6	0.5
90°-100°	323.2	5.1
100°-110°	903.3	14.1
110°-120°	880.8	13.8
120°-130°	701.4	11.0
130°-140°	553.6	8.7
140°-150°	413.0	6.5
150°-160°	288.1	4.5
160°-170°	169.3	2.6
170°-180°	55.1	0.9
0°-30°	682.7	10.7
0°-40°	1078.2	16.9
0°-60°	1766.1	27.6
0°-90°	2110.2	33.0
90°-120°	2107.3	32.9
90°-150°	3775.3	59.0
90°-180°	4288.0	67.0
0°-180°	6397.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	933	933	933	933	933	
5°	933	929	920	927	925	88
15°	890	881	860	856	851	251
25°	809	790	756	740	731	372
35°	700	673	626	594	580	438
45°	576	542	483	440	422	444
55°	437	400	336	292	277	392
65°	299	257	198	161	153	296
75°	158	122	80	73	71	168
85°	40	23	21	20	20	44
90°	2	14	29	32	33	5
95°	39	127	683	199	134	41
105°	134	197	926	1619	1464	142
115°	236	294	708	1552	1781	234
125°	328	387	661	1197	1404	291
135°	384	459	652	986	1139	297
145°	439	502	644	809	890	275
155°	498	538	623	708	738	229
165°	544	560	596	633	644	153
175°	568	568	572	580	579	54
180°	569	569	569	569	569	

TEST NUMBER: P1012587

CATALOG NUMBER: S123RDIP-B560D1195UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	932.6	932.6	932.6	932.6	932.6
2.5°	936.4	933.4	924.3	932.6	931.1
5°	932.6	928.9	919.8	926.6	925.1
7.5°	925.8	922.1	910.7	915.2	913.0
10°	916.8	911.5	897.8	898.6	894.8
12.5°	903.9	897.8	880.4	879.7	875.2
15°	889.5	881.2	860.0	856.2	850.9
17.5°	872.1	863.1	836.6	829.0	821.4
20°	852.5	840.4	811.6	801.8	792.7
22.5°	830.5	816.2	785.1	772.3	764.0
25°	809.3	790.4	755.6	739.8	731.4
27.5°	783.6	763.2	725.4	704.2	691.3
30°	757.2	734.5	692.1	666.4	654.3
32.5°	730.7	704.2	658.8	630.1	617.2
35°	700.4	673.2	626.3	593.8	580.2
37.5°	670.2	640.7	591.5	555.2	538.6
40°	641.4	608.1	554.4	515.1	497.7
42.5°	608.9	575.6	519.6	475.8	460.6
45°	575.6	541.6	483.3	440.2	422.1
47.5°	543.1	505.3	447.8	400.9	385.0
50°	506.8	471.2	410.0	363.1	345.7
52.5°	474.3	434.9	374.4	325.3	310.1
55°	437.2	400.1	335.8	292.0	276.8
57.5°	403.9	363.8	298.8	257.2	244.3
60°	369.1	327.5	264.7	223.9	211.0
62.5°	334.3	292.7	229.9	192.1	178.5
65°	298.8	257.2	198.2	161.1	152.8
67.5°	263.2	220.9	163.4	135.4	126.3
70°	228.4	187.6	134.6	108.2	99.8
72.5°	193.6	153.5	106.7	86.2	84.0
75°	158.1	121.8	80.2	72.6	71.1
77.5°	125.6	92.3	62.8	58.2	56.7
80°	94.5	63.5	47.7	45.4	43.9
82.5°	65.1	39.3	34.0	31.8	31.8
85°	40.1	23.4	21.2	19.7	19.7
87.5°	18.2	9.8	9.8	9.1	8.3
90°	2.3	13.8	28.8	32.2	33.4
92.5°	17.3	69.1	214.1	73.1	61.0
95°	39.1	127.2	682.7	199.2	133.5
97.5°	62.2	145.6	1049.9	500.8	274.0
100°	85.2	160.6	1090.2	1047.6	721.8
102.5°	109.4	177.8	1015.4	1402.8	1143.2
105°	133.5	197.4	925.6	1618.6	1464.4
107.5°	158.9	220.5	846.1	1713.6	1673.9
110°	186.5	244.0	780.5	1716.5	1793.6

TEST NUMBER: P1012587

CATALOG NUMBER: S123RDIP-B560D1195UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	211.8	268.8	736.8	1651.4	1817.8
115°	236.0	294.2	708.0	1552.4	1780.9
117.5°	260.2	318.3	688.4	1446.6	1700.4
120°	285.5	342.5	675.8	1346.4	1594.4
122.5°	307.4	365.6	667.7	1267.5	1495.4
125°	328.1	387.4	660.8	1197.2	1404.5
127.5°	344.2	408.2	657.3	1139.7	1326.2
130°	359.2	426.6	653.9	1086.8	1261.7
132.5°	370.7	443.2	652.7	1037.2	1198.4
135°	384.5	458.8	651.6	986.0	1138.6
137.5°	397.2	471.4	649.3	937.6	1075.2
140°	409.8	482.9	648.1	890.4	1008.5
142.5°	423.7	493.3	645.8	847.3	946.3
145°	438.6	502.5	643.5	808.7	889.9
147.5°	453.6	512.3	640.1	778.8	841.5
150°	468.5	520.4	635.5	752.3	800.1
152.5°	483.5	529.0	629.7	729.3	765.6
155°	498.5	537.7	622.8	708.0	737.9
157.5°	510.0	545.1	617.1	687.2	711.5
160°	523.8	551.4	610.1	668.3	686.1
162.5°	534.2	556.0	603.2	650.4	663.1
165°	544.5	560.0	596.3	632.6	643.5
167.5°	552.6	563.5	589.4	617.1	624.0
170°	559.5	565.2	582.5	603.2	606.7
172.5°	564.1	567.0	576.8	591.2	590.6
175°	567.6	568.2	572.2	580.2	579.1
177.5°	569.9	568.7	568.7	573.3	571.0
180°	568.7	568.7	568.7	568.7	568.7

(END OF REPORT)