

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012593

Luminaire Tested: S123RDIP-B560D1195UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012593
REPORT IS A COMBINATION OF REPORTS P993380 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D1195UB30-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6453.1 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012593

CATALOG NUMBER: S123RDIP-B560D1195UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012593

CATALOG NUMBER: S123RDIP-B560D1195UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	35
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	29
3	78	69	62	57	70	63	57	52	51	46	43	39	36	34	29	27	25
4	72	61	54	48	64	56	49	44	45	40	37	35	32	29	26	24	22
5	66	55	47	41	59	50	43	38	40	35	32	31	28	25	23	21	19
6	61	49	41	36	55	45	38	33	36	31	28	28	25	22	21	19	17
7	56	44	37	31	50	40	34	29	33	28	24	26	22	20	19	17	15
8	52	40	33	28	47	37	30	25	30	25	21	24	20	17	18	15	14
9	48	37	29	24	44	33	27	23	27	23	19	22	18	16	16	14	12
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10125	10125	10125
5°	10141	9766	9740
10°	10061	9399	9214
15°	9930	8946	8638
20°	9759	8451	7994
25°	9583	7939	7384
30°	9356	7393	6663
35°	9123	6857	6006
40°	8903	6275	5281
45°	8621	5706	4629
50°	8311	5098	3953
55°	7989	4447	3335
60°	7682	3780	2706
65°	7284	3096	2113
70°	6785	2341	1510
75°	6063	1586	1196
80°	5179	1103	838
85°	3881	596	439

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8621 cd/sqm

TEST NUMBER: P1012593

CATALOG NUMBER: S123RDIP-B560D1195UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.4	1.4
10°-20°	246.0	3.8
20°-30°	354.2	5.5
30°-40°	398.8	6.2
40°-50°	381.5	5.9
50°-60°	312.3	4.8
60°-70°	210.6	3.3
70°-80°	105.6	1.6
80°-90°	30.8	0.5
90°-100°	326.0	5.1
100°-110°	911.1	14.1
110°-120°	888.4	13.8
120°-130°	707.4	11.0
130°-140°	558.4	8.7
140°-150°	416.6	6.5
150°-160°	290.6	4.5
160°-170°	170.7	2.6
170°-180°	55.5	0.9
0°-30°	688.6	10.7
0°-40°	1087.4	16.9
0°-60°	1781.2	27.6
0°-90°	2128.2	33.0
90°-120°	2125.5	32.9
90°-150°	3807.9	59.0
90°-180°	4325.0	67.0
0°-180°	6453.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	941	941	941	941	941	
5°	941	937	928	934	933	89
15°	897	889	867	864	858	253
25°	816	797	762	746	738	375
35°	706	679	632	599	585	442
45°	580	546	488	444	426	448
55°	441	404	339	294	279	395
65°	301	259	200	162	154	298
75°	159	123	81	73	72	170
85°	40	24	21	20	20	44
90°	2	14	29	33	34	6
95°	40	128	689	201	135	42
105°	135	199	934	1633	1477	143
115°	238	297	714	1566	1796	236
125°	331	391	666	1208	1417	294
135°	388	463	657	995	1148	300
145°	442	507	649	816	898	277
155°	503	542	628	714	744	231
165°	549	565	602	638	649	155
175°	572	573	577	585	584	54
180°	574	574	574	574	574	

TEST NUMBER: P1012593

CATALOG NUMBER: S123RDIP-B560D1195UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	940.6	940.6	940.6	940.6	940.6
2.5°	944.4	941.4	932.2	940.6	939.1
5°	940.6	936.8	927.6	934.5	933.0
7.5°	933.7	929.9	918.5	923.1	920.8
10°	924.6	919.2	905.5	906.3	902.5
12.5°	911.6	905.5	888.0	887.2	882.6
15°	897.1	888.7	867.4	863.6	858.2
17.5°	879.6	870.4	843.7	836.1	828.5
20°	859.7	847.5	818.5	808.6	799.5
22.5°	837.6	823.1	791.8	778.9	770.5
25°	816.3	797.2	762.1	746.1	737.7
27.5°	790.3	769.7	731.6	710.2	697.3
30°	763.6	740.7	698.0	672.1	659.9
32.5°	736.9	710.2	664.5	635.5	622.5
35°	706.4	678.9	631.6	598.8	585.1
37.5°	675.9	646.1	596.6	559.9	543.2
40°	646.9	613.3	559.2	519.5	502.0
42.5°	614.1	580.5	524.1	479.8	464.6
45°	580.5	546.2	487.5	444.0	425.7
47.5°	547.7	509.6	451.6	404.3	388.3
50°	511.1	475.3	413.5	366.2	348.6
52.5°	478.3	438.6	377.6	328.0	312.8
55°	440.9	403.6	338.7	294.5	279.2
57.5°	407.4	366.9	301.3	259.4	246.4
60°	372.3	330.3	267.0	225.8	212.8
62.5°	337.2	295.2	231.9	193.8	180.0
65°	301.3	259.4	199.9	162.5	154.1
67.5°	265.5	222.8	164.8	136.6	127.4
70°	230.4	189.2	135.8	109.1	100.7
72.5°	195.3	154.9	107.6	87.0	84.7
75°	159.4	122.8	80.9	73.2	71.7
77.5°	126.6	93.1	63.3	58.7	57.2
80°	95.4	64.1	48.1	45.8	44.2
82.5°	65.6	39.7	34.3	32.0	32.0
85°	40.4	23.6	21.4	19.8	19.8
87.5°	18.3	9.9	9.9	9.2	8.4
90°	2.3	14.0	29.0	32.6	33.7
92.5°	17.4	69.6	216.0	73.8	61.5
95°	39.5	128.4	688.6	200.9	134.7
97.5°	62.7	146.9	1059.0	505.1	276.4
100°	85.9	162.0	1099.6	1056.6	728.1
102.5°	110.3	179.4	1024.2	1414.9	1153.0
105°	134.7	199.1	933.6	1632.6	1477.0
107.5°	160.2	222.4	853.5	1728.4	1688.3
110°	188.1	246.2	787.3	1731.4	1809.1

TEST NUMBER: P1012593

CATALOG NUMBER: S123RDIP-B560D1195UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	213.7	271.2	743.2	1665.7	1833.5
115°	238.0	296.7	714.1	1565.8	1796.3
117.5°	262.4	321.0	694.4	1459.0	1715.1
120°	288.0	345.4	681.6	1358.0	1608.2
122.5°	310.0	368.6	673.5	1278.4	1508.4
125°	330.9	390.8	666.5	1207.6	1416.6
127.5°	347.2	411.6	663.0	1149.6	1337.7
130°	362.3	430.2	659.5	1096.2	1272.6
132.5°	373.9	447.0	658.4	1046.2	1208.8
135°	387.8	462.8	657.2	994.6	1148.4
137.5°	400.6	475.5	654.9	945.8	1084.5
140°	413.4	487.1	653.7	898.2	1017.2
142.5°	427.3	497.6	651.4	854.6	954.5
145°	442.4	506.8	649.1	815.8	897.6
147.5°	457.5	516.7	645.6	785.5	848.8
150°	472.6	524.8	641.0	758.8	807.0
152.5°	487.7	533.6	635.2	735.6	772.2
155°	502.8	542.2	628.2	714.2	744.3
157.5°	514.4	549.8	622.4	693.2	717.6
160°	528.3	556.2	615.4	674.0	692.1
162.5°	538.8	560.8	608.5	656.0	668.8
165°	549.2	564.9	601.5	638.1	649.1
167.5°	557.4	568.4	594.5	622.4	629.4
170°	564.3	570.2	587.6	608.4	611.9
172.5°	569.0	571.9	581.7	596.2	595.7
175°	572.5	573.0	577.1	585.2	584.1
177.5°	574.8	573.6	573.6	578.3	575.9
180°	573.6	573.6	573.6	573.6	573.6

(END OF REPORT)