

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012236

Luminaire Tested: S123RDIP-B1000D805UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012236
REPORT IS A COMBINATION OF REPORTS P992883 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D805UB27-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6408.0 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012236

CATALOG NUMBER: S123RDIP-B1000D805UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012236

CATALOG NUMBER: S123RDIP-B1000D805UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64
1	100	96	92	89	93	90	86	83	78	75	73	67	65	64	57	56	55
2	91	84	78	73	85	79	73	69	69	65	61	59	56	54	51	48	47
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	45	42	40
4	77	66	58	52	71	62	55	50	54	49	45	47	43	40	41	37	35
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	33	31
6	65	53	45	39	61	50	43	37	44	38	34	39	34	30	33	30	27
7	60	48	40	35	56	45	38	33	40	34	30	35	31	27	31	27	24
8	56	44	36	31	52	41	34	29	37	31	27	32	28	24	28	25	22
9	52	40	33	28	49	38	31	26	34	28	24	30	25	22	26	22	20
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17800	17800	17800
5°	17829	17170	17124
10°	17689	16525	16199
15°	17460	15727	15186
20°	17158	14859	14055
25°	16848	13958	12981
30°	16449	12998	11714
35°	16039	12056	10560
40°	15652	11032	9284
45°	15159	10031	8138
50°	14612	8963	6950
55°	14046	7819	5863
60°	13505	6646	4759
65°	12807	5442	3714
70°	11927	4115	2654
75°	10662	2788	2104
80°	9099	1937	1475
85°	6829	1047	774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15159 cd/sqm

TEST NUMBER: P1012236

CATALOG NUMBER: S123RDIP-B1000D805UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.5	2.4
10°-20°	432.5	6.7
20°-30°	622.7	9.7
30°-40°	701.2	10.9
40°-50°	670.7	10.5
50°-60°	549.1	8.6
60°-70°	370.2	5.8
70°-80°	185.7	2.9
80°-90°	50.6	0.8
90°-100°	62.0	1.0
100°-110°	187.7	2.9
110°-120°	319.6	5.0
120°-130°	420.5	6.6
130°-140°	472.6	7.4
140°-150°	464.7	7.3
150°-160°	391.2	6.1
160°-170°	260.4	4.1
170°-180°	91.2	1.4
0°-30°	1210.6	18.9
0°-40°	1911.8	29.8
0°-60°	3131.6	48.9
0°-90°	3738.0	58.3
90°-120°	569.4	8.9
90°-150°	1927.2	30.1
90°-180°	2670.0	41.7
0°-180°	6408.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1654	1654	1654	1654	1654	
5°	1654	1647	1631	1643	1640	157
15°	1577	1562	1525	1518	1509	444
25°	1435	1402	1340	1312	1297	660
35°	1242	1194	1110	1053	1029	777
45°	1021	960	857	781	748	788
55°	775	710	596	518	491	695
65°	530	456	351	286	271	524
75°	280	216	142	129	126	299
85°	71	42	38	35	35	78
90°	1	8	18	21	23	8
95°	45	50	56	59	59	49
105°	170	172	179	179	180	182
115°	322	324	322	323	322	318
125°	471	473	472	469	466	420
135°	611	615	615	612	610	471
145°	741	743	745	744	741	463
155°	848	848	849	852	847	391
165°	924	922	922	926	921	261
175°	961	958	958	963	958	91
180°	964	964	964	964	964	

TEST NUMBER: P1012236

CATALOG NUMBER: S123RDIP-B1000D805UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1653.7	1653.7	1653.7	1653.7	1653.7
2.5°	1660.4	1655.0	1638.9	1653.7	1651.0
5°	1653.7	1647.0	1630.9	1643.0	1640.3
7.5°	1641.6	1634.9	1614.8	1622.9	1618.8
10°	1625.5	1616.1	1592.0	1593.3	1586.6
12.5°	1602.7	1592.0	1561.2	1559.8	1551.8
15°	1577.3	1562.5	1524.9	1518.2	1508.8
17.5°	1546.4	1530.3	1483.4	1470.0	1456.5
20°	1511.5	1490.1	1439.1	1421.7	1405.6
22.5°	1472.6	1447.2	1392.2	1369.4	1354.6
25°	1435.1	1401.6	1339.9	1311.7	1296.9
27.5°	1389.5	1353.3	1286.2	1248.7	1225.9
30°	1342.5	1302.3	1227.2	1181.6	1160.1
32.5°	1295.6	1248.7	1168.2	1117.2	1094.4
35°	1242.0	1193.7	1110.5	1052.8	1028.7
37.5°	1188.3	1136.0	1048.8	984.4	954.9
40°	1137.3	1078.3	983.1	913.4	882.5
42.5°	1079.7	1020.7	921.4	843.6	816.8
45°	1020.7	960.3	857.0	780.6	748.4
47.5°	963.0	895.9	794.0	710.8	682.7
50°	898.6	835.6	726.9	643.8	612.9
52.5°	840.9	771.2	663.9	576.7	549.9
55°	775.2	709.5	595.5	517.7	490.9
57.5°	716.2	645.1	529.8	456.0	433.2
60°	654.5	580.7	469.4	397.0	374.2
62.5°	592.8	519.0	407.7	340.7	316.5
65°	529.8	456.0	351.4	285.7	270.9
67.5°	466.7	391.6	289.7	240.1	224.0
70°	405.0	332.6	238.7	191.8	177.0
72.5°	343.3	272.3	189.1	152.9	148.9
75°	280.3	215.9	142.2	128.8	126.1
77.5°	222.6	163.6	111.3	103.3	100.6
80°	167.6	112.7	84.5	80.5	77.8
82.5°	115.3	69.7	60.4	56.3	56.3
85°	71.1	41.6	37.6	34.9	34.9
87.5°	32.2	17.4	17.4	16.1	14.8
90°	0.8	8.3	18.2	21.2	22.7
92.5°	22.7	27.3	31.8	34.1	32.5
95°	44.7	50.0	56.0	59.0	59.0
97.5°	73.4	77.2	81.8	85.5	84.8
100°	102.9	107.5	111.3	113.5	115.1
102.5°	137.0	139.3	144.6	146.8	146.1
105°	170.3	171.8	178.6	178.6	180.2
107.5°	209.7	210.4	213.5	215.7	215.0
110°	246.0	247.5	249.0	252.1	250.6

TEST NUMBER: P1012236

CATALOG NUMBER: S123RDIP-B1000D805UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	283.9	284.6	284.6	288.4	288.4
115°	321.7	324.0	322.5	323.2	322.5
117.5°	360.3	361.1	359.6	359.6	357.3
120°	395.9	400.4	396.6	395.9	394.4
122.5°	433.0	436.0	434.5	432.2	429.9
125°	470.8	473.1	471.6	468.6	465.5
127.5°	505.6	510.2	508.7	504.1	501.1
130°	540.5	546.5	544.2	541.2	535.9
132.5°	575.3	581.3	579.8	576.0	572.3
135°	610.9	615.4	614.6	611.6	610.1
137.5°	643.4	647.2	649.5	645.7	643.4
140°	677.5	681.3	682.0	681.3	676.0
142.5°	708.5	712.3	713.8	713.0	709.3
145°	741.1	742.6	744.8	744.1	741.1
147.5°	769.1	772.1	774.4	774.4	769.8
150°	798.6	800.1	801.6	801.6	797.1
152.5°	822.8	825.1	825.8	827.3	823.6
155°	848.5	848.5	849.3	852.3	847.0
157.5°	870.5	869.7	870.5	873.5	869.0
160°	890.9	889.4	889.4	893.2	890.2
162.5°	909.1	906.8	907.6	911.4	906.1
165°	924.2	922.0	922.0	926.5	921.2
167.5°	937.1	934.1	934.8	939.4	934.8
170°	947.7	944.7	944.7	950.0	944.7
172.5°	956.0	953.0	953.0	957.5	952.2
175°	961.3	958.3	958.3	962.8	957.5
177.5°	964.4	961.3	961.3	965.9	960.6
180°	963.6	963.6	963.6	963.6	963.6

(END OF REPORT)