

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012604

Luminaire Tested: S123RDIP-B560D1195UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012604
REPORT IS A COMBINATION OF REPORTS P993391 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D1195UB40-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6188.0 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012604

CATALOG NUMBER: S123RDIP-B560D1195UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012604

CATALOG NUMBER: S123RDIP-B560D1195UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42
1	94	90	87	83	85	82	79	76	66	63	62	51	49	48	37	36	36
2	86	79	73	68	78	72	67	62	58	54	51	45	43	40	33	31	30
3	79	70	63	57	71	63	57	52	51	47	43	40	37	34	29	28	26
4	72	62	54	48	65	56	50	44	45	41	37	36	32	30	26	24	23
5	66	55	47	41	59	50	43	38	41	36	32	32	28	26	24	22	20
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	19	17
7	56	44	37	31	51	41	34	29	33	28	24	26	23	20	20	17	16
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	48	37	29	25	44	34	27	23	28	23	19	22	19	16	17	14	13
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10067	10067	10067
5°	10084	9711	9685
10°	10005	9346	9162
15°	9875	8895	8589
20°	9704	8404	7949
25°	9529	7894	7342
30°	9303	7352	6625
35°	9071	6819	5972
40°	8853	6239	5251
45°	8574	5673	4603
50°	8264	5069	3932
55°	7944	4422	3316
60°	7639	3759	2691
65°	7242	3077	2100
70°	6747	2327	1501
75°	6029	1576	1190
80°	5147	1096	834
85°	3861	590	437

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8574 cd/sqm

TEST NUMBER: P1012604

CATALOG NUMBER: S123RDIP-B560D1195UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.9	1.4
10°-20°	244.6	4.0
20°-30°	352.2	5.7
30°-40°	396.6	6.4
40°-50°	379.4	6.1
50°-60°	310.5	5.0
60°-70°	209.4	3.4
70°-80°	105.0	1.7
80°-90°	30.6	0.5
90°-100°	94.6	1.5
100°-110°	286.3	4.6
110°-120°	487.4	7.9
120°-130°	641.3	10.4
130°-140°	720.8	11.6
140°-150°	708.6	11.5
150°-160°	596.6	9.6
160°-170°	397.2	6.4
170°-180°	139.1	2.2
0°-30°	684.7	11.1
0°-40°	1081.3	17.5
0°-60°	1771.2	28.6
0°-90°	2116.1	34.2
90°-120°	868.4	14.0
90°-150°	2939.0	47.5
90°-180°	4072.0	65.8
0°-180°	6188.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	935	935	935	935	935	
5°	935	932	922	929	928	89
15°	892	884	862	859	853	251
25°	812	793	758	742	734	373
35°	702	675	628	596	582	440
45°	577	543	485	442	423	445
55°	438	401	337	293	278	393
65°	300	258	199	162	153	297
75°	158	122	80	73	71	169
85°	40	24	21	20	20	44
90°	1	13	28	32	35	8
95°	68	76	85	90	90	75
105°	260	262	272	272	275	278
115°	491	494	492	493	492	486
125°	718	722	719	715	710	640
135°	932	938	937	933	930	718
145°	1130	1132	1136	1135	1130	706
155°	1294	1294	1295	1300	1292	596
165°	1410	1406	1406	1413	1405	398
175°	1466	1462	1462	1468	1460	139
180°	1470	1470	1470	1470	1470	

TEST NUMBER: P1012604

CATALOG NUMBER: S123RDIP-B560D1195UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	935.3	935.3	935.3	935.3	935.3
2.5°	939.1	936.1	927.0	935.3	933.8
5°	935.3	931.5	922.4	929.2	927.7
7.5°	928.5	924.7	913.3	917.8	915.6
10°	919.4	914.1	900.4	901.2	897.4
12.5°	906.5	900.4	883.0	882.2	877.6
15°	892.1	883.7	862.5	858.7	853.4
17.5°	874.6	865.5	839.0	831.4	823.8
20°	854.9	842.8	813.9	804.1	795.0
22.5°	832.9	818.5	787.4	774.5	766.1
25°	811.7	792.7	757.8	741.9	733.5
27.5°	785.9	765.4	727.5	706.2	693.3
30°	759.3	736.6	694.1	668.3	656.1
32.5°	732.8	706.2	660.7	631.9	619.0
35°	702.4	675.1	628.1	595.5	581.8
37.5°	672.1	642.5	593.2	556.8	540.1
40°	643.3	609.9	556.0	516.6	499.1
42.5°	610.6	577.3	521.1	477.1	462.0
45°	577.3	543.1	484.7	441.5	423.3
47.5°	544.6	506.7	449.1	402.0	386.1
50°	508.2	472.6	411.1	364.1	346.7
52.5°	475.6	436.2	375.5	326.2	311.0
55°	438.4	401.3	336.8	292.8	277.6
57.5°	405.1	364.9	299.6	257.9	245.0
60°	370.2	328.5	265.5	224.5	211.6
62.5°	335.3	293.6	230.6	192.7	179.0
65°	299.6	257.9	198.7	161.6	153.2
67.5°	264.0	221.5	163.8	135.8	126.7
70°	229.1	188.1	135.0	108.5	100.1
72.5°	194.2	154.0	107.0	86.5	84.2
75°	158.5	122.1	80.4	72.8	71.3
77.5°	125.9	92.5	63.0	58.4	56.9
80°	94.8	63.7	47.8	45.5	44.0
82.5°	65.2	39.4	34.1	31.9	31.9
85°	40.2	23.5	21.2	19.7	19.7
87.5°	18.2	9.9	9.9	9.1	8.3
90°	1.2	12.7	27.7	32.3	34.6
92.5°	34.6	41.6	48.5	51.9	49.6
95°	68.1	76.2	85.4	90.0	90.0
97.5°	112.0	117.7	124.7	130.4	129.3
100°	157.0	163.9	169.7	173.2	175.5
102.5°	208.9	212.4	220.5	224.0	222.8
105°	259.7	262.1	272.4	272.4	274.7
107.5°	319.8	320.9	325.5	329.0	327.9
110°	375.2	377.5	379.8	384.4	382.1

TEST NUMBER: P1012604

CATALOG NUMBER: S123RDIP-B560D1195UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	432.9	434.1	434.1	439.8	439.8
115°	490.6	494.1	491.8	492.9	491.8
117.5°	549.5	550.7	548.3	548.3	544.9
120°	603.8	610.7	604.9	603.8	601.4
122.5°	660.3	664.9	662.6	659.2	655.7
125°	718.0	721.5	719.2	714.6	710.0
127.5°	771.1	778.1	775.8	768.8	764.2
130°	824.2	833.5	830.0	825.4	817.3
132.5°	877.4	886.6	884.3	878.5	872.7
135°	931.6	938.5	937.4	932.8	930.5
137.5°	981.2	987.0	990.5	984.7	981.2
140°	1033.2	1039.0	1040.1	1039.0	1030.9
142.5°	1080.5	1086.3	1088.6	1087.5	1081.7
145°	1130.2	1132.5	1135.9	1134.8	1130.2
147.5°	1172.9	1177.5	1181.0	1181.0	1174.0
150°	1217.9	1220.2	1222.5	1222.5	1215.6
152.5°	1254.8	1258.3	1259.5	1261.8	1256.0
155°	1294.1	1294.1	1295.2	1299.9	1291.8
157.5°	1327.6	1326.4	1327.6	1332.2	1325.3
160°	1358.7	1356.4	1356.4	1362.2	1357.6
162.5°	1386.4	1383.0	1384.1	1389.9	1381.8
165°	1409.5	1406.1	1406.1	1413.0	1404.9
167.5°	1429.2	1424.5	1425.7	1432.6	1425.7
170°	1445.3	1440.7	1440.7	1448.8	1440.7
172.5°	1458.0	1453.4	1453.4	1460.3	1452.2
175°	1466.1	1461.5	1461.5	1468.4	1460.3
177.5°	1470.7	1466.1	1466.1	1473.0	1464.9
180°	1469.6	1469.6	1469.6	1469.6	1469.6

(END OF REPORT)