

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012622

Luminaire Tested: S123RDIP-B560D365UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012622
REPORT IS A COMBINATION OF REPORTS P993419 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D365UB30-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3380.0 lumens
Efficiency: N/A
Efficacy: 101.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012622

CATALOG NUMBER: S123RDIP-B560D365UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012622

CATALOG NUMBER: S123RDIP-B560D365UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68
1	101	97	93	90	95	91	88	85	80	78	75	70	68	67	61	59	58
2	92	85	79	74	86	80	75	70	71	67	63	62	59	56	54	52	50
3	85	75	68	62	79	71	64	59	63	58	53	55	51	48	48	45	43
4	78	67	59	53	73	63	56	51	56	50	46	49	45	41	43	40	37
5	71	60	52	46	67	57	49	44	50	44	40	45	40	36	39	36	33
6	66	54	46	40	62	51	44	38	46	40	35	40	36	32	36	32	29
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	33	29	26
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23
9	53	41	33	28	50	39	32	27	35	29	25	31	27	23	28	24	21
10	50	38	30	25	47	36	29	25	32	27	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10125	10125	10125
5°	10141	9766	9740
10°	10061	9399	9214
15°	9930	8946	8638
20°	9759	8451	7994
25°	9583	7939	7384
30°	9356	7393	6663
35°	9123	6857	6006
40°	8903	6275	5281
45°	8621	5706	4629
50°	8311	5098	3953
55°	7989	4447	3335
60°	7682	3780	2706
65°	7284	3096	2113
70°	6785	2341	1510
75°	6063	1586	1196
80°	5179	1103	838
85°	3881	596	439

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8621 cd/sqm

TEST NUMBER: P1012622

CATALOG NUMBER: S123RDIP-B560D365UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.4	2.6
10°-20°	246.0	7.3
20°-30°	354.2	10.5
30°-40°	398.8	11.8
40°-50°	381.5	11.3
50°-60°	312.3	9.2
60°-70°	210.6	6.2
70°-80°	105.6	3.1
80°-90°	28.6	0.8
90°-100°	29.1	0.9
100°-110°	88.2	2.6
110°-120°	150.1	4.4
120°-130°	197.5	5.8
130°-140°	222.0	6.6
140°-150°	218.2	6.5
150°-160°	183.7	5.4
160°-170°	122.3	3.6
170°-180°	42.8	1.3
0°-30°	688.6	20.4
0°-40°	1087.4	32.2
0°-60°	1781.2	52.7
0°-90°	2126.0	62.9
90°-120°	267.5	7.9
90°-150°	905.2	26.8
90°-180°	1254.0	37.1
0°-180°	3380.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	941	941	941	941	941	
5°	941	937	928	934	933	89
15°	897	889	867	864	858	253
25°	816	797	762	746	738	375
35°	706	679	632	599	585	442
45°	580	546	488	444	426	448
55°	441	404	339	294	279	395
65°	301	259	200	162	154	298
75°	159	123	81	73	72	170
85°	40	24	21	20	20	44
90°	0	4	8	10	11	4
95°	21	24	26	28	28	23
105°	80	81	84	84	85	86
115°	151	152	152	152	152	150
125°	221	222	222	220	219	197
135°	287	289	289	287	287	221
145°	348	349	350	350	348	217
155°	398	398	399	400	398	183
165°	434	433	433	435	433	122
175°	452	450	450	452	450	43
180°	453	453	453	453	453	

TEST NUMBER: P1012622

CATALOG NUMBER: S123RDIP-B560D365UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	940.6	940.6	940.6	940.6	940.6
2.5°	944.4	941.4	932.2	940.6	939.1
5°	940.6	936.8	927.6	934.5	933.0
7.5°	933.7	929.9	918.5	923.1	920.8
10°	924.6	919.2	905.5	906.3	902.5
12.5°	911.6	905.5	888.0	887.2	882.6
15°	897.1	888.7	867.4	863.6	858.2
17.5°	879.6	870.4	843.7	836.1	828.5
20°	859.7	847.5	818.5	808.6	799.5
22.5°	837.6	823.1	791.8	778.9	770.5
25°	816.3	797.2	762.1	746.1	737.7
27.5°	790.3	769.7	731.6	710.2	697.3
30°	763.6	740.7	698.0	672.1	659.9
32.5°	736.9	710.2	664.5	635.5	622.5
35°	706.4	678.9	631.6	598.8	585.1
37.5°	675.9	646.1	596.6	559.9	543.2
40°	646.9	613.3	559.2	519.5	502.0
42.5°	614.1	580.5	524.1	479.8	464.6
45°	580.5	546.2	487.5	444.0	425.7
47.5°	547.7	509.6	451.6	404.3	388.3
50°	511.1	475.3	413.5	366.2	348.6
52.5°	478.3	438.6	377.6	328.0	312.8
55°	440.9	403.6	338.7	294.5	279.2
57.5°	407.4	366.9	301.3	259.4	246.4
60°	372.3	330.3	267.0	225.8	212.8
62.5°	337.2	295.2	231.9	193.8	180.0
65°	301.3	259.4	199.9	162.5	154.1
67.5°	265.5	222.8	164.8	136.6	127.4
70°	230.4	189.2	135.8	109.1	100.7
72.5°	195.3	154.9	107.6	87.0	84.7
75°	159.4	122.8	80.9	73.2	71.7
77.5°	126.6	93.1	63.3	58.7	57.2
80°	95.4	64.1	48.1	45.8	44.2
82.5°	65.6	39.7	34.3	32.0	32.0
85°	40.4	23.6	21.4	19.8	19.8
87.5°	18.3	9.9	9.9	9.2	8.4
90°	0.4	3.9	8.5	10.0	10.7
92.5°	10.7	12.8	14.9	16.0	15.3
95°	21.0	23.5	26.3	27.7	27.7
97.5°	34.5	36.3	38.4	40.2	39.8
100°	48.4	50.5	52.3	53.3	54.0
102.5°	64.4	65.4	67.9	69.0	68.6
105°	80.0	80.7	83.9	83.9	84.6
107.5°	98.5	98.8	100.3	101.3	101.0
110°	115.5	116.3	117.0	118.4	117.7



TEST NUMBER: P1012622

CATALOG NUMBER: S123RDIP-B560D365UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	133.3	133.7	133.7	135.5	135.5
115°	151.1	152.2	151.5	151.8	151.5
117.5°	169.2	169.6	168.9	168.9	167.8
120°	185.9	188.1	186.3	185.9	185.2
122.5°	203.4	204.8	204.1	203.0	201.9
125°	221.1	222.2	221.5	220.1	218.7
127.5°	237.5	239.6	238.9	236.8	235.4
130°	253.8	256.7	255.6	254.2	251.7
132.5°	270.2	273.0	272.3	270.6	268.8
135°	286.9	289.0	288.7	287.3	286.6
137.5°	302.2	304.0	305.0	303.3	302.2
140°	318.2	320.0	320.3	320.0	317.5
142.5°	332.8	334.6	335.3	334.9	333.1
145°	348.1	348.8	349.8	349.5	348.1
147.5°	361.2	362.6	363.7	363.7	361.6
150°	375.1	375.8	376.5	376.5	374.4
152.5°	386.5	387.5	387.9	388.6	386.8
155°	398.5	398.5	398.9	400.3	397.8
157.5°	408.9	408.5	408.9	410.3	408.1
160°	418.5	417.7	417.7	419.5	418.1
162.5°	427.0	425.9	426.3	428.1	425.6
165°	434.1	433.0	433.0	435.2	432.7
167.5°	440.1	438.7	439.1	441.2	439.1
170°	445.1	443.7	443.7	446.2	443.7
172.5°	449.0	447.6	447.6	449.7	447.3
175°	451.5	450.1	450.1	452.2	449.7
177.5°	452.9	451.5	451.5	453.7	451.2
180°	452.6	452.6	452.6	452.6	452.6

(END OF REPORT)