

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012645

Luminaire Tested: S123RDIP-B560D585UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012645
REPORT IS A COMBINATION OF REPORTS P993444 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D585UB27-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4218.9 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012645

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012645

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48
2	90	82	76	71	82	76	71	67	65	61	58	54	52	49	44	43	41
3	82	73	66	60	75	67	61	56	57	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31
5	69	58	50	44	64	54	47	41	46	41	36	39	35	32	32	29	27
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	29	26	24
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	25	22	19
9	51	39	32	27	47	36	30	25	32	26	23	27	23	20	23	20	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10038	10038	10038
5°	10055	9684	9658
10°	9977	9319	9136
15°	9846	8869	8564
20°	9677	8380	7926
25°	9501	7871	7321
30°	9277	7330	6607
35°	9045	6799	5956
40°	8827	6221	5236
45°	8548	5657	4590
50°	8241	5055	3920
55°	7922	4409	3306
60°	7616	3748	2683
65°	7223	3070	2095
70°	6726	2320	1496
75°	6014	1572	1186
80°	5130	1093	833
85°	3852	590	437

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8548 cd/sqm

TEST NUMBER: P1012645

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	2.1
10°-20°	243.9	5.8
20°-30°	351.2	8.3
30°-40°	395.5	9.4
40°-50°	378.3	9.0
50°-60°	309.7	7.3
60°-70°	208.8	4.9
70°-80°	104.7	2.5
80°-90°	28.9	0.7
90°-100°	159.1	3.8
100°-110°	444.6	10.5
110°-120°	433.5	10.3
120°-130°	345.2	8.2
130°-140°	272.5	6.5
140°-150°	203.3	4.8
150°-160°	141.8	3.4
160°-170°	83.3	2.0
170°-180°	27.1	0.6
0°-30°	682.7	16.2
0°-40°	1078.2	25.6
0°-60°	1766.1	41.9
0°-90°	2108.5	50.0
90°-120°	1037.2	24.6
90°-150°	1858.1	44.0
90°-180°	2110.0	50.0
0°-180°	4218.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	933	933	933	933	933	
5°	933	929	920	927	925	88
15°	890	881	860	856	851	251
25°	809	790	756	740	731	372
35°	700	673	626	594	580	438
45°	576	542	483	440	422	444
55°	437	400	336	292	277	392
65°	299	257	198	161	153	296
75°	158	122	80	73	71	168
85°	40	23	21	20	20	44
90°	1	7	14	16	16	4
95°	19	63	336	98	66	20
105°	66	97	456	797	721	70
115°	116	145	348	764	876	115
125°	162	191	325	589	691	143
135°	189	226	321	485	560	146
145°	216	247	317	398	438	135
155°	245	265	306	348	363	113
165°	268	276	294	311	317	76
175°	279	280	282	286	285	27
180°	280	280	280	280	280	

TEST NUMBER: P1012645

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	932.6	932.6	932.6	932.6	932.6
2.5°	936.4	933.4	924.3	932.6	931.1
5°	932.6	928.9	919.8	926.6	925.1
7.5°	925.8	922.1	910.7	915.2	913.0
10°	916.8	911.5	897.8	898.6	894.8
12.5°	903.9	897.8	880.4	879.7	875.2
15°	889.5	881.2	860.0	856.2	850.9
17.5°	872.1	863.1	836.6	829.0	821.4
20°	852.5	840.4	811.6	801.8	792.7
22.5°	830.5	816.2	785.1	772.3	764.0
25°	809.3	790.4	755.6	739.8	731.4
27.5°	783.6	763.2	725.4	704.2	691.3
30°	757.2	734.5	692.1	666.4	654.3
32.5°	730.7	704.2	658.8	630.1	617.2
35°	700.4	673.2	626.3	593.8	580.2
37.5°	670.2	640.7	591.5	555.2	538.6
40°	641.4	608.1	554.4	515.1	497.7
42.5°	608.9	575.6	519.6	475.8	460.6
45°	575.6	541.6	483.3	440.2	422.1
47.5°	543.1	505.3	447.8	400.9	385.0
50°	506.8	471.2	410.0	363.1	345.7
52.5°	474.3	434.9	374.4	325.3	310.1
55°	437.2	400.1	335.8	292.0	276.8
57.5°	403.9	363.8	298.8	257.2	244.3
60°	369.1	327.5	264.7	223.9	211.0
62.5°	334.3	292.7	229.9	192.1	178.5
65°	298.8	257.2	198.2	161.1	152.8
67.5°	263.2	220.9	163.4	135.4	126.3
70°	228.4	187.6	134.6	108.2	99.8
72.5°	193.6	153.5	106.7	86.2	84.0
75°	158.1	121.8	80.2	72.6	71.1
77.5°	125.6	92.3	62.8	58.2	56.7
80°	94.5	63.5	47.7	45.4	43.9
82.5°	65.1	39.3	34.0	31.8	31.8
85°	40.1	23.4	21.2	19.7	19.7
87.5°	18.2	9.8	9.8	9.1	8.3
90°	1.1	6.8	14.2	15.8	16.4
92.5°	8.5	34.0	105.4	36.0	30.0
95°	19.3	62.6	336.0	98.0	65.7
97.5°	30.6	71.7	516.7	246.5	134.9
100°	41.9	79.0	536.6	515.6	355.3
102.5°	53.8	87.6	499.7	690.4	562.6
105°	65.7	97.2	455.5	796.6	720.7
107.5°	78.2	108.5	416.5	843.4	823.8
110°	91.8	120.2	384.2	844.8	882.8

TEST NUMBER: P1012645

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	104.3	132.4	362.6	812.8	894.7
115°	116.2	144.8	348.5	764.0	876.5
117.5°	128.1	156.6	338.8	711.9	836.9
120°	140.5	168.6	332.6	662.6	784.7
122.5°	151.3	179.8	328.6	623.8	736.0
125°	161.5	190.6	325.2	589.2	691.3
127.5°	169.4	200.8	323.5	561.0	652.7
130°	176.8	210.0	321.8	534.8	621.0
132.5°	182.4	218.2	321.3	510.5	589.8
135°	189.2	225.8	320.7	485.2	560.4
137.5°	195.5	232.0	319.6	461.4	529.2
140°	201.7	237.7	319.0	438.2	496.3
142.5°	208.5	242.8	317.9	417.0	465.7
145°	215.9	247.3	316.7	398.0	438.0
147.5°	223.2	252.2	315.0	383.4	414.2
150°	230.6	256.1	312.8	370.3	393.8
152.5°	238.0	260.4	309.9	359.0	376.8
155°	245.3	264.6	306.5	348.5	363.2
157.5°	251.0	268.3	303.7	338.2	350.2
160°	257.8	271.4	300.3	328.9	337.7
162.5°	262.9	273.6	296.9	320.1	326.4
165°	268.0	275.6	293.5	311.4	316.7
167.5°	272.0	277.4	290.1	303.7	307.1
170°	275.4	278.2	286.7	296.9	298.6
172.5°	277.6	279.0	283.9	291.0	290.7
175°	279.3	279.6	281.6	285.6	285.0
177.5°	280.5	279.9	279.9	282.2	281.0
180°	279.9	279.9	279.9	279.9	279.9

(END OF REPORT)