

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012650

Luminaire Tested: S123RDIP-B560D585UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012650
REPORT IS A COMBINATION OF REPORTS P993459 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D585UB30-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4143.0 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012650

CATALOG NUMBER: S123RDIP-B560D585UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012650

CATALOG NUMBER: S123RDIP-B560D585UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	51
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	51	50	49	49	49	44
2	90	83	77	72	83	77	71	67	65	62	58	55	52	50	45	44	42	42	42	37
3	82	73	66	60	76	68	61	56	58	53	49	49	45	43	41	38	36	36	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	36	34	31	31	31	28
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	27	27	24
6	64	52	44	38	59	49	41	36	42	36	32	36	31	28	30	27	24	24	24	21
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	27	24	22	22	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	20	20	17
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	23	20	18	18	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10125	10125	10125
5°	10141	9766	9740
10°	10061	9399	9214
15°	9930	8946	8638
20°	9759	8451	7994
25°	9583	7939	7384
30°	9356	7393	6663
35°	9123	6857	6006
40°	8903	6275	5281
45°	8621	5706	4629
50°	8311	5098	3953
55°	7989	4447	3335
60°	7682	3780	2706
65°	7284	3096	2113
70°	6785	2341	1510
75°	6063	1586	1196
80°	5179	1103	838
85°	3881	596	439

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8621 cd/sqm

TEST NUMBER: P1012650

CATALOG NUMBER: S123RDIP-B560D585UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.4	2.1
10°-20°	246.0	5.9
20°-30°	354.2	8.5
30°-40°	398.8	9.6
40°-50°	381.5	9.2
50°-60°	312.3	7.5
60°-70°	210.6	5.1
70°-80°	105.6	2.5
80°-90°	29.1	0.7
90°-100°	46.8	1.1
100°-110°	141.8	3.4
110°-120°	241.4	5.8
120°-130°	317.6	7.7
130°-140°	356.9	8.6
140°-150°	350.9	8.5
150°-160°	295.4	7.1
160°-170°	196.7	4.7
170°-180°	68.9	1.7
0°-30°	688.6	16.6
0°-40°	1087.4	26.2
0°-60°	1781.2	43.0
0°-90°	2126.5	51.3
90°-120°	430.0	10.4
90°-150°	1455.5	35.1
90°-180°	2016.0	48.7
0°-180°	4143.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	941	941	941	941	941	
5°	941	937	928	934	933	89
15°	897	889	867	864	858	253
25°	816	797	762	746	738	375
35°	706	679	632	599	585	442
45°	580	546	488	444	426	448
55°	441	404	339	294	279	395
65°	301	259	200	162	154	298
75°	159	123	81	73	72	170
85°	40	24	21	20	20	44
90°	1	6	14	16	17	5
95°	34	38	42	45	45	37
105°	129	130	135	135	136	138
115°	243	245	244	244	244	240
125°	356	357	356	354	352	317
135°	461	465	464	462	461	355
145°	560	561	562	562	560	350
155°	641	641	641	644	640	295
165°	698	696	696	700	696	197
175°	726	724	724	727	723	69
180°	728	728	728	728	728	

TEST NUMBER: P1012650

CATALOG NUMBER: S123RDIP-B560D585UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	940.6	940.6	940.6	940.6	940.6
2.5°	944.4	941.4	932.2	940.6	939.1
5°	940.6	936.8	927.6	934.5	933.0
7.5°	933.7	929.9	918.5	923.1	920.8
10°	924.6	919.2	905.5	906.3	902.5
12.5°	911.6	905.5	888.0	887.2	882.6
15°	897.1	888.7	867.4	863.6	858.2
17.5°	879.6	870.4	843.7	836.1	828.5
20°	859.7	847.5	818.5	808.6	799.5
22.5°	837.6	823.1	791.8	778.9	770.5
25°	816.3	797.2	762.1	746.1	737.7
27.5°	790.3	769.7	731.6	710.2	697.3
30°	763.6	740.7	698.0	672.1	659.9
32.5°	736.9	710.2	664.5	635.5	622.5
35°	706.4	678.9	631.6	598.8	585.1
37.5°	675.9	646.1	596.6	559.9	543.2
40°	646.9	613.3	559.2	519.5	502.0
42.5°	614.1	580.5	524.1	479.8	464.6
45°	580.5	546.2	487.5	444.0	425.7
47.5°	547.7	509.6	451.6	404.3	388.3
50°	511.1	475.3	413.5	366.2	348.6
52.5°	478.3	438.6	377.6	328.0	312.8
55°	440.9	403.6	338.7	294.5	279.2
57.5°	407.4	366.9	301.3	259.4	246.4
60°	372.3	330.3	267.0	225.8	212.8
62.5°	337.2	295.2	231.9	193.8	180.0
65°	301.3	259.4	199.9	162.5	154.1
67.5°	265.5	222.8	164.8	136.6	127.4
70°	230.4	189.2	135.8	109.1	100.7
72.5°	195.3	154.9	107.6	87.0	84.7
75°	159.4	122.8	80.9	73.2	71.7
77.5°	126.6	93.1	63.3	58.7	57.2
80°	95.4	64.1	48.1	45.8	44.2
82.5°	65.6	39.7	34.3	32.0	32.0
85°	40.4	23.6	21.4	19.8	19.8
87.5°	18.3	9.9	9.9	9.2	8.4
90°	0.6	6.3	13.7	16.0	17.2
92.5°	17.2	20.6	24.0	25.7	24.6
95°	33.7	37.7	42.3	44.6	44.6
97.5°	55.5	58.3	61.7	64.6	64.0
100°	77.7	81.2	84.0	85.8	86.9
102.5°	103.5	105.2	109.2	110.9	110.3
105°	128.6	129.8	134.9	134.9	136.1
107.5°	158.4	158.9	161.2	162.9	162.4
110°	185.8	186.9	188.1	190.4	189.2



TEST NUMBER: P1012650

CATALOG NUMBER: S123RDIP-B560D585UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	214.4	215.0	215.0	217.8	217.8
115°	243.0	244.7	243.5	244.1	243.5
117.5°	272.1	272.7	271.5	271.5	269.8
120°	299.0	302.4	299.6	299.0	297.8
122.5°	327.0	329.3	328.1	326.4	324.7
125°	355.6	357.3	356.2	353.9	351.6
127.5°	381.9	385.3	384.2	380.7	378.5
130°	408.2	412.8	411.0	408.8	404.7
132.5°	434.5	439.1	437.9	435.0	432.2
135°	461.3	464.8	464.2	461.9	460.8
137.5°	485.9	488.8	490.5	487.6	485.9
140°	511.7	514.5	515.1	514.5	510.5
142.5°	535.1	538.0	539.1	538.5	535.7
145°	559.7	560.8	562.5	562.0	559.7
147.5°	580.8	583.1	584.8	584.8	581.4
150°	603.1	604.3	605.4	605.4	602.0
152.5°	621.4	623.1	623.7	624.8	622.0
155°	640.9	640.9	641.4	643.7	639.7
157.5°	657.4	656.9	657.4	659.7	656.3
160°	672.9	671.7	671.7	674.6	672.3
162.5°	686.6	684.9	685.4	688.3	684.3
165°	698.0	696.3	696.3	699.7	695.7
167.5°	707.7	705.5	706.0	709.5	706.0
170°	715.7	713.5	713.5	717.5	713.5
172.5°	722.0	719.7	719.7	723.2	719.2
175°	726.0	723.7	723.7	727.2	723.2
177.5°	728.3	726.0	726.0	729.5	725.5
180°	727.7	727.7	727.7	727.7	727.7

(END OF REPORT)