

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012656

Luminaire Tested: S123RDIP-B560D585UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012656
REPORT IS A COMBINATION OF REPORTS P993465 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D585UB35-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4160.0 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012656

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012656

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	51
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	51	50	49	49	49	44
2	90	83	77	72	83	77	71	67	65	62	58	55	52	50	45	44	42	42	42	37
3	82	73	66	60	76	68	61	56	58	53	49	49	45	43	41	38	36	36	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	36	34	31	31	31	28
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	27	27	24
6	64	52	44	38	59	49	41	36	42	36	32	36	31	28	30	27	24	24	24	21
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	27	24	22	22	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	20	20	17
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	23	20	18	18	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10168	10168	10168
5°	10184	9808	9781
10°	10104	9440	9253
15°	9972	8983	8675
20°	9801	8487	8028
25°	9623	7972	7415
30°	9396	7425	6691
35°	9161	6886	6032
40°	8940	6301	5303
45°	8658	5730	4648
50°	8347	5119	3970
55°	8023	4466	3349
60°	7715	3796	2718
65°	7315	3108	2122
70°	6814	2351	1516
75°	6090	1592	1201
80°	5201	1107	842
85°	3900	599	441

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8658 cd/sqm

TEST NUMBER: P1012656

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.8	2.1
10°-20°	247.0	5.9
20°-30°	355.7	8.5
30°-40°	400.5	9.6
40°-50°	383.1	9.2
50°-60°	313.6	7.5
60°-70°	211.5	5.1
70°-80°	106.1	2.5
80°-90°	29.3	0.7
90°-100°	47.0	1.1
100°-110°	142.4	3.4
110°-120°	242.3	5.8
120°-130°	318.8	7.7
130°-140°	358.4	8.6
140°-150°	352.3	8.5
150°-160°	296.6	7.1
160°-170°	197.5	4.7
170°-180°	69.1	1.7
0°-30°	691.5	16.6
0°-40°	1092.0	26.3
0°-60°	1788.8	43.0
0°-90°	2135.6	51.3
90°-120°	431.8	10.4
90°-150°	1461.2	35.1
90°-180°	2024.0	48.7
0°-180°	4160.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	945	945	945	945	945	
5°	945	941	932	938	937	90
15°	901	892	871	867	862	254
25°	820	801	765	749	741	377
35°	709	682	634	601	588	444
45°	583	548	490	446	428	450
55°	443	405	340	296	280	397
65°	303	260	201	163	155	299
75°	160	123	81	74	72	171
85°	41	24	22	20	20	44
90°	1	6	14	16	17	5
95°	34	38	42	45	45	37
105°	129	130	136	136	137	138
115°	244	246	244	245	244	241
125°	357	359	358	355	353	318
135°	463	467	466	464	463	357
145°	562	563	565	564	562	351
155°	643	643	644	646	642	296
165°	701	699	699	702	698	198
175°	729	727	727	730	726	69
180°	731	731	731	731	731	

TEST NUMBER: P1012656

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	944.6	944.6	944.6	944.6	944.6
2.5°	948.4	945.4	936.2	944.6	943.1
5°	944.6	940.8	931.6	938.5	936.9
7.5°	937.7	933.9	922.4	927.0	924.7
10°	928.5	923.1	909.4	910.1	906.3
12.5°	915.5	909.4	891.7	891.0	886.4
15°	900.9	892.5	871.0	867.2	861.9
17.5°	883.3	874.1	847.3	839.6	832.0
20°	863.4	851.1	822.0	812.1	802.9
22.5°	841.2	826.6	795.2	782.2	773.8
25°	819.7	800.6	765.3	749.2	740.8
27.5°	793.7	773.0	734.7	713.2	700.2
30°	766.9	743.9	701.0	674.9	662.7
32.5°	740.0	713.2	667.3	638.2	625.1
35°	709.4	681.8	634.3	601.4	587.6
37.5°	678.8	648.9	599.1	562.3	545.5
40°	649.6	615.9	561.5	521.7	504.1
42.5°	616.7	583.0	526.3	481.9	466.6
45°	583.0	548.5	489.5	445.9	427.5
47.5°	550.1	511.7	453.5	406.0	389.9
50°	513.3	477.3	415.2	367.7	350.1
52.5°	480.3	440.5	379.2	329.4	314.1
55°	442.8	405.3	340.1	295.7	280.4
57.5°	409.1	368.5	302.6	260.5	247.4
60°	373.9	331.7	268.1	226.8	213.7
62.5°	338.6	296.5	232.9	194.6	180.8
65°	302.6	260.5	200.7	163.2	154.8
67.5°	266.6	223.7	165.5	137.1	127.9
70°	231.4	190.0	136.4	109.6	101.1
72.5°	196.1	155.5	108.0	87.3	85.0
75°	160.1	123.3	81.2	73.5	72.0
77.5°	127.2	93.5	63.6	59.0	57.5
80°	95.8	64.4	48.3	46.0	44.4
82.5°	65.9	39.8	34.5	32.2	32.2
85°	40.6	23.7	21.5	19.9	19.9
87.5°	18.4	10.0	10.0	9.2	8.4
90°	0.6	6.3	13.8	16.1	17.2
92.5°	17.2	20.7	24.1	25.8	24.7
95°	33.9	37.9	42.5	44.8	44.8
97.5°	55.7	58.5	62.0	64.9	64.3
100°	78.1	81.5	84.4	86.1	87.2
102.5°	103.9	105.6	109.6	111.3	110.8
105°	129.1	130.3	135.5	135.5	136.6
107.5°	159.0	159.6	161.9	163.6	163.0
110°	186.5	187.7	188.8	191.1	190.0



TEST NUMBER: P1012656

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	215.2	215.8	215.8	218.7	218.7
115°	243.9	245.6	244.5	245.1	244.5
117.5°	273.2	273.8	272.6	272.6	270.9
120°	300.2	303.6	300.7	300.2	299.0
122.5°	328.3	330.6	329.4	327.7	326.0
125°	357.0	358.7	357.6	355.3	353.0
127.5°	383.4	386.8	385.7	382.2	380.0
130°	409.8	414.4	412.7	410.4	406.4
132.5°	436.2	440.8	439.6	436.8	433.9
135°	463.2	466.6	466.0	463.7	462.6
137.5°	487.9	490.7	492.4	489.6	487.9
140°	513.7	516.6	517.1	516.6	512.5
142.5°	537.2	540.1	541.2	540.7	537.8
145°	561.9	563.0	564.8	564.2	561.9
147.5°	583.1	585.4	587.1	587.1	583.7
150°	605.5	606.7	607.8	607.8	604.4
152.5°	623.9	625.6	626.2	627.3	624.5
155°	643.4	643.4	644.0	646.3	642.2
157.5°	660.0	659.5	660.0	662.3	658.9
160°	675.5	674.4	674.4	677.3	675.0
162.5°	689.3	687.6	688.2	691.0	687.0
165°	700.8	699.1	699.1	702.5	698.5
167.5°	710.5	708.3	708.8	712.3	708.8
170°	718.6	716.3	716.3	720.3	716.3
172.5°	724.9	722.6	722.6	726.0	722.0
175°	728.9	726.6	726.6	730.1	726.0
177.5°	731.2	728.9	728.9	732.4	728.3
180°	730.6	730.6	730.6	730.6	730.6

(END OF REPORT)