

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012657

Luminaire Tested: S123RDIP-B560D585UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012657
REPORT IS A COMBINATION OF REPORTS P993466 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D585UB35-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4273.0 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012657

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012657

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83		69	69	69		56
1	98	94	90	87	90	87	84	81	74	71	69		61	60	58		50
2	90	82	76	71	82	76	71	67	65	61	58		54	52	49		44
3	82	73	66	60	75	67	61	56	57	53	49		48	45	42		40
4	75	65	57	51	69	60	53	48	51	46	42		43	39	36		36
5	69	58	50	44	64	54	47	41	46	41	36		39	35	32		32
6	64	52	44	38	59	48	41	36	42	36	32		35	31	28		29
7	59	47	39	34	54	44	37	32	38	32	28		32	28	25		27
8	55	43	35	30	50	40	33	28	34	29	25		29	25	22		25
9	51	39	32	27	47	36	30	25	32	26	23		27	23	20		23
10	48	36	29	24	44	33	27	23	29	24	20		25	21	18		21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10168	10168	10168
5°	10184	9808	9781
10°	10104	9440	9253
15°	9972	8983	8675
20°	9801	8487	8028
25°	9623	7972	7415
30°	9396	7425	6691
35°	9161	6886	6032
40°	8940	6301	5303
45°	8658	5730	4648
50°	8347	5119	3970
55°	8023	4466	3349
60°	7715	3796	2718
65°	7315	3108	2122
70°	6814	2351	1516
75°	6090	1592	1201
80°	5201	1107	842
85°	3900	599	441

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8658 cd/sqm

TEST NUMBER: P1012657

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.8	2.1
10°-20°	247.0	5.8
20°-30°	355.7	8.3
30°-40°	400.5	9.4
40°-50°	383.1	9.0
50°-60°	313.6	7.3
60°-70°	211.5	4.9
70°-80°	106.1	2.5
80°-90°	29.3	0.7
90°-100°	161.1	3.8
100°-110°	450.3	10.5
110°-120°	439.1	10.3
120°-130°	349.6	8.2
130°-140°	276.0	6.5
140°-150°	205.9	4.8
150°-160°	143.6	3.4
160°-170°	84.4	2.0
170°-180°	27.4	0.6
0°-30°	691.5	16.2
0°-40°	1092.0	25.6
0°-60°	1788.8	41.9
0°-90°	2135.6	50.0
90°-120°	1050.4	24.6
90°-150°	1881.9	44.0
90°-180°	2137.0	50.0
0°-180°	4273.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	945	945	945	945	945	
5°	945	941	932	938	937	90
15°	901	892	871	867	862	254
25°	820	801	765	749	741	377
35°	709	682	634	601	588	444
45°	583	548	490	446	428	450
55°	443	405	340	296	280	397
65°	303	260	201	163	155	299
75°	160	123	81	74	72	171
85°	41	24	22	20	20	44
90°	1	7	14	16	17	4
95°	20	63	340	99	67	21
105°	67	98	461	807	730	71
115°	118	147	353	774	888	116
125°	164	193	329	597	700	145
135°	192	229	325	492	568	148
145°	219	250	321	403	444	137
155°	248	268	310	353	368	114
165°	271	279	297	315	321	77
175°	283	283	285	289	289	27
180°	284	284	284	284	284	

TEST NUMBER: P1012657

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	944.6	944.6	944.6	944.6	944.6
2.5°	948.4	945.4	936.2	944.6	943.1
5°	944.6	940.8	931.6	938.5	936.9
7.5°	937.7	933.9	922.4	927.0	924.7
10°	928.5	923.1	909.4	910.1	906.3
12.5°	915.5	909.4	891.7	891.0	886.4
15°	900.9	892.5	871.0	867.2	861.9
17.5°	883.3	874.1	847.3	839.6	832.0
20°	863.4	851.1	822.0	812.1	802.9
22.5°	841.2	826.6	795.2	782.2	773.8
25°	819.7	800.6	765.3	749.2	740.8
27.5°	793.7	773.0	734.7	713.2	700.2
30°	766.9	743.9	701.0	674.9	662.7
32.5°	740.0	713.2	667.3	638.2	625.1
35°	709.4	681.8	634.3	601.4	587.6
37.5°	678.8	648.9	599.1	562.3	545.5
40°	649.6	615.9	561.5	521.7	504.1
42.5°	616.7	583.0	526.3	481.9	466.6
45°	583.0	548.5	489.5	445.9	427.5
47.5°	550.1	511.7	453.5	406.0	389.9
50°	513.3	477.3	415.2	367.7	350.1
52.5°	480.3	440.5	379.2	329.4	314.1
55°	442.8	405.3	340.1	295.7	280.4
57.5°	409.1	368.5	302.6	260.5	247.4
60°	373.9	331.7	268.1	226.8	213.7
62.5°	338.6	296.5	232.9	194.6	180.8
65°	302.6	260.5	200.7	163.2	154.8
67.5°	266.6	223.7	165.5	137.1	127.9
70°	231.4	190.0	136.4	109.6	101.1
72.5°	196.1	155.5	108.0	87.3	85.0
75°	160.1	123.3	81.2	73.5	72.0
77.5°	127.2	93.5	63.6	59.0	57.5
80°	95.8	64.4	48.3	46.0	44.4
82.5°	65.9	39.8	34.5	32.2	32.2
85°	40.6	23.7	21.5	19.9	19.9
87.5°	18.4	10.0	10.0	9.2	8.4
90°	1.1	6.9	14.3	16.0	16.6
92.5°	8.6	34.4	106.7	36.4	30.4
95°	19.5	63.4	340.3	99.2	66.6
97.5°	31.0	72.6	523.4	249.6	136.6
100°	42.5	80.1	543.4	522.2	359.8
102.5°	54.5	88.6	506.1	699.2	569.8
105°	66.6	98.4	461.4	806.8	730.0
107.5°	79.2	109.9	421.8	854.2	834.4
110°	93.0	121.6	389.1	855.6	894.1



TEST NUMBER: P1012657

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	105.6	134.0	367.3	823.2	906.1
115°	117.6	146.6	352.9	773.8	887.8
117.5°	129.7	158.6	343.2	721.0	847.6
120°	142.3	170.8	336.9	671.2	794.8
122.5°	153.2	182.2	332.8	631.8	745.4
125°	163.6	193.2	329.4	596.8	700.1
127.5°	171.6	203.4	327.7	568.2	661.1
130°	179.0	212.6	326.0	541.7	629.0
132.5°	184.8	221.0	325.4	517.0	597.4
135°	191.7	228.6	324.8	491.6	567.6
137.5°	198.0	235.0	323.7	467.4	536.0
140°	204.3	240.8	323.1	443.8	502.7
142.5°	211.2	245.9	321.9	422.4	471.7
145°	218.6	250.5	320.8	403.2	443.6
147.5°	226.1	255.4	319.1	388.2	419.5
150°	233.6	259.4	316.8	375.0	398.8
152.5°	241.0	263.7	313.9	363.5	381.6
155°	248.5	268.0	310.5	353.0	367.8
157.5°	254.2	271.8	307.6	342.6	354.6
160°	261.1	274.9	304.1	333.1	342.0
162.5°	266.3	277.2	300.7	324.2	330.5
165°	271.4	279.2	297.3	315.4	320.8
167.5°	275.5	280.9	293.8	307.5	311.0
170°	278.9	281.8	290.4	300.7	302.4
172.5°	281.2	282.6	287.5	294.7	294.4
175°	282.9	283.2	285.2	289.2	288.7
177.5°	284.1	283.5	283.5	285.8	284.6
180°	283.5	283.5	283.5	283.5	283.5

(END OF REPORT)