

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012662

Luminaire Tested: S123RDIP-B560D585UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012662
REPORT IS A COMBINATION OF REPORTS P993471 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D585UB40-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4119.0 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012662

CATALOG NUMBER: S123RDIP-B560D585UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012662

CATALOG NUMBER: S123RDIP-B560D585UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	57
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	51	50	49	49	49	49
2	90	83	77	72	83	77	71	67	65	62	58	55	52	50	45	44	42	42	42	42
3	82	73	66	60	76	68	61	56	58	53	49	49	45	43	41	38	36	36	36	36
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	36	34	31	31	31	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	27	27	27
6	64	52	44	38	59	49	41	36	42	36	32	36	31	28	30	27	24	24	24	24
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	27	24	22	22	22	22
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	20	20	20
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	23	20	18	18	18	18
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	18	16	16	16	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10067	10067	10067
5°	10084	9711	9685
10°	10005	9346	9162
15°	9875	8895	8589
20°	9704	8404	7949
25°	9529	7894	7342
30°	9303	7352	6625
35°	9071	6819	5972
40°	8853	6239	5251
45°	8574	5673	4603
50°	8264	5069	3932
55°	7944	4422	3316
60°	7639	3759	2691
65°	7242	3077	2100
70°	6747	2327	1501
75°	6029	1576	1190
80°	5147	1096	834
85°	3861	590	437

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8574 cd/sqm

TEST NUMBER: P1012662

CATALOG NUMBER: S123RDIP-B560D585UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.9	2.1
10°-20°	244.6	5.9
20°-30°	352.2	8.5
30°-40°	396.6	9.6
40°-50°	379.4	9.2
50°-60°	310.5	7.5
60°-70°	209.4	5.1
70°-80°	105.0	2.5
80°-90°	29.0	0.7
90°-100°	46.6	1.1
100°-110°	141.0	3.4
110°-120°	240.0	5.8
120°-130°	315.7	7.7
130°-140°	354.8	8.6
140°-150°	348.8	8.5
150°-160°	293.7	7.1
160°-170°	195.5	4.7
170°-180°	68.5	1.7
0°-30°	684.7	16.6
0°-40°	1081.3	26.3
0°-60°	1771.2	43.0
0°-90°	2114.5	51.3
90°-120°	427.5	10.4
90°-150°	1446.8	35.1
90°-180°	2004.0	48.7
0°-180°	4119.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	935	935	935	935	935	
5°	935	932	922	929	928	89
15°	892	884	862	859	853	251
25°	812	793	758	742	734	373
35°	702	675	628	596	582	440
45°	577	543	485	442	423	445
55°	438	401	337	293	278	393
65°	300	258	199	162	153	297
75°	158	122	80	73	71	169
85°	40	24	21	20	20	44
90°	1	6	14	16	17	5
95°	34	38	42	44	44	37
105°	128	129	134	134	135	137
115°	242	243	242	243	242	239
125°	354	355	354	352	350	315
135°	459	462	461	459	458	353
145°	556	558	559	559	556	347
155°	637	637	638	640	636	293
165°	694	692	692	696	692	196
175°	722	719	719	723	719	69
180°	723	723	723	723	723	

TEST NUMBER: P1012662

CATALOG NUMBER: S123RDIP-B560D585UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	935.3	935.3	935.3	935.3	935.3
2.5°	939.1	936.1	927.0	935.3	933.8
5°	935.3	931.5	922.4	929.2	927.7
7.5°	928.5	924.7	913.3	917.8	915.6
10°	919.4	914.1	900.4	901.2	897.4
12.5°	906.5	900.4	883.0	882.2	877.6
15°	892.1	883.7	862.5	858.7	853.4
17.5°	874.6	865.5	839.0	831.4	823.8
20°	854.9	842.8	813.9	804.1	795.0
22.5°	832.9	818.5	787.4	774.5	766.1
25°	811.7	792.7	757.8	741.9	733.5
27.5°	785.9	765.4	727.5	706.2	693.3
30°	759.3	736.6	694.1	668.3	656.1
32.5°	732.8	706.2	660.7	631.9	619.0
35°	702.4	675.1	628.1	595.5	581.8
37.5°	672.1	642.5	593.2	556.8	540.1
40°	643.3	609.9	556.0	516.6	499.1
42.5°	610.6	577.3	521.1	477.1	462.0
45°	577.3	543.1	484.7	441.5	423.3
47.5°	544.6	506.7	449.1	402.0	386.1
50°	508.2	472.6	411.1	364.1	346.7
52.5°	475.6	436.2	375.5	326.2	311.0
55°	438.4	401.3	336.8	292.8	277.6
57.5°	405.1	364.9	299.6	257.9	245.0
60°	370.2	328.5	265.5	224.5	211.6
62.5°	335.3	293.6	230.6	192.7	179.0
65°	299.6	257.9	198.7	161.6	153.2
67.5°	264.0	221.5	163.8	135.8	126.7
70°	229.1	188.1	135.0	108.5	100.1
72.5°	194.2	154.0	107.0	86.5	84.2
75°	158.5	122.1	80.4	72.8	71.3
77.5°	125.9	92.5	63.0	58.4	56.9
80°	94.8	63.7	47.8	45.5	44.0
82.5°	65.2	39.4	34.1	31.9	31.9
85°	40.2	23.5	21.2	19.7	19.7
87.5°	18.2	9.9	9.9	9.1	8.3
90°	0.6	6.3	13.6	15.9	17.0
92.5°	17.0	20.5	23.9	25.6	24.4
95°	33.5	37.5	42.1	44.3	44.3
97.5°	55.1	58.0	61.4	64.2	63.6
100°	77.3	80.7	83.5	85.2	86.4
102.5°	102.9	104.6	108.5	110.2	109.7
105°	127.9	129.0	134.1	134.1	135.3
107.5°	157.4	158.0	160.3	162.0	161.4
110°	184.7	185.8	187.0	189.2	188.1

TEST NUMBER: P1012662

CATALOG NUMBER: S123RDIP-B560D585UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	213.1	213.7	213.7	216.5	216.5
115°	241.5	243.2	242.1	242.7	242.1
117.5°	270.5	271.1	269.9	269.9	268.2
120°	297.2	300.6	297.8	297.2	296.1
122.5°	325.1	327.3	326.2	324.5	322.8
125°	353.5	355.2	354.0	351.8	349.5
127.5°	379.6	383.0	381.9	378.5	376.2
130°	405.8	410.3	408.6	406.3	402.3
132.5°	431.9	436.4	435.3	432.5	429.6
135°	458.6	462.0	461.4	459.2	458.0
137.5°	483.0	485.9	487.6	484.7	483.0
140°	508.6	511.5	512.0	511.5	507.5
142.5°	531.9	534.8	535.9	535.3	532.5
145°	556.3	557.5	559.2	558.6	556.3
147.5°	577.4	579.6	581.4	581.4	577.9
150°	599.5	600.7	601.8	601.8	598.4
152.5°	617.7	619.4	620.0	621.1	618.3
155°	637.0	637.0	637.6	639.9	635.9
157.5°	653.5	653.0	653.5	655.8	652.4
160°	668.9	667.7	667.7	670.6	668.3
162.5°	682.5	680.8	681.4	684.2	680.2
165°	693.9	692.2	692.2	695.6	691.6
167.5°	703.5	701.3	701.8	705.2	701.8
170°	711.5	709.2	709.2	713.2	709.2
172.5°	717.7	715.5	715.5	718.9	714.9
175°	721.7	719.4	719.4	722.9	718.9
177.5°	724.0	721.7	721.7	725.1	721.1
180°	723.4	723.4	723.4	723.4	723.4

(END OF REPORT)