

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012295

Luminaire Tested: S123RDIP-B1165D1195UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012295
REPORT IS A COMBINATION OF REPORTS P992964 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1165D1195UB27-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8641.9 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012295

CATALOG NUMBER: S123RDIP-B1165D1195UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012295

CATALOG NUMBER: S123RDIP-B1165D1195UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56
1	98	94	90	87	91	87	84	81	74	71	69	62	60	59	50	49	48
2	90	82	76	71	83	76	71	67	65	61	58	54	52	49	45	43	41
3	82	73	66	60	75	68	61	56	58	53	49	48	45	42	40	38	35
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31
5	69	58	50	44	64	54	47	41	46	41	36	39	35	32	32	29	27
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19
9	51	39	32	27	47	36	30	25	32	26	23	27	23	20	23	20	17
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20730	20730	20730
5°	20764	19997	19943
10°	20601	19245	18866
15°	20334	18316	17686
20°	19983	17305	16368
25°	19621	16255	15119
30°	19156	15137	13642
35°	18679	14040	12298
40°	18230	12848	10813
45°	17654	11683	9477
50°	17017	10438	8094
55°	16358	9106	6828
60°	15727	7740	5542
65°	14915	6338	4325
70°	13891	4792	3092
75°	12420	3246	2449
80°	10597	2255	1718
85°	7953	1217	900

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17654 cd/sqm

TEST NUMBER: P1012295

CATALOG NUMBER: S123RDIP-B1165D1195UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	2.1
10°-20°	503.7	5.8
20°-30°	725.2	8.4
30°-40°	816.6	9.4
40°-50°	781.2	9.0
50°-60°	639.4	7.4
60°-70°	431.1	5.0
70°-80°	216.2	2.5
80°-90°	59.7	0.7
90°-100°	323.2	3.7
100°-110°	903.3	10.5
110°-120°	880.8	10.2
120°-130°	701.4	8.1
130°-140°	553.6	6.4
140°-150°	413.0	4.8
150°-160°	288.1	3.3
160°-170°	169.3	2.0
170°-180°	55.1	0.6
0°-30°	1409.9	16.3
0°-40°	2226.5	25.8
0°-60°	3647.1	42.2
0°-90°	4354.2	50.4
90°-120°	2107.3	24.4
90°-150°	3775.3	43.7
90°-180°	4288.0	49.6
0°-180°	8641.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1926	1926	1926	1926	1926	
5°	1926	1918	1899	1913	1910	183
15°	1837	1820	1776	1768	1757	518
25°	1671	1632	1560	1528	1510	769
35°	1446	1390	1293	1226	1198	905
45°	1189	1118	998	909	872	917
55°	903	826	694	603	572	810
65°	617	531	409	333	316	611
75°	326	252	166	150	147	348
85°	83	48	44	41	41	91
90°	2	14	29	32	33	8
95°	39	127	683	199	134	41
105°	134	197	926	1619	1464	142
115°	236	294	708	1552	1781	234
125°	328	387	661	1197	1404	291
135°	384	459	652	986	1139	297
145°	439	502	644	809	890	275
155°	498	538	623	708	738	229
165°	544	560	596	633	644	153
175°	568	568	572	580	579	54
180°	569	569	569	569	569	

TEST NUMBER: P1012295

CATALOG NUMBER: S123RDIP-B1165D1195UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1925.9	1925.9	1925.9	1925.9	1925.9
2.5°	1933.7	1927.5	1908.7	1925.9	1922.8
5°	1925.9	1918.1	1899.4	1913.4	1910.3
7.5°	1911.9	1904.1	1880.6	1890.0	1885.3
10°	1893.1	1882.2	1854.1	1855.6	1847.8
12.5°	1866.6	1854.1	1818.1	1816.6	1807.2
15°	1836.9	1819.7	1776.0	1768.2	1757.2
17.5°	1801.0	1782.2	1727.6	1711.9	1696.3
20°	1760.4	1735.4	1676.0	1655.7	1637.0
22.5°	1715.1	1685.4	1621.3	1594.8	1577.6
25°	1671.3	1632.3	1560.4	1527.6	1510.4
27.5°	1618.2	1576.0	1497.9	1454.2	1427.7
30°	1563.5	1516.7	1429.2	1376.1	1351.1
32.5°	1508.9	1454.2	1360.5	1301.1	1274.6
35°	1446.4	1390.2	1293.3	1226.2	1198.0
37.5°	1383.9	1323.0	1221.5	1146.5	1112.1
40°	1324.6	1255.8	1144.9	1063.7	1027.8
42.5°	1257.4	1188.7	1073.1	982.5	951.2
45°	1188.7	1118.4	998.1	909.1	871.6
47.5°	1121.5	1043.4	924.7	827.8	795.0
50°	1046.5	973.1	846.6	749.8	713.8
52.5°	979.4	898.1	773.2	671.7	640.4
55°	902.8	826.3	693.5	602.9	571.7
57.5°	834.1	751.3	617.0	531.1	504.5
60°	762.2	676.3	546.7	462.3	435.8
62.5°	690.4	604.5	474.8	396.7	368.6
65°	617.0	531.1	409.2	332.7	315.5
67.5°	543.6	456.1	337.4	279.6	260.9
70°	471.7	387.4	278.0	223.4	206.2
72.5°	399.9	317.1	220.2	178.1	173.4
75°	326.5	251.5	165.6	150.0	146.8
77.5°	259.3	190.6	129.6	120.3	117.1
80°	195.2	131.2	98.4	93.7	90.6
82.5°	134.3	81.2	70.3	65.6	65.6
85°	82.8	48.4	43.7	40.6	40.6
87.5°	37.5	20.3	20.3	18.7	17.2
90°	2.3	13.8	28.8	32.2	33.4
92.5°	17.3	69.1	214.1	73.1	61.0
95°	39.1	127.2	682.7	199.2	133.5
97.5°	62.2	145.6	1049.9	500.8	274.0
100°	85.2	160.6	1090.2	1047.6	721.8
102.5°	109.4	177.8	1015.4	1402.8	1143.2
105°	133.5	197.4	925.6	1618.6	1464.4
107.5°	158.9	220.5	846.1	1713.6	1673.9
110°	186.5	244.0	780.5	1716.5	1793.6



TEST NUMBER: P1012295

CATALOG NUMBER: S123RDIP-B1165D1195UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	211.8	268.8	736.8	1651.4	1817.8
115°	236.0	294.2	708.0	1552.4	1780.9
117.5°	260.2	318.3	688.4	1446.6	1700.4
120°	285.5	342.5	675.8	1346.4	1594.4
122.5°	307.4	365.6	667.7	1267.5	1495.4
125°	328.1	387.4	660.8	1197.2	1404.5
127.5°	344.2	408.2	657.3	1139.7	1326.2
130°	359.2	426.6	653.9	1086.8	1261.7
132.5°	370.7	443.2	652.7	1037.2	1198.4
135°	384.5	458.8	651.6	986.0	1138.6
137.5°	397.2	471.4	649.3	937.6	1075.2
140°	409.8	482.9	648.1	890.4	1008.5
142.5°	423.7	493.3	645.8	847.3	946.3
145°	438.6	502.5	643.5	808.7	889.9
147.5°	453.6	512.3	640.1	778.8	841.5
150°	468.5	520.4	635.5	752.3	800.1
152.5°	483.5	529.0	629.7	729.3	765.6
155°	498.5	537.7	622.8	708.0	737.9
157.5°	510.0	545.1	617.1	687.2	711.5
160°	523.8	551.4	610.1	668.3	686.1
162.5°	534.2	556.0	603.2	650.4	663.1
165°	544.5	560.0	596.3	632.6	643.5
167.5°	552.6	563.5	589.4	617.1	624.0
170°	559.5	565.2	582.5	603.2	606.7
172.5°	564.1	567.0	576.8	591.2	590.6
175°	567.6	568.2	572.2	580.2	579.1
177.5°	569.9	568.7	568.7	573.3	571.0
180°	568.7	568.7	568.7	568.7	568.7

(END OF REPORT)