

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012691

Luminaire Tested: S123RDIP-B560D805UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012691
REPORT IS A COMBINATION OF REPORTS P993512 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D805UB40-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4942.6 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012691

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012691

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	96	92	89	85	88	84	81	78	70	68	66	57	55	54	44	43	42
2	88	81	75	70	80	74	69	65	62	58	55	50	47	45	39	38	36
3	80	71	64	59	73	65	59	54	55	50	46	44	41	39	35	33	31
4	74	63	56	50	67	58	51	46	49	44	40	40	36	33	31	29	27
5	68	56	49	43	62	52	45	40	44	38	34	36	32	29	28	26	24
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21
7	58	46	38	33	53	42	35	31	36	30	26	29	25	23	24	21	19
8	54	42	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10067	10067	10067
5°	10084	9711	9685
10°	10005	9346	9162
15°	9875	8895	8589
20°	9704	8404	7949
25°	9529	7894	7342
30°	9303	7352	6625
35°	9071	6819	5972
40°	8853	6239	5251
45°	8574	5673	4603
50°	8264	5069	3932
55°	7944	4422	3316
60°	7639	3759	2691
65°	7242	3077	2100
70°	6747	2327	1501
75°	6029	1576	1190
80°	5147	1096	834
85°	3861	590	437

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8574 cd/sqm

TEST NUMBER: P1012691

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.9	1.8
10°-20°	244.6	4.9
20°-30°	352.2	7.1
30°-40°	396.6	8.0
40°-50°	379.4	7.7
50°-60°	310.5	6.3
60°-70°	209.4	4.2
70°-80°	105.0	2.1
80°-90°	29.5	0.6
90°-100°	213.1	4.3
100°-110°	595.7	12.1
110°-120°	580.8	11.8
120°-130°	462.5	9.4
130°-140°	365.1	7.4
140°-150°	272.4	5.5
150°-160°	190.0	3.8
160°-170°	111.6	2.3
170°-180°	36.3	0.7
0°-30°	684.7	13.9
0°-40°	1081.3	21.9
0°-60°	1771.2	35.8
0°-90°	2115.1	42.8
90°-120°	1389.6	28.1
90°-150°	2489.6	50.4
90°-180°	2828.0	57.2
0°-180°	4942.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	935	935	935	935	935	
5°	935	932	922	929	928	89
15°	892	884	862	859	853	251
25°	812	793	758	742	734	373
35°	702	675	628	596	582	440
45°	577	543	485	442	423	445
55°	438	401	337	293	278	393
65°	300	258	199	162	153	297
75°	158	122	80	73	71	169
85°	40	24	21	20	20	44
90°	2	9	19	21	22	4
95°	26	84	450	131	88	27
105°	88	130	610	1067	966	94
115°	156	194	467	1024	1174	154
125°	216	255	436	790	926	192
135°	254	303	430	650	751	196
145°	289	331	424	533	587	181
155°	329	354	411	467	487	151
165°	359	369	393	417	424	101
175°	374	375	377	383	382	36
180°	375	375	375	375	375	

TEST NUMBER: P1012691

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	935.3	935.3	935.3	935.3	935.3
2.5°	939.1	936.1	927.0	935.3	933.8
5°	935.3	931.5	922.4	929.2	927.7
7.5°	928.5	924.7	913.3	917.8	915.6
10°	919.4	914.1	900.4	901.2	897.4
12.5°	906.5	900.4	883.0	882.2	877.6
15°	892.1	883.7	862.5	858.7	853.4
17.5°	874.6	865.5	839.0	831.4	823.8
20°	854.9	842.8	813.9	804.1	795.0
22.5°	832.9	818.5	787.4	774.5	766.1
25°	811.7	792.7	757.8	741.9	733.5
27.5°	785.9	765.4	727.5	706.2	693.3
30°	759.3	736.6	694.1	668.3	656.1
32.5°	732.8	706.2	660.7	631.9	619.0
35°	702.4	675.1	628.1	595.5	581.8
37.5°	672.1	642.5	593.2	556.8	540.1
40°	643.3	609.9	556.0	516.6	499.1
42.5°	610.6	577.3	521.1	477.1	462.0
45°	577.3	543.1	484.7	441.5	423.3
47.5°	544.6	506.7	449.1	402.0	386.1
50°	508.2	472.6	411.1	364.1	346.7
52.5°	475.6	436.2	375.5	326.2	311.0
55°	438.4	401.3	336.8	292.8	277.6
57.5°	405.1	364.9	299.6	257.9	245.0
60°	370.2	328.5	265.5	224.5	211.6
62.5°	335.3	293.6	230.6	192.7	179.0
65°	299.6	257.9	198.7	161.6	153.2
67.5°	264.0	221.5	163.8	135.8	126.7
70°	229.1	188.1	135.0	108.5	100.1
72.5°	194.2	154.0	107.0	86.5	84.2
75°	158.5	122.1	80.4	72.8	71.3
77.5°	125.9	92.5	63.0	58.4	56.9
80°	94.8	63.7	47.8	45.5	44.0
82.5°	65.2	39.4	34.1	31.9	31.9
85°	40.2	23.5	21.2	19.7	19.7
87.5°	18.2	9.9	9.9	9.1	8.3
90°	1.5	9.2	19.0	21.2	22.0
92.5°	11.4	45.6	141.2	48.2	40.2
95°	25.8	83.9	450.2	131.4	88.1
97.5°	41.0	96.1	692.3	330.2	180.7
100°	56.2	105.9	718.9	690.8	476.0
102.5°	72.1	117.3	669.6	925.0	753.8
105°	88.1	130.2	610.4	1067.4	965.6
107.5°	104.8	145.4	558.0	1130.0	1103.8
110°	123.0	161.0	514.7	1131.9	1182.7

TEST NUMBER: P1012691

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	139.7	177.2	485.9	1089.0	1198.7
115°	155.6	194.0	466.9	1023.7	1174.4
117.5°	171.6	209.9	454.0	953.9	1121.3
120°	188.3	225.8	445.6	887.8	1051.4
122.5°	202.7	241.0	440.3	835.8	986.1
125°	216.4	255.4	435.7	789.5	926.2
127.5°	227.0	269.2	433.5	751.6	874.5
130°	236.9	281.2	431.2	716.6	832.0
132.5°	244.4	292.2	430.4	684.0	790.3
135°	253.6	302.6	429.7	650.2	750.8
137.5°	261.9	310.9	428.2	618.4	709.0
140°	270.3	318.5	427.4	587.2	665.0
142.5°	279.4	325.3	425.9	558.8	624.0
145°	289.2	331.4	424.4	533.3	586.8
147.5°	299.1	337.8	422.1	513.6	554.9
150°	309.0	343.2	419.0	496.1	527.6
152.5°	318.8	348.8	415.3	480.9	504.8
155°	328.7	354.5	410.7	466.8	486.6
157.5°	336.3	359.5	406.9	453.2	469.2
160°	345.4	363.6	402.3	440.6	452.5
162.5°	352.2	366.6	397.8	428.9	437.3
165°	359.1	369.4	393.2	417.2	424.4
167.5°	364.4	371.6	388.7	406.9	411.5
170°	368.9	372.8	384.1	397.8	400.1
172.5°	372.0	373.9	380.3	389.8	389.4
175°	374.3	374.6	377.3	382.6	381.9
177.5°	375.8	375.0	375.0	378.1	376.5
180°	375.0	375.0	375.0	375.0	375.0

(END OF REPORT)