

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012709

Luminaire Tested: S123RDIP-B775D1025UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012709
REPORT IS A COMBINATION OF REPORTS P993540 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B775D1025UB30-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6615.6 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012709

CATALOG NUMBER: S123RDIP-B775D1025UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012709

CATALOG NUMBER: S123RDIP-B775D1025UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	93	89	86	89	85	82	79	71	68	66	58	56	55	45	44	44
2	88	81	75	70	81	75	70	65	62	59	55	51	48	46	40	39	37
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28
5	68	57	49	43	62	52	45	40	44	39	35	36	33	29	29	26	24
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	27	33	28	24	28	23	21	22	19	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	19	21	18	16
10	47	35	28	23	43	33	26	22	28	23	19	23	20	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13969	13969	13969
5°	13992	13475	13439
10°	13882	12969	12713
15°	13702	12343	11918
20°	13465	11661	11030
25°	13221	10953	10188
30°	12909	10201	9194
35°	12588	9461	8287
40°	12284	8657	7286
45°	11896	7873	6386
50°	11467	7034	5455
55°	11024	6136	4601
60°	10600	5216	3735
65°	10051	4272	2915
70°	9362	3230	2083
75°	8369	2188	1650
80°	7145	1520	1157
85°	5360	821	607

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11896 cd/sqm

TEST NUMBER: P1012709

CATALOG NUMBER: S123RDIP-B775D1025UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.0	1.8
10°-20°	339.4	5.1
20°-30°	488.7	7.4
30°-40°	550.3	8.3
40°-50°	526.4	8.0
50°-60°	430.9	6.5
60°-70°	290.5	4.4
70°-80°	145.7	2.2
80°-90°	40.8	0.6
90°-100°	277.4	4.2
100°-110°	775.4	11.7
110°-120°	756.1	11.4
120°-130°	602.1	9.1
130°-140°	475.2	7.2
140°-150°	354.6	5.4
150°-160°	247.4	3.7
160°-170°	145.3	2.2
170°-180°	47.3	0.7
0°-30°	950.1	14.4
0°-40°	1500.4	22.7
0°-60°	2457.7	37.1
0°-90°	2934.7	44.4
90°-120°	1809.0	27.3
90°-150°	3240.9	49.0
90°-180°	3681.0	55.6
0°-180°	6615.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1298	1298	1298	1298	1298	
5°	1298	1293	1280	1289	1287	123
15°	1238	1226	1197	1192	1184	349
25°	1126	1100	1052	1029	1018	518
35°	975	937	872	826	807	610
45°	801	754	673	613	587	618
55°	608	557	467	406	385	546
65°	416	358	276	224	213	411
75°	220	170	112	101	99	234
85°	56	33	30	27	27	61
90°	2	12	25	28	29	6
95°	34	109	586	171	115	36
105°	115	170	795	1389	1257	122
115°	203	252	608	1333	1529	201
125°	282	332	567	1028	1206	250
135°	330	394	559	846	977	255
145°	376	431	552	694	764	236
155°	428	462	535	608	634	197
165°	467	481	512	543	552	132
175°	487	488	491	498	497	46
180°	488	488	488	488	488	

TEST NUMBER: P1012709

CATALOG NUMBER: S123RDIP-B775D1025UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1297.8	1297.8	1297.8	1297.8	1297.8
2.5°	1303.1	1298.9	1286.2	1297.8	1295.7
5°	1297.8	1292.6	1279.9	1289.4	1287.3
7.5°	1288.3	1283.1	1267.3	1273.6	1270.5
10°	1275.7	1268.3	1249.4	1250.5	1245.2
12.5°	1257.8	1249.4	1225.2	1224.1	1217.8
15°	1237.8	1226.2	1196.8	1191.5	1184.1
17.5°	1213.6	1201.0	1164.1	1153.6	1143.1
20°	1186.2	1169.4	1129.4	1115.7	1103.1
22.5°	1155.7	1135.7	1092.6	1074.7	1063.1
25°	1126.2	1099.9	1051.5	1029.4	1017.8
27.5°	1090.5	1062.0	1009.4	979.9	962.0
30°	1053.6	1022.0	963.1	927.3	910.5
32.5°	1016.8	979.9	916.8	876.8	858.9
35°	974.7	936.8	871.5	826.3	807.3
37.5°	932.6	891.5	823.1	772.6	749.4
40°	892.6	846.3	771.5	716.8	692.6
42.5°	847.3	801.0	723.1	662.1	641.0
45°	801.0	753.6	672.6	612.6	587.3
47.5°	755.7	703.1	623.1	557.9	535.8
50°	705.2	655.8	570.5	505.2	481.0
52.5°	660.0	605.2	521.0	452.6	431.6
55°	608.4	556.8	467.3	406.3	385.2
57.5°	562.1	506.3	415.8	357.9	340.0
60°	513.7	455.8	368.4	311.6	293.7
62.5°	465.2	407.3	320.0	267.4	248.4
65°	415.8	357.9	275.8	224.2	212.6
67.5°	366.3	307.4	227.4	188.4	175.8
70°	317.9	261.0	187.4	150.5	138.9
72.5°	269.5	213.7	148.4	120.0	116.8
75°	220.0	169.5	111.6	101.0	98.9
77.5°	174.7	128.4	87.4	81.0	78.9
80°	131.6	88.4	66.3	63.2	61.0
82.5°	90.5	54.7	47.4	44.2	44.2
85°	55.8	32.6	29.5	27.4	27.4
87.5°	25.3	13.7	13.7	12.6	11.6
90°	2.0	11.9	24.7	27.7	28.7
92.5°	14.8	59.3	183.8	62.8	52.4
95°	33.6	109.2	586.0	171.0	114.6
97.5°	53.4	125.0	901.3	429.9	235.2
100°	73.1	137.8	935.9	899.4	619.6
102.5°	93.9	152.7	871.6	1204.2	981.3
105°	114.6	169.5	794.6	1389.4	1257.1
107.5°	136.4	189.2	726.4	1471.1	1436.9
110°	160.1	209.5	670.0	1473.5	1539.7

TEST NUMBER: P1012709

CATALOG NUMBER: S123RDIP-B775D1025UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	181.8	230.8	632.5	1417.6	1560.5
115°	202.6	252.5	607.8	1332.6	1528.8
117.5°	223.3	273.2	591.0	1241.8	1459.7
120°	245.1	294.0	580.1	1155.8	1368.7
122.5°	263.9	313.8	573.2	1088.0	1283.8
125°	281.7	332.5	567.3	1027.8	1205.7
127.5°	295.5	350.4	564.3	978.4	1138.5
130°	308.3	366.2	561.3	932.9	1083.1
132.5°	318.2	380.5	560.3	890.4	1028.8
135°	330.1	393.8	559.4	846.4	977.4
137.5°	341.0	404.6	557.4	804.9	923.0
140°	351.8	414.6	556.4	764.4	865.7
142.5°	363.7	423.4	554.4	727.4	812.4
145°	376.5	431.4	552.4	694.2	763.9
147.5°	389.4	439.8	549.5	668.6	722.4
150°	402.2	446.7	545.5	645.8	686.8
152.5°	415.1	454.1	540.6	626.1	657.2
155°	427.9	461.5	534.6	607.8	633.5
157.5°	437.8	468.0	529.7	590.0	610.7
160°	449.7	473.4	523.8	573.7	589.0
162.5°	458.6	477.4	517.8	558.3	569.2
165°	467.4	480.8	511.9	543.0	552.4
167.5°	474.4	483.8	506.0	529.7	535.6
170°	480.3	485.2	500.1	517.8	520.8
172.5°	484.2	486.7	495.1	507.5	507.0
175°	487.2	487.7	491.2	498.1	497.1
177.5°	489.2	488.2	488.2	492.2	490.2
180°	488.2	488.2	488.2	488.2	488.2

(END OF REPORT)