

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007474

Luminaire Tested: S123IP-B1025UB2750-4F0-XX-W2A-1_3500K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007474
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B1025UB2750-4F0-XX-W2A-1_3500K
Description: Define 3 Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3503.0 lumens
Efficiency: N/A
Efficacy: 122.9 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007474

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A-1_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1007474

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A-1_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007474

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A-1_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.7	0.1
90°-100°	81.3	2.3
100°-110°	246.1	7.0
110°-120°	419.0	12.0
120°-130°	551.2	15.7
130°-140°	619.6	17.7
140°-150°	609.2	17.4
150°-160°	512.8	14.6
160°-170°	341.4	9.7
170°-180°	119.6	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.7	0.1
90°-120°	746.5	21.3
90°-150°	2526.5	72.1
90°-180°	3500.0	99.9
0°-180°	3503.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	11	24	28	30	4
95°	58	66	73	77	77	65
105°	223	225	234	234	236	239
115°	422	425	423	424	423	417
125°	617	620	618	614	610	550
135°	801	807	806	802	800	617
145°	972	974	976	976	972	607
155°	1112	1112	1113	1117	1110	512
165°	1212	1209	1209	1215	1208	342
175°	1260	1256	1256	1262	1255	120
180°	1263	1263	1263	1263	1263	

TEST NUMBER: P1007474

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	10.9	23.8	27.8	29.8
92.5°	29.8	35.7	41.7	44.7	42.7
95°	58.5	65.5	73.4	77.4	77.4
97.5°	96.3	101.2	107.2	112.1	111.1
100°	135.0	140.9	145.9	148.9	150.8
102.5°	179.6	182.6	189.5	192.5	191.5
105°	223.3	225.3	234.2	234.2	236.2
107.5°	274.9	275.9	279.8	282.8	281.8
110°	322.5	324.5	326.5	330.5	328.5

TEST NUMBER: P1007474

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	372.1	373.1	373.1	378.1	378.1
115°	421.8	424.7	422.7	423.7	422.7
117.5°	472.4	473.4	471.4	471.4	468.4
120°	519.0	525.0	520.0	519.0	517.0
122.5°	567.6	571.6	569.6	566.6	563.7
125°	617.3	620.2	618.2	614.3	610.3
127.5°	662.9	668.9	666.9	660.9	656.9
130°	708.6	716.5	713.5	709.5	702.6
132.5°	754.2	762.1	760.2	755.2	750.2
135°	800.8	806.8	805.8	801.8	799.8
137.5°	843.5	848.5	851.5	846.5	843.5
140°	888.2	893.1	894.1	893.1	886.2
142.5°	928.9	933.8	935.8	934.8	929.8
145°	971.5	973.5	976.5	975.5	971.5
147.5°	1008.2	1012.2	1015.2	1015.2	1009.2
150°	1046.9	1048.9	1050.9	1050.9	1045.0
152.5°	1078.7	1081.7	1082.7	1084.7	1079.7
155°	1112.4	1112.4	1113.4	1117.4	1110.5
157.5°	1141.2	1140.2	1141.2	1145.2	1139.2
160°	1168.0	1166.0	1166.0	1171.0	1167.0
162.5°	1191.8	1188.9	1189.8	1194.8	1187.9
165°	1211.7	1208.7	1208.7	1214.7	1207.7
167.5°	1228.6	1224.6	1225.6	1231.5	1225.6
170°	1242.4	1238.5	1238.5	1245.4	1238.5
172.5°	1253.4	1249.4	1249.4	1255.3	1248.4
175°	1260.3	1256.3	1256.3	1262.3	1255.3
177.5°	1264.3	1260.3	1260.3	1266.3	1259.3
180°	1263.3	1263.3	1263.3	1263.3	1263.3

(END OF REPORT)