

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012331

Luminaire Tested: S123RDIP-B1165D365UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012331
REPORT IS A COMBINATION OF REPORTS P993020 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1165D365UB30-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5713.1 lumens
Efficiency: N/A
Efficacy: 80.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012331

CATALOG NUMBER: S123RDIP-B1165D365UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012331

CATALOG NUMBER: S123RDIP-B1165D365UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81
1	104	100	96	93	99	96	92	89	87	84	82	79	77	75	72	71	69
2	95	88	82	77	91	84	79	74	77	73	69	70	67	64	64	62	59
3	87	78	70	64	83	75	68	62	68	63	58	63	58	55	57	54	51
4	80	69	61	55	76	66	59	53	61	55	50	56	51	47	52	48	44
5	74	62	54	48	70	60	52	46	55	49	44	51	45	41	47	42	39
6	68	56	48	42	65	54	46	41	50	43	39	46	41	37	43	38	34
7	64	51	43	37	60	49	42	36	45	39	34	42	37	33	39	34	31
8	59	47	39	33	56	45	37	32	42	35	31	39	33	29	36	31	28
9	55	43	35	30	53	41	34	29	38	32	28	36	30	27	33	29	25
10	52	39	32	27	49	38	31	26	36	30	25	33	28	24	31	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20907	20907	20907
5°	20941	20167	20112
10°	20776	19408	19026
15°	20506	18472	17837
20°	20152	17453	16507
25°	19787	16393	15248
30°	19319	15266	13759
35°	18838	14159	12402
40°	18384	12958	10904
45°	17804	11782	9558
50°	17162	10527	8164
55°	16498	9184	6885
60°	15862	7805	5589
65°	15041	6392	4362
70°	14009	4834	3117
75°	12523	3274	2471
80°	10690	2274	1733
85°	8021	1228	909

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17804 cd/sqm

TEST NUMBER: P1012331

CATALOG NUMBER: S123RDIP-B1165D365UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.6	3.2
10°-20°	507.9	8.9
20°-30°	731.3	12.8
30°-40°	823.6	14.4
40°-50°	787.8	13.8
50°-60°	644.9	11.3
60°-70°	434.8	7.6
70°-80°	218.1	3.8
80°-90°	58.0	1.0
90°-100°	99.8	1.7
100°-110°	278.9	4.9
110°-120°	272.0	4.8
120°-130°	216.6	3.8
130°-140°	171.0	3.0
140°-150°	127.6	2.2
150°-160°	89.0	1.6
160°-170°	52.3	0.9
170°-180°	17.0	0.3
0°-30°	1421.8	24.9
0°-40°	2245.4	39.3
0°-60°	3678.1	64.4
0°-90°	4389.0	76.8
90°-120°	650.7	11.4
90°-150°	1165.8	20.4
90°-180°	1324.0	23.2
0°-180°	5713.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1942	1942	1942	1942	1942	
5°	1942	1934	1916	1930	1926	184
15°	1852	1835	1791	1783	1772	522
25°	1686	1646	1574	1541	1523	775
35°	1459	1402	1304	1237	1208	913
45°	1199	1128	1007	917	879	925
55°	910	833	699	608	576	817
65°	622	536	413	336	318	616
75°	329	254	167	151	148	351
85°	84	49	44	41	41	91
90°	1	4	9	10	10	6
95°	12	39	211	62	41	13
105°	41	61	286	500	452	44
115°	73	91	219	479	550	72
125°	101	120	204	370	434	90
135°	119	142	201	304	352	92
145°	135	155	199	250	275	85
155°	154	166	192	219	228	71
165°	168	173	184	195	199	47
175°	175	175	177	179	179	17
180°	176	176	176	176	176	

TEST NUMBER: P1012331

CATALOG NUMBER: S123RDIP-B1165D365UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1942.3	1942.3	1942.3	1942.3	1942.3
2.5°	1950.2	1943.9	1925.0	1942.3	1939.1
5°	1942.3	1934.4	1915.5	1929.7	1926.5
7.5°	1928.1	1920.2	1896.6	1906.1	1901.3
10°	1909.2	1898.2	1869.8	1871.4	1863.5
12.5°	1882.4	1869.8	1833.6	1832.0	1822.6
15°	1852.5	1835.2	1791.1	1783.2	1772.2
17.5°	1816.3	1797.4	1742.2	1726.5	1710.7
20°	1775.3	1750.1	1690.3	1669.8	1650.9
22.5°	1729.6	1699.7	1635.1	1608.3	1591.0
25°	1685.5	1646.2	1573.7	1540.6	1523.3
27.5°	1632.0	1589.4	1510.7	1466.6	1439.8
30°	1576.8	1529.6	1441.4	1387.8	1362.6
32.5°	1521.7	1466.6	1372.1	1312.2	1285.4
35°	1458.7	1402.0	1304.3	1236.6	1208.2
37.5°	1395.7	1334.2	1231.9	1156.2	1121.6
40°	1335.8	1266.5	1154.7	1072.8	1036.5
42.5°	1268.1	1198.8	1082.2	990.8	959.3
45°	1198.8	1127.9	1006.6	916.8	879.0
47.5°	1131.0	1052.3	932.6	834.9	801.8
50°	1055.4	981.4	853.8	756.1	719.9
52.5°	987.7	905.8	779.8	677.4	645.9
55°	910.5	833.3	699.4	608.1	576.5
57.5°	841.2	757.7	622.2	535.6	508.8
60°	768.7	682.1	551.3	466.3	439.5
62.5°	696.3	609.6	478.9	400.1	371.8
65°	622.2	535.6	412.7	335.5	318.2
67.5°	548.2	460.0	340.3	282.0	263.1
70°	475.7	390.7	280.4	225.3	207.9
72.5°	403.3	319.8	222.1	179.6	174.9
75°	329.2	253.6	167.0	151.2	148.1
77.5°	261.5	192.2	130.7	121.3	118.1
80°	196.9	132.3	99.2	94.5	91.4
82.5°	135.5	81.9	70.9	66.2	66.2
85°	83.5	48.8	44.1	41.0	41.0
87.5°	37.8	20.5	20.5	18.9	17.3
90°	0.7	4.2	8.9	10.0	10.3
92.5°	5.3	21.3	66.1	22.6	18.8
95°	12.1	39.3	210.8	61.5	41.2
97.5°	19.2	45.0	324.2	154.6	84.6
100°	26.3	49.6	336.7	323.6	222.9
102.5°	33.8	54.9	313.6	433.2	353.0
105°	41.2	61.0	285.8	499.8	452.2
107.5°	49.1	68.0	261.3	529.2	516.9
110°	57.6	75.4	241.0	530.0	553.9

TEST NUMBER: P1012331

CATALOG NUMBER: S123RDIP-B1165D365UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.4	83.0	227.5	510.0	561.3
115°	72.9	90.8	218.6	479.4	550.0
117.5°	80.3	98.3	212.6	446.7	525.1
120°	88.2	105.8	208.7	415.8	492.4
122.5°	94.9	112.9	206.2	391.5	461.8
125°	101.3	119.6	204.1	369.7	433.7
127.5°	106.3	126.0	203.0	352.0	409.5
130°	110.9	131.7	201.9	335.6	389.6
132.5°	114.5	136.8	201.6	320.3	370.1
135°	118.7	141.7	201.2	304.5	351.6
137.5°	122.6	145.6	200.5	289.6	332.0
140°	126.6	149.1	200.1	275.0	311.4
142.5°	130.8	152.3	199.4	261.7	292.2
145°	135.4	155.2	198.7	249.8	274.8
147.5°	140.1	158.2	197.7	240.5	259.9
150°	144.7	160.7	196.2	232.3	247.1
152.5°	149.3	163.4	194.5	225.2	236.4
155°	153.9	166.0	192.3	218.6	227.9
157.5°	157.5	168.4	190.6	212.2	219.7
160°	161.8	170.3	188.4	206.4	211.9
162.5°	165.0	171.7	186.3	200.9	204.8
165°	168.2	173.0	184.2	195.4	198.7
167.5°	170.6	174.0	182.0	190.6	192.7
170°	172.8	174.6	179.9	186.2	187.4
172.5°	174.2	175.1	178.1	182.6	182.4
175°	175.3	175.4	176.7	179.2	178.8
177.5°	176.0	175.6	175.6	177.0	176.3
180°	175.6	175.6	175.6	175.6	175.6

(END OF REPORT)