

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007476

Luminaire Tested: S123IP-B1025UB2750-4F0-XX-W2A-1_5000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007476
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B1025UB2750-4F0-XX-W2A-1_5000K
Description: Define 3 Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3354.0 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007476

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A-1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007476

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A-1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007476

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A-1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.6	0.1
90°-100°	77.9	2.3
100°-110°	235.7	7.0
110°-120°	401.2	12.0
120°-130°	527.8	15.7
130°-140°	593.3	17.7
140°-150°	583.2	17.4
150°-160°	491.0	14.6
160°-170°	326.9	9.7
170°-180°	114.5	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.6	0.1
90°-120°	714.7	21.3
90°-150°	2419.0	72.1
90°-180°	3351.0	99.9
0°-180°	3354.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	10	23	27	28	4
95°	56	63	70	74	74	62
105°	214	216	224	224	226	229
115°	404	407	405	406	405	400
125°	591	594	592	588	584	527
135°	767	772	772	768	766	591
145°	930	932	935	934	930	581
155°	1065	1065	1066	1070	1063	490
165°	1160	1157	1157	1163	1156	327
175°	1207	1203	1203	1209	1202	115
180°	1210	1210	1210	1210	1210	

TEST NUMBER: P1007476

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	10.5	22.8	26.6	28.5
92.5°	28.5	34.2	39.9	42.8	40.9
95°	56.1	62.7	70.3	74.1	74.1
97.5°	92.2	96.9	102.6	107.4	106.4
100°	129.2	134.9	139.7	142.5	144.4
102.5°	172.0	174.8	181.5	184.3	183.4
105°	213.8	215.7	224.2	224.2	226.1
107.5°	263.2	264.1	267.9	270.8	269.8
110°	308.8	310.7	312.6	316.4	314.5

TEST NUMBER: P1007476

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	356.3	357.3	357.3	362.0	362.0
115°	403.8	406.7	404.8	405.7	404.8
117.5°	452.3	453.2	451.3	451.3	448.5
120°	496.9	502.6	497.9	496.9	495.0
122.5°	543.5	547.3	545.4	542.5	539.7
125°	591.0	593.8	591.9	588.1	584.3
127.5°	634.7	640.4	638.5	632.8	629.0
130°	678.4	686.0	683.2	679.4	672.7
132.5°	722.1	729.7	727.8	723.1	718.3
135°	766.8	772.5	771.5	767.7	765.8
137.5°	807.6	812.4	815.2	810.5	807.6
140°	850.4	855.1	856.1	855.1	848.5
142.5°	889.3	894.1	896.0	895.0	890.3
145°	930.2	932.1	935.0	934.0	930.2
147.5°	965.4	969.2	972.0	972.0	966.3
150°	1002.4	1004.3	1006.2	1006.2	1000.5
152.5°	1032.8	1035.7	1036.6	1038.5	1033.8
155°	1065.1	1065.1	1066.1	1069.9	1063.2
157.5°	1092.7	1091.7	1092.7	1096.5	1090.8
160°	1118.3	1116.4	1116.4	1121.2	1117.4
162.5°	1141.1	1138.3	1139.2	1144.0	1137.3
165°	1160.1	1157.3	1157.3	1163.0	1156.3
167.5°	1176.3	1172.5	1173.4	1179.1	1173.4
170°	1189.6	1185.8	1185.8	1192.4	1185.8
172.5°	1200.0	1196.2	1196.2	1201.9	1195.3
175°	1206.7	1202.9	1202.9	1208.6	1201.9
177.5°	1210.5	1206.7	1206.7	1212.4	1205.7
180°	1209.5	1209.5	1209.5	1209.5	1209.5

(END OF REPORT)