

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007484

Luminaire Tested: S123IP-B1025UB2750-4F0-XX-W2A_3500K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007484
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B1025UB2750-4F0-XX-W2A_3500K
Description: Define 3 Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4075.0 lumens
Efficiency: N/A
Efficacy: 143.0 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007484

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1007484

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007484

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.7	0.1
90°-100°	47.1	1.2
100°-110°	227.8	5.6
110°-120°	558.1	13.7
120°-130°	708.5	17.4
130°-140°	756.9	18.6
140°-150°	707.8	17.4
150°-160°	570.9	14.0
160°-170°	368.4	9.0
170°-180°	127.0	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.7	0.1
90°-120°	833.0	20.4
90°-150°	3006.1	73.8
90°-180°	4072.0	99.9
0°-180°	4075.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	11	24	28	30	3
95°	60	20	31	38	38	72
105°	296	307	217	42	44	314
115°	555	561	570	580	584	548
125°	782	790	794	796	798	699
135°	974	980	984	986	984	750
145°	1123	1130	1132	1134	1134	703
155°	1238	1236	1237	1242	1236	570
165°	1305	1302	1301	1309	1302	369
175°	1336	1331	1332	1339	1331	127
180°	1336	1336	1336	1336	1336	

TEST NUMBER: P1007484

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	10.9	23.8	27.8	29.8
92.5°	22.8	16.9	25.8	32.8	33.7
95°	60.5	19.8	30.8	37.7	37.7
97.5°	110.2	82.4	31.8	39.7	40.7
100°	167.7	187.6	32.8	40.7	41.7
102.5°	233.2	246.1	73.4	40.7	42.7
105°	295.7	306.7	217.3	41.7	43.7
107.5°	362.2	371.2	386.1	233.2	103.2
110°	428.7	436.7	447.6	414.8	272.9

TEST NUMBER: P1007484

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	492.2	499.2	510.1	519.0	517.1
115°	554.8	560.7	569.7	579.6	583.5
117.5°	616.3	623.2	628.2	636.1	637.1
120°	672.9	681.8	684.8	692.7	692.7
122.5°	730.4	737.4	741.3	746.3	747.3
125°	782.0	790.0	793.9	795.9	797.9
127.5°	833.6	841.6	846.5	849.5	847.5
130°	881.3	889.2	893.2	897.2	895.2
132.5°	926.9	934.9	937.8	941.8	938.8
135°	973.6	979.5	983.5	986.5	983.5
137.5°	1013.3	1021.2	1023.2	1028.2	1026.2
140°	1053.0	1058.9	1061.9	1065.9	1063.9
142.5°	1089.7	1095.6	1098.6	1101.6	1098.6
145°	1123.4	1130.4	1132.4	1134.3	1134.3
147.5°	1156.2	1161.1	1163.1	1165.1	1160.2
150°	1186.0	1188.9	1190.9	1192.9	1189.9
152.5°	1212.7	1213.7	1214.7	1218.7	1213.7
155°	1237.6	1235.6	1236.6	1241.5	1235.6
157.5°	1257.4	1257.4	1256.4	1262.4	1254.4
160°	1275.3	1274.3	1273.3	1279.2	1272.3
162.5°	1292.1	1289.2	1288.2	1295.1	1289.2
165°	1305.0	1302.1	1301.1	1309.0	1302.1
167.5°	1316.0	1312.0	1312.0	1319.9	1312.0
170°	1324.9	1320.9	1320.9	1328.9	1320.9
172.5°	1330.8	1325.9	1326.9	1334.8	1325.9
175°	1335.8	1330.8	1331.8	1338.8	1330.8
177.5°	1337.8	1332.8	1333.8	1341.8	1331.8
180°	1335.8	1335.8	1335.8	1335.8	1335.8

(END OF REPORT)