

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007506

Luminaire Tested: S123IP-B1195UB2750-4F0-XX-W2A-1_5000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007506
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B1195UB2750-4F0-XX-W2A-1_5000K
Description: Define 3 Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3941.0 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 35
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007506

CATALOG NUMBER: S123IP-B119SUB2750-4F0-XX-W2A-1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007506

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A-1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007506

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A-1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.0	0.1
90°-100°	91.5	2.3
100°-110°	276.9	7.0
110°-120°	471.4	12.0
120°-130°	620.2	15.7
130°-140°	697.1	17.7
140°-150°	685.3	17.4
150°-160°	577.0	14.6
160°-170°	384.1	9.7
170°-180°	134.5	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.0	0.1
90°-120°	839.8	21.3
90°-150°	2842.4	72.1
90°-180°	3938.0	99.9
0°-180°	3941.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	12	27	31	34	5
95°	66	74	83	87	87	73
105°	251	253	264	264	266	269
115°	474	478	476	477	476	470
125°	694	698	696	691	687	619
135°	901	908	907	902	900	694
145°	1093	1095	1099	1098	1093	683
155°	1252	1252	1253	1257	1249	576
165°	1363	1360	1360	1366	1359	384
175°	1418	1413	1413	1420	1412	135
180°	1421	1421	1421	1421	1421	

TEST NUMBER: P1007506

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.1	12.3	26.8	31.3	33.5
92.5°	33.5	40.2	46.9	50.2	48.0
95°	65.9	73.7	82.6	87.1	87.1
97.5°	108.3	113.9	120.6	126.2	125.0
100°	151.8	158.5	164.1	167.5	169.7
102.5°	202.1	205.4	213.2	216.6	215.5
105°	251.2	253.4	263.5	263.5	265.7
107.5°	309.3	310.4	314.8	318.2	317.1
110°	362.8	365.1	367.3	371.8	369.5

TEST NUMBER: P1007506

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	418.7	419.8	419.8	425.4	425.4
115°	474.5	477.8	475.6	476.7	475.6
117.5°	531.4	532.5	530.3	530.3	527.0
120°	583.9	590.6	585.0	583.9	581.7
122.5°	638.6	643.1	640.8	637.5	634.1
125°	694.4	697.8	695.5	691.1	686.6
127.5°	745.8	752.5	750.3	743.6	739.1
130°	797.1	806.1	802.7	798.3	790.4
132.5°	848.5	857.4	855.2	849.6	844.0
135°	901.0	907.7	906.6	902.1	899.9
137.5°	949.0	954.6	957.9	952.3	949.0
140°	999.2	1004.8	1005.9	1004.8	997.0
142.5°	1045.0	1050.6	1052.8	1051.7	1046.1
145°	1093.0	1095.2	1098.6	1097.5	1093.0
147.5°	1134.3	1138.8	1142.1	1142.1	1135.4
150°	1177.9	1180.1	1182.3	1182.3	1175.6
152.5°	1213.6	1216.9	1218.0	1220.3	1214.7
155°	1251.5	1251.5	1252.7	1257.1	1249.3
157.5°	1283.9	1282.8	1283.9	1288.4	1281.7
160°	1314.1	1311.8	1311.8	1317.4	1312.9
162.5°	1340.9	1337.5	1338.6	1344.2	1336.4
165°	1363.2	1359.8	1359.8	1366.5	1358.7
167.5°	1382.2	1377.7	1378.8	1385.5	1378.8
170°	1397.8	1393.3	1393.3	1401.1	1393.3
172.5°	1410.1	1405.6	1405.6	1412.3	1404.5
175°	1417.9	1413.4	1413.4	1420.1	1412.3
177.5°	1422.4	1417.9	1417.9	1424.6	1416.8
180°	1421.2	1421.2	1421.2	1421.2	1421.2

(END OF REPORT)