

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012375

Luminaire Tested: S123RDIP-B1165D585UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012375
REPORT IS A COMBINATION OF REPORTS P993076 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1165D585UB50-4F0-XX-W2A-F
Description: Define 3 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6476.0 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012375

CATALOG NUMBER: S123RDIP-B1165D585UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1012375

CATALOG NUMBER: S123RDIP-B1165D585UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70
1	102	97	94	90	95	92	88	85	81	79	76	72	70	68	63	61	60
2	93	86	79	74	87	81	75	71	72	68	64	63	60	57	56	53	51
3	85	76	68	62	80	71	65	60	64	59	54	56	52	49	50	47	44
4	78	67	59	53	73	64	57	51	57	51	47	51	46	42	45	41	38
5	72	60	52	46	67	57	50	44	51	45	41	46	41	37	40	37	34
6	66	54	46	40	62	51	44	39	46	40	36	41	36	33	37	33	30
7	62	49	41	36	58	47	39	34	42	36	32	38	33	29	34	30	27
8	57	45	37	32	54	43	36	31	39	33	28	35	30	26	31	27	24
9	53	41	34	28	50	39	32	27	35	30	26	32	27	24	29	25	22
10	50	38	31	26	47	36	29	25	33	27	23	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20106	20106	20106
5°	20139	19395	19343
10°	19980	18665	18298
15°	19721	17764	17154
20°	19381	16784	15875
25°	19030	15765	14664
30°	18581	14682	13231
35°	18116	13618	11928
40°	17681	12462	10487
45°	17122	11332	9191
50°	16505	10124	7851
55°	15865	8832	6623
60°	15255	7507	5376
65°	14465	6147	4195
70°	13473	4649	2999
75°	12043	3148	2376
80°	10282	2187	1667
85°	7713	1181	873

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17122 cd/sqm

TEST NUMBER: P1012375

CATALOG NUMBER: S123RDIP-B1165D585UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.6	2.7
10°-20°	488.5	7.5
20°-30°	703.3	10.9
30°-40°	792.1	12.2
40°-50°	757.6	11.7
50°-60°	620.2	9.6
60°-70°	418.1	6.5
70°-80°	209.7	3.2
80°-90°	56.3	0.9
90°-100°	26.1	0.4
100°-110°	126.1	1.9
110°-120°	309.0	4.8
120°-130°	392.2	6.1
130°-140°	419.0	6.5
140°-150°	391.8	6.1
150°-160°	316.0	4.9
160°-170°	204.0	3.1
170°-180°	70.3	1.1
0°-30°	1367.4	21.1
0°-40°	2159.5	33.3
0°-60°	3537.3	54.6
0°-90°	4221.5	65.2
90°-120°	461.1	7.1
90°-150°	1664.2	25.7
90°-180°	2255.0	34.8
0°-180°	6476.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1868	1868	1868	1868	1868	
5°	1868	1860	1842	1856	1853	177
15°	1782	1765	1722	1715	1704	502
25°	1621	1583	1513	1482	1465	746
35°	1403	1348	1254	1189	1162	878
45°	1153	1085	968	882	845	890
55°	876	801	673	585	554	785
65°	598	515	397	323	306	592
75°	317	244	161	145	142	337
85°	80	47	42	39	39	88
90°	0	6	13	15	16	7
95°	34	11	17	21	21	40
105°	164	170	120	23	24	174
115°	307	310	315	321	323	303
125°	433	437	440	441	442	387
135°	539	542	544	546	544	415
145°	622	626	627	628	628	389
155°	685	684	685	687	684	316
165°	722	721	720	725	721	204
175°	740	737	737	741	737	70
180°	740	740	740	740	740	

TEST NUMBER: P1012375

CATALOG NUMBER: S123RDIP-B1165D585UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1867.9	1867.9	1867.9	1867.9	1867.9
2.5°	1875.5	1869.5	1851.3	1867.9	1864.9
5°	1867.9	1860.4	1842.2	1855.8	1852.8
7.5°	1854.3	1846.7	1824.0	1833.1	1828.5
10°	1836.1	1825.5	1798.2	1799.8	1792.2
12.5°	1810.4	1798.2	1763.4	1761.9	1752.8
15°	1781.6	1764.9	1722.5	1714.9	1704.3
17.5°	1746.7	1728.6	1675.5	1660.4	1645.2
20°	1707.4	1683.1	1625.5	1605.8	1587.7
22.5°	1663.4	1634.6	1572.5	1546.8	1530.1
25°	1621.0	1583.1	1513.4	1481.6	1465.0
27.5°	1569.5	1528.6	1452.8	1410.4	1384.7
30°	1516.5	1471.0	1386.2	1334.7	1310.4
32.5°	1463.4	1410.4	1319.5	1262.0	1236.2
35°	1402.8	1348.3	1254.4	1189.2	1162.0
37.5°	1342.2	1283.2	1184.7	1112.0	1078.6
40°	1284.7	1218.0	1110.5	1031.7	996.8
42.5°	1219.5	1152.9	1040.8	952.9	922.6
45°	1152.9	1084.7	968.1	881.7	845.3
47.5°	1087.7	1012.0	896.9	802.9	771.1
50°	1015.0	943.8	821.1	727.2	692.3
52.5°	949.9	871.1	749.9	651.4	621.1
55°	875.6	801.4	672.6	584.8	554.5
57.5°	809.0	728.7	598.4	515.1	489.3
60°	739.3	656.0	530.2	448.4	422.7
62.5°	669.6	586.3	460.5	384.8	357.5
65°	598.4	515.1	396.9	322.7	306.0
67.5°	527.2	442.4	327.2	271.2	253.0
70°	457.5	375.7	269.7	216.6	200.0
72.5°	387.8	307.5	213.6	172.7	168.2
75°	316.6	243.9	160.6	145.4	142.4
77.5°	251.5	184.8	125.7	116.7	113.6
80°	189.4	127.3	95.4	90.9	87.9
82.5°	130.3	78.8	68.2	63.6	63.6
85°	80.3	47.0	42.4	39.4	39.4
87.5°	36.4	19.7	19.7	18.2	16.7
90°	0.5	6.0	13.2	15.4	16.5
92.5°	12.6	9.3	14.3	18.1	18.7
95°	33.5	11.0	17.0	20.9	20.9
97.5°	61.0	45.6	17.6	22.0	22.5
100°	92.9	103.8	18.1	22.5	23.1
102.5°	129.1	136.3	40.7	22.5	23.6
105°	163.7	169.8	120.3	23.1	24.2
107.5°	200.5	205.5	213.7	129.1	57.1
110°	237.4	241.7	247.8	229.7	151.1

TEST NUMBER: P1012375

CATALOG NUMBER: S123RDIP-B1165D585UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	272.5	276.4	282.4	287.4	286.3
115°	307.1	310.4	315.4	320.9	323.1
117.5°	341.2	345.0	347.8	352.2	352.7
120°	372.5	377.5	379.1	383.5	383.5
122.5°	404.4	408.2	410.4	413.2	413.7
125°	432.9	437.3	439.5	440.6	441.7
127.5°	461.5	465.9	468.7	470.3	469.2
130°	487.9	492.3	494.5	496.7	495.6
132.5°	513.2	517.6	519.2	521.4	519.8
135°	539.0	542.3	544.5	546.1	544.5
137.5°	561.0	565.4	566.5	569.2	568.1
140°	582.9	586.2	587.9	590.1	589.0
142.5°	603.3	606.6	608.2	609.9	608.2
145°	622.0	625.8	626.9	628.0	628.0
147.5°	640.1	642.8	643.9	645.0	642.3
150°	656.6	658.2	659.3	660.4	658.8
152.5°	671.4	672.0	672.5	674.7	672.0
155°	685.1	684.0	684.6	687.3	684.0
157.5°	696.1	696.1	695.6	698.9	694.5
160°	706.0	705.5	704.9	708.2	704.4
162.5°	715.4	713.7	713.2	717.0	713.7
165°	722.5	720.9	720.3	724.7	720.9
167.5°	728.5	726.3	726.3	730.7	726.3
170°	733.5	731.3	731.3	735.7	731.3
172.5°	736.8	734.0	734.6	739.0	734.0
175°	739.5	736.8	737.3	741.2	736.8
177.5°	740.6	737.9	738.4	742.8	737.3
180°	739.5	739.5	739.5	739.5	739.5

(END OF REPORT)